

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P926027

Luminaire Tested: DFN2DIP-SQ4F0-140D090US950-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P926027
REPORT IS A COMBINATION OF REPORTS P901648 AND P898471
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-140D090US950-RLLONL
Description: 4 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 19852.7 lumens
Efficiency: N/A
Efficacy: 94.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 210.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P926027

CATALOG NUMBER: DFN2DIP-SQ4F0-140D090US950-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P926027

CATALOG NUMBER: DFN2DIP-SQ4F0-140D090US950-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					0
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	109	109	109	109		101	101	101	101		87	87	87		75	75	75		63	63	63
1	100	96	92	89		93	89	86	83		77	75	73		66	65	63		56	55	54
2	91	84	78	73		85	79	74	69		69	65	61		59	56	54		50	48	46
3	84	75	67	62		78	70	64	59		61	56	52		53	49	46		45	42	40
4	77	66	59	53		72	62	55	50		55	49	45		47	43	40		41	38	35
5	71	60	52	46		66	56	49	44		49	44	39		43	38	35		37	34	31
6	66	54	46	40		61	51	43	38		45	39	35		39	34	31		34	30	28
7	61	49	41	35		57	46	39	34		41	35	31		36	31	28		31	27	25
8	57	44	37	31		53	42	35	30		37	32	27		33	28	25		29	25	22
9	53	41	33	28		49	38	32	27		34	29	25		30	26	23		26	23	20
10	49	37	30	26		46	35	29	25		32	26	23		28	24	21		25	21	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3873	3873	3873
5°	3879	3813	3837
10°	3841	3739	3714
15°	3788	3616	3522
20°	3718	3446	3286
25°	3646	3256	3058
30°	3550	3061	2768
35°	3456	2851	2514
40°	3360	2634	2222
45°	3248	2392	1958
50°	3133	2149	1699
55°	3013	1889	1451
60°	2873	1616	1195
65°	2713	1339	1077
70°	2519	1081	976
75°	2275	955	891
80°	1922	803	777
85°	1337	540	591

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3248 cd/sqm

TEST NUMBER: P926027

CATALOG NUMBER: DFN2DIP-SQ4F0-140D090US950-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	517.3	2.6
10°-20°	1420.2	7.2
20°-30°	1993.9	10.0
30°-40°	2173.5	10.9
40°-50°	1997.7	10.1
50°-60°	1568.9	7.9
60°-70°	1021.2	5.1
70°-80°	525.7	2.6
80°-90°	139.3	0.7
90°-100°	95.6	0.5
100°-110°	356.2	1.8
110°-120°	944.7	4.8
120°-130°	1566.8	7.9
130°-140°	1664.3	8.4
140°-150°	1546.8	7.8
150°-160°	1243.6	6.3
160°-170°	801.3	4.0
170°-180°	275.8	1.4
0°-30°	3931.5	19.8
0°-40°	6105.0	30.8
0°-60°	9671.6	48.7
0°-90°	11357.7	57.2
90°-120°	1396.4	7.0
90°-150°	6174.3	31.1
90°-180°	8495.0	42.8
0°-180°	19852.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	5520	5520	5520	5520	5520	
5°	5520	5495	5430	5475	5460	523
15°	5250	5195	5026	4931	4881	1479
25°	4766	4606	4276	4072	3996	2192
35°	4106	3852	3412	3097	2987	2570
45°	3357	3022	2498	2143	2023	2593
55°	2552	2163	1623	1324	1229	2281
65°	1724	1319	869	700	684	1709
75°	919	569	400	365	360	972
85°	215	110	95	95	95	246
90°	2	25	42	53	56	19
95°	136	67	82	92	90	161
105°	637	700	128	151	159	681
115°	1206	1241	1294	323	172	1187
125°	1704	1732	1772	1786	1793	1520
135°	2109	2143	2162	2183	2179	1629
145°	2447	2445	2480	2495	2485	1530
155°	2694	2676	2701	2713	2696	1242
165°	2839	2826	2833	2847	2833	802
175°	2904	2889	2894	2908	2887	276
180°	2898	2898	2898	2898	2898	

TEST NUMBER: P926027

CATALOG NUMBER: DFN2DIP-SQ4F0-140D090US950-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	5520.0	5520.0	5520.0	5520.0	5520.0
2.5°	5544.9	5520.0	5464.9	5515.3	5505.2
5°	5520.0	5495.1	5429.9	5475.0	5460.1
7.5°	5475.0	5445.2	5375.3	5395.0	5370.1
10°	5415.1	5380.1	5280.5	5265.0	5235.4
12.5°	5340.3	5295.3	5160.1	5130.4	5075.4
15°	5250.2	5195.1	5025.5	4930.7	4880.9
17.5°	5145.3	5065.3	4855.4	4745.7	4665.6
20°	5025.5	4925.3	4675.7	4551.2	4441.0
22.5°	4895.6	4780.7	4490.8	4321.1	4246.4
25°	4765.8	4605.7	4276.1	4071.5	3996.2
27.5°	4611.1	4441.0	4076.3	3841.5	3726.5
30°	4446.2	4256.0	3856.4	3601.9	3466.7
32.5°	4286.1	4056.1	3647.0	3347.0	3221.9
35°	4106.5	3851.6	3412.2	3097.4	2987.1
37.5°	3931.6	3656.5	3192.2	2847.2	2722.6
40°	3746.6	3447.2	2962.2	2607.7	2477.8
42.5°	3556.9	3237.3	2732.7	2362.8	2238.2
45°	3357.0	3022.1	2498.0	2142.8	2023.1
47.5°	3167.3	2812.8	2273.2	1918.1	1808.4
50°	2957.4	2602.9	2053.2	1708.2	1603.8
52.5°	2752.3	2377.6	1843.3	1513.7	1418.8
55°	2552.5	2162.9	1623.4	1324.0	1229.0
57.5°	2347.9	1948.3	1428.9	1149.1	1069.1
60°	2138.0	1738.4	1223.8	969.4	889.3
62.5°	1933.5	1533.8	1048.9	809.3	769.6
65°	1723.6	1318.6	869.2	699.6	684.2
67.5°	1523.7	1118.9	699.6	614.3	599.4
70°	1313.8	924.3	579.3	529.5	509.3
72.5°	1114.1	744.1	484.4	444.7	434.6
75°	919.0	569.3	399.6	364.6	359.8
77.5°	724.6	404.4	314.8	294.7	284.6
80°	544.4	289.9	239.5	220.0	220.0
82.5°	379.5	195.0	164.9	154.7	154.7
85°	214.6	109.7	94.8	94.8	94.8
87.5°	80.0	39.8	39.8	35.0	35.0
90°	2.0	25.2	41.8	52.6	56.5
92.5°	52.6	44.1	50.3	54.6	56.5
95°	136.2	67.0	81.7	92.3	90.2
97.5°	245.3	73.5	106.8	113.2	115.2
100°	371.2	84.0	119.5	136.2	140.4
102.5°	509.4	505.4	123.7	146.6	153.1
105°	637.4	700.4	127.9	150.9	159.3
107.5°	786.3	838.6	132.2	155.1	163.6
110°	928.9	972.8	367.0	157.3	165.6

TEST NUMBER: P926027

CATALOG NUMBER: DFN2DIP-SQ4F0-140D090US950-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1063.1	1100.7	1065.1	161.3	167.8
115°	1205.6	1241.2	1293.7	322.9	172.0
117.5°	1329.3	1371.2	1407.0	1107.0	557.7
120°	1467.7	1499.1	1537.0	1562.1	1279.0
122.5°	1585.1	1618.7	1660.7	1673.1	1675.4
125°	1704.5	1731.9	1771.8	1786.5	1792.7
127.5°	1813.6	1842.9	1874.6	1895.5	1897.5
130°	1916.4	1950.1	1973.0	1996.1	1994.1
132.5°	2021.2	2048.6	2071.5	2090.5	2088.5
135°	2109.4	2143.0	2161.7	2182.8	2178.6
137.5°	2201.5	2226.6	2247.8	2268.7	2262.5
140°	2291.6	2308.6	2331.5	2350.4	2340.0
142.5°	2367.4	2382.0	2409.1	2425.8	2415.4
145°	2447.0	2444.7	2480.4	2495.1	2484.6
147.5°	2516.0	2509.8	2545.4	2555.9	2547.6
150°	2583.2	2568.5	2602.1	2614.5	2604.1
152.5°	2639.7	2623.0	2654.4	2667.1	2652.4
155°	2694.3	2675.6	2700.7	2713.2	2696.5
157.5°	2738.4	2721.7	2740.6	2755.2	2738.4
160°	2776.1	2763.5	2776.1	2788.6	2773.9
162.5°	2809.5	2797.0	2807.5	2822.2	2803.3
165°	2838.9	2826.4	2832.7	2847.4	2832.7
167.5°	2862.1	2849.4	2855.8	2870.5	2851.6
170°	2881.0	2868.3	2872.5	2887.2	2868.3
172.5°	2893.5	2881.0	2885.2	2899.9	2881.0
175°	2903.9	2889.2	2893.5	2908.1	2887.2
177.5°	2908.1	2893.5	2895.7	2910.4	2891.5
180°	2897.7	2897.7	2897.7	2897.7	2897.7

TEST NUMBER: P926027

CATALOG NUMBER: DFN2DIP-SQ4F0-140D090US950-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.51	13.40	13.41	14.32	15.49	8.47	9.37	9.37	10.28	11.45
	3H	14.20	15.00	15.11	15.92	17.11	9.67	10.47	10.58	11.39	12.58
	4H	14.81	15.57	15.74	16.50	17.70	10.12	10.87	11.05	11.80	13.01
	6H	15.24	15.94	16.18	16.87	18.09	10.45	11.14	11.38	12.07	13.29
	8H	15.37	16.03	16.32	16.98	18.20	10.54	11.20	11.48	12.15	13.36
	12H	15.44	16.07	16.39	17.01	18.25	10.58	11.21	11.53	12.16	13.40
4H	2H	12.54	13.29	13.47	14.22	15.42	9.08	9.83	10.01	10.76	11.96
	3H	14.38	15.00	15.32	15.96	17.18	10.44	11.06	11.38	12.02	13.24
	4H	15.08	15.65	16.03	16.60	17.84	10.99	11.56	11.94	12.51	13.75
	6H	15.60	16.09	16.56	17.07	18.31	11.41	11.90	12.38	12.88	14.12
	8H	15.78	16.24	16.74	17.21	18.46	11.54	12.00	12.51	12.97	14.23
	12H	15.88	16.29	16.86	17.28	18.54	11.61	12.02	12.59	13.01	14.27
8H	4H	15.05	15.51	16.02	16.48	17.73	11.27	11.73	12.24	12.70	13.96
	6H	15.62	16.00	16.61	17.01	18.27	11.80	12.17	12.79	13.19	14.44
	8H	15.84	16.18	16.84	17.18	18.45	11.99	12.32	12.99	13.32	14.60
	12H	15.99	16.28	16.99	17.28	18.59	12.11	12.40	13.11	13.40	14.72
12H	4H	15.00	15.42	15.99	16.41	17.66	11.28	11.70	12.27	12.68	13.94
	6H	15.60	15.93	16.60	16.93	18.21	11.85	12.18	12.85	13.18	14.45
	8H	15.82	16.12	16.83	17.11	18.43	12.06	12.35	13.06	13.35	14.67