

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P920579

Luminaire Tested: DFN2DIP-SQ4F0-140D110US935-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P920579
REPORT IS A COMBINATION OF REPORTS P901684 AND P898471
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-140D110US935-RLLONL
Description: 4 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 19622.1 lumens
Efficiency: N/A
Efficacy: 86.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 226.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P920579

CATALOG NUMBER: DFN2DIP-SQ4F0-140D110US935-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P920579

CATALOG NUMBER: DFN2DIP-SQ4F0-140D110US935-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	58	58	58
1	99	95	91	88	91	88	85	82	75	73	71	63	61	60	52	51	50
2	90	83	77	72	83	77	72	68	66	62	59	56	53	51	47	45	43
3	83	74	67	61	76	69	62	57	59	54	50	50	47	44	42	39	37
4	76	65	58	52	70	61	54	49	53	47	43	45	41	38	38	35	32
5	70	59	51	45	65	55	48	42	47	42	38	41	36	33	34	31	29
6	65	53	45	39	60	49	42	37	43	37	33	37	33	29	31	28	25
7	60	48	40	35	55	45	38	33	39	34	29	34	29	26	29	25	23
8	56	44	36	31	52	41	34	29	36	30	26	31	27	23	26	23	21
9	52	40	33	28	48	37	31	26	33	28	24	29	24	21	24	21	19
10	49	37	30	25	45	35	28	24	30	25	22	26	22	19	23	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3496	3496	3496
5°	3501	3441	3463
10°	3467	3374	3351
15°	3419	3263	3178
20°	3356	3110	2965
25°	3291	2938	2759
30°	3204	2762	2498
35°	3119	2573	2269
40°	3032	2377	2005
45°	2932	2159	1767
50°	2828	1939	1533
55°	2719	1705	1309
60°	2593	1459	1079
65°	2449	1209	972
70°	2273	976	881
75°	2053	862	804
80°	1734	725	701
85°	1207	488	533

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2932 cd/sqm

TEST NUMBER: P920579

CATALOG NUMBER: DFN2DIP-SQ4F0-140D110US935-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	466.9	2.4
10°-20°	1281.8	6.5
20°-30°	1799.5	9.2
30°-40°	1961.6	10.0
40°-50°	1802.9	9.2
50°-60°	1415.9	7.2
60°-70°	921.6	4.7
70°-80°	474.4	2.4
80°-90°	126.7	0.6
90°-100°	105.4	0.5
100°-110°	392.9	2.0
110°-120°	1042.0	5.3
120°-130°	1728.3	8.8
130°-140°	1835.9	9.4
140°-150°	1706.2	8.7
150°-160°	1371.8	7.0
160°-170°	883.9	4.5
170°-180°	304.2	1.6
0°-30°	3548.2	18.1
0°-40°	5509.8	28.1
0°-60°	8728.7	44.5
0°-90°	10251.5	52.2
90°-120°	1540.3	7.9
90°-150°	6810.7	34.7
90°-180°	9371.0	47.8
0°-180°	19622.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4982	4982	4982	4982	4982	
5°	4982	4959	4900	4941	4928	472
15°	4738	4689	4536	4450	4405	1335
25°	4301	4157	3859	3675	3607	1978
35°	3706	3476	3080	2795	2696	2320
45°	3030	2728	2254	1934	1826	2340
55°	2304	1952	1465	1195	1109	2059
65°	1556	1190	784	631	618	1542
75°	829	514	361	329	325	877
85°	194	99	86	86	86	222
90°	2	28	46	58	62	18
95°	150	74	90	102	99	178
105°	703	773	141	166	176	751
115°	1330	1369	1427	356	190	1309
125°	1880	1910	1954	1971	1978	1677
135°	2327	2364	2384	2408	2403	1797
145°	2699	2697	2736	2752	2741	1688
155°	2972	2951	2979	2993	2974	1370
165°	3132	3118	3125	3141	3125	885
175°	3203	3187	3192	3208	3185	305
180°	3196	3196	3196	3196	3196	

TEST NUMBER: P920579

CATALOG NUMBER: DFN2DIP-SQ4F0-140D110US935-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4981.9	4981.9	4981.9	4981.9	4981.9
2.5°	5004.4	4981.9	4932.1	4977.6	4968.5
5°	4981.9	4959.4	4900.5	4941.3	4927.8
7.5°	4941.3	4914.4	4851.3	4869.0	4846.6
10°	4887.2	4855.6	4765.7	4751.8	4725.0
12.5°	4819.7	4779.1	4657.1	4630.3	4580.6
15°	4738.4	4688.6	4535.6	4450.0	4405.0
17.5°	4643.7	4571.5	4382.0	4283.0	4210.8
20°	4535.6	4445.2	4219.9	4107.5	4008.0
22.5°	4418.4	4314.6	4053.0	3899.9	3832.5
25°	4301.2	4156.7	3859.3	3674.6	3606.6
27.5°	4161.5	4008.0	3678.9	3467.0	3363.2
30°	4012.8	3841.1	3480.4	3250.8	3128.8
32.5°	3868.3	3660.7	3291.4	3020.7	2907.8
35°	3706.2	3476.1	3079.5	2795.4	2695.9
37.5°	3548.3	3300.0	2881.0	2569.6	2457.2
40°	3381.4	3111.1	2673.4	2353.5	2236.3
42.5°	3210.1	2921.7	2466.3	2132.4	2020.0
45°	3029.8	2727.5	2254.4	1933.9	1825.8
47.5°	2858.5	2538.6	2051.6	1731.1	1632.1
50°	2669.1	2349.1	1853.0	1541.7	1447.4
52.5°	2484.0	2145.8	1663.6	1366.1	1280.5
55°	2303.7	1952.1	1465.2	1194.9	1109.2
57.5°	2119.0	1758.3	1289.6	1037.1	964.8
60°	1929.6	1568.9	1104.5	874.9	802.6
62.5°	1745.0	1384.3	946.7	730.4	694.6
65°	1555.6	1190.1	784.5	631.4	617.5
67.5°	1375.2	1009.8	631.4	554.4	541.0
70°	1185.8	834.2	522.8	477.9	459.7
72.5°	1005.5	671.6	437.2	401.3	392.3
75°	829.4	513.8	360.7	329.1	324.8
77.5°	653.9	365.0	284.1	266.0	256.8
80°	491.3	261.7	216.2	198.5	198.5
82.5°	342.5	176.0	148.8	139.7	139.7
85°	193.7	99.0	85.6	85.6	85.6
87.5°	72.2	35.9	35.9	31.6	31.6
90°	2.2	27.7	46.1	57.9	62.3
92.5°	57.9	48.6	55.4	60.2	62.3
95°	150.2	73.9	90.1	101.9	99.4
97.5°	270.5	81.0	117.8	124.9	127.2
100°	409.5	92.6	131.8	150.2	154.9
102.5°	561.9	557.5	136.5	161.8	168.9
105°	703.1	772.6	141.2	166.4	175.8
107.5°	867.4	925.0	145.9	171.1	180.5
110°	1024.7	1073.1	404.8	173.6	182.6



TEST NUMBER: P920579

CATALOG NUMBER: DFN2DIP-SQ4F0-140D110US935-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1172.8	1214.2	1174.9	178.0	185.1
115°	1329.8	1369.1	1427.1	356.2	189.8
117.5°	1466.4	1512.5	1552.0	1221.1	615.2
120°	1619.0	1653.6	1695.4	1723.1	1410.8
122.5°	1748.4	1785.5	1831.9	1845.6	1848.1
125°	1880.2	1910.5	1954.4	1970.6	1977.5
127.5°	2000.5	2032.9	2067.8	2090.8	2093.1
130°	2113.9	2151.0	2176.3	2201.8	2199.7
132.5°	2229.6	2259.8	2285.1	2305.9	2303.8
135°	2326.8	2363.9	2384.4	2407.9	2403.1
137.5°	2428.4	2456.2	2479.5	2502.6	2495.7
140°	2527.9	2546.5	2571.8	2592.6	2581.1
142.5°	2611.3	2627.5	2657.5	2675.9	2664.4
145°	2699.2	2696.7	2736.0	2752.3	2740.7
147.5°	2775.3	2768.5	2807.7	2819.3	2810.2
150°	2849.5	2833.3	2870.3	2884.1	2872.5
152.5°	2911.8	2893.4	2928.0	2942.0	2925.8
155°	2972.0	2951.3	2979.1	2992.8	2974.4
157.5°	3020.6	3002.1	3023.0	3039.2	3020.6
160°	3062.3	3048.3	3062.3	3076.0	3059.8
162.5°	3099.1	3085.4	3096.9	3113.1	3092.3
165°	3131.5	3117.8	3124.6	3140.8	3124.6
167.5°	3157.0	3143.1	3150.2	3166.4	3145.6
170°	3177.9	3163.9	3168.6	3184.8	3163.9
172.5°	3191.6	3177.9	3182.6	3198.8	3177.9
175°	3203.2	3187.0	3191.6	3207.9	3184.8
177.5°	3207.9	3191.6	3194.1	3210.3	3189.5
180°	3196.4	3196.4	3196.4	3196.4	3196.4

TEST NUMBER: P920579

CATALOG NUMBER: DFN2DIP-SQ4F0-140D110US935-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.72	12.56	12.66	13.52	14.76	7.68	8.53	8.62	9.48	10.72
	3H	13.40	14.16	14.35	15.12	16.39	8.87	9.63	9.82	10.59	11.86
	4H	14.01	14.73	14.98	15.70	16.97	9.32	10.04	10.29	11.01	12.28
	6H	14.44	15.10	15.42	16.07	17.36	9.64	10.30	10.62	11.28	12.56
	8H	14.57	15.19	15.55	16.19	17.47	9.73	10.36	10.72	11.35	12.64
	12H	14.63	15.23	15.62	16.21	17.52	9.78	10.37	10.77	11.36	12.67
4H	2H	11.74	12.45	12.71	13.42	14.70	8.28	8.99	9.25	9.96	11.24
	3H	13.57	14.17	14.56	15.17	16.45	9.63	10.23	10.61	11.22	12.51
	4H	14.27	14.81	15.26	15.80	17.12	10.18	10.72	11.17	11.72	13.03
	6H	14.79	15.26	15.79	16.27	17.58	10.60	11.07	11.61	12.08	13.39
	8H	14.97	15.40	15.97	16.41	17.74	10.73	11.17	11.74	12.18	13.50
	12H	15.07	15.46	16.09	16.48	17.81	10.80	11.19	11.82	12.21	13.54
8H	4H	14.24	14.67	15.24	15.68	17.01	10.46	10.90	11.47	11.91	13.23
	6H	14.81	15.17	15.84	16.22	17.54	10.98	11.34	12.01	12.39	13.72
	8H	15.03	15.35	16.07	16.38	17.72	11.18	11.49	12.21	12.53	13.87
	12H	15.17	15.45	16.21	16.48	17.87	11.30	11.58	12.34	12.61	13.99
12H	4H	14.19	14.58	15.21	15.61	16.94	10.47	10.86	11.49	11.89	13.22
	6H	14.78	15.10	15.82	16.14	17.48	11.03	11.35	12.07	12.39	13.73
	8H	15.01	15.29	16.05	16.32	17.70	11.25	11.53	12.29	12.56	13.94

END OF REPORT