

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P926061

Luminaire Tested: DFN2DIP-SQ4F0-160D090US950-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P926061
REPORT IS A COMBINATION OF REPORTS P901649 AND P898471
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-160D090US950-FLLONL
Description: 4 foot, Square Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 23611.5 lumens
Efficiency: N/A
Efficacy: 101.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 233.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P926061

CATALOG NUMBER: DFN2DIP-SQ4F0-160D090US950-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P926061

CATALOG NUMBER: DFN2DIP-SQ4F0-160D090US950-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	104	104	104	104	91	91	91	80	80	80	69	69	69
1	101	97	93	89	95	91	87	84	80	77	75	70	68	66	61	60	58
2	92	84	78	73	86	79	74	69	70	66	62	62	58	55	54	51	49
3	84	74	67	61	78	70	63	58	62	57	52	55	50	47	48	45	42
4	77	66	58	51	72	62	55	49	55	49	45	49	44	40	43	39	36
5	71	59	50	44	66	55	48	42	49	43	39	44	39	35	38	35	31
6	65	53	44	38	61	50	42	37	45	38	34	40	35	31	35	31	28
7	60	48	40	34	56	45	38	32	40	34	30	36	31	27	32	28	25
8	56	43	35	30	52	41	34	29	37	31	27	33	28	24	29	25	22
9	52	40	32	27	49	38	31	26	34	28	24	30	25	22	27	23	20
10	49	36	29	24	46	35	28	23	31	26	22	28	23	20	25	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4167	4167	4167
5°	4174	4110	4138
10°	4140	4056	4083
15°	4079	3990	3997
20°	3997	3898	3909
25°	3915	3788	3806
30°	3812	3685	3675
35°	3715	3564	3537
40°	3595	3442	3406
45°	3476	3320	3272
50°	3346	3192	3116
55°	3209	3043	2973
60°	3054	2867	2809
65°	2886	2684	2616
70°	2672	2462	2409
75°	2374	2196	2220
80°	2017	1857	1855
85°	1458	1270	1246

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3476 cd/sqm

TEST NUMBER: P926061

CATALOG NUMBER: DFN2DIP-SQ4F0-160D090US950-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	559.0	2.4
10°-20°	1572.8	6.7
20°-30°	2311.4	9.8
30°-40°	2684.6	11.4
40°-50°	2681.3	11.4
50°-60°	2338.0	9.9
60°-70°	1728.3	7.3
70°-80°	977.8	4.1
80°-90°	263.2	1.1
90°-100°	95.6	0.4
100°-110°	356.2	1.5
110°-120°	944.7	4.0
120°-130°	1566.8	6.6
130°-140°	1664.3	7.0
140°-150°	1546.8	6.6
150°-160°	1243.6	5.3
160°-170°	801.3	3.4
170°-180°	275.8	1.2
0°-30°	4443.3	18.8
0°-40°	7127.9	30.2
0°-60°	12147.2	51.4
0°-90°	15116.4	64.0
90°-120°	1396.4	5.9
90°-150°	6174.3	26.1
90°-180°	8495.0	36.0
0°-180°	23611.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	5939	5939	5939	5939	5939	
5°	5939	5917	5854	5899	5888	564
15°	5654	5620	5545	5568	5540	1592
25°	5117	5072	4975	4986	4975	2355
35°	4415	4358	4266	4232	4203	2757
45°	3593	3552	3466	3404	3381	2773
55°	2719	2684	2616	2547	2519	2431
65°	1834	1799	1742	1691	1662	1813
75°	959	948	919	885	897	1024
85°	234	228	223	205	200	261
90°	2	25	42	53	56	22
95°	136	67	82	92	90	161
105°	637	700	128	151	159	681
115°	1206	1241	1294	323	172	1187
125°	1704	1732	1772	1786	1793	1520
135°	2109	2143	2162	2183	2179	1629
145°	2447	2445	2480	2495	2485	1530
155°	2694	2676	2701	2713	2696	1242
165°	2839	2826	2833	2847	2833	802
175°	2904	2889	2894	2908	2887	276
180°	2898	2898	2898	2898	2898	

TEST NUMBER: P926061

CATALOG NUMBER: DFN2DIP-SQ4F0-160D090US950-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	5939.3	5939.3	5939.3	5939.3	5939.3
2.5°	5973.9	5945.3	5882.4	5939.3	5928.3
5°	5939.3	5916.9	5853.8	5899.3	5888.4
7.5°	5899.3	5865.4	5802.3	5848.4	5836.9
10°	5836.9	5796.9	5728.5	5773.9	5756.9
12.5°	5750.9	5716.9	5648.4	5677.0	5665.4
15°	5653.9	5620.0	5545.4	5568.5	5540.0
17.5°	5534.0	5500.0	5425.5	5453.9	5425.5
20°	5402.4	5368.5	5288.5	5305.5	5283.1
22.5°	5271.6	5220.1	5145.5	5145.5	5134.0
25°	5117.1	5071.7	4974.6	4985.6	4974.6
27.5°	4945.5	4905.6	4831.6	4814.7	4786.2
30°	4774.7	4728.7	4643.2	4626.2	4603.2
32.5°	4591.7	4557.8	4466.2	4431.7	4408.7
35°	4414.8	4357.9	4266.3	4231.8	4203.3
37.5°	4214.9	4163.4	4071.9	4031.8	4003.4
40°	4009.4	3963.4	3871.9	3821.0	3798.0
42.5°	3809.5	3763.4	3672.5	3615.0	3581.0
45°	3592.6	3552.5	3466.5	3404.1	3381.1
47.5°	3381.1	3341.1	3249.6	3186.6	3152.7
50°	3158.1	3129.6	3049.7	2969.6	2941.2
52.5°	2941.2	2901.2	2827.3	2764.2	2724.2
55°	2718.8	2684.3	2615.8	2547.3	2518.8
57.5°	2495.9	2467.3	2392.8	2324.3	2301.3
60°	2272.8	2250.4	2170.4	2107.4	2090.4
62.5°	2055.9	2015.9	1958.9	1902.0	1879.0
65°	1833.5	1799.0	1742.0	1690.6	1662.1
67.5°	1605.1	1576.0	1525.2	1485.1	1462.1
70°	1393.6	1370.6	1319.1	1279.1	1256.7
72.5°	1176.7	1153.7	1125.2	1085.2	1068.3
75°	959.2	948.3	919.2	885.2	896.8
77.5°	765.3	742.3	730.8	713.8	696.8
80°	571.4	565.3	553.8	536.8	525.4
82.5°	388.4	388.4	382.9	359.9	359.9
85°	233.9	228.4	222.9	205.4	200.0
87.5°	103.0	91.5	79.9	63.1	57.0
90°	2.0	25.2	41.8	52.6	56.5
92.5°	52.6	44.1	50.3	54.6	56.5
95°	136.2	67.0	81.7	92.3	90.2
97.5°	245.3	73.5	106.8	113.2	115.2
100°	371.2	84.0	119.5	136.2	140.4
102.5°	509.4	505.4	123.7	146.6	153.1
105°	637.4	700.4	127.9	150.9	159.3
107.5°	786.3	838.6	132.2	155.1	163.6
110°	928.9	972.8	367.0	157.3	165.6

TEST NUMBER: P926061

CATALOG NUMBER: DFN2DIP-SQ4F0-160D090US950-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1063.1	1100.7	1065.1	161.3	167.8
115°	1205.6	1241.2	1293.7	322.9	172.0
117.5°	1329.3	1371.2	1407.0	1107.0	557.7
120°	1467.7	1499.1	1537.0	1562.1	1279.0
122.5°	1585.1	1618.7	1660.7	1673.1	1675.4
125°	1704.5	1731.9	1771.8	1786.5	1792.7
127.5°	1813.6	1842.9	1874.6	1895.5	1897.5
130°	1916.4	1950.1	1973.0	1996.1	1994.1
132.5°	2021.2	2048.6	2071.5	2090.5	2088.5
135°	2109.4	2143.0	2161.7	2182.8	2178.6
137.5°	2201.5	2226.6	2247.8	2268.7	2262.5
140°	2291.6	2308.6	2331.5	2350.4	2340.0
142.5°	2367.4	2382.0	2409.1	2425.8	2415.4
145°	2447.0	2444.7	2480.4	2495.1	2484.6
147.5°	2516.0	2509.8	2545.4	2555.9	2547.6
150°	2583.2	2568.5	2602.1	2614.5	2604.1
152.5°	2639.7	2623.0	2654.4	2667.1	2652.4
155°	2694.3	2675.6	2700.7	2713.2	2696.5
157.5°	2738.4	2721.7	2740.6	2755.2	2738.4
160°	2776.1	2763.5	2776.1	2788.6	2773.9
162.5°	2809.5	2797.0	2807.5	2822.2	2803.3
165°	2838.9	2826.4	2832.7	2847.4	2832.7
167.5°	2862.1	2849.4	2855.8	2870.5	2851.6
170°	2881.0	2868.3	2872.5	2887.2	2868.3
172.5°	2893.5	2881.0	2885.2	2899.9	2881.0
175°	2903.9	2889.2	2893.5	2908.1	2887.2
177.5°	2908.1	2893.5	2895.7	2910.4	2891.5
180°	2897.7	2897.7	2897.7	2897.7	2897.7

TEST NUMBER: P926061

CATALOG NUMBER: DFN2DIP-SQ4F0-160D090US950-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.45	14.45	14.27	15.30	16.35	13.00	14.00	13.83	14.85	15.91
	3H	15.12	16.02	15.96	16.88	17.96	14.63	15.53	15.47	16.39	17.47
	4H	15.72	16.57	16.57	17.43	18.53	15.22	16.07	16.08	16.94	18.03
	6H	16.13	16.91	17.00	17.79	18.89	15.63	16.41	16.50	17.29	18.39
	8H	16.24	16.99	17.12	17.88	18.99	15.74	16.48	16.61	17.38	18.48
	12H	16.29	17.01	17.18	17.89	19.02	15.78	16.50	16.67	17.38	18.51
4H	2H	13.92	14.77	14.78	15.64	16.73	13.57	14.42	14.43	15.29	16.38
	3H	15.81	16.52	16.68	17.42	18.53	15.40	16.11	16.27	17.01	18.12
	4H	16.53	17.18	17.42	18.07	19.21	16.11	16.75	16.99	17.65	18.79
	6H	17.06	17.62	17.96	18.54	19.67	16.63	17.19	17.53	18.10	19.24
	8H	17.21	17.74	18.12	18.65	19.80	16.78	17.30	17.68	18.21	19.36
	12H	17.30	17.77	18.22	18.70	19.86	16.85	17.32	17.77	18.25	19.41
8H	4H	16.74	17.26	17.64	18.18	19.33	16.36	16.89	17.26	17.80	18.95
	6H	17.38	17.81	18.31	18.77	19.92	17.00	17.43	17.93	18.39	19.54
	8H	17.61	17.99	18.55	18.94	20.11	17.21	17.60	18.15	18.54	19.71
	12H	17.75	18.09	18.69	19.02	20.24	17.34	17.67	18.28	18.61	19.83
12H	4H	16.73	17.20	17.65	18.14	19.29	16.36	16.84	17.29	17.77	18.92
	6H	17.41	17.80	18.35	18.74	19.91	17.04	17.43	17.98	18.37	19.54
	8H	17.66	18.00	18.61	18.94	20.16	17.28	17.62	18.23	18.56	19.78