

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P926068

Luminaire Tested: DFN2DIP-SQ4F0-160D110US950-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P926068
REPORT IS A COMBINATION OF REPORTS P900165 AND P896915
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-160D110US950-FLLFLL
Description: 4 foot, Square Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 24398.6 lumens
Efficiency: N/A
Efficacy: 97.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 249.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P926068

CATALOG NUMBER: DFN2DIP-SQ4F0-160D110US950-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P926068

CATALOG NUMBER: DFN2DIP-SQ4F0-160D110US950-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67
1	100	96	92	89	94	90	87	84	79	76	74	69	67	65	59	58	57
2	92	84	78	72	85	79	73	69	69	65	61	60	57	54	52	50	48
3	84	74	66	60	78	69	63	57	61	56	52	53	49	46	46	43	41
4	76	65	57	51	71	62	54	49	54	49	44	48	43	40	41	38	35
5	70	58	50	44	66	55	48	42	49	43	38	43	38	34	37	34	31
6	65	52	44	38	60	49	42	37	44	38	33	39	34	30	34	30	27
7	60	47	39	34	56	45	37	32	40	34	29	35	30	27	31	27	24
8	56	43	35	30	52	41	34	29	36	30	26	32	27	24	28	25	22
9	52	39	32	27	49	37	30	26	33	28	24	30	25	21	26	22	19
10	49	36	29	24	46	34	28	23	31	25	21	28	23	19	24	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4167	4167	4167
5°	4174	4110	4138
10°	4140	4056	4083
15°	4079	3990	3997
20°	3997	3898	3909
25°	3915	3788	3806
30°	3812	3685	3675
35°	3715	3564	3537
40°	3595	3442	3406
45°	3476	3320	3272
50°	3346	3192	3116
55°	3209	3043	2973
60°	3054	2867	2809
65°	2886	2684	2616
70°	2672	2462	2409
75°	2374	2196	2220
80°	2017	1857	1855
85°	1458	1270	1246

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3476 cd/sqm

TEST NUMBER: P926068

CATALOG NUMBER: DFN2DIP-SQ4F0-160D110US950-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	559.0	2.3
10°-20°	1572.8	6.4
20°-30°	2311.4	9.5
30°-40°	2684.6	11.0
40°-50°	2681.3	11.0
50°-60°	2338.0	9.6
60°-70°	1728.3	7.1
70°-80°	977.8	4.0
80°-90°	267.5	1.1
90°-100°	205.4	0.8
100°-110°	652.5	2.7
110°-120°	1116.7	4.6
120°-130°	1468.6	6.0
130°-140°	1648.4	6.8
140°-150°	1616.5	6.6
150°-160°	1356.0	5.6
160°-170°	899.3	3.7
170°-180°	314.3	1.3
0°-30°	4443.3	18.2
0°-40°	7127.9	29.2
0°-60°	12147.2	49.8
0°-90°	15120.8	62.0
90°-120°	1974.6	8.1
90°-150°	6708.2	27.5
90°-180°	9278.0	38.0
0°-180°	24398.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	5939	5939	5939	5939	5939	
5°	5939	5917	5854	5899	5888	564
15°	5654	5620	5545	5568	5540	1592
25°	5117	5072	4975	4986	4975	2355
35°	4415	4358	4266	4232	4203	2757
45°	3593	3552	3466	3404	3381	2773
55°	2719	2684	2616	2547	2519	2431
65°	1834	1799	1742	1691	1662	1813
75°	959	948	919	885	897	1024
85°	234	228	223	205	200	261
90°	3	36	98	92	95	23
95°	146	174	179	179	174	163
105°	602	610	616	621	621	636
115°	1121	1137	1132	1129	1121	1108
125°	1630	1655	1647	1638	1635	1457
135°	2108	2139	2145	2142	2134	1630
145°	2559	2579	2596	2598	2587	1599
155°	2927	2935	2944	2958	2949	1347
165°	3184	3181	3181	3201	3187	898
175°	3313	3305	3299	3319	3302	315
180°	3319	3319	3319	3319	3319	

TEST NUMBER: P926068

CATALOG NUMBER: DFN2DIP-SQ4F0-160D110US950-FLLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	5939.3	5939.3	5939.3	5939.3	5939.3
2.5°	5973.9	5945.3	5882.4	5939.3	5928.3
5°	5939.3	5916.9	5853.8	5899.3	5888.4
7.5°	5899.3	5865.4	5802.3	5848.4	5836.9
10°	5836.9	5796.9	5728.5	5773.9	5756.9
12.5°	5750.9	5716.9	5648.4	5677.0	5665.4
15°	5653.9	5620.0	5545.4	5568.5	5540.0
17.5°	5534.0	5500.0	5425.5	5453.9	5425.5
20°	5402.4	5368.5	5288.5	5305.5	5283.1
22.5°	5271.6	5220.1	5145.5	5145.5	5134.0
25°	5117.1	5071.7	4974.6	4985.6	4974.6
27.5°	4945.5	4905.6	4831.6	4814.7	4786.2
30°	4774.7	4728.7	4643.2	4626.2	4603.2
32.5°	4591.7	4557.8	4466.2	4431.7	4408.7
35°	4414.8	4357.9	4266.3	4231.8	4203.3
37.5°	4214.9	4163.4	4071.9	4031.8	4003.4
40°	4009.4	3963.4	3871.9	3821.0	3798.0
42.5°	3809.5	3763.4	3672.5	3615.0	3581.0
45°	3592.6	3552.5	3466.5	3404.1	3381.1
47.5°	3381.1	3341.1	3249.6	3186.6	3152.7
50°	3158.1	3129.6	3049.7	2969.6	2941.2
52.5°	2941.2	2901.2	2827.3	2764.2	2724.2
55°	2718.8	2684.3	2615.8	2547.3	2518.8
57.5°	2495.9	2467.3	2392.8	2324.3	2301.3
60°	2272.8	2250.4	2170.4	2107.4	2090.4
62.5°	2055.9	2015.9	1958.9	1902.0	1879.0
65°	1833.5	1799.0	1742.0	1690.6	1662.1
67.5°	1605.1	1576.0	1525.2	1485.1	1462.1
70°	1393.6	1370.6	1319.1	1279.1	1256.7
72.5°	1176.7	1153.7	1125.2	1085.2	1068.3
75°	959.2	948.3	919.2	885.2	896.8
77.5°	765.3	742.3	730.8	713.8	696.8
80°	571.4	565.3	553.8	536.8	525.4
82.5°	388.4	388.4	382.9	359.9	359.9
85°	233.9	228.4	222.9	205.4	200.0
87.5°	103.0	91.5	79.9	63.1	57.0
90°	3.0	36.1	98.1	92.1	95.0
92.5°	62.0	84.0	87.0	90.1	90.1
95°	146.1	174.1	179.1	179.1	174.1
97.5°	243.2	269.1	280.2	280.2	280.2
100°	355.2	378.2	386.2	386.2	383.2
102.5°	473.3	490.3	501.3	504.3	501.3
105°	602.4	610.4	616.4	621.3	621.3
107.5°	730.4	742.4	742.4	744.4	730.4
110°	854.5	870.5	870.5	870.5	862.5

TEST NUMBER: P926068

CATALOG NUMBER: DFN2DIP-SQ4F0-160D110US950-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	988.5	1005.5	1002.6	994.5	988.5
115°	1120.7	1136.6	1131.6	1128.7	1120.7
117.5°	1251.7	1273.7	1259.7	1251.7	1243.7
120°	1383.8	1405.8	1383.8	1383.8	1374.8
122.5°	1503.9	1531.8	1517.8	1509.8	1503.9
125°	1629.9	1654.9	1646.9	1637.9	1634.9
127.5°	1753.0	1784.0	1773.0	1761.0	1753.0
130°	1868.0	1904.1	1899.0	1893.0	1882.1
132.5°	1997.1	2025.2	2027.2	2013.1	2005.1
135°	2108.1	2139.2	2145.2	2142.2	2134.2
137.5°	2232.3	2257.3	2262.2	2260.2	2248.3
140°	2341.3	2366.3	2380.3	2380.3	2369.4
142.5°	2453.4	2478.4	2486.4	2489.4	2478.4
145°	2559.4	2579.4	2595.5	2598.4	2587.4
147.5°	2654.5	2679.5	2691.5	2696.5	2685.5
150°	2752.6	2769.6	2780.5	2789.6	2780.5
152.5°	2839.6	2856.6	2870.6	2881.7	2870.6
155°	2926.7	2934.6	2943.7	2957.7	2948.6
157.5°	3001.7	3007.7	3012.6	3032.7	3018.6
160°	3068.7	3074.7	3077.7	3094.8	3082.8
162.5°	3130.7	3130.7	3133.8	3152.8	3138.8
165°	3183.8	3180.7	3180.7	3200.8	3186.7
167.5°	3231.8	3222.8	3222.8	3242.8	3228.8
170°	3267.8	3259.8	3256.9	3276.8	3259.8
172.5°	3292.8	3284.8	3281.9	3301.9	3284.8
175°	3312.9	3304.8	3298.8	3318.9	3301.9
177.5°	3323.8	3315.8	3309.8	3326.9	3309.8
180°	3318.9	3318.9	3318.9	3318.9	3318.9

TEST NUMBER: P926068

CATALOG NUMBER: DFN2DIP-SQ4F0-160D110US950-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.28	14.26	14.13	15.13	16.22	12.83	13.82	13.68	14.68	15.77
	3H	14.95	15.83	15.81	16.71	17.83	14.46	15.34	15.32	16.22	17.34
	4H	15.55	16.38	16.42	17.27	18.39	15.05	15.89	15.93	16.77	17.90
	6H	15.96	16.73	16.85	17.62	18.76	15.46	16.23	16.35	17.12	18.26
	8H	16.07	16.80	16.96	17.71	18.85	15.57	16.30	16.46	17.21	18.35
	12H	16.12	16.82	17.02	17.72	18.89	15.61	16.31	16.51	17.21	18.38
4H	2H	13.76	14.59	14.64	15.47	16.60	13.40	14.23	14.28	15.12	16.24
	3H	15.64	16.33	16.53	17.25	18.39	15.23	15.92	16.12	16.84	17.98
	4H	16.36	16.99	17.26	17.91	19.07	15.94	16.57	16.84	17.48	18.65
	6H	16.89	17.43	17.80	18.37	19.54	16.45	17.00	17.37	17.94	19.11
	8H	17.04	17.55	17.96	18.48	19.66	16.60	17.11	17.52	18.04	19.23
	12H	17.12	17.58	18.06	18.53	19.72	16.67	17.13	17.61	18.08	19.27
8H	4H	16.57	17.08	17.49	18.01	19.19	16.19	16.70	17.11	17.63	18.81
	6H	17.21	17.63	18.15	18.60	19.78	16.82	17.25	17.77	18.22	19.40
	8H	17.43	17.81	18.39	18.77	19.97	17.04	17.41	18.00	18.38	19.58
	12H	17.57	17.90	18.53	18.86	20.11	17.16	17.49	18.12	18.45	19.70
12H	4H	16.56	17.02	17.50	17.97	19.16	16.19	16.65	17.13	17.60	18.79
	6H	17.24	17.61	18.19	18.58	19.78	16.87	17.24	17.82	18.20	19.40
	8H	17.49	17.82	18.45	18.78	20.02	17.11	17.44	18.07	18.39	19.64