

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P920613

Luminaire Tested: DFN2DIP-SQ4F0-160D110US935-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P920613
REPORT IS A COMBINATION OF REPORTS P901685 AND P898471
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-160D110US935-FLLONL
Description: 4 foot, Square Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 23014.4 lumens
Efficiency: N/A
Efficacy: 92.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 249.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P920613

CATALOG NUMBER: DFN2DIP-SQ4F0-160D110US935-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P920613

CATALOG NUMBER: DFN2DIP-SQ4F0-160D110US935-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	65	65	65
1	100	95	92	88	93	89	86	83	78	75	73	67	65	63	57	56	55
2	91	83	77	72	85	78	73	68	68	64	60	59	56	53	50	48	46
3	83	73	66	60	77	69	62	57	60	55	51	52	48	45	45	42	39
4	76	65	57	51	71	61	54	48	53	48	43	46	42	38	40	37	34
5	70	58	50	44	65	54	47	41	48	42	37	42	37	33	36	32	29
6	64	52	44	38	60	49	42	36	43	37	33	38	33	29	33	29	26
7	60	47	39	33	55	44	37	32	39	33	29	34	30	26	30	26	23
8	55	43	35	30	52	40	33	28	36	30	26	31	27	23	27	24	21
9	52	39	32	26	48	37	30	25	33	27	23	29	24	21	25	22	19
10	48	36	29	24	45	34	27	23	30	25	21	27	22	19	24	20	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3761	3761	3761
5°	3767	3710	3735
10°	3736	3660	3685
15°	3682	3601	3607
20°	3607	3518	3528
25°	3533	3418	3435
30°	3441	3326	3317
35°	3353	3217	3192
40°	3245	3107	3074
45°	3137	2996	2953
50°	3019	2881	2812
55°	2896	2746	2683
60°	2757	2587	2535
65°	2605	2423	2361
70°	2411	2222	2174
75°	2143	1982	2003
80°	1820	1676	1674
85°	1316	1147	1125

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3137 cd/sqm

TEST NUMBER: P920613

CATALOG NUMBER: DFN2DIP-SQ4F0-160D110US935-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	504.5	2.2
10°-20°	1419.5	6.2
20°-30°	2086.1	9.1
30°-40°	2422.9	10.5
40°-50°	2419.9	10.5
50°-60°	2110.1	9.2
60°-70°	1559.8	6.8
70°-80°	882.5	3.8
80°-90°	238.5	1.0
90°-100°	105.4	0.5
100°-110°	392.9	1.7
110°-120°	1042.0	4.5
120°-130°	1728.3	7.5
130°-140°	1835.9	8.0
140°-150°	1706.2	7.4
150°-160°	1371.8	6.0
160°-170°	883.9	3.8
170°-180°	304.2	1.3
0°-30°	4010.1	17.4
0°-40°	6433.0	28.0
0°-60°	10963.0	47.6
0°-90°	13643.8	59.3
90°-120°	1540.3	6.7
90°-150°	6810.7	29.6
90°-180°	9371.0	40.7
0°-180°	23014.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	5360	5360	5360	5360	5360	
5°	5360	5340	5283	5324	5314	509
15°	5103	5072	5005	5026	5000	1437
25°	4618	4577	4490	4500	4490	2125
35°	3984	3933	3850	3819	3794	2488
45°	3242	3206	3129	3072	3052	2502
55°	2454	2423	2361	2299	2273	2194
65°	1655	1624	1572	1526	1500	1636
75°	866	856	830	799	809	924
85°	211	206	201	185	180	235
90°	2	28	46	58	62	21
95°	150	74	90	102	99	178
105°	703	773	141	166	176	751
115°	1330	1369	1427	356	190	1309
125°	1880	1910	1954	1971	1978	1677
135°	2327	2364	2384	2408	2403	1797
145°	2699	2697	2736	2752	2741	1688
155°	2972	2951	2979	2993	2974	1370
165°	3132	3118	3125	3141	3125	885
175°	3203	3187	3192	3208	3185	305
180°	3196	3196	3196	3196	3196	

TEST NUMBER: P920613

CATALOG NUMBER: DFN2DIP-SQ4F0-160D110US935-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	5360.3	5360.3	5360.3	5360.3	5360.3
2.5°	5391.5	5365.7	5308.9	5360.3	5350.4
5°	5360.3	5340.1	5283.2	5324.2	5314.3
7.5°	5324.2	5293.6	5236.7	5278.3	5267.8
10°	5267.8	5231.8	5170.0	5211.0	5195.7
12.5°	5190.3	5159.6	5097.8	5123.5	5113.1
15°	5102.7	5072.1	5004.8	5025.6	4999.9
17.5°	4994.5	4963.8	4896.6	4922.2	4896.6
20°	4875.7	4845.2	4772.9	4788.3	4768.0
22.5°	4757.7	4711.2	4643.9	4643.9	4633.5
25°	4618.2	4577.2	4489.7	4499.6	4489.7
27.5°	4463.4	4427.3	4360.6	4345.4	4319.6
30°	4309.2	4267.7	4190.6	4175.2	4154.5
32.5°	4144.1	4113.5	4030.8	3999.7	3978.9
35°	3984.4	3933.0	3850.4	3819.2	3793.6
37.5°	3804.0	3757.5	3674.9	3638.7	3613.1
40°	3618.5	3577.0	3494.4	3448.5	3427.7
42.5°	3438.1	3396.6	3314.5	3262.6	3231.9
45°	3242.3	3206.2	3128.6	3072.2	3051.5
47.5°	3051.5	3015.4	2932.8	2875.9	2845.3
50°	2850.2	2824.5	2752.4	2680.1	2654.5
52.5°	2654.5	2618.4	2551.7	2494.7	2458.7
55°	2453.8	2422.6	2360.8	2299.0	2273.3
57.5°	2252.5	2226.8	2159.6	2097.7	2077.0
60°	2051.2	2031.0	1958.9	1901.9	1886.6
62.5°	1855.5	1819.4	1768.0	1716.6	1695.8
65°	1654.8	1623.6	1572.2	1525.8	1500.0
67.5°	1448.6	1422.4	1376.5	1340.3	1319.6
70°	1257.7	1237.0	1190.5	1154.4	1134.2
72.5°	1062.0	1041.2	1015.5	979.4	964.1
75°	865.6	855.8	829.6	798.9	809.3
77.5°	690.7	669.9	659.5	644.2	628.9
80°	515.7	510.2	499.8	484.5	474.2
82.5°	350.5	350.5	345.6	324.9	324.9
85°	211.1	206.1	201.2	185.4	180.5
87.5°	93.0	82.6	72.2	56.9	51.4
90°	2.2	27.7	46.1	57.9	62.3
92.5°	57.9	48.6	55.4	60.2	62.3
95°	150.2	73.9	90.1	101.9	99.4
97.5°	270.5	81.0	117.8	124.9	127.2
100°	409.5	92.6	131.8	150.2	154.9
102.5°	561.9	557.5	136.5	161.8	168.9
105°	703.1	772.6	141.2	166.4	175.8
107.5°	867.4	925.0	145.9	171.1	180.5
110°	1024.7	1073.1	404.8	173.6	182.6



TEST NUMBER: P920613

CATALOG NUMBER: DFN2DIP-SQ4F0-160D110US935-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1172.8	1214.2	1174.9	178.0	185.1
115°	1329.8	1369.1	1427.1	356.2	189.8
117.5°	1466.4	1512.5	1552.0	1221.1	615.2
120°	1619.0	1653.6	1695.4	1723.1	1410.8
122.5°	1748.4	1785.5	1831.9	1845.6	1848.1
125°	1880.2	1910.5	1954.4	1970.6	1977.5
127.5°	2000.5	2032.9	2067.8	2090.8	2093.1
130°	2113.9	2151.0	2176.3	2201.8	2199.7
132.5°	2229.6	2259.8	2285.1	2305.9	2303.8
135°	2326.8	2363.9	2384.4	2407.9	2403.1
137.5°	2428.4	2456.2	2479.5	2502.6	2495.7
140°	2527.9	2546.5	2571.8	2592.6	2581.1
142.5°	2611.3	2627.5	2657.5	2675.9	2664.4
145°	2699.2	2696.7	2736.0	2752.3	2740.7
147.5°	2775.3	2768.5	2807.7	2819.3	2810.2
150°	2849.5	2833.3	2870.3	2884.1	2872.5
152.5°	2911.8	2893.4	2928.0	2942.0	2925.8
155°	2972.0	2951.3	2979.1	2992.8	2974.4
157.5°	3020.6	3002.1	3023.0	3039.2	3020.6
160°	3062.3	3048.3	3062.3	3076.0	3059.8
162.5°	3099.1	3085.4	3096.9	3113.1	3092.3
165°	3131.5	3117.8	3124.6	3140.8	3124.6
167.5°	3157.0	3143.1	3150.2	3166.4	3145.6
170°	3177.9	3163.9	3168.6	3184.8	3163.9
172.5°	3191.6	3177.9	3182.6	3198.8	3177.9
175°	3203.2	3187.0	3191.6	3207.9	3184.8
177.5°	3207.9	3191.6	3194.1	3210.3	3189.5
180°	3196.4	3196.4	3196.4	3196.4	3196.4

TEST NUMBER: P920613

CATALOG NUMBER: DFN2DIP-SQ4F0-160D110US935-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.70	13.65	13.58	14.55	15.68	12.26	13.21	13.13	14.10	15.24
	3H	14.37	15.23	15.26	16.13	17.29	13.88	14.74	14.77	15.64	16.80
	4H	14.97	15.78	15.87	16.69	17.85	14.47	15.28	15.38	16.19	17.36
	6H	15.38	16.12	16.29	17.04	18.22	14.88	15.62	15.79	16.54	17.72
	8H	15.49	16.19	16.41	17.13	18.31	14.98	15.69	15.90	16.63	17.81
	12H	15.54	16.21	16.46	17.14	18.35	15.03	15.70	15.96	16.63	17.84
4H	2H	13.17	13.98	14.08	14.89	16.06	12.82	13.63	13.73	14.54	15.70
	3H	15.05	15.73	15.97	16.67	17.85	14.65	15.32	15.56	16.26	17.44
	4H	15.77	16.39	16.70	17.33	18.53	15.35	15.97	16.28	16.90	18.11
	6H	16.30	16.83	17.24	17.79	19.00	15.87	16.40	16.81	17.36	18.57
	8H	16.45	16.95	17.40	17.90	19.13	16.02	16.51	16.96	17.47	18.69
	12H	16.53	16.98	17.50	17.95	19.18	16.08	16.53	17.05	17.50	18.73
8H	4H	15.98	16.47	16.92	17.43	18.65	15.60	16.10	16.55	17.05	18.27
	6H	16.62	17.03	17.59	18.02	19.25	16.24	16.65	17.21	17.64	18.86
	8H	16.84	17.21	17.82	18.19	19.43	16.45	16.81	17.43	17.80	19.04
	12H	16.98	17.30	17.96	18.28	19.57	16.57	16.89	17.55	17.87	19.16
12H	4H	15.97	16.42	16.93	17.39	18.62	15.60	16.05	16.56	17.02	18.25
	6H	16.65	17.01	17.63	18.00	19.24	16.28	16.64	17.26	17.63	18.87
	8H	16.90	17.22	17.88	18.20	19.48	16.52	16.84	17.50	17.82	19.10

END OF REPORT