

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P926076

Luminaire Tested: DFN2DIP-SQ4F0-160D140US950-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P926076
REPORT IS A COMBINATION OF REPORTS P900201 AND P896915
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-160D140US950-FLLFLL
Description: 4 foot, Square Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 26931.4 lumens
Efficiency: N/A
Efficacy: 98.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 272.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P926076

CATALOG NUMBER: DFN2DIP-SQ4F0-160D140US950-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P926076

CATALOG NUMBER: DFN2DIP-SQ4F0-160D140US950-FLLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	109	109	109	109		101	101	101	101		87	87	87		74	74	74		62	62	62
1	99	95	91	87		92	88	85	82		76	74	71		65	63	61		55	53	52
2	90	83	77	71		84	77	72	67		67	63	59		57	54	51		48	46	44
3	82	73	65	59		76	68	61	56		59	54	50		50	47	43		43	40	37
4	75	64	56	50		70	60	53	48		52	47	42		45	41	37		38	35	32
5	69	57	49	43		64	54	46	41		47	41	37		40	36	32		34	31	28
6	64	52	43	38		59	48	41	36		42	36	32		37	32	28		31	28	25
7	59	47	39	33		55	44	37	31		38	32	28		33	29	25		28	25	22
8	55	42	35	29		51	40	33	28		35	29	25		30	26	22		26	23	20
9	51	39	31	26		47	36	30	25		32	26	23		28	23	20		24	21	18
10	48	36	28	23		44	34	27	22		30	24	20		26	21	18		22	19	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4167	4167	4167
5°	4174	4110	4138
10°	4140	4056	4083
15°	4079	3990	3997
20°	3997	3898	3909
25°	3915	3788	3806
30°	3812	3685	3675
35°	3715	3564	3537
40°	3595	3442	3406
45°	3476	3320	3272
50°	3346	3192	3116
55°	3209	3043	2973
60°	3054	2867	2809
65°	2886	2684	2616
70°	2672	2462	2409
75°	2374	2196	2220
80°	2017	1857	1855
85°	1458	1270	1246

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3476 cd/sqm

TEST NUMBER: P926076

CATALOG NUMBER: DFN2DIP-SQ4F0-160D140US950-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	559.0	2.1
10°-20°	1572.8	5.8
20°-30°	2311.4	8.6
30°-40°	2684.6	10.0
40°-50°	2681.3	10.0
50°-60°	2338.0	8.7
60°-70°	1728.3	6.4
70°-80°	977.8	3.6
80°-90°	270.1	1.0
90°-100°	261.4	1.0
100°-110°	830.5	3.1
110°-120°	1421.2	5.3
120°-130°	1869.1	6.9
130°-140°	2098.0	7.8
140°-150°	2057.4	7.6
150°-160°	1725.8	6.4
160°-170°	1144.5	4.2
170°-180°	400.0	1.5
0°-30°	4443.3	16.5
0°-40°	7127.9	26.5
0°-60°	12147.2	45.1
0°-90°	15123.3	56.2
90°-120°	2513.1	9.3
90°-150°	8537.6	31.7
90°-180°	11808.0	43.8
0°-180°	26931.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	5939	5939	5939	5939	5939	
5°	5939	5917	5854	5899	5888	564
15°	5654	5620	5545	5568	5540	1592
25°	5117	5072	4975	4986	4975	2355
35°	4415	4358	4266	4232	4203	2757
45°	3593	3552	3466	3404	3381	2773
55°	2719	2684	2616	2547	2519	2431
65°	1834	1799	1742	1691	1662	1813
75°	959	948	919	885	897	1024
85°	234	228	223	205	200	261
90°	4	46	125	117	121	26
95°	186	222	228	228	222	207
105°	767	777	784	791	791	809
115°	1426	1447	1440	1436	1426	1411
125°	2074	2106	2096	2085	2081	1854
135°	2683	2723	2730	2726	2716	2074
145°	3257	3283	3303	3307	3293	2035
155°	3725	3735	3746	3764	3753	1714
165°	4052	4048	4048	4074	4056	1143
175°	4216	4206	4199	4224	4202	401
180°	4224	4224	4224	4224	4224	

TEST NUMBER: P926076

CATALOG NUMBER: DFN2DIP-SQ4F0-160D140US950-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	5939.3	5939.3	5939.3	5939.3	5939.3
2.5°	5973.9	5945.3	5882.4	5939.3	5928.3
5°	5939.3	5916.9	5853.8	5899.3	5888.4
7.5°	5899.3	5865.4	5802.3	5848.4	5836.9
10°	5836.9	5796.9	5728.5	5773.9	5756.9
12.5°	5750.9	5716.9	5648.4	5677.0	5665.4
15°	5653.9	5620.0	5545.4	5568.5	5540.0
17.5°	5534.0	5500.0	5425.5	5453.9	5425.5
20°	5402.4	5368.5	5288.5	5305.5	5283.1
22.5°	5271.6	5220.1	5145.5	5145.5	5134.0
25°	5117.1	5071.7	4974.6	4985.6	4974.6
27.5°	4945.5	4905.6	4831.6	4814.7	4786.2
30°	4774.7	4728.7	4643.2	4626.2	4603.2
32.5°	4591.7	4557.8	4466.2	4431.7	4408.7
35°	4414.8	4357.9	4266.3	4231.8	4203.3
37.5°	4214.9	4163.4	4071.9	4031.8	4003.4
40°	4009.4	3963.4	3871.9	3821.0	3798.0
42.5°	3809.5	3763.4	3672.5	3615.0	3581.0
45°	3592.6	3552.5	3466.5	3404.1	3381.1
47.5°	3381.1	3341.1	3249.6	3186.6	3152.7
50°	3158.1	3129.6	3049.7	2969.6	2941.2
52.5°	2941.2	2901.2	2827.3	2764.2	2724.2
55°	2718.8	2684.3	2615.8	2547.3	2518.8
57.5°	2495.9	2467.3	2392.8	2324.3	2301.3
60°	2272.8	2250.4	2170.4	2107.4	2090.4
62.5°	2055.9	2015.9	1958.9	1902.0	1879.0
65°	1833.5	1799.0	1742.0	1690.6	1662.1
67.5°	1605.1	1576.0	1525.2	1485.1	1462.1
70°	1393.6	1370.6	1319.1	1279.1	1256.7
72.5°	1176.7	1153.7	1125.2	1085.2	1068.3
75°	959.2	948.3	919.2	885.2	896.8
77.5°	765.3	742.3	730.8	713.8	696.8
80°	571.4	565.3	553.8	536.8	525.4
82.5°	388.4	388.4	382.9	359.9	359.9
85°	233.9	228.4	222.9	205.4	200.0
87.5°	103.0	91.5	79.9	63.1	57.0
90°	3.8	45.9	124.8	117.2	121.0
92.5°	79.0	106.9	110.8	114.6	114.6
95°	185.9	221.6	227.9	227.9	221.6
97.5°	309.5	342.6	356.6	356.6	356.6
100°	452.1	481.4	491.5	491.5	487.7
102.5°	602.4	624.0	638.0	641.9	638.0
105°	766.6	776.8	784.5	790.8	790.8
107.5°	929.6	944.9	944.9	947.4	929.6
110°	1087.6	1107.9	1107.9	1107.9	1097.7

TEST NUMBER: P926076

CATALOG NUMBER: DFN2DIP-SQ4F0-160D140US950-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1258.1	1279.8	1276.0	1265.8	1258.1
115°	1426.2	1446.6	1440.3	1436.4	1426.2
117.5°	1593.1	1621.1	1603.3	1593.1	1582.9
120°	1761.2	1789.2	1761.2	1761.2	1749.7
122.5°	1914.0	1949.6	1931.8	1921.6	1914.0
125°	2074.5	2106.2	2096.0	2084.6	2080.8
127.5°	2231.0	2270.5	2256.5	2241.2	2231.0
130°	2377.5	2423.4	2417.0	2409.3	2395.3
132.5°	2541.7	2577.4	2580.0	2562.2	2552.0
135°	2683.1	2722.6	2730.3	2726.4	2716.2
137.5°	2841.0	2872.9	2879.3	2876.7	2861.4
140°	2979.8	3011.7	3029.5	3029.5	3015.5
142.5°	3122.4	3154.3	3164.5	3168.3	3154.3
145°	3257.4	3282.9	3303.3	3307.1	3293.1
147.5°	3378.4	3410.3	3425.5	3431.9	3417.9
150°	3503.2	3524.8	3538.9	3550.3	3538.9
152.5°	3614.0	3635.7	3653.5	3667.5	3653.5
155°	3724.8	3735.0	3746.5	3764.3	3752.8
157.5°	3820.3	3827.9	3834.3	3859.8	3841.9
160°	3905.7	3913.3	3917.1	3938.8	3923.4
162.5°	3984.6	3984.6	3988.4	4012.6	3994.8
165°	4052.1	4048.3	4048.3	4073.8	4055.9
167.5°	4113.2	4101.7	4101.7	4127.2	4109.4
170°	4159.1	4148.9	4145.0	4170.5	4148.9
172.5°	4190.9	4180.7	4176.9	4202.4	4180.7
175°	4216.4	4206.2	4198.6	4224.0	4202.4
177.5°	4230.3	4220.2	4212.6	4234.1	4212.6
180°	4224.0	4224.0	4224.0	4224.0	4224.0

TEST NUMBER: P926076

CATALOG NUMBER: DFN2DIP-SQ4F0-160D140US950-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.79	13.71	13.69	14.63	15.81	12.35	13.27	13.25	14.19	15.37
	3H	14.46	15.29	15.38	16.22	17.42	13.97	14.80	14.89	15.73	16.93
	4H	15.05	15.83	15.98	16.77	17.99	14.56	15.34	15.49	16.28	17.49
	6H	15.46	16.18	16.40	17.12	18.35	14.96	15.68	15.90	16.62	17.85
	8H	15.57	16.25	16.52	17.21	18.44	15.07	15.75	16.02	16.71	17.94
	12H	15.62	16.27	16.57	17.23	18.48	15.11	15.76	16.06	16.72	17.97
4H	2H	13.26	14.04	14.20	14.98	16.19	12.91	13.69	13.84	14.62	15.84
	3H	15.14	15.79	16.08	16.75	17.98	14.73	15.38	15.67	16.35	17.58
	4H	15.86	16.45	16.81	17.41	18.67	15.43	16.03	16.39	16.99	18.24
	6H	16.38	16.89	17.35	17.88	19.13	15.95	16.46	16.91	17.45	18.70
	8H	16.53	17.01	17.50	17.99	19.26	16.10	16.57	17.07	17.55	18.82
	12H	16.61	17.04	17.60	18.04	19.31	16.16	16.59	17.15	17.59	18.86
8H	4H	16.06	16.54	17.03	17.52	18.78	15.68	16.16	16.65	17.14	18.41
	6H	16.70	17.09	17.69	18.11	19.38	16.31	16.71	17.31	17.73	19.00
	8H	16.92	17.27	17.93	18.28	19.56	16.53	16.88	17.53	17.89	19.17
	12H	17.06	17.37	18.07	18.37	19.70	16.65	16.96	17.66	17.96	19.29
12H	4H	16.05	16.48	17.04	17.47	18.75	15.68	16.11	16.67	17.11	18.38
	6H	16.73	17.08	17.73	18.09	19.37	16.36	16.71	17.36	17.71	19.00
	8H	16.98	17.28	17.98	18.29	19.62	16.60	16.90	17.60	17.91	19.24