

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P904260

Luminaire Tested: DFN2DIP-TR2F0-020D020US830-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P904260
REPORT IS A COMBINATION OF REPORTS P900221 AND P897145
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR2F0-020D020US830-FLLFLL
Description: 2 foot, Triangle Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3534.5 lumens
Efficiency: N/A
Efficacy: 115.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.04' x L: 2.36' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 30.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P904260

CATALOG NUMBER: DFN2DIP-TR2F0-020D020US830-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P904260

CATALOG NUMBER: DFN2DIP-TR2F0-020D020US830-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59
1	98	94	90	87	91	87	84	81	74	72	70	63	61	59	52	51	50
2	90	82	76	71	83	76	71	66	65	61	58	55	52	50	46	44	42
3	82	72	65	59	75	67	61	55	58	53	49	49	45	42	41	38	36
4	75	64	56	50	69	60	52	47	51	46	41	43	39	36	36	33	31
5	69	57	49	43	63	53	46	40	46	40	36	39	35	31	33	29	27
6	63	51	43	37	58	48	40	35	41	36	31	35	31	27	30	26	24
7	59	46	38	33	54	43	36	31	37	32	28	32	28	24	27	24	21
8	54	42	34	29	50	39	32	27	34	29	24	29	25	22	25	21	19
9	51	38	31	26	47	36	29	24	31	26	22	27	23	19	23	20	17
10	47	35	28	23	44	33	26	22	29	23	20	25	21	18	21	18	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1636	1636	1636
5°	1636	1609	1621
10°	1621	1584	1597
15°	1594	1555	1559
20°	1560	1515	1521
25°	1525	1468	1478
30°	1483	1424	1424
35°	1442	1373	1367
40°	1392	1321	1312
45°	1343	1268	1256
50°	1288	1213	1191
55°	1231	1150	1130
60°	1167	1076	1062
65°	1095	998	981
70°	1005	902	892
75°	882	788	807
80°	731	643	652
85°	497	405	405

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 1343 cd/sqm

TEST NUMBER: P904260

CATALOG NUMBER: DFN2DIP-TR2F0-020D020US830-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	69.0	2.0
10°-20°	194.2	5.5
20°-30°	285.5	8.1
30°-40°	331.5	9.4
40°-50°	331.1	9.4
50°-60°	288.7	8.2
60°-70°	213.4	6.0
70°-80°	120.8	3.4
80°-90°	33.6	0.9
90°-100°	36.9	1.0
100°-110°	117.2	3.3
110°-120°	200.6	5.7
120°-130°	263.8	7.5
130°-140°	296.1	8.4
140°-150°	290.4	8.2
150°-160°	243.6	6.9
160°-170°	161.5	4.6
170°-180°	56.5	1.6
0°-30°	548.7	15.5
0°-40°	880.3	24.9
0°-60°	1500.2	42.4
0°-90°	1867.9	52.8
90°-120°	354.7	10.0
90°-150°	1205.0	34.1
90°-180°	1667.0	47.2
0°-180°	3534.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	734	734	734	734	734	
5°	734	731	723	729	727	70
15°	698	694	685	688	684	197
25°	632	626	614	616	614	291
35°	545	538	527	523	519	340
45°	444	439	428	420	418	342
55°	336	332	323	315	311	300
65°	226	222	215	209	205	224
75°	118	117	114	109	111	126
85°	29	28	28	25	25	32
90°	1	6	18	16	17	3
95°	26	31	32	32	31	29
105°	108	110	111	112	112	114
115°	201	204	203	203	201	199
125°	293	297	296	294	294	262
135°	379	384	385	385	383	293
145°	460	463	466	467	465	287
155°	526	527	529	531	530	242
165°	572	571	571	575	572	161
175°	595	594	593	596	593	57
180°	596	596	596	596	596	

TEST NUMBER: P904260

CATALOG NUMBER: DFN2DIP-TR2F0-020D020US830-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	733.5	733.5	733.5	733.5	733.5
2.5°	737.7	734.2	726.4	733.5	732.2
5°	733.5	730.8	722.9	728.6	727.2
7.5°	728.6	724.3	716.6	722.3	720.9
10°	720.9	716.0	707.5	713.0	711.0
12.5°	710.2	706.1	697.6	701.1	699.6
15°	698.2	694.1	684.9	687.7	684.2
17.5°	683.4	679.3	670.1	673.5	670.1
20°	667.2	663.0	653.1	655.3	652.4
22.5°	651.0	644.7	635.5	635.5	634.0
25°	632.0	626.3	614.3	615.7	614.3
27.5°	610.8	605.9	596.7	594.6	591.1
30°	589.7	584.0	573.4	571.4	568.4
32.5°	567.0	562.9	551.6	547.3	544.5
35°	545.3	538.2	526.9	522.6	519.1
37.5°	520.6	514.2	502.8	497.9	494.4
40°	495.1	489.5	478.2	471.9	469.0
42.5°	470.4	464.8	453.6	446.5	442.2
45°	443.7	438.8	428.1	420.4	417.5
47.5°	417.5	412.6	401.3	393.5	389.4
50°	390.0	386.5	376.6	366.7	363.3
52.5°	363.3	358.3	349.1	341.4	336.5
55°	335.7	331.5	323.0	314.6	311.0
57.5°	308.2	304.7	295.5	287.1	284.2
60°	280.7	278.0	268.1	260.2	258.2
62.5°	253.9	248.9	242.0	234.9	232.1
65°	226.4	222.2	215.2	208.8	205.3
67.5°	198.2	194.6	188.3	183.4	180.6
70°	172.1	169.3	162.9	158.0	155.2
72.5°	145.3	142.5	138.9	134.0	132.0
75°	118.5	117.2	113.5	109.3	110.7
77.5°	94.5	91.7	90.2	88.1	86.1
80°	70.6	69.8	68.4	66.3	64.8
82.5°	48.0	48.0	47.3	44.5	44.5
85°	28.8	28.2	27.5	25.4	24.7
87.5°	12.7	11.3	9.9	7.8	7.1
90°	0.6	6.5	17.6	16.5	17.1
92.5°	11.1	15.1	15.6	16.2	16.2
95°	26.2	31.3	32.1	32.1	31.3
97.5°	43.6	48.4	50.3	50.3	50.3
100°	63.8	68.0	69.4	69.4	68.8
102.5°	85.0	88.0	90.0	90.6	90.0
105°	108.2	109.6	110.7	111.6	111.6
107.5°	131.2	133.4	133.4	133.7	131.2
110°	153.5	156.4	156.4	156.4	155.0

TEST NUMBER: P904260

CATALOG NUMBER: DFN2DIP-TR2F0-020D020US830-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	177.6	180.6	180.1	178.6	177.6
115°	201.3	204.2	203.3	202.7	201.3
117.5°	224.9	228.8	226.3	224.9	223.4
120°	248.5	252.5	248.5	248.5	246.9
122.5°	270.1	275.1	272.7	271.3	270.1
125°	292.8	297.3	295.9	294.3	293.7
127.5°	314.9	320.5	318.5	316.3	314.9
130°	335.5	342.0	341.1	340.1	338.1
132.5°	358.7	363.8	364.1	361.7	360.1
135°	378.7	384.3	385.3	384.8	383.3
137.5°	401.0	405.5	406.4	406.0	403.9
140°	420.6	425.1	427.6	427.6	425.7
142.5°	440.7	445.2	446.7	447.1	445.2
145°	459.8	463.4	466.3	466.7	464.8
147.5°	476.8	481.4	483.5	484.4	482.4
150°	494.5	497.5	499.5	501.1	499.5
152.5°	510.1	513.1	515.7	517.6	515.7
155°	525.8	527.2	528.8	531.3	529.7
157.5°	539.2	540.3	541.2	544.8	542.2
160°	551.3	552.3	552.9	555.9	553.7
162.5°	562.4	562.4	562.9	566.4	563.8
165°	571.9	571.4	571.4	575.0	572.5
167.5°	580.5	578.9	578.9	582.5	580.0
170°	587.0	585.6	585.0	588.6	585.6
172.5°	591.5	590.0	589.6	593.1	590.0
175°	595.1	593.7	592.6	596.2	593.1
177.5°	597.1	595.7	594.6	597.6	594.6
180°	596.2	596.2	596.2	596.2	596.2

TEST NUMBER: P904260

CATALOG NUMBER: DFN2DIP-TR2F0-020D020US830-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.11	10.00	10.04	10.95	12.18	8.69	9.58	9.62	10.53	11.76
	3H	10.75	11.55	11.69	12.51	13.76	10.29	11.09	11.23	12.05	13.30
	4H	11.32	12.08	12.28	13.04	14.30	10.86	11.62	11.82	12.58	13.84
	6H	11.71	12.40	12.68	13.37	14.65	11.25	11.94	12.22	12.91	14.19
	8H	11.80	12.46	12.78	13.45	14.72	11.34	12.01	12.32	12.99	14.26
	12H	11.84	12.47	12.83	13.45	14.75	11.38	12.01	12.36	12.99	14.29
4H	2H	9.57	10.32	10.53	11.28	12.55	9.23	9.98	10.19	10.95	12.21
	3H	11.41	12.04	12.38	13.03	14.31	11.03	11.65	12.00	12.65	13.92
	4H	12.11	12.68	13.09	13.67	14.97	11.71	12.29	12.69	13.27	14.57
	6H	12.60	13.10	13.59	14.11	15.40	12.20	12.70	13.20	13.71	15.01
	8H	12.74	13.20	13.74	14.21	15.52	12.34	12.80	13.34	13.81	15.12
	12H	12.80	13.22	13.82	14.24	15.56	12.40	12.81	13.41	13.83	15.15
8H	4H	12.29	12.76	13.29	13.76	15.07	11.94	12.40	12.94	13.41	14.72
	6H	12.90	13.28	13.92	14.33	15.64	12.55	12.93	13.57	13.97	15.29
	8H	13.10	13.44	14.13	14.47	15.80	12.75	13.08	13.78	14.12	15.45
	12H	13.22	13.52	14.25	14.54	15.92	12.85	13.15	13.88	14.18	15.55
12H	4H	12.28	12.70	13.29	13.72	15.03	11.93	12.35	12.95	13.37	14.69
	6H	12.92	13.26	13.95	14.29	15.62	12.58	12.92	13.61	13.95	15.28
	8H	13.15	13.45	14.18	14.47	15.85	12.80	13.10	13.84	14.13	15.50