

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P904262

Luminaire Tested: DFN2DIP-TR2F0-020D020US830-RLFL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P904262
REPORT IS A COMBINATION OF REPORTS P900222 AND P897145
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR2F0-020D020US830-RLLFLL
Description: 2 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3270.6 lumens
Efficiency: N/A
Efficacy: 107.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.04' x L: 2.36' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 30.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P904262

CATALOG NUMBER: DFN2DIP-TR2F0-020D020US830-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P904262

CATALOG NUMBER: DFN2DIP-TR2F0-020D020US830-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83	68	68	68	55	55	55
1	98	94	90	87	90	87	84	81	73	71	69	61	59	58	50	49	48
2	90	83	77	72	82	76	71	67	65	61	58	54	51	49	44	42	41
3	82	73	66	60	75	68	61	57	58	53	49	48	45	42	40	37	35
4	75	65	57	51	69	60	54	48	51	46	42	43	40	36	36	33	31
5	69	58	50	44	64	54	47	42	46	41	37	39	35	32	32	29	27
6	64	52	44	39	59	49	42	37	42	36	32	35	31	28	30	26	24
7	59	47	40	34	55	44	37	32	38	33	29	32	28	25	27	24	22
8	55	43	36	30	51	40	33	29	35	29	26	30	26	23	25	22	20
9	51	39	32	27	47	37	30	26	32	27	23	27	23	20	23	20	18
10	48	36	29	24	44	34	28	23	30	24	21	25	21	19	22	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1738	1738	1738
5°	1738	1706	1718
10°	1718	1669	1659
15°	1692	1610	1570
20°	1658	1531	1462
25°	1623	1442	1357
30°	1578	1351	1226
35°	1533	1255	1110
40°	1487	1155	978
45°	1434	1045	859
50°	1379	934	742
55°	1321	816	630
60°	1254	693	516
65°	1177	569	461
70°	1083	453	413
75°	965	392	370
80°	795	318	312
85°	522	197	220

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1434 cd/sqm

TEST NUMBER: P904262

CATALOG NUMBER: DFN2DIP-TR2F0-020D020US830-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	73.0	2.2
10°-20°	200.4	6.1
20°-30°	281.4	8.6
30°-40°	306.8	9.4
40°-50°	282.0	8.6
50°-60°	221.4	6.8
60°-70°	144.1	4.4
70°-80°	74.2	2.3
80°-90°	20.6	0.6
90°-100°	36.9	1.1
100°-110°	117.2	3.6
110°-120°	200.6	6.1
120°-130°	263.8	8.1
130°-140°	296.1	9.1
140°-150°	290.4	8.9
150°-160°	243.6	7.4
160°-170°	161.5	4.9
170°-180°	56.5	1.7
0°-30°	554.9	17.0
0°-40°	861.7	26.3
0°-60°	1365.1	41.7
0°-90°	1604.0	49.0
90°-120°	354.7	10.8
90°-150°	1205.0	36.8
90°-180°	1667.0	51.0
0°-180°	3270.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	779	779	779	779	779	
5°	779	776	766	773	771	74
15°	741	733	709	696	689	209
25°	673	650	604	575	564	309
35°	580	544	482	437	422	363
45°	474	426	353	302	286	366
55°	360	305	229	187	173	322
65°	243	186	123	99	97	241
75°	130	80	56	52	51	137
85°	30	16	13	13	13	35
90°	1	6	18	16	17	3
95°	26	31	32	32	31	29
105°	108	110	111	112	112	114
115°	201	204	203	203	201	199
125°	293	297	296	294	294	262
135°	379	384	385	385	383	293
145°	460	463	466	467	465	287
155°	526	527	529	531	530	242
165°	572	571	571	575	572	161
175°	595	594	593	596	593	57
180°	596	596	596	596	596	

TEST NUMBER: P904262

CATALOG NUMBER: DFN2DIP-TR2F0-020D020US830-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	779.1	779.1	779.1	779.1	779.1
2.5°	782.6	779.1	771.3	778.4	777.0
5°	779.1	775.6	766.4	772.8	770.6
7.5°	772.8	768.5	758.7	761.5	757.9
10°	764.3	759.3	745.3	743.1	739.0
12.5°	753.8	747.3	728.3	724.2	716.3
15°	741.0	733.2	709.3	695.9	688.9
17.5°	726.2	714.9	685.3	669.8	658.6
20°	709.3	695.1	660.0	642.3	626.8
22.5°	691.0	674.8	633.9	609.9	599.4
25°	672.7	650.1	603.5	574.7	564.0
27.5°	650.8	626.8	575.3	542.2	525.9
30°	627.5	600.7	544.3	508.4	489.3
32.5°	604.9	572.5	514.7	472.4	454.8
35°	579.6	543.7	481.6	437.2	421.6
37.5°	554.9	516.0	450.5	401.9	384.3
40°	528.8	486.5	418.1	368.1	349.7
42.5°	502.0	456.9	385.7	333.5	315.9
45°	473.8	426.5	352.6	302.5	285.5
47.5°	447.0	397.0	320.8	270.7	255.2
50°	417.5	367.4	289.8	241.1	226.4
52.5°	388.4	335.5	260.1	213.7	200.3
55°	360.2	305.3	229.1	186.9	173.4
57.5°	331.4	274.9	201.7	162.2	150.9
60°	301.8	245.3	172.8	136.9	125.5
62.5°	272.9	216.5	148.1	114.2	108.6
65°	243.3	186.2	122.7	98.8	96.6
67.5°	215.1	157.9	98.8	86.7	84.6
70°	185.4	130.4	81.7	74.7	71.9
72.5°	157.2	105.0	68.3	62.8	61.4
75°	129.7	80.3	56.4	51.5	50.8
77.5°	102.3	57.1	44.4	41.6	40.2
80°	76.8	40.9	33.8	31.0	31.0
82.5°	53.5	27.5	23.3	21.9	21.9
85°	30.3	15.5	13.4	13.4	13.4
87.5°	11.3	5.7	5.7	4.9	4.9
90°	0.6	6.5	17.6	16.5	17.1
92.5°	11.1	15.1	15.6	16.2	16.2
95°	26.2	31.3	32.1	32.1	31.3
97.5°	43.6	48.4	50.3	50.3	50.3
100°	63.8	68.0	69.4	69.4	68.8
102.5°	85.0	88.0	90.0	90.6	90.0
105°	108.2	109.6	110.7	111.6	111.6
107.5°	131.2	133.4	133.4	133.7	131.2
110°	153.5	156.4	156.4	156.4	155.0

TEST NUMBER: P904262

CATALOG NUMBER: DFN2DIP-TR2F0-020D020US830-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	177.6	180.6	180.1	178.6	177.6
115°	201.3	204.2	203.3	202.7	201.3
117.5°	224.9	228.8	226.3	224.9	223.4
120°	248.5	252.5	248.5	248.5	246.9
122.5°	270.1	275.1	272.7	271.3	270.1
125°	292.8	297.3	295.9	294.3	293.7
127.5°	314.9	320.5	318.5	316.3	314.9
130°	335.5	342.0	341.1	340.1	338.1
132.5°	358.7	363.8	364.1	361.7	360.1
135°	378.7	384.3	385.3	384.8	383.3
137.5°	401.0	405.5	406.4	406.0	403.9
140°	420.6	425.1	427.6	427.6	425.7
142.5°	440.7	445.2	446.7	447.1	445.2
145°	459.8	463.4	466.3	466.7	464.8
147.5°	476.8	481.4	483.5	484.4	482.4
150°	494.5	497.5	499.5	501.1	499.5
152.5°	510.1	513.1	515.7	517.6	515.7
155°	525.8	527.2	528.8	531.3	529.7
157.5°	539.2	540.3	541.2	544.8	542.2
160°	551.3	552.3	552.9	555.9	553.7
162.5°	562.4	562.4	562.9	566.4	563.8
165°	571.9	571.4	571.4	575.0	572.5
167.5°	580.5	578.9	578.9	582.5	580.0
170°	587.0	585.6	585.0	588.6	585.6
172.5°	591.5	590.0	589.6	593.1	590.0
175°	595.1	593.7	592.6	596.2	593.1
177.5°	597.1	595.7	594.6	597.6	594.6
180°	596.2	596.2	596.2	596.2	596.2

TEST NUMBER: P904262

CATALOG NUMBER: DFN2DIP-TR2F0-020D020US830-RLFL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.84	9.67	9.82	10.65	11.94	4.83	5.65	5.80	6.63	7.92
	3H	10.50	11.23	11.48	12.22	13.53	6.00	6.74	6.98	7.73	9.04
	4H	11.09	11.79	12.09	12.78	14.10	6.44	7.14	7.44	8.13	9.45
	6H	11.49	12.13	12.50	13.13	14.46	6.75	7.39	7.75	8.39	9.72
	8H	11.61	12.22	12.62	13.23	14.56	6.83	7.44	7.84	8.45	9.78
	12H	11.66	12.24	12.68	13.25	14.60	6.87	7.45	7.88	8.45	9.81
4H	2H	8.86	9.55	9.86	10.55	11.87	5.41	6.11	6.41	7.10	8.42
	3H	10.66	11.24	11.67	12.26	13.59	6.74	7.32	7.75	8.34	9.67
	4H	11.33	11.86	12.35	12.88	14.23	7.28	7.80	8.29	8.82	10.17
	6H	11.83	12.28	12.86	13.32	14.67	7.68	8.13	8.71	9.17	10.52
	8H	11.99	12.41	13.02	13.44	14.81	7.80	8.22	8.83	9.25	10.62
	12H	12.07	12.45	13.12	13.50	14.87	7.85	8.24	8.90	9.28	10.65
8H	4H	11.30	11.72	12.33	12.75	14.12	7.54	7.96	8.57	9.00	10.36
	6H	11.84	12.19	12.89	13.26	14.62	8.04	8.39	9.09	9.46	10.82
	8H	12.04	12.35	13.10	13.40	14.79	8.22	8.52	9.28	9.58	10.96
	12H	12.16	12.43	13.22	13.48	14.91	8.32	8.59	9.39	9.65	11.07
12H	4H	11.25	11.63	12.30	12.68	14.05	7.54	7.92	8.59	8.97	10.34
	6H	11.81	12.12	12.87	13.18	14.56	8.08	8.39	9.14	9.45	10.83
	8H	12.01	12.29	13.08	13.34	14.76	8.28	8.55	9.34	9.60	11.03