

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P904269

Luminaire Tested: DFN2DIP-TR2F0-020D040US830-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P904269
REPORT IS A COMBINATION OF REPORTS P901761 AND P897145
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR2F0-020D040US830-FLLONL
Description: 2 foot, Triangle Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5202.8 lumens
Efficiency: N/A
Efficacy: 116.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.04' x L: 2.36' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 44.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P904269

CATALOG NUMBER: DFN2DIP-TR2F0-020D040US830-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P904269

CATALOG NUMBER: DFN2DIP-TR2F0-020D040US830-FLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	43	43	43
1	95	90	87	83	85	82	79	76	66	64	62	52	50	49	38	37	36
2	86	79	73	68	78	72	66	62	58	54	51	45	43	41	34	32	31
3	79	69	62	56	71	63	57	52	51	47	43	40	37	34	30	28	26
4	72	61	54	48	65	56	49	44	45	40	37	36	32	29	27	24	22
5	66	54	47	41	59	50	43	38	40	35	31	32	28	25	24	22	20
6	61	49	41	35	55	45	38	33	36	31	27	29	25	22	22	19	17
7	56	44	36	31	50	40	33	28	33	28	24	26	22	20	20	17	15
8	52	40	32	27	47	36	30	25	30	25	21	24	20	17	18	16	14
9	48	36	29	24	44	33	27	22	27	22	19	22	18	16	17	14	12
10	45	33	26	21	41	30	24	20	25	20	17	20	17	14	16	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1636	1636	1636
5°	1636	1609	1621
10°	1621	1584	1597
15°	1594	1555	1559
20°	1560	1515	1521
25°	1525	1468	1478
30°	1483	1424	1424
35°	1442	1373	1367
40°	1392	1321	1312
45°	1343	1268	1256
50°	1288	1213	1191
55°	1231	1150	1130
60°	1167	1076	1062
65°	1095	998	981
70°	1005	902	892
75°	882	788	807
80°	731	643	652
85°	497	405	405

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 1555 cd/sqm

TEST NUMBER: P904269

CATALOG NUMBER: DFN2DIP-TR2F0-020D040US830-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	69.0	1.3
10°-20°	194.2	3.7
20°-30°	285.5	5.5
30°-40°	331.5	6.4
40°-50°	331.1	6.4
50°-60°	288.7	5.5
60°-70°	213.4	4.1
70°-80°	120.8	2.3
80°-90°	35.3	0.7
90°-100°	73.8	1.4
100°-110°	234.4	4.5
110°-120°	401.2	7.7
120°-130°	527.6	10.1
130°-140°	592.2	11.4
140°-150°	580.8	11.2
150°-160°	487.2	9.4
160°-170°	323.1	6.2
170°-180°	112.9	2.2
0°-30°	548.7	10.5
0°-40°	880.3	16.9
0°-60°	1500.2	28.8
0°-90°	1869.6	35.9
90°-120°	709.4	13.6
90°-150°	2410.0	46.3
90°-180°	3333.0	64.1
0°-180°	5202.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	734	734	734	734	734	
5°	734	731	723	729	727	70
15°	698	694	685	688	684	197
25°	632	626	614	616	614	291
35°	545	538	527	523	519	340
45°	444	439	428	420	418	342
55°	336	332	323	315	311	300
65°	226	222	215	209	205	224
75°	118	117	114	109	111	126
85°	29	28	28	25	25	32
90°	1	13	35	33	34	5
95°	52	63	64	64	63	58
105°	216	219	221	223	223	228
115°	403	408	406	406	403	398
125°	586	595	592	588	587	523
135°	757	768	771	770	767	585
145°	920	927	932	934	930	575
155°	1051	1054	1058	1063	1059	484
165°	1144	1143	1143	1150	1145	323
175°	1190	1187	1185	1192	1186	113
180°	1192	1192	1192	1192	1192	

TEST NUMBER: P904269

CATALOG NUMBER: DFN2DIP-TR2F0-020D040US830-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	733.5	733.5	733.5	733.5	733.5
2.5°	737.7	734.2	726.4	733.5	732.2
5°	733.5	730.8	722.9	728.6	727.2
7.5°	728.6	724.3	716.6	722.3	720.9
10°	720.9	716.0	707.5	713.0	711.0
12.5°	710.2	706.1	697.6	701.1	699.6
15°	698.2	694.1	684.9	687.7	684.2
17.5°	683.4	679.3	670.1	673.5	670.1
20°	667.2	663.0	653.1	655.3	652.4
22.5°	651.0	644.7	635.5	635.5	634.0
25°	632.0	626.3	614.3	615.7	614.3
27.5°	610.8	605.9	596.7	594.6	591.1
30°	589.7	584.0	573.4	571.4	568.4
32.5°	567.0	562.9	551.6	547.3	544.5
35°	545.3	538.2	526.9	522.6	519.1
37.5°	520.6	514.2	502.8	497.9	494.4
40°	495.1	489.5	478.2	471.9	469.0
42.5°	470.4	464.8	453.6	446.5	442.2
45°	443.7	438.8	428.1	420.4	417.5
47.5°	417.5	412.6	401.3	393.5	389.4
50°	390.0	386.5	376.6	366.7	363.3
52.5°	363.3	358.3	349.1	341.4	336.5
55°	335.7	331.5	323.0	314.6	311.0
57.5°	308.2	304.7	295.5	287.1	284.2
60°	280.7	278.0	268.1	260.2	258.2
62.5°	253.9	248.9	242.0	234.9	232.1
65°	226.4	222.2	215.2	208.8	205.3
67.5°	198.2	194.6	188.3	183.4	180.6
70°	172.1	169.3	162.9	158.0	155.2
72.5°	145.3	142.5	138.9	134.0	132.0
75°	118.5	117.2	113.5	109.3	110.7
77.5°	94.5	91.7	90.2	88.1	86.1
80°	70.6	69.8	68.4	66.3	64.8
82.5°	48.0	48.0	47.3	44.5	44.5
85°	28.8	28.2	27.5	25.4	24.7
87.5°	12.7	11.3	9.9	7.8	7.1
90°	1.0	12.9	35.3	33.1	34.1
92.5°	22.2	30.2	31.3	32.3	32.3
95°	52.5	62.6	64.4	64.4	62.6
97.5°	87.4	96.7	100.7	100.7	100.7
100°	127.6	135.9	138.7	138.7	137.7
102.5°	170.0	176.2	180.1	181.2	180.1
105°	216.4	219.2	221.4	223.2	223.2
107.5°	262.4	266.7	266.7	267.4	262.4
110°	307.0	312.7	312.7	312.7	309.9

TEST NUMBER: P904269

CATALOG NUMBER: DFN2DIP-TR2F0-020D040US830-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	355.1	361.3	360.1	357.3	355.1
115°	402.6	408.4	406.5	405.5	402.6
117.5°	449.7	457.6	452.6	449.7	446.9
120°	497.2	505.0	497.2	497.2	493.9
122.5°	540.3	550.4	545.4	542.4	540.3
125°	585.6	594.6	591.7	588.4	587.4
127.5°	629.8	640.9	637.0	632.6	629.8
130°	671.1	684.1	682.3	680.1	676.2
132.5°	717.5	727.5	728.3	723.2	720.4
135°	757.4	768.5	770.7	769.6	766.8
137.5°	802.0	811.0	812.8	812.0	807.8
140°	841.1	850.2	855.2	855.2	851.2
142.5°	881.5	890.4	893.2	894.4	890.4
145°	919.5	926.7	932.5	933.6	929.6
147.5°	953.7	962.6	967.0	968.7	964.8
150°	988.9	995.0	999.0	1002.2	999.0
152.5°	1020.2	1026.2	1031.3	1035.3	1031.3
155°	1051.4	1054.3	1057.5	1062.6	1059.3
157.5°	1078.5	1080.5	1082.3	1089.6	1084.5
160°	1102.5	1104.7	1105.7	1111.8	1107.5
162.5°	1124.7	1124.7	1125.9	1132.7	1127.7
165°	1143.9	1142.7	1142.7	1149.9	1144.9
167.5°	1161.1	1157.8	1157.8	1165.1	1160.0
170°	1174.0	1171.1	1170.1	1177.2	1171.1
172.5°	1183.0	1180.2	1179.0	1186.3	1180.2
175°	1190.2	1187.3	1185.2	1192.3	1186.3
177.5°	1194.2	1191.3	1189.1	1195.2	1189.1
180°	1192.3	1192.3	1192.3	1192.3	1192.3

TEST NUMBER: P904269

CATALOG NUMBER: DFN2DIP-TR2F0-020D040US830-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.39	8.14	8.46	9.21	10.67	6.97	7.71	8.04	8.79	10.24
	3H	9.02	9.69	10.10	10.77	12.24	8.56	9.23	9.64	10.31	11.78
	4H	9.58	10.22	10.67	11.30	12.78	9.12	9.76	10.21	10.84	12.32
	6H	9.96	10.55	11.06	11.63	13.12	9.50	10.08	10.60	11.17	12.66
	8H	10.05	10.61	11.15	11.71	13.20	9.59	10.15	10.70	11.25	12.74
	12H	10.09	10.62	11.20	11.71	13.22	9.63	10.15	10.73	11.25	12.76
4H	2H	7.83	8.46	8.92	9.54	11.03	7.49	8.13	8.59	9.21	10.69
	3H	9.66	10.19	10.76	11.29	12.79	9.27	9.80	10.38	10.91	12.41
	4H	10.35	10.83	11.46	11.93	13.45	9.95	10.44	11.06	11.54	13.05
	6H	10.83	11.25	11.95	12.37	13.88	10.44	10.85	11.55	11.98	13.49
	8H	10.97	11.36	12.08	12.47	14.00	10.57	10.96	11.69	12.07	13.60
	12H	11.03	11.38	12.16	12.51	14.04	10.62	10.97	11.75	12.10	13.63
8H	4H	10.52	10.91	11.64	12.03	13.55	10.17	10.56	11.29	11.68	13.20
	6H	11.12	11.45	12.26	12.60	14.12	10.77	11.09	11.91	12.25	13.77
	8H	11.33	11.61	12.47	12.74	14.29	10.97	11.25	12.11	12.39	13.93
	12H	11.44	11.69	12.58	12.82	14.40	11.07	11.32	12.22	12.45	14.03
12H	4H	10.50	10.86	11.63	11.98	13.51	10.16	10.51	11.29	11.64	13.17
	6H	11.15	11.43	12.29	12.57	14.11	10.80	11.09	11.95	12.22	13.77
	8H	11.37	11.61	12.51	12.75	14.32	11.02	11.27	12.17	12.40	13.98