

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P904272

Luminaire Tested: DFN2DIP-TR2F0-020D050US830-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P904272
REPORT IS A COMBINATION OF REPORTS P900251 AND P897145
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR2F0-020D050US830-FLLFLL
Description: 2 foot, Triangle Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6037.0 lumens
Efficiency: N/A
Efficacy: 112.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.04' x L: 2.36' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 53.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P904272

CATALOG NUMBER: DFN2DIP-TR2F0-020D050US830-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P904272

CATALOG NUMBER: DFN2DIP-TR2F0-020D050US830-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	39	39	39
1	94	89	86	82	84	80	77	74	64	61	60	48	47	46	34	33	33
2	85	78	72	67	76	70	65	61	56	52	49	42	40	38	30	29	27
3	78	68	61	56	69	62	56	51	49	45	41	37	35	32	27	25	23
4	71	60	53	47	63	55	48	43	44	39	35	33	30	28	24	22	20
5	65	54	46	40	58	49	42	37	39	34	30	30	26	24	21	19	17
6	60	48	40	35	54	44	37	32	35	30	26	27	23	21	19	17	15
7	55	43	36	30	49	39	33	28	32	27	23	24	21	18	18	15	14
8	51	39	32	27	46	36	29	24	29	24	20	22	19	16	16	14	12
9	47	36	28	24	43	32	26	22	26	21	18	20	17	15	15	13	11
10	44	33	26	21	40	30	24	19	24	19	16	19	15	13	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1636	1636	1636
5°	1636	1609	1621
10°	1621	1584	1597
15°	1594	1555	1559
20°	1560	1515	1521
25°	1525	1468	1478
30°	1483	1424	1424
35°	1442	1373	1367
40°	1392	1321	1312
45°	1343	1268	1256
50°	1288	1213	1191
55°	1231	1150	1130
60°	1167	1076	1062
65°	1095	998	981
70°	1005	902	892
75°	882	788	807
80°	731	643	652
85°	497	405	405

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 1947 cd/sqm

TEST NUMBER: P904272

CATALOG NUMBER: DFN2DIP-TR2F0-020D050US830-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	69.0	1.1
10°-20°	194.2	3.2
20°-30°	285.5	4.7
30°-40°	331.5	5.5
40°-50°	331.1	5.5
50°-60°	288.7	4.8
60°-70°	213.4	3.5
70°-80°	120.8	2.0
80°-90°	36.1	0.6
90°-100°	92.2	1.5
100°-110°	293.0	4.9
110°-120°	501.5	8.3
120°-130°	659.5	10.9
130°-140°	740.3	12.3
140°-150°	725.9	12.0
150°-160°	609.0	10.1
160°-170°	403.9	6.7
170°-180°	141.2	2.3
0°-30°	548.7	9.1
0°-40°	880.3	14.6
0°-60°	1500.2	24.8
0°-90°	1870.5	31.0
90°-120°	886.7	14.7
90°-150°	3012.5	49.9
90°-180°	4167.0	69.0
0°-180°	6037.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	734	734	734	734	734	
5°	734	731	723	729	727	70
15°	698	694	685	688	684	197
25°	632	626	614	616	614	291
35°	545	538	527	523	519	340
45°	444	439	428	420	418	342
55°	336	332	323	315	311	300
65°	226	222	215	209	205	224
75°	118	117	114	109	111	126
85°	29	28	28	25	25	32
90°	1	16	44	41	43	6
95°	66	78	80	80	78	73
105°	270	274	277	279	279	285
115°	503	510	508	507	503	498
125°	732	743	740	736	734	654
135°	947	961	963	962	958	732
145°	1149	1158	1166	1167	1162	718
155°	1314	1318	1322	1328	1324	605
165°	1430	1428	1428	1438	1431	403
175°	1488	1484	1482	1490	1483	141
180°	1490	1490	1490	1490	1490	

TEST NUMBER: P904272

CATALOG NUMBER: DFN2DIP-TR2F0-020D050US830-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	733.5	733.5	733.5	733.5	733.5
2.5°	737.7	734.2	726.4	733.5	732.2
5°	733.5	730.8	722.9	728.6	727.2
7.5°	728.6	724.3	716.6	722.3	720.9
10°	720.9	716.0	707.5	713.0	711.0
12.5°	710.2	706.1	697.6	701.1	699.6
15°	698.2	694.1	684.9	687.7	684.2
17.5°	683.4	679.3	670.1	673.5	670.1
20°	667.2	663.0	653.1	655.3	652.4
22.5°	651.0	644.7	635.5	635.5	634.0
25°	632.0	626.3	614.3	615.7	614.3
27.5°	610.8	605.9	596.7	594.6	591.1
30°	589.7	584.0	573.4	571.4	568.4
32.5°	567.0	562.9	551.6	547.3	544.5
35°	545.3	538.2	526.9	522.6	519.1
37.5°	520.6	514.2	502.8	497.9	494.4
40°	495.1	489.5	478.2	471.9	469.0
42.5°	470.4	464.8	453.6	446.5	442.2
45°	443.7	438.8	428.1	420.4	417.5
47.5°	417.5	412.6	401.3	393.5	389.4
50°	390.0	386.5	376.6	366.7	363.3
52.5°	363.3	358.3	349.1	341.4	336.5
55°	335.7	331.5	323.0	314.6	311.0
57.5°	308.2	304.7	295.5	287.1	284.2
60°	280.7	278.0	268.1	260.2	258.2
62.5°	253.9	248.9	242.0	234.9	232.1
65°	226.4	222.2	215.2	208.8	205.3
67.5°	198.2	194.6	188.3	183.4	180.6
70°	172.1	169.3	162.9	158.0	155.2
72.5°	145.3	142.5	138.9	134.0	132.0
75°	118.5	117.2	113.5	109.3	110.7
77.5°	94.5	91.7	90.2	88.1	86.1
80°	70.6	69.8	68.4	66.3	64.8
82.5°	48.0	48.0	47.3	44.5	44.5
85°	28.8	28.2	27.5	25.4	24.7
87.5°	12.7	11.3	9.9	7.8	7.1
90°	1.3	16.2	44.0	41.4	42.7
92.5°	27.9	37.7	39.1	40.4	40.4
95°	65.6	78.2	80.4	80.4	78.2
97.5°	109.1	120.8	125.8	125.8	125.8
100°	159.5	169.8	173.4	173.4	172.1
102.5°	212.5	220.2	225.1	226.5	225.1
105°	270.5	274.1	276.8	279.0	279.0
107.5°	328.0	333.4	333.4	334.3	328.0
110°	383.7	391.0	391.0	391.0	387.3

TEST NUMBER: P904272

CATALOG NUMBER: DFN2DIP-TR2F0-020D050US830-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	443.9	451.6	450.3	446.7	443.9
115°	503.2	510.5	508.2	506.9	503.2
117.5°	562.1	572.0	565.7	562.1	558.6
120°	621.4	631.3	621.4	621.4	617.4
122.5°	675.3	688.0	681.6	678.1	675.3
125°	732.0	743.2	739.6	735.6	734.2
127.5°	787.2	801.2	796.3	790.8	787.2
130°	839.0	855.1	852.8	850.2	845.2
132.5°	896.9	909.5	910.4	904.1	900.5
135°	946.8	960.6	963.4	962.1	958.5
137.5°	1002.5	1013.7	1016.0	1015.0	1009.7
140°	1051.4	1062.7	1068.9	1068.9	1064.0
142.5°	1101.7	1113.0	1116.6	1117.9	1113.0
145°	1149.4	1158.4	1165.5	1167.0	1162.0
147.5°	1192.1	1203.3	1208.7	1211.0	1206.0
150°	1236.1	1243.8	1248.7	1252.7	1248.7
152.5°	1275.3	1282.9	1289.1	1294.1	1289.1
155°	1314.3	1317.9	1321.9	1328.2	1324.2
157.5°	1348.0	1350.7	1352.9	1362.0	1355.7
160°	1378.1	1380.8	1382.1	1389.8	1384.4
162.5°	1406.0	1406.0	1407.3	1415.9	1409.6
165°	1429.8	1428.4	1428.4	1437.5	1431.2
167.5°	1451.3	1447.3	1447.3	1456.3	1450.0
170°	1467.5	1464.0	1462.6	1471.6	1464.0
172.5°	1478.8	1475.2	1473.9	1482.8	1475.2
175°	1487.8	1484.1	1481.5	1490.4	1482.8
177.5°	1492.7	1489.1	1486.4	1494.0	1486.4
180°	1490.4	1490.4	1490.4	1490.4	1490.4

TEST NUMBER: P904272

CATALOG NUMBER: DFN2DIP-TR2F0-020D050US830-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.77	7.48	7.87	8.58	10.10	6.35	7.06	7.45	8.16	9.68
	3H	8.39	9.03	9.51	10.14	11.68	7.93	8.57	9.05	9.68	11.22
	4H	8.96	9.57	10.08	10.68	12.22	8.50	9.11	9.62	10.22	11.76
	6H	9.33	9.89	10.47	11.00	12.56	8.87	9.43	10.01	10.54	12.10
	8H	9.42	9.96	10.56	11.08	12.63	8.97	9.50	10.10	10.63	12.17
	12H	9.46	9.96	10.60	11.09	12.66	9.00	9.50	10.14	10.62	12.19
4H	2H	7.20	7.81	8.33	8.92	10.46	6.87	7.47	8.00	8.58	10.12
	3H	9.03	9.53	10.16	10.67	12.22	8.64	9.15	9.78	10.29	11.84
	4H	9.72	10.18	10.86	11.31	12.88	9.32	9.79	10.46	10.91	12.49
	6H	10.20	10.60	11.35	11.75	13.31	9.81	10.20	10.95	11.35	12.92
	8H	10.34	10.71	11.48	11.85	13.43	9.94	10.31	11.08	11.45	13.03
	12H	10.39	10.73	11.55	11.88	13.47	9.99	10.32	11.15	11.48	13.06
8H	4H	9.89	10.26	11.04	11.40	12.99	9.54	9.91	10.69	11.05	12.63
	6H	10.49	10.80	11.66	11.98	13.56	10.14	10.44	11.30	11.63	13.20
	8H	10.69	10.96	11.87	12.12	13.72	10.34	10.60	11.51	11.77	13.36
	12H	10.80	11.04	11.98	12.20	13.83	10.43	10.67	11.61	11.83	13.46
12H	4H	9.87	10.21	11.03	11.36	12.94	9.52	9.86	10.69	11.01	12.60
	6H	10.51	10.78	11.69	11.94	13.54	10.17	10.44	11.34	11.60	13.20
	8H	10.73	10.97	11.91	12.13	13.76	10.38	10.62	11.56	11.78	13.41

END OF REPORT