

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P904278

Luminaire Tested: DFN2DIP-TR2F0-020D060US830-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P904278
REPORT IS A COMBINATION OF REPORTS P900262 AND P897145
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR2F0-020D060US830-RLLFLL
Description: 2 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6607.2 lumens
Efficiency: N/A
Efficacy: 103.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.04' x L: 2.36' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 63.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P904278

CATALOG NUMBER: DFN2DIP-TR2F0-020D060US830-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P904278

CATALOG NUMBER: DFN2DIP-TR2F0-020D060US830-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	33	33	33
1	92	88	85	81	82	79	76	73	61	59	57	44	43	42	29	28	28
2	84	77	71	67	75	69	64	60	53	50	47	39	37	35	26	25	24
3	77	68	61	56	68	61	55	50	47	43	40	35	32	30	23	22	20
4	70	60	53	47	62	54	48	43	42	38	34	31	28	26	21	19	18
5	64	54	46	40	57	48	42	37	38	33	29	28	25	22	19	17	16
6	59	48	40	35	53	43	37	32	34	29	26	25	22	20	17	15	14
7	55	43	36	30	49	39	32	28	31	26	23	23	20	17	16	14	12
8	51	39	32	27	45	35	29	24	28	23	20	21	18	16	14	12	11
9	47	36	29	24	42	32	26	22	25	21	18	19	16	14	13	11	10
10	44	33	26	21	39	29	23	19	23	19	16	18	15	13	12	10	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1738	1738	1738
5°	1738	1706	1718
10°	1718	1669	1659
15°	1692	1610	1570
20°	1658	1531	1462
25°	1623	1442	1357
30°	1578	1351	1226
35°	1533	1255	1110
40°	1487	1155	978
45°	1434	1045	859
50°	1379	934	742
55°	1321	816	630
60°	1254	693	516
65°	1177	569	461
70°	1083	453	413
75°	965	392	370
80°	795	318	312
85°	522	197	220

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 2334 cd/sqm

TEST NUMBER: P904278

CATALOG NUMBER: DFN2DIP-TR2F0-020D060US830-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	73.0	1.1
10°-20°	200.4	3.0
20°-30°	281.4	4.3
30°-40°	306.8	4.6
40°-50°	282.0	4.3
50°-60°	221.4	3.4
60°-70°	144.1	2.2
70°-80°	74.2	1.1
80°-90°	24.0	0.4
90°-100°	110.7	1.7
100°-110°	351.6	5.3
110°-120°	601.8	9.1
120°-130°	791.4	12.0
130°-140°	888.4	13.4
140°-150°	871.1	13.2
150°-160°	730.8	11.1
160°-170°	484.6	7.3
170°-180°	169.4	2.6
0°-30°	554.9	8.4
0°-40°	861.7	13.0
0°-60°	1365.1	20.7
0°-90°	1607.4	24.3
90°-120°	1064.1	16.1
90°-150°	3615.0	54.7
90°-180°	5000.0	75.7
0°-180°	6607.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	779	779	779	779	779	
5°	779	776	766	773	771	74
15°	741	733	709	696	689	209
25°	673	650	604	575	564	309
35°	580	544	482	437	422	363
45°	474	426	353	302	286	366
55°	360	305	229	187	173	322
65°	243	186	123	99	97	241
75°	130	80	56	52	51	137
85°	30	16	13	13	13	35
90°	2	19	53	50	51	7
95°	79	94	96	96	94	88
105°	325	329	332	335	335	343
115°	604	613	610	608	604	597
125°	878	892	888	883	881	785
135°	1136	1153	1156	1154	1150	878
145°	1379	1390	1399	1400	1394	862
155°	1577	1582	1586	1594	1589	726
165°	1716	1714	1714	1725	1717	484
175°	1785	1781	1778	1789	1779	170
180°	1789	1789	1789	1789	1789	

TEST NUMBER: P904278

CATALOG NUMBER: DFN2DIP-TR2F0-020D060US830-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	779.1	779.1	779.1	779.1	779.1
2.5°	782.6	779.1	771.3	778.4	777.0
5°	779.1	775.6	766.4	772.8	770.6
7.5°	772.8	768.5	758.7	761.5	757.9
10°	764.3	759.3	745.3	743.1	739.0
12.5°	753.8	747.3	728.3	724.2	716.3
15°	741.0	733.2	709.3	695.9	688.9
17.5°	726.2	714.9	685.3	669.8	658.6
20°	709.3	695.1	660.0	642.3	626.8
22.5°	691.0	674.8	633.9	609.9	599.4
25°	672.7	650.1	603.5	574.7	564.0
27.5°	650.8	626.8	575.3	542.2	525.9
30°	627.5	600.7	544.3	508.4	489.3
32.5°	604.9	572.5	514.7	472.4	454.8
35°	579.6	543.7	481.6	437.2	421.6
37.5°	554.9	516.0	450.5	401.9	384.3
40°	528.8	486.5	418.1	368.1	349.7
42.5°	502.0	456.9	385.7	333.5	315.9
45°	473.8	426.5	352.6	302.5	285.5
47.5°	447.0	397.0	320.8	270.7	255.2
50°	417.5	367.4	289.8	241.1	226.4
52.5°	388.4	335.5	260.1	213.7	200.3
55°	360.2	305.3	229.1	186.9	173.4
57.5°	331.4	274.9	201.7	162.2	150.9
60°	301.8	245.3	172.8	136.9	125.5
62.5°	272.9	216.5	148.1	114.2	108.6
65°	243.3	186.2	122.7	98.8	96.6
67.5°	215.1	157.9	98.8	86.7	84.6
70°	185.4	130.4	81.7	74.7	71.9
72.5°	157.2	105.0	68.3	62.8	61.4
75°	129.7	80.3	56.4	51.5	50.8
77.5°	102.3	57.1	44.4	41.6	40.2
80°	76.8	40.9	33.8	31.0	31.0
82.5°	53.5	27.5	23.3	21.9	21.9
85°	30.3	15.5	13.4	13.4	13.4
87.5°	11.3	5.7	5.7	4.9	4.9
90°	1.6	19.4	52.9	49.6	51.2
92.5°	33.5	45.3	46.9	48.5	48.5
95°	78.7	93.8	96.5	96.5	93.8
97.5°	131.0	145.1	151.0	151.0	151.0
100°	191.4	203.8	208.1	208.1	206.5
102.5°	255.1	264.2	270.1	271.7	270.1
105°	324.6	328.9	332.2	334.9	334.9
107.5°	393.6	400.1	400.1	401.1	393.6
110°	460.5	469.1	469.1	469.1	464.8

TEST NUMBER: P904278

CATALOG NUMBER: DFN2DIP-TR2F0-020D060US830-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	532.7	541.9	540.3	535.9	532.7
115°	603.9	612.6	609.8	608.2	603.9
117.5°	674.6	686.5	678.8	674.6	670.2
120°	745.7	757.6	745.7	745.7	740.8
122.5°	810.4	825.5	817.9	813.7	810.4
125°	878.4	891.8	887.5	882.7	881.1
127.5°	944.7	961.4	955.5	949.0	944.7
130°	1006.7	1026.1	1023.4	1020.2	1014.3
132.5°	1076.3	1091.4	1092.4	1084.9	1080.5
135°	1136.1	1152.8	1156.0	1154.4	1150.1
137.5°	1203.0	1216.4	1219.2	1218.0	1211.6
140°	1261.8	1275.3	1282.8	1282.8	1276.9
142.5°	1322.1	1335.6	1339.9	1341.5	1335.6
145°	1379.3	1390.1	1398.7	1400.3	1394.4
147.5°	1430.5	1444.0	1450.5	1453.1	1447.2
150°	1483.4	1492.5	1498.5	1503.3	1498.5
152.5°	1530.2	1539.5	1547.0	1552.9	1547.0
155°	1577.2	1581.5	1586.3	1593.9	1589.0
157.5°	1617.6	1620.9	1623.5	1634.4	1626.8
160°	1653.8	1657.0	1658.6	1667.7	1661.3
162.5°	1687.2	1687.2	1688.8	1699.0	1691.5
165°	1715.7	1714.1	1714.1	1724.9	1717.4
167.5°	1741.6	1736.8	1736.8	1747.6	1740.0
170°	1761.0	1756.7	1755.1	1765.9	1756.7
172.5°	1774.5	1770.2	1768.6	1779.3	1770.2
175°	1785.3	1781.0	1777.7	1788.6	1779.3
177.5°	1791.2	1787.0	1783.7	1792.8	1783.7
180°	1788.6	1788.6	1788.6	1788.6	1788.6

TEST NUMBER: P904278

CATALOG NUMBER: DFN2DIP-TR2F0-020D060US830-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	5.85	6.51	7.01	7.65	9.25	1.84	2.49	2.99	3.63	5.23
	3H	7.49	8.08	8.65	9.23	10.84	3.00	3.58	4.16	4.73	6.34
	4H	8.08	8.63	9.25	9.78	11.40	3.43	3.99	4.60	5.13	6.75
	6H	8.47	8.98	9.65	10.13	11.76	3.73	4.24	4.90	5.39	7.02
	8H	8.58	9.07	9.76	10.23	11.85	3.80	4.29	4.98	5.46	7.08
	12H	8.63	9.09	9.81	10.25	11.89	3.83	4.30	5.02	5.46	7.10
4H	2H	5.84	6.40	7.02	7.55	9.17	2.40	2.96	3.58	4.10	5.72
	3H	7.63	8.10	8.81	9.27	10.90	3.71	4.18	4.89	5.35	6.98
	4H	8.30	8.73	9.48	9.89	11.53	4.24	4.67	5.42	5.83	7.48
	6H	8.78	9.15	9.97	10.33	11.97	4.63	5.00	5.82	6.18	7.82
	8H	8.94	9.28	10.13	10.46	12.11	4.75	5.09	5.94	6.26	7.92
	12H	9.01	9.32	10.22	10.51	12.17	4.80	5.11	6.00	6.29	7.95
8H	4H	8.25	8.59	9.44	9.76	11.42	4.49	4.83	5.68	6.01	7.66
	6H	8.78	9.06	9.99	10.28	11.93	4.98	5.26	6.19	6.48	8.13
	8H	8.98	9.23	10.19	10.42	12.09	5.16	5.41	6.37	6.60	8.27
	12H	9.10	9.31	10.31	10.50	12.21	5.26	5.47	6.47	6.67	8.37
12H	4H	8.19	8.50	9.39	9.69	11.35	4.49	4.80	5.69	5.98	7.64
	6H	8.76	9.00	9.97	10.20	11.87	5.02	5.27	6.24	6.46	8.14
	8H	8.95	9.17	10.17	10.36	12.06	5.21	5.43	6.43	6.62	8.32

END OF REPORT