

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P923094

Luminaire Tested: DFN2DIP-SQ4F0-070D120US940-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P923094
REPORT IS A COMBINATION OF REPORTS P900170 AND P896915
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-070D120US940-RLLFLL
Description: 4 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 14775.6 lumens
Efficiency: N/A
Efficacy: 97.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 151.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9967
Total Harmonic Distortion (THDi): 0.063
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P923094

CATALOG NUMBER: DFN2DIP-SQ4F0-070D120US940-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P923094

CATALOG NUMBER: DFN2DIP-SQ4F0-070D120US940-RLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	43	43	43
1	95	91	87	84	86	82	79	77	67	64	63	52	51	49	39	38	37
2	87	80	74	69	78	72	68	63	59	55	52	46	44	42	34	33	32
3	79	70	63	58	72	64	58	53	52	48	44	41	38	36	31	29	27
4	73	62	55	49	66	57	50	45	46	42	38	37	34	31	28	26	24
5	67	56	48	42	60	51	44	39	42	37	33	33	30	27	25	23	21
6	62	50	42	37	56	46	39	34	38	33	29	30	26	24	23	21	19
7	57	45	38	32	51	41	35	30	34	29	25	27	24	21	21	19	17
8	53	41	34	28	48	38	31	26	31	26	23	25	21	19	19	17	15
9	49	37	30	25	45	34	28	24	29	24	20	23	20	17	18	15	14
10	46	34	27	23	42	32	25	21	26	22	18	21	18	15	17	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1810	1810	1810
5°	1813	1782	1793
10°	1795	1747	1736
15°	1770	1690	1646
20°	1738	1611	1536
25°	1704	1522	1429
30°	1659	1430	1294
35°	1615	1332	1175
40°	1570	1231	1038
45°	1518	1118	915
50°	1464	1004	794
55°	1408	883	678
60°	1343	755	559
65°	1268	626	503
70°	1177	505	456
75°	1063	446	416
80°	898	376	363
85°	625	252	276

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 2663 cd/sqm

TEST NUMBER: P923094

CATALOG NUMBER: DFN2DIP-SQ4F0-070D120US940-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	241.8	1.6
10°-20°	663.7	4.5
20°-30°	931.9	6.3
30°-40°	1015.8	6.9
40°-50°	933.6	6.3
50°-60°	733.2	5.0
60°-70°	477.3	3.2
70°-80°	245.7	1.7
80°-90°	72.3	0.5
90°-100°	209.4	1.4
100°-110°	665.4	4.5
110°-120°	1138.7	7.7
120°-130°	1497.5	10.1
130°-140°	1680.9	11.4
140°-150°	1648.3	11.2
150°-160°	1382.7	9.4
160°-170°	917.0	6.2
170°-180°	320.5	2.2
0°-30°	1837.4	12.4
0°-40°	2853.2	19.3
0°-60°	4520.0	30.6
0°-90°	5315.3	36.0
90°-120°	2013.4	13.6
90°-150°	6840.1	46.3
90°-180°	9460.0	64.0
0°-180°	14775.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2580	2580	2580	2580	2580	
5°	2580	2568	2538	2559	2552	245
15°	2454	2428	2349	2304	2281	691
25°	2227	2152	1998	1903	1868	1024
35°	1919	1800	1595	1448	1396	1201
45°	1569	1412	1167	1002	946	1212
55°	1193	1011	759	619	574	1066
65°	806	616	406	327	320	799
75°	430	266	187	170	168	454
85°	100	51	44	44	44	115
90°	3	37	100	94	97	15
95°	149	178	183	183	178	166
105°	614	622	628	634	634	648
115°	1143	1159	1154	1151	1143	1130
125°	1662	1688	1679	1670	1667	1485
135°	2150	2181	2188	2184	2176	1662
145°	2610	2630	2646	2650	2638	1631
155°	2984	2992	3002	3016	3007	1374
165°	3246	3243	3243	3264	3250	916
175°	3378	3370	3364	3384	3367	321
180°	3384	3384	3384	3384	3384	

TEST NUMBER: P923094

CATALOG NUMBER: DFN2DIP-SQ4F0-070D120US940-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2579.8	2579.8	2579.8	2579.8	2579.8
2.5°	2591.4	2579.8	2554.0	2577.6	2572.9
5°	2579.8	2568.1	2537.7	2558.8	2551.8
7.5°	2558.8	2544.9	2512.2	2521.3	2509.7
10°	2530.8	2514.4	2467.8	2460.7	2446.8
12.5°	2495.8	2474.8	2411.6	2397.7	2371.9
15°	2453.7	2427.9	2348.7	2304.4	2281.1
17.5°	2404.7	2367.3	2269.2	2217.9	2180.5
20°	2348.7	2301.9	2185.2	2127.0	2075.5
22.5°	2288.0	2234.3	2098.7	2019.5	1984.6
25°	2227.3	2152.5	1998.4	1902.8	1867.7
27.5°	2155.0	2075.5	1905.1	1795.4	1741.6
30°	2078.0	1989.0	1802.2	1683.4	1620.2
32.5°	2003.1	1895.7	1704.4	1564.2	1505.7
35°	1919.1	1800.0	1594.7	1447.6	1396.1
37.5°	1837.5	1708.9	1491.9	1330.6	1272.5
40°	1751.0	1611.1	1384.4	1218.7	1158.0
42.5°	1662.3	1513.0	1277.1	1104.2	1046.1
45°	1569.0	1412.4	1167.4	1001.5	945.5
47.5°	1480.2	1314.6	1062.4	896.4	845.2
50°	1382.2	1216.5	959.6	798.3	749.6
52.5°	1286.3	1111.2	861.5	707.4	663.1
55°	1192.9	1010.8	758.7	618.8	574.4
57.5°	1097.3	910.5	667.8	537.0	499.6
60°	999.3	812.4	571.9	453.1	415.6
62.5°	903.6	716.8	490.2	378.3	359.6
65°	805.5	616.3	406.3	327.0	319.8
67.5°	712.1	522.9	327.0	287.0	280.2
70°	614.0	431.9	270.7	247.4	238.0
72.5°	520.7	347.8	226.4	207.9	203.1
75°	429.5	266.0	186.7	170.4	168.2
77.5°	338.6	189.0	147.1	137.7	133.0
80°	254.4	135.5	112.0	102.8	102.8
82.5°	177.4	91.1	77.0	72.3	72.3
85°	100.3	51.3	44.3	44.3	44.3
87.5°	37.4	18.5	18.5	16.3	16.3
90°	3.0	36.7	100.0	93.9	96.9
92.5°	63.2	85.7	88.7	91.8	91.8
95°	148.9	177.5	182.6	182.6	177.5
97.5°	247.9	274.5	285.7	285.7	285.7
100°	362.2	385.7	393.8	393.8	390.7
102.5°	482.6	499.9	511.1	514.2	511.1
105°	614.2	622.3	628.5	633.6	633.6
107.5°	744.8	757.1	757.1	759.0	744.8
110°	871.3	887.6	887.6	887.6	879.5

TEST NUMBER: P923094

CATALOG NUMBER: DFN2DIP-SQ4F0-070D120US940-RLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1008.0	1025.4	1022.3	1014.1	1008.0
115°	1142.6	1159.0	1153.9	1150.8	1142.6
117.5°	1276.3	1298.8	1284.5	1276.3	1268.2
120°	1411.0	1433.4	1411.0	1411.0	1401.9
122.5°	1533.5	1562.0	1547.7	1539.5	1533.5
125°	1662.0	1687.5	1679.4	1670.2	1667.1
127.5°	1787.5	1819.1	1807.9	1795.6	1787.5
130°	1904.8	1941.5	1936.4	1930.3	1919.0
132.5°	2036.4	2065.0	2067.0	2052.7	2044.6
135°	2149.6	2181.3	2187.5	2184.3	2176.2
137.5°	2276.2	2301.7	2306.8	2304.7	2292.5
140°	2387.4	2412.9	2427.1	2427.1	2415.9
142.5°	2501.7	2527.2	2535.3	2538.3	2527.2
145°	2609.8	2630.2	2646.5	2649.6	2638.4
147.5°	2706.7	2732.2	2744.5	2749.6	2738.4
150°	2806.7	2824.0	2835.3	2844.5	2835.3
152.5°	2895.5	2912.8	2927.1	2938.4	2927.1
155°	2984.2	2992.4	3001.6	3015.9	3006.7
157.5°	3060.8	3066.9	3071.9	3092.4	3078.1
160°	3129.1	3135.3	3138.3	3155.7	3143.4
162.5°	3192.3	3192.3	3195.4	3214.8	3200.5
165°	3246.4	3243.4	3243.4	3263.7	3249.5
167.5°	3295.4	3286.2	3286.2	3306.6	3292.4
170°	3332.1	3323.9	3320.9	3341.3	3323.9
172.5°	3357.6	3349.4	3346.4	3366.8	3349.4
175°	3378.1	3369.9	3363.8	3384.1	3366.8
177.5°	3389.3	3381.1	3374.9	3392.3	3374.9
180°	3384.1	3384.1	3384.1	3384.1	3384.1

TEST NUMBER: P923094

CATALOG NUMBER: DFN2DIP-SQ4F0-070D120US940-RLFL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.75	8.48	8.82	9.55	11.01	3.71	4.44	4.78	5.51	6.97
	3H	9.42	10.07	10.51	11.15	12.63	4.89	5.54	5.97	6.62	8.10
	4H	10.03	10.65	11.12	11.73	13.21	5.34	5.95	6.43	7.03	8.52
	6H	10.45	11.02	11.55	12.10	13.60	5.65	6.22	6.76	7.30	8.80
	8H	10.57	11.11	11.68	12.21	13.71	5.74	6.28	6.85	7.38	8.87
	12H	10.64	11.15	11.75	12.24	13.75	5.78	6.29	6.89	7.39	8.90
4H	2H	7.75	8.37	8.86	9.45	10.94	4.29	4.91	5.40	5.99	7.48
	3H	9.58	10.09	10.69	11.20	12.70	5.64	6.15	6.74	7.26	8.75
	4H	10.27	10.74	11.38	11.84	13.36	6.18	6.65	7.29	7.75	9.27
	6H	10.78	11.19	11.90	12.31	13.82	6.59	7.00	7.71	8.12	9.63
	8H	10.96	11.34	12.08	12.45	13.98	6.72	7.10	7.84	8.21	9.74
	12H	11.05	11.39	12.19	12.52	14.05	6.78	7.12	7.92	8.25	9.78
8H	4H	10.23	10.61	11.35	11.72	13.25	6.46	6.83	7.57	7.95	9.47
	6H	10.80	11.11	11.94	12.26	13.79	6.97	7.28	8.11	8.44	9.96
	8H	11.02	11.29	12.16	12.42	13.97	7.16	7.43	8.31	8.57	10.11
	12H	11.15	11.39	12.30	12.52	14.10	7.28	7.52	8.43	8.65	10.23
12H	4H	10.18	10.52	11.31	11.64	13.18	6.46	6.80	7.59	7.92	9.45
	6H	10.77	11.04	11.92	12.18	13.72	7.02	7.29	8.17	8.43	9.97
	8H	10.99	11.23	12.14	12.36	13.94	7.23	7.47	8.38	8.60	10.18

END OF REPORT