

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P904282

Luminaire Tested: DFN2DIP-TR2F0-030D020US830-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P904282
REPORT IS A COMBINATION OF REPORTS P900224 AND P897145
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR2F0-030D020US830-RLLFLL
Description: 2 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4071.8 lumens
Efficiency: N/A
Efficacy: 100.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.04' x L: 2.36' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 40.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P904282
CATALOG NUMBER: DFN2DIP-TR2F0-030D020US830-RLLFLL

Luminous Intensity Polar Plot





TEST NUMBER: P904282
 CATALOG NUMBER: DFN2DIP-TR2F0-030D020US830-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64	59			59
1	100	96	92	89	94	90	87	84	78	76	74	68	66	64	58	57	56	51			51
2	92	85	79	74	86	79	74	70	69	65	62	60	57	55	52	50	48	44			44
3	84	75	68	62	78	70	64	59	62	57	53	54	50	47	46	44	41	38			38
4	77	67	59	53	72	63	56	51	55	50	46	48	44	41	42	39	36	33			33
5	71	60	52	46	66	56	49	44	50	44	40	44	39	36	38	34	32	29			29
6	66	54	46	40	61	51	44	39	45	39	35	40	35	32	35	31	28	26			26
7	61	49	41	36	57	46	39	34	41	35	31	36	32	28	32	28	25	23			23
8	57	45	37	32	53	42	35	30	38	32	28	33	29	25	29	26	23	21			21
9	53	41	34	29	50	39	32	27	35	29	25	31	26	23	27	24	21	19			19
10	50	38	31	26	47	36	29	25	32	27	23	29	24	21	25	22	19	17			17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2607	2607	2607
5°	2607	2559	2577
10°	2577	2503	2489
15°	2538	2415	2355
20°	2487	2296	2193
25°	2435	2163	2036
30°	2366	2027	1838
35°	2299	1882	1665
40°	2230	1732	1467
45°	2151	1567	1288
50°	2068	1401	1113
55°	1982	1224	946
60°	1881	1040	774
65°	1765	853	692
70°	1625	679	620
75°	1447	588	555
80°	1194	477	469
85°	783	296	330

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2151 cd/sqm



TEST NUMBER: P904282

CATALOG NUMBER: DFN2DIP-TR2F0-030D020US830-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	109.5	2.7
10°-20°	300.7	7.4
20°-30°	422.1	10.4
30°-40°	460.2	11.3
40°-50°	422.9	10.4
50°-60°	332.2	8.2
60°-70°	216.2	5.3
70°-80°	111.3	2.7
80°-90°	30.1	0.7
90°-100°	36.9	0.9
100°-110°	117.2	2.9
110°-120°	200.6	4.9
120°-130°	263.8	6.5
130°-140°	296.1	7.3
140°-150°	290.4	7.1
150°-160°	243.6	6.0
160°-170°	161.5	4.0
170°-180°	56.5	1.4
0°-30°	832.3	20.4
0°-40°	1292.5	31.7
0°-60°	2047.6	50.3
0°-90°	2405.2	59.1
90°-120°	354.7	8.7
90°-150°	1205.0	29.6
90°-180°	1667.0	40.9
0°-180°	4071.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1169	1169	1169	1169	1169	
5°	1169	1163	1150	1159	1156	111
15°	1112	1100	1064	1044	1033	313
25°	1009	975	905	862	846	464
35°	869	815	722	656	632	544
45°	711	640	529	454	428	549
55°	540	458	344	280	260	483
65°	365	279	184	148	145	362
75°	194	121	85	77	76	206
85°	45	23	20	20	20	52
90°	1	6	18	16	17	4
95°	26	31	32	32	31	29
105°	108	110	111	112	112	114
115°	201	204	203	203	201	199
125°	293	297	296	294	294	262
135°	379	384	385	385	383	293
145°	460	463	466	467	465	287
155°	526	527	529	531	530	242
165°	572	571	571	575	572	161
175°	595	594	593	596	593	57
180°	596	596	596	596	596	



TEST NUMBER: P904282

CATALOG NUMBER: DFN2DIP-TR2FO-030D020US830-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1168.7	1168.7	1168.7	1168.7	1168.7
2.5°	1173.9	1168.7	1157.0	1167.6	1165.5
5°	1168.7	1163.4	1149.6	1159.1	1155.9
7.5°	1159.1	1152.8	1138.0	1142.2	1136.9
10°	1146.4	1139.1	1117.9	1114.7	1108.4
12.5°	1130.6	1121.1	1092.5	1086.2	1074.5
15°	1111.5	1099.9	1063.9	1043.9	1033.3
17.5°	1089.3	1072.4	1027.9	1004.8	987.8
20°	1063.9	1042.7	989.9	963.6	940.2
22.5°	1036.5	1012.1	950.7	914.8	899.0
25°	1009.0	975.1	905.3	862.0	846.0
27.5°	976.2	940.2	863.0	813.3	788.9
30°	941.3	901.1	816.4	762.6	734.0
32.5°	907.4	858.8	772.1	708.6	682.1
35°	869.4	815.4	722.4	655.7	632.4
37.5°	832.4	774.1	675.8	602.8	576.5
40°	793.2	729.8	627.2	552.0	524.6
42.5°	753.0	685.4	578.5	500.2	473.8
45°	710.8	639.8	528.9	453.6	428.3
47.5°	670.5	595.5	481.3	406.0	382.9
50°	626.1	551.0	434.7	361.7	339.5
52.5°	582.7	503.4	390.3	320.5	300.4
55°	540.4	457.9	343.7	280.3	260.2
57.5°	497.1	412.5	302.6	243.3	226.3
60°	452.6	368.1	259.1	205.2	188.3
62.5°	409.3	324.7	222.1	171.4	163.0
65°	364.9	279.2	184.0	148.1	144.9
67.5°	322.6	236.9	148.1	130.1	126.9
70°	278.1	195.7	122.6	112.1	107.8
72.5°	235.8	157.5	102.5	94.2	92.0
75°	194.5	120.6	84.6	77.2	76.2
77.5°	153.4	85.6	66.6	62.4	60.2
80°	115.3	61.4	50.7	46.6	46.6
82.5°	80.3	41.3	34.9	32.8	32.8
85°	45.4	23.2	20.1	20.1	20.1
87.5°	17.0	8.4	8.4	7.4	7.4
90°	0.6	6.5	17.6	16.5	17.1
92.5°	11.1	15.1	15.6	16.2	16.2
95°	26.2	31.3	32.1	32.1	31.3
97.5°	43.6	48.4	50.3	50.3	50.3
100°	63.8	68.0	69.4	69.4	68.8
102.5°	85.0	88.0	90.0	90.6	90.0
105°	108.2	109.6	110.7	111.6	111.6
107.5°	131.2	133.4	133.4	133.7	131.2
110°	153.5	156.4	156.4	156.4	155.0



TEST NUMBER: P904282

CATALOG NUMBER: DFN2DIP-TR2F0-030D020US830-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	177.6	180.6	180.1	178.6	177.6
115°	201.3	204.2	203.3	202.7	201.3
117.5°	224.9	228.8	226.3	224.9	223.4
120°	248.5	252.5	248.5	248.5	246.9
122.5°	270.1	275.1	272.7	271.3	270.1
125°	292.8	297.3	295.9	294.3	293.7
127.5°	314.9	320.5	318.5	316.3	314.9
130°	335.5	342.0	341.1	340.1	338.1
132.5°	358.7	363.8	364.1	361.7	360.1
135°	378.7	384.3	385.3	384.8	383.3
137.5°	401.0	405.5	406.4	406.0	403.9
140°	420.6	425.1	427.6	427.6	425.7
142.5°	440.7	445.2	446.7	447.1	445.2
145°	459.8	463.4	466.3	466.7	464.8
147.5°	476.8	481.4	483.5	484.4	482.4
150°	494.5	497.5	499.5	501.1	499.5
152.5°	510.1	513.1	515.7	517.6	515.7
155°	525.8	527.2	528.8	531.3	529.7
157.5°	539.2	540.3	541.2	544.8	542.2
160°	551.3	552.3	552.9	555.9	553.7
162.5°	562.4	562.4	562.9	566.4	563.8
165°	571.9	571.4	571.4	575.0	572.5
167.5°	580.5	578.9	578.9	582.5	580.0
170°	587.0	585.6	585.0	588.6	585.6
172.5°	591.5	590.0	589.6	593.1	590.0
175°	595.1	593.7	592.6	596.2	593.1
177.5°	597.1	595.7	594.6	597.6	594.6
180°	596.2	596.2	596.2	596.2	596.2



TEST NUMBER: P904282
 CATALOG NUMBER: DFN2DIP-TR2F0-030D020US830-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.15	12.06	12.04	12.96	14.10	7.14	8.05	8.02	8.94	10.08
	3H	12.81	13.63	13.71	14.53	15.70	8.31	9.13	9.21	10.04	11.20
	4H	13.41	14.18	14.32	15.09	16.26	8.76	9.53	9.67	10.44	11.61
	6H	13.82	14.52	14.74	15.44	16.63	9.07	9.78	9.99	10.70	11.88
	8H	13.93	14.61	14.86	15.54	16.73	9.15	9.83	10.08	10.76	11.95
	12H	13.99	14.63	14.92	15.56	16.77	9.19	9.83	10.13	10.76	11.97
4H	2H	11.18	11.95	12.09	12.86	14.03	7.73	8.50	8.64	9.41	10.58
	3H	12.99	13.63	13.91	14.57	15.76	9.07	9.70	9.99	10.65	11.84
	4H	13.66	14.25	14.60	15.18	16.40	9.60	10.19	10.54	11.12	12.34
	6H	14.16	14.66	15.11	15.62	16.84	10.01	10.51	10.96	11.47	12.69
	8H	14.32	14.79	15.28	15.75	16.98	10.13	10.60	11.08	11.56	12.78
	12H	14.41	14.83	15.38	15.81	17.04	10.19	10.61	11.16	11.59	12.82
8H	4H	13.63	14.10	14.59	15.06	16.29	9.88	10.34	10.83	11.30	12.53
	6H	14.18	14.56	15.15	15.56	16.79	10.37	10.76	11.35	11.76	12.99
	8H	14.38	14.72	15.36	15.71	16.95	10.55	10.90	11.54	11.88	13.13
	12H	14.50	14.80	15.49	15.79	17.08	10.66	10.96	11.65	11.95	13.24
12H	4H	13.59	14.01	14.56	14.98	16.22	9.88	10.30	10.85	11.28	12.51
	6H	14.15	14.49	15.14	15.48	16.73	10.42	10.76	11.40	11.75	12.99
	8H	14.36	14.66	15.35	15.64	16.93	10.62	10.92	11.61	11.90	13.19