

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P923102

Luminaire Tested: DFN2DIP-SQ4F0-070D160US940-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P923102
REPORT IS A COMBINATION OF REPORTS P900206 AND P896915
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-070D160US940-RLLFLL
Description: 4 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 17933.1 lumens
Efficiency: N/A
Efficacy: 97.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 183.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9967
Total Harmonic Distortion (THDi): 0.063
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P923102

CATALOG NUMBER: DFN2DIP-SQ4F0-070D160US940-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P923102

CATALOG NUMBER: DFN2DIP-SQ4F0-070D160US940-RLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	37	37	37
1	93	89	86	82	84	80	77	75	63	61	59	48	47	45	33	33	32
2	85	78	73	68	76	71	66	62	56	53	50	42	40	38	30	29	27
3	78	69	62	57	70	62	56	52	49	45	42	38	35	33	27	25	24
4	71	61	54	48	64	55	49	44	44	40	36	34	31	28	24	22	21
5	66	55	47	41	59	49	43	38	39	35	31	30	27	25	22	20	18
6	60	49	41	36	54	44	38	33	36	31	27	27	24	22	20	18	16
7	56	44	37	31	50	40	33	29	32	27	24	25	22	19	18	16	14
8	52	40	33	28	46	36	30	25	29	25	21	23	19	17	17	15	13
9	48	36	29	24	43	33	27	23	27	22	19	21	18	15	15	13	12
10	45	33	26	22	40	30	24	20	25	20	17	19	16	14	14	12	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1810	1810	1810
5°	1813	1782	1793
10°	1795	1747	1736
15°	1770	1690	1646
20°	1738	1611	1536
25°	1704	1522	1429
30°	1659	1430	1294
35°	1615	1332	1175
40°	1570	1231	1038
45°	1518	1118	915
50°	1464	1004	794
55°	1408	883	678
60°	1343	755	559
65°	1268	626	503
70°	1177	505	456
75°	1063	446	416
80°	898	376	363
85°	625	252	276

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 3551 cd/sqm

TEST NUMBER: P923102

CATALOG NUMBER: DFN2DIP-SQ4F0-070D160US940-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	241.8	1.3
10°-20°	663.7	3.7
20°-30°	931.9	5.2
30°-40°	1015.8	5.7
40°-50°	933.6	5.2
50°-60°	733.2	4.1
60°-70°	477.3	2.7
70°-80°	245.7	1.4
80°-90°	75.5	0.4
90°-100°	279.2	1.6
100°-110°	887.2	4.9
110°-120°	1518.3	8.5
120°-130°	1996.8	11.1
130°-140°	2241.4	12.5
140°-150°	2197.9	12.3
150°-160°	1843.7	10.3
160°-170°	1222.7	6.8
170°-180°	427.4	2.4
0°-30°	1837.4	10.2
0°-40°	2853.2	15.9
0°-60°	4520.0	25.2
0°-90°	5318.5	29.7
90°-120°	2684.7	15.0
90°-150°	9120.8	50.9
90°-180°	12615.0	70.3
0°-180°	17933.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2580	2580	2580	2580	2580	
5°	2580	2568	2538	2559	2552	245
15°	2454	2428	2349	2304	2281	691
25°	2227	2152	1998	1903	1868	1024
35°	1919	1800	1595	1448	1396	1201
45°	1569	1412	1167	1002	946	1212
55°	1193	1011	759	619	574	1066
65°	806	616	406	327	320	799
75°	430	266	187	170	168	454
85°	100	51	44	44	44	115
90°	4	49	133	125	129	18
95°	199	237	244	244	237	221
105°	819	830	838	845	845	864
115°	1524	1545	1539	1534	1524	1507
125°	2216	2250	2239	2227	2223	1980
135°	2866	2909	2917	2913	2902	2216
145°	3480	3507	3529	3533	3518	2174
155°	3979	3990	4002	4021	4009	1832
165°	4329	4325	4325	4352	4333	1221
175°	4504	4494	4485	4513	4489	428
180°	4513	4513	4513	4513	4513	

TEST NUMBER: P923102

CATALOG NUMBER: DFN2DIP-SQ4F0-070D160US940-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2579.8	2579.8	2579.8	2579.8	2579.8
2.5°	2591.4	2579.8	2554.0	2577.6	2572.9
5°	2579.8	2568.1	2537.7	2558.8	2551.8
7.5°	2558.8	2544.9	2512.2	2521.3	2509.7
10°	2530.8	2514.4	2467.8	2460.7	2446.8
12.5°	2495.8	2474.8	2411.6	2397.7	2371.9
15°	2453.7	2427.9	2348.7	2304.4	2281.1
17.5°	2404.7	2367.3	2269.2	2217.9	2180.5
20°	2348.7	2301.9	2185.2	2127.0	2075.5
22.5°	2288.0	2234.3	2098.7	2019.5	1984.6
25°	2227.3	2152.5	1998.4	1902.8	1867.7
27.5°	2155.0	2075.5	1905.1	1795.4	1741.6
30°	2078.0	1989.0	1802.2	1683.4	1620.2
32.5°	2003.1	1895.7	1704.4	1564.2	1505.7
35°	1919.1	1800.0	1594.7	1447.6	1396.1
37.5°	1837.5	1708.9	1491.9	1330.6	1272.5
40°	1751.0	1611.1	1384.4	1218.7	1158.0
42.5°	1662.3	1513.0	1277.1	1104.2	1046.1
45°	1569.0	1412.4	1167.4	1001.5	945.5
47.5°	1480.2	1314.6	1062.4	896.4	845.2
50°	1382.2	1216.5	959.6	798.3	749.6
52.5°	1286.3	1111.2	861.5	707.4	663.1
55°	1192.9	1010.8	758.7	618.8	574.4
57.5°	1097.3	910.5	667.8	537.0	499.6
60°	999.3	812.4	571.9	453.1	415.6
62.5°	903.6	716.8	490.2	378.3	359.6
65°	805.5	616.3	406.3	327.0	319.8
67.5°	712.1	522.9	327.0	287.0	280.2
70°	614.0	431.9	270.7	247.4	238.0
72.5°	520.7	347.8	226.4	207.9	203.1
75°	429.5	266.0	186.7	170.4	168.2
77.5°	338.6	189.0	147.1	137.7	133.0
80°	254.4	135.5	112.0	102.8	102.8
82.5°	177.4	91.1	77.0	72.3	72.3
85°	100.3	51.3	44.3	44.3	44.3
87.5°	37.4	18.5	18.5	16.3	16.3
90°	4.1	49.0	133.3	125.2	129.2
92.5°	84.4	114.3	118.3	122.4	122.4
95°	198.6	236.7	243.5	243.5	236.7
97.5°	330.6	366.0	380.9	380.9	380.9
100°	483.0	514.2	525.1	525.1	521.0
102.5°	643.5	666.6	681.5	685.6	681.5
105°	818.9	829.8	838.0	844.8	844.8
107.5°	993.1	1009.4	1009.4	1012.2	993.1
110°	1161.8	1183.6	1183.6	1183.6	1172.7

TEST NUMBER: P923102

CATALOG NUMBER: DFN2DIP-SQ4F0-070D160US940-RLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1344.1	1367.3	1363.2	1352.3	1344.1
115°	1523.7	1545.4	1538.6	1534.5	1523.7
117.5°	1701.9	1731.8	1712.8	1701.9	1691.0
120°	1881.5	1911.4	1881.5	1881.5	1869.2
122.5°	2044.7	2082.9	2063.8	2052.9	2044.7
125°	2216.2	2250.1	2239.3	2227.0	2222.9
127.5°	2383.5	2425.6	2410.6	2394.3	2383.5
130°	2539.9	2588.9	2582.1	2573.9	2558.9
132.5°	2715.4	2753.5	2756.2	2737.2	2726.3
135°	2866.4	2908.6	2916.8	2912.7	2901.8
137.5°	3035.1	3069.1	3076.0	3073.2	3056.9
140°	3183.4	3217.4	3236.5	3236.5	3221.5
142.5°	3335.8	3369.8	3380.7	3384.8	3369.8
145°	3480.0	3507.2	3528.9	3533.0	3518.1
147.5°	3609.2	3643.3	3659.6	3666.4	3651.4
150°	3742.5	3765.7	3780.7	3792.9	3780.7
152.5°	3860.9	3884.0	3903.1	3918.0	3903.1
155°	3979.3	3990.1	4002.4	4021.4	4009.2
157.5°	4081.3	4089.5	4096.2	4123.4	4104.5
160°	4172.4	4180.6	4184.7	4207.8	4191.5
162.5°	4256.8	4256.8	4260.9	4286.7	4267.6
165°	4328.9	4324.8	4324.8	4352.0	4333.0
167.5°	4394.2	4382.0	4382.0	4409.2	4390.1
170°	4443.1	4432.2	4428.2	4455.4	4432.2
172.5°	4477.2	4466.3	4462.2	4489.4	4466.3
175°	4504.4	4493.5	4485.3	4512.6	4489.4
177.5°	4519.4	4508.5	4500.3	4523.5	4500.3
180°	4512.6	4512.6	4512.6	4512.6	4512.6

TEST NUMBER: P923102

CATALOG NUMBER: DFN2DIP-SQ4F0-070D160US940-RLFL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.94	7.63	8.06	8.74	10.27	2.90	3.59	4.02	4.70	6.23
	3H	8.61	9.22	9.74	10.34	11.90	4.08	4.69	5.20	5.81	7.36
	4H	9.21	9.80	10.35	10.92	12.47	4.52	5.11	5.66	6.22	7.78
	6H	9.63	10.17	10.78	11.29	12.86	4.84	5.37	5.98	6.49	8.06
	8H	9.76	10.27	10.90	11.40	12.97	4.92	5.43	6.07	6.57	8.13
	12H	9.82	10.30	10.97	11.43	13.02	4.96	5.45	6.11	6.58	8.16
4H	2H	6.94	7.52	8.08	8.64	10.20	3.48	4.06	4.62	5.18	6.74
	3H	8.76	9.25	9.91	10.39	11.96	4.82	5.30	5.97	6.45	8.02
	4H	9.45	9.90	10.60	11.03	12.62	5.36	5.81	6.51	6.94	8.53
	6H	9.96	10.34	11.12	11.50	13.08	5.77	6.15	6.93	7.31	8.89
	8H	10.14	10.49	11.29	11.64	13.24	5.90	6.26	7.06	7.40	9.00
	12H	10.23	10.55	11.40	11.71	13.31	5.96	6.28	7.13	7.44	9.04
8H	4H	9.41	9.76	10.56	10.91	12.51	5.63	5.99	6.79	7.14	8.73
	6H	9.97	10.27	11.15	11.46	13.05	6.15	6.44	7.32	7.63	9.23
	8H	10.19	10.45	11.37	11.62	13.23	6.34	6.59	7.52	7.76	9.38
	12H	10.33	10.55	11.51	11.72	13.37	6.45	6.68	7.64	7.84	9.49
12H	4H	9.35	9.68	10.53	10.83	12.44	5.63	5.95	6.80	7.11	8.72
	6H	9.95	10.20	11.13	11.37	12.99	6.20	6.45	7.38	7.62	9.24
	8H	10.16	10.39	11.35	11.56	13.20	6.40	6.63	7.59	7.79	9.44

END OF REPORT