

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P904323

Luminaire Tested: DFN2DIP-TR2F0-050D020US830-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P904323
REPORT IS A COMBINATION OF REPORTS P901748 AND P897145
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR2F0-050D020US830-RLLONL
Description: 2 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5674.1 lumens
Efficiency: N/A
Efficacy: 90.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.04' x L: 2.36' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 62.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P904323

CATALOG NUMBER: DFN2DIP-TR2F0-050D020US830-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P904323

CATALOG NUMBER: DFN2DIP-TR2F0-050D020US830-RLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	112	112	112	112	106	106	106	106	95	95	95	85	85	85	75	75	75
1	103	99	95	92	97	94	90	88	84	82	79	76	74	72	67	66	65
2	94	87	81	76	89	83	78	73	75	71	67	67	64	61	60	58	56
3	87	77	70	64	82	74	67	62	67	61	57	60	56	53	54	51	48
4	80	69	61	55	75	66	59	53	60	54	49	54	49	46	49	45	42
5	74	62	54	48	69	59	52	46	54	48	43	49	44	40	44	40	37
6	68	56	48	42	64	54	46	41	49	43	38	44	39	36	40	36	33
7	63	51	43	37	60	49	41	36	45	38	34	41	36	32	37	33	30
8	59	47	39	33	56	45	37	32	41	35	31	37	32	29	34	30	27
9	55	43	35	30	52	41	34	29	38	32	28	35	30	26	32	28	24
10	52	39	32	27	49	38	31	27	35	29	25	32	27	24	30	25	22

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4344	4344	4344
5°	4345	4266	4295
10°	4295	4172	4148
15°	4230	4025	3925
20°	4145	3826	3654
25°	4058	3605	3393
30°	3944	3379	3064
35°	3832	3137	2775
40°	3717	2887	2445
45°	3585	2612	2147
50°	3447	2334	1855
55°	3303	2039	1576
60°	3135	1733	1290
65°	2942	1422	1154
70°	2708	1132	1033
75°	2413	979	925
80°	1990	795	780
85°	1307	493	550

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3585 cd/sqm

TEST NUMBER: P904323

CATALOG NUMBER: DFN2DIP-TR2F0-050D020US830-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	182.5	3.2
10°-20°	501.1	8.8
20°-30°	703.6	12.4
30°-40°	766.9	13.5
40°-50°	704.9	12.4
50°-60°	553.6	9.8
60°-70°	360.3	6.4
70°-80°	185.5	3.3
80°-90°	49.0	0.9
90°-100°	36.9	0.6
100°-110°	117.2	2.1
110°-120°	200.6	3.5
120°-130°	263.8	4.6
130°-140°	296.1	5.2
140°-150°	290.4	5.1
150°-160°	243.6	4.3
160°-170°	161.5	2.8
170°-180°	56.5	1.0
0°-30°	1387.2	24.4
0°-40°	2154.2	38.0
0°-60°	3412.7	60.1
0°-90°	4007.5	70.6
90°-120°	354.7	6.3
90°-150°	1205.0	21.2
90°-180°	1667.0	29.4
0°-180°	5674.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1948	1948	1948	1948	1948	
5°	1948	1939	1916	1932	1927	185
15°	1853	1833	1773	1740	1722	522
25°	1682	1625	1509	1437	1410	773
35°	1449	1359	1204	1093	1054	907
45°	1185	1066	881	756	714	915
55°	901	763	573	467	434	805
65°	608	465	307	247	242	603
75°	324	201	141	129	127	343
85°	76	39	34	34	34	87
90°	1	6	18	16	17	6
95°	26	31	32	32	31	29
105°	108	110	111	112	112	114
115°	201	204	203	203	201	199
125°	293	297	296	294	294	262
135°	379	384	385	385	383	293
145°	460	463	466	467	465	287
155°	526	527	529	531	530	242
165°	572	571	571	575	572	161
175°	595	594	593	596	593	57
180°	596	596	596	596	596	

TEST NUMBER: P904323

CATALOG NUMBER: DFN2DIP-TR2F0-050D020US830-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1947.8	1947.8	1947.8	1947.8	1947.8
2.5°	1956.5	1947.8	1928.3	1946.1	1942.5
5°	1947.8	1939.0	1916.0	1931.8	1926.7
7.5°	1931.8	1921.4	1896.7	1903.7	1894.8
10°	1910.7	1898.4	1863.2	1857.8	1847.3
12.5°	1884.3	1868.5	1820.8	1810.3	1790.8
15°	1852.6	1833.2	1773.3	1739.8	1722.2
17.5°	1815.5	1787.3	1713.3	1674.5	1646.2
20°	1773.3	1738.0	1649.8	1605.9	1567.0
22.5°	1727.5	1686.9	1584.6	1524.8	1498.4
25°	1681.6	1625.1	1508.8	1436.6	1410.0
27.5°	1627.0	1567.0	1438.3	1355.5	1314.9
30°	1568.9	1501.8	1360.7	1270.9	1223.2
32.5°	1512.4	1431.3	1286.9	1181.0	1136.9
35°	1449.0	1359.1	1204.0	1092.9	1054.0
37.5°	1387.2	1290.2	1126.4	1004.7	960.7
40°	1322.0	1216.4	1045.2	920.1	874.3
42.5°	1255.1	1142.3	964.2	833.7	789.8
45°	1184.6	1066.4	881.4	756.1	713.8
47.5°	1117.6	992.5	802.1	676.8	638.1
50°	1043.6	918.4	724.5	602.8	565.9
52.5°	971.2	839.0	650.4	534.1	500.7
55°	900.7	763.2	572.8	467.1	433.7
57.5°	828.5	687.5	504.2	405.5	377.2
60°	754.4	613.4	431.8	342.0	313.8
62.5°	682.2	541.2	370.1	285.6	271.5
65°	608.1	465.3	306.7	246.9	241.5
67.5°	537.6	394.8	246.9	216.8	211.5
70°	463.6	326.1	204.4	186.8	179.7
72.5°	393.1	262.6	171.0	156.9	153.4
75°	324.3	200.9	141.0	128.7	127.0
77.5°	255.6	142.7	111.1	104.0	100.4
80°	192.1	102.3	84.5	77.6	77.6
82.5°	133.9	68.8	58.2	54.6	54.6
85°	75.8	38.7	33.5	33.5	33.5
87.5°	28.3	14.0	14.0	12.3	12.3
90°	0.6	6.5	17.6	16.5	17.1
92.5°	11.1	15.1	15.6	16.2	16.2
95°	26.2	31.3	32.1	32.1	31.3
97.5°	43.6	48.4	50.3	50.3	50.3
100°	63.8	68.0	69.4	69.4	68.8
102.5°	85.0	88.0	90.0	90.6	90.0
105°	108.2	109.6	110.7	111.6	111.6
107.5°	131.2	133.4	133.4	133.7	131.2
110°	153.5	156.4	156.4	156.4	155.0



TEST NUMBER: P904323

CATALOG NUMBER: DFN2DIP-TR2F0-050D020US830-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	177.6	180.6	180.1	178.6	177.6
115°	201.3	204.2	203.3	202.7	201.3
117.5°	224.9	228.8	226.3	224.9	223.4
120°	248.5	252.5	248.5	248.5	246.9
122.5°	270.1	275.1	272.7	271.3	270.1
125°	292.8	297.3	295.9	294.3	293.7
127.5°	314.9	320.5	318.5	316.3	314.9
130°	335.5	342.0	341.1	340.1	338.1
132.5°	358.7	363.8	364.1	361.7	360.1
135°	378.7	384.3	385.3	384.8	383.3
137.5°	401.0	405.5	406.4	406.0	403.9
140°	420.6	425.1	427.6	427.6	425.7
142.5°	440.7	445.2	446.7	447.1	445.2
145°	459.8	463.4	466.3	466.7	464.8
147.5°	476.8	481.4	483.5	484.4	482.4
150°	494.5	497.5	499.5	501.1	499.5
152.5°	510.1	513.1	515.7	517.6	515.7
155°	525.8	527.2	528.8	531.3	529.7
157.5°	539.2	540.3	541.2	544.8	542.2
160°	551.3	552.3	552.9	555.9	553.7
162.5°	562.4	562.4	562.9	566.4	563.8
165°	571.9	571.4	571.4	575.0	572.5
167.5°	580.5	578.9	578.9	582.5	580.0
170°	587.0	585.6	585.0	588.6	585.6
172.5°	591.5	590.0	589.6	593.1	590.0
175°	595.1	593.7	592.6	596.2	593.1
177.5°	597.1	595.7	594.6	597.6	594.6
180°	596.2	596.2	596.2	596.2	596.2

TEST NUMBER: P904323

CATALOG NUMBER: DFN2DIP-TR2F0-050D020US830-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.86	14.90	14.63	15.68	16.62	9.84	10.88	10.61	11.66	12.60
	3H	15.53	16.46	16.31	17.25	18.22	11.03	11.96	11.81	12.75	13.72
	4H	16.13	17.00	16.93	17.80	18.79	11.48	12.35	12.28	13.15	14.14
	6H	16.55	17.35	17.35	18.16	19.16	11.80	12.60	12.61	13.41	14.41
	8H	16.67	17.43	17.49	18.26	19.26	11.89	12.65	12.71	13.48	14.48
	12H	16.73	17.45	17.55	18.27	19.30	11.93	12.66	12.75	13.48	14.51
4H	2H	13.90	14.77	14.70	15.57	16.56	10.45	11.32	11.25	12.12	13.11
	3H	15.72	16.45	16.53	17.28	18.28	11.80	12.52	12.61	13.36	14.36
	4H	16.40	17.06	17.23	17.89	18.93	12.34	13.00	13.17	13.83	14.87
	6H	16.91	17.47	17.75	18.33	19.37	12.76	13.32	13.60	14.18	15.22
	8H	17.07	17.60	17.92	18.45	19.50	12.88	13.41	13.73	14.26	15.31
	12H	17.16	17.64	18.03	18.51	19.57	12.95	13.42	13.81	14.29	15.35
8H	4H	16.38	16.91	17.23	17.76	18.81	12.62	13.15	13.47	14.01	15.06
	6H	16.93	17.37	17.80	18.26	19.31	13.13	13.57	14.00	14.46	15.51
	8H	17.13	17.52	18.02	18.41	19.48	13.31	13.70	14.19	14.59	15.65
	12H	17.26	17.61	18.15	18.49	19.61	13.42	13.76	14.31	14.64	15.77
12H	4H	16.34	16.82	17.21	17.69	18.75	12.63	13.11	13.50	13.98	15.04
	6H	16.90	17.29	17.79	18.18	19.25	13.17	13.56	14.06	14.45	15.52
	8H	17.12	17.46	18.00	18.34	19.46	13.38	13.72	14.26	14.60	15.72