

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P923170

Luminaire Tested: DFN2DIP-SQ4F0-090D140US940-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P923170
REPORT IS A COMBINATION OF REPORTS P900192 AND P896915
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-090D140US940-RLLFLL
Description: 4 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 17869.9 lumens
Efficiency: N/A
Efficacy: 94.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 188.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.983
Total Harmonic Distortion (THDi): 0.073
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P923170

CATALOG NUMBER: DFN2DIP-SQ4F0-090D140US940-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P923170

CATALOG NUMBER: DFN2DIP-SQ4F0-090D140US940-RLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	95	95	95	95	77	77	77	60	60	60	45	45	45
1	96	91	88	84	87	83	80	77	68	66	64	54	52	51	41	40	39
2	87	80	74	69	79	73	68	64	60	56	53	48	45	43	36	35	33
3	80	71	64	58	72	65	59	54	53	49	45	42	39	37	32	30	29
4	73	63	55	50	66	57	51	46	47	43	39	38	35	32	29	27	25
5	67	56	48	43	61	51	45	40	42	37	34	34	31	28	26	24	22
6	62	50	43	37	56	46	39	34	38	33	29	31	27	24	24	22	20
7	57	46	38	33	52	42	35	30	35	30	26	28	25	22	22	20	18
8	53	41	34	29	48	38	31	27	32	27	23	26	22	19	20	18	16
9	50	38	31	26	45	35	28	24	29	24	21	24	20	18	19	16	14
10	46	35	28	23	42	32	26	22	27	22	19	22	18	16	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2327	2327	2327
5°	2331	2291	2306
10°	2308	2246	2231
15°	2276	2173	2116
20°	2234	2071	1974
25°	2191	1956	1837
30°	2133	1839	1663
35°	2077	1713	1510
40°	2019	1582	1335
45°	1952	1437	1176
50°	1883	1291	1021
55°	1810	1135	872
60°	1727	971	718
65°	1630	805	647
70°	1514	650	587
75°	1367	574	535
80°	1155	483	467
85°	803	325	355

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 3108 cd/sqm

TEST NUMBER: P923170

CATALOG NUMBER: DFN2DIP-SQ4F0-090D140US940-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	310.9	1.7
10°-20°	853.4	4.8
20°-30°	1198.1	6.7
30°-40°	1306.0	7.3
40°-50°	1200.4	6.7
50°-60°	942.7	5.3
60°-70°	613.6	3.4
70°-80°	315.9	1.8
80°-90°	91.9	0.5
90°-100°	244.3	1.4
100°-110°	776.3	4.3
110°-120°	1328.4	7.4
120°-130°	1747.1	9.8
130°-140°	1961.0	11.0
140°-150°	1923.0	10.8
150°-160°	1613.2	9.0
160°-170°	1069.8	6.0
170°-180°	373.9	2.1
0°-30°	2362.4	13.2
0°-40°	3668.4	20.5
0°-60°	5811.5	32.5
0°-90°	6832.8	38.2
90°-120°	2349.0	13.1
90°-150°	7980.2	44.7
90°-180°	11037.0	61.8
0°-180°	17869.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3317	3317	3317	3317	3317	
5°	3317	3302	3263	3290	3281	315
15°	3155	3122	3020	2963	2933	889
25°	2864	2768	2570	2446	2401	1317
35°	2468	2314	2050	1861	1795	1544
45°	2017	1816	1501	1288	1216	1558
55°	1534	1300	975	796	738	1371
65°	1036	792	522	420	411	1027
75°	552	342	240	219	216	584
85°	129	66	57	57	57	148
90°	4	43	117	110	113	18
95°	174	207	213	213	207	193
105°	717	726	733	739	739	756
115°	1333	1352	1346	1343	1333	1319
125°	1939	1969	1959	1948	1945	1733
135°	2508	2545	2552	2548	2539	1938
145°	3045	3069	3088	3091	3078	1902
155°	3482	3491	3502	3518	3508	1603
165°	3788	3784	3784	3808	3791	1068
175°	3941	3932	3924	3948	3928	374
180°	3948	3948	3948	3948	3948	

TEST NUMBER: P923170

CATALOG NUMBER: DFN2DIP-SQ4F0-090D140US940-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3316.9	3316.9	3316.9	3316.9	3316.9
2.5°	3331.9	3316.9	3283.7	3314.0	3308.0
5°	3316.9	3301.9	3262.8	3289.8	3280.9
7.5°	3289.8	3272.0	3230.0	3241.7	3226.7
10°	3253.9	3232.8	3173.0	3163.7	3145.9
12.5°	3208.9	3181.9	3100.7	3082.8	3049.6
15°	3154.8	3121.7	3019.8	2962.7	2932.8
17.5°	3091.7	3043.7	2917.5	2851.6	2803.5
20°	3019.8	2959.6	2809.5	2734.7	2668.4
22.5°	2941.8	2872.6	2698.4	2596.5	2551.6
25°	2863.7	2767.5	2569.5	2446.5	2401.3
27.5°	2770.7	2668.4	2449.4	2308.3	2239.2
30°	2671.7	2557.3	2317.2	2164.4	2083.1
32.5°	2575.4	2437.2	2191.4	2011.2	1936.0
35°	2467.5	2314.3	2050.3	1861.2	1794.9
37.5°	2362.4	2197.2	1918.2	1710.8	1636.0
40°	2251.3	2071.4	1779.9	1566.9	1488.9
42.5°	2137.3	1945.3	1642.0	1419.8	1344.9
45°	2017.2	1816.0	1500.9	1287.5	1215.6
47.5°	1903.2	1690.1	1365.9	1152.5	1086.6
50°	1777.1	1564.0	1233.8	1026.4	963.7
52.5°	1653.9	1428.7	1107.7	909.5	852.6
55°	1533.7	1299.7	975.4	795.6	738.5
57.5°	1410.9	1170.7	858.6	690.5	642.4
60°	1284.7	1044.5	735.4	582.5	534.4
62.5°	1161.8	921.7	630.3	486.3	462.4
65°	1035.6	792.4	522.3	420.4	411.2
67.5°	915.6	672.3	420.4	369.1	360.2
70°	789.5	555.4	348.1	318.2	306.0
72.5°	669.4	447.1	291.1	267.2	261.2
75°	552.2	342.1	240.1	219.1	216.2
77.5°	435.3	243.0	189.1	177.1	171.0
80°	327.1	174.2	143.9	132.2	132.2
82.5°	228.0	117.2	99.1	93.0	93.0
85°	128.9	65.9	57.0	57.0	57.0
87.5°	48.1	23.9	23.9	21.0	21.0
90°	3.6	42.9	116.6	109.5	113.1
92.5°	73.8	100.0	103.5	107.1	107.1
95°	173.8	207.1	213.0	213.0	207.1
97.5°	289.3	320.2	333.3	333.3	333.3
100°	422.6	450.0	459.4	459.4	455.8
102.5°	563.0	583.3	596.4	599.9	596.4
105°	716.6	726.1	733.3	739.1	739.1
107.5°	868.9	883.2	883.2	885.6	868.9
110°	1016.5	1035.5	1035.5	1035.5	1026.0

TEST NUMBER: P923170

CATALOG NUMBER: DFN2DIP-SQ4F0-090D140US940-RLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1176.0	1196.2	1192.7	1183.1	1176.0
115°	1333.1	1352.2	1346.2	1342.6	1333.1
117.5°	1489.1	1515.3	1498.6	1489.1	1479.5
120°	1646.2	1672.4	1646.2	1646.2	1635.5
122.5°	1789.0	1822.3	1805.7	1796.2	1789.0
125°	1939.0	1968.7	1959.2	1948.5	1944.9
127.5°	2085.4	2122.3	2109.2	2094.9	2085.4
130°	2222.2	2265.1	2259.1	2252.0	2238.9
132.5°	2375.8	2409.1	2411.5	2394.9	2385.3
135°	2507.9	2544.9	2552.0	2548.4	2538.9
137.5°	2655.5	2685.3	2691.3	2688.9	2674.6
140°	2785.3	2815.0	2831.7	2831.7	2818.6
142.5°	2918.6	2948.4	2957.9	2961.5	2948.4
145°	3044.7	3068.6	3087.6	3091.2	3078.1
147.5°	3157.8	3187.6	3201.9	3207.8	3194.7
150°	3274.4	3294.7	3307.8	3318.5	3307.8
152.5°	3378.1	3398.3	3415.0	3428.0	3415.0
155°	3481.6	3491.1	3501.8	3518.5	3507.8
157.5°	3570.9	3578.0	3584.0	3607.8	3591.1
160°	3650.7	3657.8	3661.4	3681.6	3667.2
162.5°	3724.4	3724.4	3728.0	3750.6	3733.9
165°	3787.5	3784.0	3784.0	3807.8	3791.1
167.5°	3844.6	3833.9	3833.9	3857.7	3841.0
170°	3887.5	3878.0	3874.4	3898.2	3878.0
172.5°	3917.3	3907.7	3904.2	3928.0	3907.7
175°	3941.1	3931.6	3924.4	3948.2	3928.0
177.5°	3954.1	3944.7	3937.5	3957.7	3937.5
180°	3948.2	3948.2	3948.2	3948.2	3948.2



TEST NUMBER: P923170

CATALOG NUMBER: DFN2DIP-SQ4F0-090D140US940-RLFL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.88	9.63	9.94	10.68	12.12	4.85	5.59	5.90	6.65	8.08
	3H	10.56	11.22	11.63	12.29	13.74	6.03	6.69	7.10	7.76	9.21
	4H	11.17	11.80	12.25	12.86	14.32	6.47	7.10	7.55	8.17	9.63
	6H	11.59	12.17	12.68	13.24	14.71	6.79	7.37	7.88	8.44	9.91
	8H	11.71	12.26	12.81	13.35	14.81	6.88	7.43	7.97	8.52	9.98
	12H	11.77	12.30	12.87	13.38	14.86	6.92	7.44	8.02	8.52	10.01
4H	2H	8.89	9.52	9.98	10.59	12.05	5.43	6.06	6.52	7.13	8.59
	3H	10.72	11.24	11.81	12.34	13.81	6.78	7.30	7.87	8.39	9.86
	4H	11.41	11.89	12.51	12.98	14.47	7.32	7.80	8.42	8.89	10.38
	6H	11.92	12.34	13.03	13.44	14.93	7.74	8.15	8.84	9.26	10.74
	8H	12.10	12.48	13.21	13.59	15.09	7.86	8.25	8.97	9.35	10.85
	12H	12.19	12.54	13.32	13.65	15.16	7.93	8.27	9.05	9.39	10.89
8H	4H	11.37	11.76	12.48	12.86	14.36	7.60	7.98	8.70	9.08	10.58
	6H	11.94	12.26	13.07	13.40	14.90	8.11	8.43	9.24	9.57	11.07
	8H	12.16	12.44	13.29	13.56	15.08	8.31	8.58	9.44	9.71	11.22
	12H	12.30	12.54	13.43	13.66	15.21	8.42	8.66	9.56	9.78	11.34
12H	4H	11.32	11.67	12.44	12.78	14.29	7.60	7.95	8.72	9.06	10.56
	6H	11.91	12.19	13.05	13.32	14.83	8.16	8.44	9.30	9.56	11.08
	8H	12.13	12.38	13.27	13.50	15.05	8.37	8.62	9.51	9.74	11.29

END OF REPORT

FIELD PERFORMANCE MAY DIFFER FROM LABORATORY PERFORMANCE

8 of 8