

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P923174

Luminaire Tested: DFN2DIP-SQ4F0-090D160US940-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P923174
REPORT IS A COMBINATION OF REPORTS P900210 AND P896915
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-090D160US940-RLLFLL
Description: 4 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 19449.1 lumens
Efficiency: N/A
Efficacy: 95.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 204.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.983
Total Harmonic Distortion (THDi): 0.073
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P923174

CATALOG NUMBER: DFN2DIP-SQ4F0-090D160US940-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P923174

CATALOG NUMBER: DFN2DIP-SQ4F0-090D160US940-RLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	42	42	42
1	95	91	87	84	86	82	79	76	66	64	62	52	50	49	38	37	36
2	87	80	74	69	78	72	67	63	58	55	52	46	43	41	34	32	31
3	79	70	63	58	71	64	58	53	52	48	44	41	38	35	30	28	27
4	73	62	55	49	65	57	50	45	46	41	38	36	33	31	27	25	23
5	67	56	48	42	60	51	44	39	41	36	33	33	29	27	25	22	21
6	61	50	42	37	55	46	39	34	37	32	29	30	26	23	23	20	18
7	57	45	37	32	51	41	35	30	34	29	25	27	23	21	21	18	16
8	53	41	33	28	48	37	31	26	31	26	22	25	21	19	19	17	15
9	49	37	30	25	44	34	28	24	28	23	20	23	19	17	18	15	13
10	46	34	27	23	41	31	25	21	26	21	18	21	18	15	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2327	2327	2327
5°	2331	2291	2306
10°	2308	2246	2231
15°	2276	2173	2116
20°	2234	2071	1974
25°	2191	1956	1837
30°	2133	1839	1663
35°	2077	1713	1510
40°	2019	1582	1335
45°	1952	1437	1176
50°	1883	1291	1021
55°	1810	1135	872
60°	1727	971	718
65°	1630	805	647
70°	1514	650	587
75°	1367	574	535
80°	1155	483	467
85°	803	325	355

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 3551 cd/sqm

TEST NUMBER: P923174

CATALOG NUMBER: DFN2DIP-SQ4F0-090D160US940-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	310.9	1.6
10°-20°	853.4	4.4
20°-30°	1198.1	6.2
30°-40°	1306.0	6.7
40°-50°	1200.4	6.2
50°-60°	942.7	4.8
60°-70°	613.6	3.2
70°-80°	315.9	1.6
80°-90°	93.5	0.5
90°-100°	279.2	1.4
100°-110°	887.2	4.6
110°-120°	1518.3	7.8
120°-130°	1996.8	10.3
130°-140°	2241.4	11.5
140°-150°	2197.9	11.3
150°-160°	1843.7	9.5
160°-170°	1222.7	6.3
170°-180°	427.4	2.2
0°-30°	2362.4	12.1
0°-40°	3668.4	18.9
0°-60°	5811.5	29.9
0°-90°	6834.4	35.1
90°-120°	2684.7	13.8
90°-150°	9120.8	46.9
90°-180°	12615.0	64.9
0°-180°	19449.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3317	3317	3317	3317	3317	
5°	3317	3302	3263	3290	3281	315
15°	3155	3122	3020	2963	2933	889
25°	2864	2768	2570	2446	2401	1317
35°	2468	2314	2050	1861	1795	1544
45°	2017	1816	1501	1288	1216	1558
55°	1534	1300	975	796	738	1371
65°	1036	792	522	420	411	1027
75°	552	342	240	219	216	584
85°	129	66	57	57	57	148
90°	4	49	133	125	129	19
95°	199	237	244	244	237	221
105°	819	830	838	845	845	864
115°	1524	1545	1539	1534	1524	1507
125°	2216	2250	2239	2227	2223	1980
135°	2866	2909	2917	2913	2902	2216
145°	3480	3507	3529	3533	3518	2174
155°	3979	3990	4002	4021	4009	1832
165°	4329	4325	4325	4352	4333	1221
175°	4504	4494	4485	4513	4489	428
180°	4513	4513	4513	4513	4513	

TEST NUMBER: P923174

CATALOG NUMBER: DFN2DIP-SQ4F0-090D160US940-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3316.9	3316.9	3316.9	3316.9	3316.9
2.5°	3331.9	3316.9	3283.7	3314.0	3308.0
5°	3316.9	3301.9	3262.8	3289.8	3280.9
7.5°	3289.8	3272.0	3230.0	3241.7	3226.7
10°	3253.9	3232.8	3173.0	3163.7	3145.9
12.5°	3208.9	3181.9	3100.7	3082.8	3049.6
15°	3154.8	3121.7	3019.8	2962.7	2932.8
17.5°	3091.7	3043.7	2917.5	2851.6	2803.5
20°	3019.8	2959.6	2809.5	2734.7	2668.4
22.5°	2941.8	2872.6	2698.4	2596.5	2551.6
25°	2863.7	2767.5	2569.5	2446.5	2401.3
27.5°	2770.7	2668.4	2449.4	2308.3	2239.2
30°	2671.7	2557.3	2317.2	2164.4	2083.1
32.5°	2575.4	2437.2	2191.4	2011.2	1936.0
35°	2467.5	2314.3	2050.3	1861.2	1794.9
37.5°	2362.4	2197.2	1918.2	1710.8	1636.0
40°	2251.3	2071.4	1779.9	1566.9	1488.9
42.5°	2137.3	1945.3	1642.0	1419.8	1344.9
45°	2017.2	1816.0	1500.9	1287.5	1215.6
47.5°	1903.2	1690.1	1365.9	1152.5	1086.6
50°	1777.1	1564.0	1233.8	1026.4	963.7
52.5°	1653.9	1428.7	1107.7	909.5	852.6
55°	1533.7	1299.7	975.4	795.6	738.5
57.5°	1410.9	1170.7	858.6	690.5	642.4
60°	1284.7	1044.5	735.4	582.5	534.4
62.5°	1161.8	921.7	630.3	486.3	462.4
65°	1035.6	792.4	522.3	420.4	411.2
67.5°	915.6	672.3	420.4	369.1	360.2
70°	789.5	555.4	348.1	318.2	306.0
72.5°	669.4	447.1	291.1	267.2	261.2
75°	552.2	342.1	240.1	219.1	216.2
77.5°	435.3	243.0	189.1	177.1	171.0
80°	327.1	174.2	143.9	132.2	132.2
82.5°	228.0	117.2	99.1	93.0	93.0
85°	128.9	65.9	57.0	57.0	57.0
87.5°	48.1	23.9	23.9	21.0	21.0
90°	4.1	49.0	133.3	125.2	129.2
92.5°	84.4	114.3	118.3	122.4	122.4
95°	198.6	236.7	243.5	243.5	236.7
97.5°	330.6	366.0	380.9	380.9	380.9
100°	483.0	514.2	525.1	525.1	521.0
102.5°	643.5	666.6	681.5	685.6	681.5
105°	818.9	829.8	838.0	844.8	844.8
107.5°	993.1	1009.4	1009.4	1012.2	993.1
110°	1161.8	1183.6	1183.6	1183.6	1172.7

TEST NUMBER: P923174

CATALOG NUMBER: DFN2DIP-SQ4F0-090D160US940-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1344.1	1367.3	1363.2	1352.3	1344.1
115°	1523.7	1545.4	1538.6	1534.5	1523.7
117.5°	1701.9	1731.8	1712.8	1701.9	1691.0
120°	1881.5	1911.4	1881.5	1881.5	1869.2
122.5°	2044.7	2082.9	2063.8	2052.9	2044.7
125°	2216.2	2250.1	2239.3	2227.0	2222.9
127.5°	2383.5	2425.6	2410.6	2394.3	2383.5
130°	2539.9	2588.9	2582.1	2573.9	2558.9
132.5°	2715.4	2753.5	2756.2	2737.2	2726.3
135°	2866.4	2908.6	2916.8	2912.7	2901.8
137.5°	3035.1	3069.1	3076.0	3073.2	3056.9
140°	3183.4	3217.4	3236.5	3236.5	3221.5
142.5°	3335.8	3369.8	3380.7	3384.8	3369.8
145°	3480.0	3507.2	3528.9	3533.0	3518.1
147.5°	3609.2	3643.3	3659.6	3666.4	3651.4
150°	3742.5	3765.7	3780.7	3792.9	3780.7
152.5°	3860.9	3884.0	3903.1	3918.0	3903.1
155°	3979.3	3990.1	4002.4	4021.4	4009.2
157.5°	4081.3	4089.5	4096.2	4123.4	4104.5
160°	4172.4	4180.6	4184.7	4207.8	4191.5
162.5°	4256.8	4256.8	4260.9	4286.7	4267.6
165°	4328.9	4324.8	4324.8	4352.0	4333.0
167.5°	4394.2	4382.0	4382.0	4409.2	4390.1
170°	4443.1	4432.2	4428.2	4455.4	4432.2
172.5°	4477.2	4466.3	4462.2	4489.4	4466.3
175°	4504.4	4493.5	4485.3	4512.6	4489.4
177.5°	4519.4	4508.5	4500.3	4523.5	4500.3
180°	4512.6	4512.6	4512.6	4512.6	4512.6

TEST NUMBER: P923174

CATALOG NUMBER: DFN2DIP-SQ4F0-090D160US940-RLFL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.52	9.24	9.60	10.32	11.79	4.48	5.21	5.56	6.28	7.75
	3H	10.20	10.84	11.28	11.93	13.41	5.66	6.31	6.75	7.39	8.88
	4H	10.80	11.41	11.90	12.50	14.00	6.11	6.72	7.21	7.81	9.30
	6H	11.22	11.78	12.33	12.87	14.38	6.43	6.99	7.53	8.08	9.58
	8H	11.35	11.88	12.46	12.99	14.49	6.51	7.05	7.63	8.15	9.65
	12H	11.41	11.92	12.52	13.01	14.54	6.55	7.06	7.67	8.16	9.68
4H	2H	8.53	9.14	9.63	10.23	11.72	5.07	5.68	6.17	6.77	8.26
	3H	10.35	10.86	11.46	11.97	13.48	6.41	6.92	7.52	8.03	9.54
	4H	11.04	11.51	12.16	12.61	14.14	6.95	7.42	8.07	8.52	10.05
	6H	11.56	11.96	12.68	13.08	14.60	7.37	7.77	8.49	8.89	10.41
	8H	11.73	12.10	12.85	13.22	14.76	7.49	7.87	8.62	8.99	10.52
	12H	11.82	12.16	12.96	13.29	14.83	7.55	7.89	8.70	9.02	10.56
8H	4H	11.00	11.38	12.13	12.49	14.03	7.23	7.60	8.35	8.72	10.26
	6H	11.57	11.88	12.71	13.04	14.57	7.74	8.05	8.89	9.21	10.74
	8H	11.79	12.06	12.94	13.20	14.75	7.93	8.20	9.09	9.34	10.90
	12H	11.92	12.16	13.08	13.30	14.89	8.05	8.29	9.20	9.42	11.01
12H	4H	10.95	11.29	12.09	12.42	13.96	7.23	7.57	8.37	8.70	10.24
	6H	11.54	11.81	12.69	12.95	14.51	7.79	8.06	8.94	9.20	10.76
	8H	11.76	12.00	12.92	13.14	14.73	8.00	8.24	9.15	9.37	10.96