

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P907035

Luminaire Tested: DFN2DIP-TR2F0-040D030US835-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P907035
REPORT IS A COMBINATION OF REPORTS P901756 AND P897145
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR2F0-040D030US835-RLLONL
Description: 2 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6055.0 lumens
Efficiency: N/A
Efficacy: 104.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.04' x L: 2.36' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 57.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P907035

CATALOG NUMBER: DFN2DIP-TR2F0-040D030US835-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P907035

CATALOG NUMBER: DFN2DIP-TR2F0-040D030US835-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62
1	100	96	92	88	93	89	86	83	77	75	72	66	64	63	55	54	53
2	91	84	78	73	85	79	73	69	68	64	61	58	56	53	49	47	46
3	84	74	67	62	78	70	63	58	61	56	52	52	49	46	44	42	40
4	77	66	59	53	71	62	55	50	54	49	45	47	43	40	40	37	35
5	71	59	51	46	66	56	49	43	49	43	39	42	38	35	36	33	30
6	65	53	46	40	61	50	43	38	44	38	34	38	34	31	33	30	27
7	61	48	41	35	56	46	39	34	40	35	30	35	31	27	30	27	24
8	56	44	37	31	52	42	35	30	37	31	27	32	28	25	28	25	22
9	53	41	33	28	49	38	32	27	34	28	25	30	25	22	26	23	20
10	49	37	30	25	46	35	29	24	31	26	22	28	23	20	24	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3687	3687	3687
5°	3688	3621	3646
10°	3646	3541	3521
15°	3590	3416	3332
20°	3518	3247	3102
25°	3445	3059	2880
30°	3348	2868	2601
35°	3252	2662	2355
40°	3155	2450	2076
45°	3042	2217	1822
50°	2926	1981	1575
55°	2803	1731	1338
60°	2661	1471	1096
65°	2497	1207	979
70°	2299	961	877
75°	2048	831	786
80°	1688	674	663
85°	1109	418	466

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 3042 cd/sqm

TEST NUMBER: P907035

CATALOG NUMBER: DFN2DIP-TR2F0-040D030US835-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	154.9	2.6
10°-20°	425.3	7.0
20°-30°	597.2	9.9
30°-40°	650.9	10.8
40°-50°	598.3	9.9
50°-60°	469.9	7.8
60°-70°	305.8	5.1
70°-80°	157.4	2.6
80°-90°	42.9	0.7
90°-100°	58.7	1.0
100°-110°	186.5	3.1
110°-120°	319.2	5.3
120°-130°	419.8	6.9
130°-140°	471.2	7.8
140°-150°	462.1	7.6
150°-160°	387.7	6.4
160°-170°	257.1	4.2
170°-180°	89.9	1.5
0°-30°	1177.4	19.4
0°-40°	1828.4	30.2
0°-60°	2896.5	47.8
0°-90°	3402.7	56.2
90°-120°	564.5	9.3
90°-150°	1917.7	31.7
90°-180°	2652.0	43.8
0°-180°	6055.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1653	1653	1653	1653	1653	
5°	1653	1646	1626	1640	1635	157
15°	1572	1556	1505	1477	1462	443
25°	1427	1379	1281	1219	1197	656
35°	1230	1154	1022	928	895	770
45°	1005	905	748	642	606	776
55°	764	648	486	396	368	683
65°	516	395	260	210	205	512
75°	275	170	120	109	108	291
85°	64	33	28	28	28	74
90°	1	10	28	26	27	6
95°	42	50	51	51	50	46
105°	172	174	176	178	178	182
115°	320	325	324	323	320	317
125°	466	473	471	468	467	416
135°	603	612	613	612	610	466
145°	732	737	742	743	740	457
155°	837	839	842	846	843	385
165°	910	909	909	915	911	257
175°	947	945	943	949	944	90
180°	949	949	949	949	949	

TEST NUMBER: P907035

CATALOG NUMBER: DFN2DIP-TR2F0-040D030US835-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1653.2	1653.2	1653.2	1653.2	1653.2
2.5°	1660.7	1653.2	1636.7	1651.8	1648.7
5°	1653.2	1645.7	1626.2	1639.7	1635.3
7.5°	1639.7	1630.8	1609.9	1615.7	1608.3
10°	1621.8	1611.3	1581.4	1576.8	1568.0
12.5°	1599.4	1585.9	1545.4	1536.5	1520.0
15°	1572.4	1555.9	1505.1	1476.7	1461.8
17.5°	1541.0	1517.0	1454.1	1421.3	1397.3
20°	1505.1	1475.1	1400.3	1363.0	1330.0
22.5°	1466.2	1431.8	1344.9	1294.1	1271.8
25°	1427.3	1379.4	1280.6	1219.4	1196.8
27.5°	1381.0	1330.0	1220.8	1150.5	1116.0
30°	1331.6	1274.6	1154.9	1078.7	1038.3
32.5°	1283.7	1214.8	1092.2	1002.4	964.9
35°	1229.9	1153.5	1021.9	927.6	894.6
37.5°	1177.5	1095.1	956.0	852.7	815.4
40°	1122.1	1032.4	887.2	781.0	742.1
42.5°	1065.2	969.5	818.4	707.6	670.3
45°	1005.4	905.1	748.1	641.8	605.9
47.5°	948.6	842.4	680.8	574.5	541.6
50°	885.7	779.5	614.9	511.6	480.3
52.5°	824.3	712.1	552.1	453.3	424.9
55°	764.5	647.8	486.2	396.5	368.1
57.5°	703.2	583.5	427.9	344.1	320.2
60°	640.3	520.6	366.5	290.3	266.4
62.5°	579.1	459.4	314.1	242.4	230.5
65°	516.2	394.9	260.3	209.5	204.9
67.5°	456.4	335.1	209.5	184.0	179.5
70°	393.5	276.8	173.5	158.6	152.5
72.5°	333.7	222.9	145.1	133.2	130.2
75°	275.2	170.5	119.7	109.2	107.8
77.5°	217.0	121.1	94.3	88.3	85.2
80°	163.0	86.8	71.7	65.9	65.9
82.5°	113.7	58.4	49.4	46.3	46.3
85°	64.3	32.9	28.4	28.4	28.4
87.5°	24.0	11.9	11.9	10.5	10.5
90°	0.9	10.3	28.0	26.3	27.2
92.5°	17.7	24.0	24.9	25.7	25.7
95°	41.8	49.8	51.2	51.2	49.8
97.5°	69.5	76.9	80.1	80.1	80.1
100°	101.5	108.1	110.4	110.4	109.6
102.5°	135.3	140.2	143.3	144.2	143.3
105°	172.2	174.5	176.2	177.6	177.6
107.5°	208.8	212.2	212.2	212.8	208.8
110°	244.3	248.9	248.9	248.9	246.6



TEST NUMBER: P907035

CATALOG NUMBER: DFN2DIP-TR2F0-040D030US835-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	282.6	287.5	286.6	284.3	282.6
115°	320.4	324.9	323.5	322.7	320.4
117.5°	357.8	364.1	360.1	357.8	355.5
120°	395.6	401.9	395.6	395.6	393.0
122.5°	429.9	437.9	433.9	431.6	429.9
125°	466.0	473.1	470.8	468.2	467.4
127.5°	501.1	510.0	506.9	503.4	501.1
130°	534.0	544.3	542.9	541.2	538.0
132.5°	570.9	578.9	579.5	575.5	573.2
135°	602.7	611.5	613.3	612.4	610.1
137.5°	638.1	645.3	646.7	646.2	642.7
140°	669.3	676.5	680.5	680.5	677.3
142.5°	701.4	708.5	710.8	711.7	708.5
145°	731.7	737.4	742.0	742.8	739.7
147.5°	758.9	766.0	769.4	770.9	767.7
150°	786.9	791.8	794.9	797.5	794.9
152.5°	811.8	816.6	820.6	823.8	820.6
155°	836.7	838.9	841.5	845.5	843.0
157.5°	858.1	859.8	861.3	867.0	863.0
160°	877.3	879.0	879.9	884.7	881.3
162.5°	895.0	895.0	895.9	901.3	897.3
165°	910.2	909.3	909.3	915.0	911.0
167.5°	923.9	921.3	921.3	927.0	923.0
170°	934.2	931.9	931.1	936.8	931.9
172.5°	941.3	939.1	938.2	943.9	939.1
175°	947.1	944.8	943.1	948.8	943.9
177.5°	950.2	947.9	946.2	951.1	946.2
180°	948.8	948.8	948.8	948.8	948.8

TEST NUMBER: P907035

CATALOG NUMBER: DFN2DIP-TR2F0-040D030US835-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.11	12.99	13.02	13.92	15.10	8.09	8.98	9.00	9.90	11.08
	3H	13.77	14.56	14.69	15.49	16.70	9.27	10.06	10.19	10.99	12.20
	4H	14.36	15.11	15.30	16.05	17.26	9.71	10.46	10.65	11.40	12.61
	6H	14.77	15.46	15.72	16.40	17.63	10.02	10.71	10.97	11.65	12.88
	8H	14.89	15.54	15.84	16.50	17.73	10.11	10.76	11.06	11.72	12.95
	12H	14.94	15.56	15.90	16.52	17.77	10.14	10.77	11.10	11.72	12.97
4H	2H	12.13	12.88	13.07	13.82	15.03	8.68	9.43	9.62	10.37	11.58
	3H	13.94	14.56	14.89	15.53	16.76	10.02	10.64	10.97	11.61	12.84
	4H	14.62	15.18	15.58	16.14	17.40	10.55	11.12	11.52	12.08	13.34
	6H	15.11	15.60	16.08	16.58	17.84	10.96	11.45	11.93	12.43	13.69
	8H	15.27	15.73	16.25	16.71	17.98	11.08	11.53	12.06	12.51	13.78
	12H	15.36	15.77	16.35	16.76	18.04	11.14	11.55	12.13	12.54	13.82
8H	4H	14.58	15.04	15.56	16.02	17.29	10.82	11.28	11.80	12.26	13.53
	6H	15.13	15.50	16.13	16.52	17.79	11.32	11.70	12.32	12.72	13.99
	8H	15.33	15.66	16.34	16.67	17.95	11.50	11.83	12.51	12.84	14.13
	12H	15.45	15.74	16.46	16.75	18.08	11.61	11.90	12.62	12.90	14.24
12H	4H	14.54	14.95	15.53	15.94	17.22	10.83	11.24	11.82	12.23	13.51
	6H	15.10	15.43	16.11	16.44	17.73	11.37	11.70	12.38	12.71	13.99
	8H	15.31	15.60	16.32	16.60	17.93	11.56	11.86	12.58	12.86	14.19

END OF REPORT