

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P923202

Luminaire Tested: DFN2DIP-SQ4F0-100D120US940-RLLFLL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P923202  
REPORT IS A COMBINATION OF REPORTS P900176 AND P896915  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-SQ4F0-100D120US940-RLLFLL  
Description: 4 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 17049.4 lumens  
Efficiency: N/A  
Efficacy: 93.3 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')  
CIE Type: General Diffuse  
  
Input Watts (W): 182.8  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9968  
Total Harmonic Distortion (THDi): 0.064  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P923202  
CATALOG NUMBER: DFN2DIP-SQ4F0-100D120US940-RLFL

### Luminous Intensity Polar Plot





TEST NUMBER: P923202

CATALOG NUMBER: DFN2DIP-SQ4F0-100D120US940-RLFL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	45	45	45	45
1	97	93	89	86	89	85	82	79	71	69	67	58	56	55	46	45	44	38	38	38	38
2	89	82	76	71	81	75	70	66	63	59	56	51	49	47	41	39	38	33	33	33	33
3	81	72	65	59	74	66	60	55	56	51	47	46	43	40	37	34	33	28	28	28	28
4	74	64	56	51	68	59	52	47	50	45	41	41	37	35	33	30	28	25	25	25	25
5	68	57	49	44	63	53	46	41	45	39	35	37	33	30	30	27	25	22	22	22	22
6	63	51	44	38	58	48	41	36	40	35	31	34	30	27	27	24	22	19	19	19	19
7	58	47	39	33	54	43	36	31	37	31	28	31	27	24	25	22	20	17	17	17	17
8	54	42	35	30	50	39	33	28	34	28	25	28	24	21	23	20	18	16	16	16	16
9	51	39	31	27	46	36	29	25	31	26	22	26	22	19	21	18	16	14	14	14	14
10	47	36	29	24	43	33	27	23	28	23	20	24	20	17	20	17	15	13	13	13	13

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	2586	2586	2586
5°	2590	2545	2562
10°	2564	2496	2479
15°	2529	2414	2351
20°	2482	2301	2194
25°	2434	2174	2041
30°	2370	2043	1848
35°	2307	1903	1678
40°	2243	1758	1484
45°	2169	1597	1307
50°	2092	1435	1134
55°	2011	1261	969
60°	1918	1079	798
65°	1811	894	719
70°	1682	722	652
75°	1519	637	595
80°	1283	537	519
85°	893	361	394

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 90°  
 Vertical Angle: 90°  
 Luminance: 2663 cd/sqm



TEST NUMBER: P923202

CATALOG NUMBER: DFN2DIP-SQ4F0-100D120US940-RLFL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	345.4	2.0
10°-20°	948.2	5.6
20°-30°	1331.2	7.8
30°-40°	1451.1	8.5
40°-50°	1333.8	7.8
50°-60°	1047.4	6.1
60°-70°	681.8	4.0
70°-80°	351.0	2.1
80°-90°	99.2	0.6
90°-100°	209.4	1.2
100°-110°	665.4	3.9
110°-120°	1138.7	6.7
120°-130°	1497.5	8.8
130°-140°	1680.9	9.9
140°-150°	1648.3	9.7
150°-160°	1382.7	8.1
160°-170°	917.0	5.4
170°-180°	320.5	1.9
0°-30°	2624.8	15.4
0°-40°	4076.0	23.9
0°-60°	6457.2	37.9
0°-90°	7589.1	44.5
90°-120°	2013.4	11.8
90°-150°	6840.1	40.1
90°-180°	9460.0	55.5
0°-180°	17049.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	3685	3685	3685	3685	3685	
5°	3685	3669	3625	3655	3645	349
15°	3505	3468	3355	3292	3259	988
25°	3182	3075	2855	2718	2668	1463
35°	2742	2572	2278	2068	1994	1716
45°	2241	2018	1668	1431	1351	1731
55°	1704	1444	1084	884	821	1523
65°	1151	880	580	467	457	1141
75°	614	380	267	243	240	649
85°	143	73	63	63	63	164
90°	3	37	100	94	97	17
95°	149	178	183	183	178	166
105°	614	622	628	634	634	648
115°	1143	1159	1154	1151	1143	1130
125°	1662	1688	1679	1670	1667	1485
135°	2150	2181	2188	2184	2176	1662
145°	2610	2630	2646	2650	2638	1631
155°	2984	2992	3002	3016	3007	1374
165°	3246	3243	3243	3264	3250	916
175°	3378	3370	3364	3384	3367	321
180°	3384	3384	3384	3384	3384	



TEST NUMBER: P923202

CATALOG NUMBER: DFN2DIP-SQ4F0-100D120US940-RLFL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	3685.4	3685.4	3685.4	3685.4	3685.4
2.5°	3702.0	3685.4	3648.6	3682.2	3675.5
5°	3685.4	3668.8	3625.2	3655.4	3645.4
7.5°	3655.4	3635.5	3588.8	3601.9	3585.3
10°	3615.4	3592.0	3525.5	3515.2	3495.4
12.5°	3565.5	3535.4	3445.1	3425.3	3388.5
15°	3505.3	3468.5	3355.2	3291.9	3258.7
17.5°	3435.2	3381.8	3241.7	3168.4	3115.0
20°	3355.2	3288.4	3121.7	3038.6	2964.9
22.5°	3268.6	3191.8	2998.2	2885.0	2835.1
25°	3181.9	3075.1	2854.9	2718.3	2668.1
27.5°	3078.5	2964.9	2721.5	2564.7	2488.0
30°	2968.5	2841.4	2574.6	2404.9	2314.6
32.5°	2861.7	2708.0	2434.9	2234.6	2151.1
35°	2741.7	2571.5	2278.1	2068.0	1994.3
37.5°	2624.9	2441.2	2131.3	1900.9	1817.8
40°	2501.4	2301.5	1977.7	1741.0	1654.3
42.5°	2374.7	2161.3	1824.5	1577.5	1494.3
45°	2241.3	2017.7	1667.8	1430.7	1350.7
47.5°	2114.7	1877.9	1517.7	1280.6	1207.4
50°	1974.5	1737.8	1370.8	1140.5	1070.8
52.5°	1837.5	1587.4	1230.7	1010.6	947.3
55°	1704.1	1444.1	1083.9	884.0	820.6
57.5°	1567.6	1300.7	954.0	767.1	713.7
60°	1427.4	1160.7	817.1	647.2	593.8
62.5°	1290.8	1024.0	700.3	540.4	513.8
65°	1150.8	880.4	580.3	467.1	456.8
67.5°	1017.4	747.0	467.1	410.1	400.2
70°	877.2	617.2	386.7	353.5	340.1
72.5°	743.8	496.8	323.4	296.9	290.2
75°	613.6	380.0	266.8	243.4	240.2
77.5°	483.8	270.0	210.2	196.7	190.0
80°	363.4	193.6	160.0	146.9	146.9
82.5°	253.3	130.2	110.0	103.3	103.3
85°	143.3	73.2	63.3	63.3	63.3
87.5°	53.4	26.6	26.6	23.4	23.4
90°	3.0	36.7	100.0	93.9	96.9
92.5°	63.2	85.7	88.7	91.8	91.8
95°	148.9	177.5	182.6	182.6	177.5
97.5°	247.9	274.5	285.7	285.7	285.7
100°	362.2	385.7	393.8	393.8	390.7
102.5°	482.6	499.9	511.1	514.2	511.1
105°	614.2	622.3	628.5	633.6	633.6
107.5°	744.8	757.1	757.1	759.0	744.8
110°	871.3	887.6	887.6	887.6	879.5



TEST NUMBER: P923202

CATALOG NUMBER: DFN2DIP-SQ4F0-100D120US940-RLFL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	1008.0	1025.4	1022.3	1014.1	1008.0
115°	1142.6	1159.0	1153.9	1150.8	1142.6
117.5°	1276.3	1298.8	1284.5	1276.3	1268.2
120°	1411.0	1433.4	1411.0	1411.0	1401.9
122.5°	1533.5	1562.0	1547.7	1539.5	1533.5
125°	1662.0	1687.5	1679.4	1670.2	1667.1
127.5°	1787.5	1819.1	1807.9	1795.6	1787.5
130°	1904.8	1941.5	1936.4	1930.3	1919.0
132.5°	2036.4	2065.0	2067.0	2052.7	2044.6
135°	2149.6	2181.3	2187.5	2184.3	2176.2
137.5°	2276.2	2301.7	2306.8	2304.7	2292.5
140°	2387.4	2412.9	2427.1	2427.1	2415.9
142.5°	2501.7	2527.2	2535.3	2538.3	2527.2
145°	2609.8	2630.2	2646.5	2649.6	2638.4
147.5°	2706.7	2732.2	2744.5	2749.6	2738.4
150°	2806.7	2824.0	2835.3	2844.5	2835.3
152.5°	2895.5	2912.8	2927.1	2938.4	2927.1
155°	2984.2	2992.4	3001.6	3015.9	3006.7
157.5°	3060.8	3066.9	3071.9	3092.4	3078.1
160°	3129.1	3135.3	3138.3	3155.7	3143.4
162.5°	3192.3	3192.3	3195.4	3214.8	3200.5
165°	3246.4	3243.4	3243.4	3263.7	3249.5
167.5°	3295.4	3286.2	3286.2	3306.6	3292.4
170°	3332.1	3323.9	3320.9	3341.3	3323.9
172.5°	3357.6	3349.4	3346.4	3366.8	3349.4
175°	3378.1	3369.9	3363.8	3384.1	3366.8
177.5°	3389.3	3381.1	3374.9	3392.3	3374.9
180°	3384.1	3384.1	3384.1	3384.1	3384.1



TEST NUMBER: P923202  
 CATALOG NUMBER: DFN2DIP-SQ4F0-100D120US940-RLLFLL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.92	10.71	10.93	11.73	13.08	5.88	6.67	6.89	7.69	9.04
	3H	11.60	12.31	12.62	13.33	14.70	7.07	7.77	8.09	8.80	10.17
	4H	12.21	12.88	13.24	13.90	15.28	7.52	8.18	8.55	9.21	10.59
	6H	12.64	13.25	13.68	14.28	15.67	7.84	8.45	8.88	9.48	10.87
	8H	12.76	13.35	13.81	14.39	15.78	7.93	8.51	8.98	9.56	10.94
	12H	12.82	13.38	13.88	14.42	15.83	7.97	8.52	9.02	9.56	10.97
4H	2H	9.94	10.60	10.97	11.63	13.01	6.48	7.14	7.52	8.17	9.55
	3H	11.77	12.32	12.81	13.38	14.77	7.82	8.38	8.87	9.43	10.82
	4H	12.46	12.97	13.51	14.01	15.43	8.37	8.88	9.42	9.92	11.34
	6H	12.98	13.41	14.04	14.48	15.89	8.79	9.22	9.85	10.29	11.70
	8H	13.15	13.56	14.22	14.62	16.05	8.92	9.32	9.98	10.39	11.81
	12H	13.25	13.62	14.33	14.69	16.12	8.98	9.35	10.06	10.42	11.85
8H	4H	12.43	12.83	13.49	13.89	15.32	8.65	9.06	9.71	10.12	11.54
	6H	12.99	13.33	14.08	14.43	15.85	9.17	9.50	10.25	10.61	12.03
	8H	13.21	13.51	14.31	14.60	16.04	9.36	9.65	10.45	10.74	12.18
	12H	13.35	13.61	14.45	14.70	16.18	9.48	9.74	10.57	10.82	12.30
12H	4H	12.38	12.74	13.46	13.82	15.25	8.65	9.02	9.73	10.10	11.53
	6H	12.97	13.26	14.06	14.35	15.79	9.22	9.51	10.31	10.60	12.04
	8H	13.19	13.45	14.29	14.53	16.01	9.43	9.69	10.52	10.77	12.25