

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P925824

Luminaire Tested: DFN2DIP-SQ4F0-070D140US950-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P925824
REPORT IS A COMBINATION OF REPORTS P900187 AND P896915
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-070D140US950-FLLFLL
Description: 4 foot, Square Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 18431.3 lumens
Efficiency: N/A
Efficacy: 110.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 167.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9967
Total Harmonic Distortion (THDi): 0.063
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P925824

CATALOG NUMBER: DFN2DIP-SQ4F0-070D140US950-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P925824

CATALOG NUMBER: DFN2DIP-SQ4F0-070D140US950-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	43	43	43
1	95	90	87	83	85	82	79	76	66	64	62	52	50	49	38	37	36
2	86	79	73	68	78	72	66	62	58	54	51	45	43	41	34	32	31
3	79	69	62	56	71	63	57	52	51	47	43	40	37	34	30	28	26
4	72	61	54	48	65	56	49	44	45	40	37	36	32	29	27	24	22
5	66	54	47	41	59	50	43	38	40	35	31	32	28	25	24	22	20
6	61	49	41	35	55	45	38	33	36	31	27	29	25	22	22	19	17
7	56	44	36	31	50	40	33	28	33	28	24	26	22	20	20	17	15
8	52	40	32	27	47	36	30	25	30	25	21	24	20	17	18	16	14
9	48	36	29	24	44	33	27	22	27	22	19	22	18	16	17	14	12
10	45	33	26	21	41	30	24	20	25	20	17	20	17	14	16	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1823	1823	1823
5°	1826	1798	1811
10°	1811	1774	1787
15°	1785	1746	1749
20°	1749	1705	1710
25°	1713	1657	1665
30°	1668	1612	1608
35°	1625	1559	1548
40°	1573	1506	1490
45°	1521	1453	1431
50°	1464	1396	1363
55°	1404	1331	1301
60°	1336	1254	1229
65°	1263	1175	1145
70°	1169	1077	1054
75°	1039	961	971
80°	882	813	811
85°	638	556	545

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 3325 cd/sqm

TEST NUMBER: P925824

CATALOG NUMBER: DFN2DIP-SQ4F0-070D140US950-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	244.6	1.3
10°-20°	688.1	3.7
20°-30°	1011.3	5.5
30°-40°	1174.5	6.4
40°-50°	1173.1	6.4
50°-60°	1022.9	5.5
60°-70°	756.1	4.1
70°-80°	427.8	2.3
80°-90°	124.9	0.7
90°-100°	261.4	1.4
100°-110°	830.5	4.5
110°-120°	1421.2	7.7
120°-130°	1869.1	10.1
130°-140°	2098.0	11.4
140°-150°	2057.4	11.2
150°-160°	1725.8	9.4
160°-170°	1144.5	6.2
170°-180°	400.0	2.2
0°-30°	1943.9	10.5
0°-40°	3118.5	16.9
0°-60°	5314.4	28.8
0°-90°	6623.3	35.9
90°-120°	2513.1	13.6
90°-150°	8537.6	46.3
90°-180°	11808.0	64.1
0°-180°	18431.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2598	2598	2598	2598	2598	
5°	2598	2589	2561	2581	2576	247
15°	2474	2459	2426	2436	2424	697
25°	2239	2219	2176	2181	2176	1030
35°	1932	1907	1866	1851	1839	1206
45°	1572	1554	1517	1489	1479	1213
55°	1189	1174	1144	1114	1102	1063
65°	802	787	762	740	727	793
75°	420	415	402	387	392	448
85°	102	100	98	90	88	114
90°	4	46	125	117	121	18
95°	186	222	228	228	222	207
105°	767	777	784	791	791	809
115°	1426	1447	1440	1436	1426	1411
125°	2074	2106	2096	2085	2081	1854
135°	2683	2723	2730	2726	2716	2074
145°	3257	3283	3303	3307	3293	2035
155°	3725	3735	3746	3764	3753	1714
165°	4052	4048	4048	4074	4056	1143
175°	4216	4206	4199	4224	4202	401
180°	4224	4224	4224	4224	4224	

TEST NUMBER: P925824

CATALOG NUMBER: DFN2DIP-SQ4F0-070D140US950-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2598.4	2598.4	2598.4	2598.4	2598.4
2.5°	2613.6	2601.1	2573.5	2598.4	2593.6
5°	2598.4	2588.7	2561.1	2581.0	2576.2
7.5°	2581.0	2566.1	2538.5	2558.7	2553.7
10°	2553.7	2536.1	2506.2	2526.1	2518.7
12.5°	2516.0	2501.2	2471.2	2483.6	2478.6
15°	2473.6	2458.7	2426.1	2436.2	2423.7
17.5°	2421.1	2406.3	2373.6	2386.1	2373.6
20°	2363.5	2348.7	2313.7	2321.2	2311.4
22.5°	2306.3	2283.8	2251.2	2251.2	2246.1
25°	2238.8	2218.8	2176.5	2181.2	2176.5
27.5°	2163.7	2146.2	2113.9	2106.4	2093.9
30°	2089.0	2068.7	2031.4	2024.0	2013.9
32.5°	2008.8	1994.1	1954.0	1938.9	1928.8
35°	1931.5	1906.6	1866.5	1851.4	1838.9
37.5°	1844.0	1821.5	1781.4	1763.9	1751.4
40°	1754.1	1734.0	1693.9	1671.7	1661.6
42.5°	1666.6	1646.5	1606.7	1581.5	1566.7
45°	1571.7	1554.3	1516.6	1489.3	1479.2
47.5°	1479.2	1461.7	1421.7	1394.1	1379.3
50°	1381.7	1369.2	1334.2	1299.3	1286.8
52.5°	1286.8	1269.3	1237.0	1209.4	1191.8
55°	1189.4	1174.4	1144.4	1114.5	1102.0
57.5°	1091.9	1079.5	1046.8	1016.9	1006.9
60°	994.4	984.5	949.6	922.0	914.6
62.5°	899.4	882.0	857.1	832.2	822.1
65°	802.2	787.0	762.2	739.6	727.1
67.5°	702.2	689.6	667.2	649.8	639.7
70°	609.7	599.7	577.1	559.6	549.8
72.5°	514.8	504.8	492.3	474.8	467.4
75°	419.7	414.9	402.1	387.3	392.4
77.5°	334.9	324.7	319.7	312.2	304.9
80°	249.9	247.4	242.3	234.9	229.8
82.5°	169.9	169.9	167.5	157.5	157.5
85°	102.4	100.0	97.6	89.9	87.5
87.5°	45.0	40.1	35.0	27.6	24.9
90°	3.8	45.9	124.8	117.2	121.0
92.5°	79.0	106.9	110.8	114.6	114.6
95°	185.9	221.6	227.9	227.9	221.6
97.5°	309.5	342.6	356.6	356.6	356.6
100°	452.1	481.4	491.5	491.5	487.7
102.5°	602.4	624.0	638.0	641.9	638.0
105°	766.6	776.8	784.5	790.8	790.8
107.5°	929.6	944.9	944.9	947.4	929.6
110°	1087.6	1107.9	1107.9	1107.9	1097.7

TEST NUMBER: P925824

CATALOG NUMBER: DFN2DIP-SQ4F0-070D140US950-FLLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1258.1	1279.8	1276.0	1265.8	1258.1
115°	1426.2	1446.6	1440.3	1436.4	1426.2
117.5°	1593.1	1621.1	1603.3	1593.1	1582.9
120°	1761.2	1789.2	1761.2	1761.2	1749.7
122.5°	1914.0	1949.6	1931.8	1921.6	1914.0
125°	2074.5	2106.2	2096.0	2084.6	2080.8
127.5°	2231.0	2270.5	2256.5	2241.2	2231.0
130°	2377.5	2423.4	2417.0	2409.3	2395.3
132.5°	2541.7	2577.4	2580.0	2562.2	2552.0
135°	2683.1	2722.6	2730.3	2726.4	2716.2
137.5°	2841.0	2872.9	2879.3	2876.7	2861.4
140°	2979.8	3011.7	3029.5	3029.5	3015.5
142.5°	3122.4	3154.3	3164.5	3168.3	3154.3
145°	3257.4	3282.9	3303.3	3307.1	3293.1
147.5°	3378.4	3410.3	3425.5	3431.9	3417.9
150°	3503.2	3524.8	3538.9	3550.3	3538.9
152.5°	3614.0	3635.7	3653.5	3667.5	3653.5
155°	3724.8	3735.0	3746.5	3764.3	3752.8
157.5°	3820.3	3827.9	3834.3	3859.8	3841.9
160°	3905.7	3913.3	3917.1	3938.8	3923.4
162.5°	3984.6	3984.6	3988.4	4012.6	3994.8
165°	4052.1	4048.3	4048.3	4073.8	4055.9
167.5°	4113.2	4101.7	4101.7	4127.2	4109.4
170°	4159.1	4148.9	4145.0	4170.5	4148.9
172.5°	4190.9	4180.7	4176.9	4202.4	4180.7
175°	4216.4	4206.2	4198.6	4224.0	4202.4
177.5°	4230.3	4220.2	4212.6	4234.1	4212.6
180°	4224.0	4224.0	4224.0	4224.0	4224.0

TEST NUMBER: P925824

CATALOG NUMBER: DFN2DIP-SQ4F0-070D140US950-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.91	8.65	8.98	9.73	11.18	7.46	8.21	8.53	9.28	10.74
	3H	9.56	10.23	10.64	11.31	12.79	9.07	9.74	10.15	10.82	12.30
	4H	10.15	10.78	11.24	11.87	13.35	9.65	10.29	10.74	11.37	12.85
	6H	10.55	11.13	11.64	12.22	13.71	10.05	10.63	11.14	11.72	13.21
	8H	10.65	11.21	11.75	12.31	13.80	10.15	10.70	11.25	11.80	13.29
	12H	10.70	11.22	11.80	12.32	13.83	10.19	10.71	11.29	11.81	13.32
4H	2H	8.35	8.99	9.45	10.07	11.55	8.00	8.64	9.10	9.72	11.20
	3H	10.22	10.75	11.32	11.85	13.35	9.81	10.34	10.91	11.45	12.94
	4H	10.93	11.42	12.04	12.51	14.03	10.50	10.99	11.61	12.09	13.61
	6H	11.44	11.86	12.56	12.98	14.49	11.01	11.43	12.12	12.55	14.06
	8H	11.59	11.98	12.71	13.09	14.62	11.15	11.54	12.27	12.66	14.18
	12H	11.66	12.01	12.79	13.14	14.67	11.21	11.56	12.34	12.69	14.22
8H	4H	11.12	11.51	12.23	12.62	14.14	10.74	11.13	11.85	12.24	13.77
	6H	11.75	12.07	12.88	13.22	14.75	11.36	11.69	12.50	12.84	14.36
	8H	11.97	12.25	13.11	13.39	14.93	11.58	11.86	12.72	12.99	14.54
	12H	12.10	12.35	13.25	13.48	15.06	11.69	11.94	12.83	13.07	14.65
12H	4H	11.10	11.45	12.23	12.57	14.11	10.73	11.08	11.86	12.21	13.74
	6H	11.78	12.06	12.92	13.19	14.74	11.40	11.69	12.55	12.82	14.36
	8H	12.02	12.26	13.16	13.40	14.97	11.64	11.88	12.78	13.02	14.59