

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P915183

Luminaire Tested: DFN2DIP-TR2F0-020D040US927-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P915183
REPORT IS A COMBINATION OF REPORTS P901762 AND P897145
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR2F0-020D040US927-RLLONL
Description: 2 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4151.0 lumens
Efficiency: N/A
Efficacy: 93.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.04' x L: 2.36' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 44.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P915183

CATALOG NUMBER: DFN2DIP-TR2F0-020D040US927-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P915183

CATALOG NUMBER: DFN2DIP-TR2F0-020D040US927-RLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	93	93	93	93	74	74	74	56	56	56	40	40	40
1	94	90	86	83	85	81	78	75	65	63	61	50	48	47	36	35	34
2	86	79	73	68	77	71	67	62	57	54	51	44	42	40	32	31	29
3	79	70	63	57	71	63	57	52	51	46	43	39	36	34	29	27	25
4	72	62	54	49	65	56	50	45	45	41	37	35	32	29	26	24	22
5	66	55	47	42	59	50	43	38	40	36	32	32	28	26	23	21	19
6	61	49	42	36	55	45	38	33	36	32	28	29	25	23	21	19	17
7	56	45	37	32	51	41	34	29	33	28	25	26	23	20	19	17	15
8	52	40	33	28	47	37	30	26	30	25	22	24	20	18	18	16	14
9	49	37	30	25	44	34	27	23	28	23	20	22	19	16	17	14	13
10	45	34	27	22	41	31	25	21	25	21	18	20	17	15	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1460	1460	1460
5°	1461	1434	1444
10°	1444	1403	1395
15°	1422	1353	1320
20°	1393	1286	1229
25°	1365	1212	1141
30°	1326	1136	1030
35°	1288	1055	933
40°	1250	971	822
45°	1205	878	722
50°	1159	785	624
55°	1110	686	530
60°	1054	583	434
65°	989	478	388
70°	910	381	347
75°	811	329	311
80°	669	267	262
85°	438	165	184

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 1309 cd/sqm

TEST NUMBER: P915183

CATALOG NUMBER: DFN2DIP-TR2F0-020D040US927-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	61.4	1.5
10°-20°	168.5	4.1
20°-30°	236.5	5.7
30°-40°	257.8	6.2
40°-50°	237.0	5.7
50°-60°	186.1	4.5
60°-70°	121.2	2.9
70°-80°	62.3	1.5
80°-90°	18.8	0.5
90°-100°	62.0	1.5
100°-110°	197.0	4.7
110°-120°	337.2	8.1
120°-130°	443.5	10.7
130°-140°	497.8	12.0
140°-150°	488.1	11.8
150°-160°	409.5	9.9
160°-170°	271.5	6.5
170°-180°	94.9	2.3
0°-30°	466.4	11.2
0°-40°	724.2	17.4
0°-60°	1147.3	27.6
0°-90°	1349.6	32.5
90°-120°	596.2	14.4
90°-150°	2025.6	48.8
90°-180°	2801.0	67.5
0°-180°	4151.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	655	655	655	655	655	
5°	655	652	644	650	648	62
15°	623	616	596	585	579	176
25°	565	546	507	483	474	260
35°	487	457	405	367	354	305
45°	398	358	296	254	240	308
55°	303	257	193	157	146	271
65°	204	156	103	83	81	203
75°	109	68	47	43	43	115
85°	25	13	11	11	11	29
90°	1	11	30	28	29	4
95°	44	53	54	54	53	49
105°	182	184	186	188	188	192
115°	338	343	342	341	338	335
125°	492	500	497	495	494	440
135°	637	646	648	647	644	492
145°	773	779	784	785	781	483
155°	884	886	889	893	890	407
165°	961	960	960	966	962	271
175°	1000	998	996	1002	997	95
180°	1002	1002	1002	1002	1002	

TEST NUMBER: P915183

CATALOG NUMBER: DFN2DIP-TR2F0-020D040US927-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	654.8	654.8	654.8	654.8	654.8
2.5°	657.7	654.8	648.2	654.3	653.1
5°	654.8	651.9	644.1	649.5	647.7
7.5°	649.5	645.9	637.6	640.0	637.0
10°	642.4	638.2	626.4	624.6	621.1
12.5°	633.5	628.1	612.1	608.6	602.1
15°	622.8	616.2	596.1	584.9	579.0
17.5°	610.4	600.9	576.0	562.9	553.5
20°	596.1	584.2	554.7	539.9	526.8
22.5°	580.7	567.1	532.7	512.6	503.7
25°	565.4	546.4	507.2	483.0	474.0
27.5°	547.0	526.8	483.5	455.7	442.0
30°	527.4	504.9	457.5	427.3	411.2
32.5°	508.4	481.2	432.6	397.0	382.2
35°	487.1	456.9	404.8	367.4	354.3
37.5°	466.4	433.7	378.7	337.8	323.0
40°	444.4	408.9	351.4	309.3	293.9
42.5°	421.9	384.0	324.2	280.3	265.5
45°	398.2	358.5	296.4	254.2	240.0
47.5°	375.7	333.7	269.7	227.5	214.5
50°	350.9	308.8	243.6	202.6	190.3
52.5°	326.5	282.0	218.6	179.6	168.3
55°	302.8	256.6	192.6	157.1	145.8
57.5°	278.5	231.1	169.5	136.3	126.8
60°	253.7	206.2	145.2	115.0	105.5
62.5°	229.3	182.0	124.5	96.0	91.3
65°	204.5	156.5	103.1	83.0	81.2
67.5°	180.8	132.7	83.0	72.9	71.1
70°	155.8	109.6	68.7	62.8	60.4
72.5°	132.1	88.2	57.4	52.8	51.6
75°	109.0	67.5	47.4	43.3	42.7
77.5°	86.0	48.0	37.3	34.9	33.7
80°	64.6	34.4	28.4	26.1	26.1
82.5°	45.0	23.1	19.6	18.4	18.4
85°	25.4	13.0	11.2	11.2	11.2
87.5°	9.5	4.8	4.8	4.1	4.1
90°	0.9	10.9	29.6	27.8	28.7
92.5°	18.7	25.3	26.3	27.2	27.2
95°	44.1	52.6	54.1	54.1	52.6
97.5°	73.4	81.3	84.6	84.6	84.6
100°	107.3	114.2	116.6	116.6	115.7
102.5°	142.9	148.1	151.4	152.3	151.4
105°	181.9	184.3	186.1	187.6	187.6
107.5°	220.5	224.2	224.2	224.7	220.5
110°	258.0	262.8	262.8	262.8	260.5

TEST NUMBER: P915183

CATALOG NUMBER: DFN2DIP-TR2F0-020D040US927-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	298.5	303.6	302.7	300.3	298.5
115°	338.3	343.3	341.7	340.8	338.3
117.5°	377.9	384.6	380.4	377.9	375.6
120°	417.9	424.5	417.9	417.9	415.1
122.5°	454.1	462.6	458.4	455.9	454.1
125°	492.2	499.7	497.3	494.6	493.7
127.5°	529.3	538.7	535.4	531.7	529.3
130°	564.0	575.0	573.5	571.6	568.3
132.5°	603.0	611.5	612.1	607.8	605.5
135°	636.6	645.9	647.8	646.8	644.4
137.5°	674.1	681.6	683.1	682.5	678.9
140°	706.9	714.5	718.7	718.7	715.4
142.5°	740.8	748.4	750.8	751.7	748.4
145°	772.9	778.9	783.7	784.7	781.3
147.5°	801.5	809.1	812.7	814.2	810.9
150°	831.2	836.3	839.6	842.3	839.6
152.5°	857.5	862.5	866.8	870.1	866.8
155°	883.7	886.1	888.8	893.1	890.3
157.5°	906.4	908.2	909.7	915.8	911.5
160°	926.6	928.4	929.3	934.5	930.8
162.5°	945.3	945.3	946.3	952.0	947.8
165°	961.4	960.4	960.4	966.5	962.3
167.5°	975.9	973.1	973.1	979.2	974.9
170°	986.7	984.3	983.4	989.4	984.3
172.5°	994.3	991.9	990.9	997.0	991.9
175°	1000.4	997.9	996.1	1002.1	997.0
177.5°	1003.7	1001.2	999.4	1004.6	999.4
180°	1002.1	1002.1	1002.1	1002.1	1002.1

TEST NUMBER: P915183

CATALOG NUMBER: DFN2DIP-TR2F0-020D040US927-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.43	7.14	7.53	8.23	9.73	2.41	3.12	3.51	4.21	5.72
	3H	8.08	8.71	9.18	9.81	11.33	3.58	4.21	4.69	5.31	6.83
	4H	8.66	9.26	9.78	10.36	11.89	4.01	4.61	5.13	5.71	7.24
	6H	9.06	9.61	10.19	10.72	12.25	4.31	4.86	5.44	5.97	7.51
	8H	9.17	9.70	10.30	10.82	12.35	4.39	4.92	5.52	6.04	7.57
	12H	9.22	9.72	10.35	10.83	12.38	4.42	4.92	5.56	6.04	7.59
4H	2H	6.43	7.03	7.56	8.13	9.66	2.98	3.58	4.11	4.68	6.21
	3H	8.22	8.72	9.35	9.85	11.39	4.30	4.80	5.43	5.93	7.47
	4H	8.89	9.35	10.03	10.47	12.02	4.83	5.29	5.97	6.41	7.97
	6H	9.38	9.77	10.52	10.91	12.46	5.23	5.62	6.37	6.76	8.31
	8H	9.54	9.90	10.68	11.03	12.60	5.34	5.71	6.48	6.84	8.41
	12H	9.61	9.94	10.77	11.09	12.66	5.39	5.73	6.55	6.87	8.44
8H	4H	8.85	9.21	9.99	10.34	11.91	5.09	5.45	6.23	6.59	8.15
	6H	9.38	9.68	10.54	10.86	12.42	5.58	5.88	6.74	7.06	8.62
	8H	9.58	9.85	10.75	11.00	12.58	5.76	6.02	6.92	7.18	8.76
	12H	9.70	9.93	10.87	11.08	12.70	5.86	6.09	7.03	7.24	8.86
12H	4H	8.79	9.12	9.95	10.27	11.84	5.08	5.41	6.24	6.56	8.13
	6H	9.36	9.62	10.52	10.77	12.36	5.62	5.89	6.79	7.04	8.62
	8H	9.55	9.78	10.72	10.94	12.55	5.81	6.04	6.98	7.20	8.81

END OF REPORT