

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P925842

Luminaire Tested: DFN2DIP-SQ4F0-080D080US950-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P925842
REPORT IS A COMBINATION OF REPORTS P900100 AND P896915
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-080D080US950-RLLFLL
Description: 4 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 13241.5 lumens
Efficiency: N/A
Efficacy: 101.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 130.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9954
Total Harmonic Distortion (THDi): 0.076
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P925842

CATALOG NUMBER: DFN2DIP-SQ4F0-080D080US950-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P925842

CATALOG NUMBER: DFN2DIP-SQ4F0-080D080US950-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83	68	68	68	55	55	55
1	98	94	90	87	90	87	84	81	73	71	69	61	59	58	50	49	48
2	90	83	77	72	82	76	71	67	65	61	58	54	51	49	44	42	41
3	82	73	66	60	75	68	61	57	58	53	49	48	45	42	40	37	35
4	75	65	57	51	69	60	54	48	51	46	42	43	40	36	36	33	31
5	69	58	50	44	64	54	47	42	46	41	37	39	35	32	32	29	27
6	64	52	44	39	59	49	42	37	42	36	32	35	31	28	30	26	24
7	59	47	40	34	55	44	37	32	38	33	29	32	28	25	27	24	22
8	55	43	36	30	51	40	33	29	35	29	26	30	26	23	25	22	20
9	51	39	32	27	47	37	30	26	32	27	23	27	23	20	23	20	18
10	48	36	29	24	44	34	28	23	30	24	21	25	21	19	22	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2213	2213	2213
5°	2217	2179	2193
10°	2195	2136	2122
15°	2165	2066	2012
20°	2125	1969	1877
25°	2084	1860	1747
30°	2029	1749	1582
35°	1975	1629	1436
40°	1920	1505	1270
45°	1856	1367	1119
50°	1790	1228	971
55°	1722	1079	829
60°	1642	924	683
65°	1550	765	615
70°	1439	618	558
75°	1300	546	509
80°	1098	459	443
85°	765	309	338

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 1902 cd/sqm

TEST NUMBER: P925842

CATALOG NUMBER: DFN2DIP-SQ4F0-080D080US950-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	295.6	2.2
10°-20°	811.5	6.1
20°-30°	1139.4	8.6
30°-40°	1242.0	9.4
40°-50°	1141.5	8.6
50°-60°	896.5	6.8
60°-70°	583.5	4.4
70°-80°	300.4	2.3
80°-90°	83.5	0.6
90°-100°	149.4	1.1
100°-110°	474.6	3.6
110°-120°	812.1	6.1
120°-130°	1068.1	8.1
130°-140°	1198.9	9.1
140°-150°	1175.6	8.9
150°-160°	986.2	7.4
160°-170°	654.0	4.9
170°-180°	228.6	1.7
0°-30°	2246.6	17.0
0°-40°	3488.6	26.3
0°-60°	5526.6	41.7
0°-90°	6494.1	49.0
90°-120°	1436.1	10.8
90°-150°	4878.6	36.8
90°-180°	6747.0	51.0
0°-180°	13241.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3154	3154	3154	3154	3154	
5°	3154	3140	3103	3128	3120	299
15°	3000	2969	2872	2818	2789	845
25°	2723	2632	2444	2327	2284	1252
35°	2347	2201	1950	1770	1707	1469
45°	1918	1727	1427	1224	1156	1481
55°	1459	1236	928	756	702	1303
65°	985	754	497	400	391	976
75°	525	325	228	208	206	555
85°	123	63	54	54	54	141
90°	2	26	71	67	69	13
95°	106	127	130	130	127	118
105°	438	444	448	452	452	462
115°	815	827	823	821	815	806
125°	1185	1204	1198	1191	1189	1059
135°	1533	1556	1560	1558	1552	1185
145°	1861	1876	1888	1890	1882	1163
155°	2128	2134	2141	2151	2144	980
165°	2316	2313	2313	2328	2318	653
175°	2409	2404	2399	2414	2401	229
180°	2414	2414	2414	2414	2414	

TEST NUMBER: P925842

CATALOG NUMBER: DFN2DIP-SQ4F0-080D080US950-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3154.3	3154.3	3154.3	3154.3	3154.3
2.5°	3168.5	3154.3	3122.8	3151.5	3145.8
5°	3154.3	3140.1	3102.8	3128.5	3120.1
7.5°	3128.5	3111.6	3071.6	3082.9	3068.5
10°	3094.3	3074.4	3017.4	3008.6	2991.6
12.5°	3051.7	3025.9	2948.6	2931.6	2900.2
15°	3000.1	2968.7	2871.7	2817.5	2789.0
17.5°	2940.1	2894.4	2774.5	2711.8	2666.0
20°	2871.7	2814.5	2671.9	2600.7	2537.6
22.5°	2797.5	2731.8	2566.2	2469.2	2426.5
25°	2723.3	2631.9	2443.5	2326.6	2283.6
27.5°	2634.9	2537.6	2329.3	2195.2	2129.4
30°	2540.7	2431.9	2203.6	2058.3	1981.0
32.5°	2449.2	2317.8	2084.0	1912.6	1841.1
35°	2346.6	2200.9	1949.8	1770.0	1706.9
37.5°	2246.6	2089.5	1824.1	1627.0	1555.8
40°	2141.0	1969.8	1692.7	1490.1	1415.8
42.5°	2032.5	1849.9	1561.5	1350.2	1278.9
45°	1918.3	1726.9	1427.4	1224.5	1156.1
47.5°	1809.9	1607.3	1299.0	1096.1	1033.4
50°	1689.9	1487.4	1173.3	976.1	916.4
52.5°	1572.8	1358.6	1053.3	865.0	810.8
55°	1458.6	1236.0	927.7	756.5	702.3
57.5°	1341.7	1113.3	816.5	656.6	610.8
60°	1221.7	993.4	699.3	553.9	508.2
62.5°	1104.8	876.4	599.4	462.5	439.8
65°	984.9	753.5	496.7	399.8	390.9
67.5°	870.7	639.4	399.8	351.0	342.6
70°	750.8	528.2	331.0	302.5	291.1
72.5°	636.6	425.2	276.9	254.1	248.3
75°	525.2	325.3	228.4	208.4	205.7
77.5°	414.0	231.1	179.9	168.4	162.7
80°	311.0	165.7	136.9	125.6	125.6
82.5°	216.8	111.4	94.2	88.4	88.4
85°	122.7	62.7	54.2	54.2	54.2
87.5°	45.7	22.7	22.7	20.0	20.0
90°	2.2	26.2	71.4	67.0	69.2
92.5°	45.1	61.2	63.3	65.4	65.4
95°	106.3	126.6	130.2	130.2	126.6
97.5°	176.9	195.8	203.8	203.8	203.8
100°	258.3	275.0	280.9	280.9	278.7
102.5°	344.2	356.6	364.5	366.7	364.5
105°	438.1	443.9	448.3	451.9	451.9
107.5°	531.2	540.0	540.0	541.4	531.2
110°	621.4	633.1	633.1	633.1	627.3

TEST NUMBER: P925842

CATALOG NUMBER: DFN2DIP-SQ4F0-080D080US950-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	718.9	731.3	729.1	723.3	718.9
115°	815.0	826.6	823.0	820.8	815.0
117.5°	910.3	926.3	916.1	910.3	904.5
120°	1006.4	1022.4	1006.4	1006.4	999.8
122.5°	1093.7	1114.1	1103.9	1098.1	1093.7
125°	1185.3	1203.6	1197.7	1191.2	1189.1
127.5°	1274.9	1297.4	1289.4	1280.7	1274.9
130°	1358.6	1384.7	1381.1	1376.8	1368.8
132.5°	1452.5	1472.8	1474.3	1464.1	1458.3
135°	1533.2	1555.8	1560.2	1558.0	1552.2
137.5°	1623.4	1641.6	1645.3	1643.8	1635.1
140°	1702.8	1720.9	1731.1	1731.1	1723.1
142.5°	1784.3	1802.5	1808.3	1810.5	1802.5
145°	1861.4	1875.9	1887.6	1889.8	1881.8
147.5°	1930.5	1948.7	1957.4	1961.1	1953.1
150°	2001.9	2014.2	2022.2	2028.8	2022.2
152.5°	2065.1	2077.5	2087.7	2095.7	2087.7
155°	2128.5	2134.3	2140.9	2151.0	2144.5
157.5°	2183.0	2187.4	2191.1	2205.6	2195.4
160°	2231.8	2236.2	2238.4	2250.7	2242.0
162.5°	2276.9	2276.9	2279.1	2292.9	2282.7
165°	2315.5	2313.3	2313.3	2327.9	2317.6
167.5°	2350.4	2343.9	2343.9	2358.4	2348.2
170°	2376.6	2370.8	2368.6	2383.2	2370.8
172.5°	2394.8	2389.0	2386.8	2401.3	2389.0
175°	2409.3	2403.5	2399.1	2413.7	2401.3
177.5°	2417.3	2411.5	2407.1	2419.5	2407.1
180°	2413.7	2413.7	2413.7	2413.7	2413.7

TEST NUMBER: P925842

CATALOG NUMBER: DFN2DIP-SQ4F0-080D080US950-RLFL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.83	10.65	10.80	11.63	12.92	5.79	6.61	6.76	7.59	8.88
	3H	11.51	12.24	12.49	13.24	14.54	6.98	7.71	7.96	8.70	10.01
	4H	12.12	12.82	13.12	13.81	15.13	7.43	8.12	8.42	9.12	10.44
	6H	12.55	13.19	13.55	14.18	15.51	7.75	8.39	8.76	9.39	10.72
	8H	12.67	13.28	13.69	14.30	15.62	7.84	8.45	8.85	9.46	10.79
	12H	12.74	13.32	13.75	14.32	15.68	7.88	8.46	8.90	9.47	10.82
4H	2H	9.85	10.54	10.85	11.53	12.85	6.39	7.08	7.39	8.07	9.39
	3H	11.68	12.26	12.69	13.28	14.61	7.74	8.31	8.75	9.34	10.67
	4H	12.37	12.90	13.39	13.92	15.27	8.28	8.81	9.30	9.83	11.18
	6H	12.89	13.35	13.92	14.39	15.74	8.70	9.16	9.73	10.20	11.55
	8H	13.07	13.49	14.10	14.53	15.89	8.83	9.26	9.86	10.29	11.65
	12H	13.17	13.55	14.22	14.60	15.97	8.90	9.28	9.95	10.33	11.70
8H	4H	12.34	12.76	13.37	13.80	15.16	8.57	8.99	9.60	10.02	11.39
	6H	12.91	13.26	13.97	14.34	15.70	9.09	9.44	10.14	10.51	11.87
	8H	13.13	13.44	14.19	14.50	15.88	9.28	9.59	10.34	10.64	12.03
	12H	13.27	13.54	14.34	14.60	16.02	9.40	9.67	10.46	10.72	12.15
12H	4H	12.29	12.68	13.34	13.72	15.09	8.57	8.95	9.62	10.00	11.37
	6H	12.89	13.19	13.95	14.25	15.64	9.14	9.44	10.20	10.50	11.89
	8H	13.11	13.38	14.18	14.43	15.86	9.35	9.62	10.41	10.67	12.10

END OF REPORT