

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P925866

Luminaire Tested: DFN2DIP-SQ4F0-080D160US950-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P925866
REPORT IS A COMBINATION OF REPORTS P900208 AND P896915
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-080D160US950-RLLFLL
Description: 4 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 19996.8 lumens
Efficiency: N/A
Efficacy: 103.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 193.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9954
Total Harmonic Distortion (THDi): 0.076
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P925866

CATALOG NUMBER: DFN2DIP-SQ4F0-080D160US950-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P925866

CATALOG NUMBER: DFN2DIP-SQ4F0-080D160US950-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	93	93	93	93	74	74	74	56	56	56	40	40	40
1	94	90	86	83	85	81	78	75	65	63	61	50	48	47	36	35	34
2	86	79	73	68	77	71	67	62	57	54	51	44	42	40	32	31	29
3	79	70	63	57	71	63	57	52	51	46	43	39	36	34	29	27	25
4	72	62	54	49	65	56	50	45	45	41	37	35	32	29	26	24	22
5	66	55	47	42	59	50	43	38	40	36	32	32	28	26	23	21	19
6	61	49	42	36	55	45	38	33	36	32	28	29	25	23	21	19	17
7	56	45	37	32	51	41	34	29	33	28	25	26	23	20	19	17	15
8	52	40	33	28	47	37	30	26	30	25	22	24	20	18	18	16	14
9	49	37	30	25	44	34	27	23	28	23	20	22	19	16	17	14	13
10	45	34	27	22	41	31	25	21	25	21	18	20	17	15	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2213	2213	2213
5°	2217	2179	2193
10°	2195	2136	2122
15°	2165	2066	2012
20°	2125	1969	1877
25°	2084	1860	1747
30°	2029	1749	1582
35°	1975	1629	1436
40°	1920	1505	1270
45°	1856	1367	1119
50°	1790	1228	971
55°	1722	1079	829
60°	1642	924	683
65°	1550	765	615
70°	1439	618	558
75°	1300	546	509
80°	1098	459	443
85°	765	309	338

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 3798 cd/sqm

TEST NUMBER: P925866

CATALOG NUMBER: DFN2DIP-SQ4F0-080D160US950-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	295.6	1.5
10°-20°	811.5	4.1
20°-30°	1139.4	5.7
30°-40°	1242.0	6.2
40°-50°	1141.5	5.7
50°-60°	896.5	4.5
60°-70°	583.5	2.9
70°-80°	300.4	1.5
80°-90°	90.4	0.5
90°-100°	298.7	1.5
100°-110°	949.2	4.7
110°-120°	1624.4	8.1
120°-130°	2136.3	10.7
130°-140°	2397.9	12.0
140°-150°	2351.4	11.8
150°-160°	1972.5	9.9
160°-170°	1308.1	6.5
170°-180°	457.2	2.3
0°-30°	2246.6	11.2
0°-40°	3488.6	17.4
0°-60°	5526.6	27.6
0°-90°	6500.9	32.5
90°-120°	2872.3	14.4
90°-150°	9757.9	48.8
90°-180°	13496.0	67.5
0°-180°	19996.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3154	3154	3154	3154	3154	
5°	3154	3140	3103	3128	3120	299
15°	3000	2969	2872	2818	2789	845
25°	2723	2632	2444	2327	2284	1252
35°	2347	2201	1950	1770	1707	1469
45°	1918	1727	1427	1224	1156	1481
55°	1459	1236	928	756	702	1303
65°	985	754	497	400	391	976
75°	525	325	228	208	206	555
85°	123	63	54	54	54	141
90°	4	52	143	134	138	20
95°	212	253	260	260	253	236
105°	876	888	897	904	904	925
115°	1630	1653	1646	1642	1630	1612
125°	2371	2407	2396	2383	2378	2119
135°	3067	3112	3120	3116	3104	2370
145°	3723	3752	3776	3780	3764	2326
155°	4257	4269	4282	4302	4289	1960
165°	4631	4627	4627	4656	4636	1306
175°	4819	4807	4799	4828	4803	458
180°	4828	4828	4828	4828	4828	

TEST NUMBER: P925866

CATALOG NUMBER: DFN2DIP-SQ4F0-080D160US950-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3154.3	3154.3	3154.3	3154.3	3154.3
2.5°	3168.5	3154.3	3122.8	3151.5	3145.8
5°	3154.3	3140.1	3102.8	3128.5	3120.1
7.5°	3128.5	3111.6	3071.6	3082.9	3068.5
10°	3094.3	3074.4	3017.4	3008.6	2991.6
12.5°	3051.7	3025.9	2948.6	2931.6	2900.2
15°	3000.1	2968.7	2871.7	2817.5	2789.0
17.5°	2940.1	2894.4	2774.5	2711.8	2666.0
20°	2871.7	2814.5	2671.9	2600.7	2537.6
22.5°	2797.5	2731.8	2566.2	2469.2	2426.5
25°	2723.3	2631.9	2443.5	2326.6	2283.6
27.5°	2634.9	2537.6	2329.3	2195.2	2129.4
30°	2540.7	2431.9	2203.6	2058.3	1981.0
32.5°	2449.2	2317.8	2084.0	1912.6	1841.1
35°	2346.6	2200.9	1949.8	1770.0	1706.9
37.5°	2246.6	2089.5	1824.1	1627.0	1555.8
40°	2141.0	1969.8	1692.7	1490.1	1415.8
42.5°	2032.5	1849.9	1561.5	1350.2	1278.9
45°	1918.3	1726.9	1427.4	1224.5	1156.1
47.5°	1809.9	1607.3	1299.0	1096.1	1033.4
50°	1689.9	1487.4	1173.3	976.1	916.4
52.5°	1572.8	1358.6	1053.3	865.0	810.8
55°	1458.6	1236.0	927.7	756.5	702.3
57.5°	1341.7	1113.3	816.5	656.6	610.8
60°	1221.7	993.4	699.3	553.9	508.2
62.5°	1104.8	876.4	599.4	462.5	439.8
65°	984.9	753.5	496.7	399.8	390.9
67.5°	870.7	639.4	399.8	351.0	342.6
70°	750.8	528.2	331.0	302.5	291.1
72.5°	636.6	425.2	276.9	254.1	248.3
75°	525.2	325.3	228.4	208.4	205.7
77.5°	414.0	231.1	179.9	168.4	162.7
80°	311.0	165.7	136.9	125.6	125.6
82.5°	216.8	111.4	94.2	88.4	88.4
85°	122.7	62.7	54.2	54.2	54.2
87.5°	45.7	22.7	22.7	20.0	20.0
90°	4.4	52.4	142.6	133.9	138.2
92.5°	90.2	122.3	126.6	131.0	131.0
95°	212.5	253.3	260.5	260.5	253.3
97.5°	353.6	391.5	407.5	407.5	407.5
100°	516.7	550.2	561.8	561.8	557.4
102.5°	688.4	713.2	729.1	733.5	729.1
105°	876.2	887.8	896.6	903.8	903.8
107.5°	1062.5	1079.9	1079.9	1082.9	1062.5
110°	1243.0	1266.2	1266.2	1266.2	1254.6

TEST NUMBER: P925866

CATALOG NUMBER: DFN2DIP-SQ4F0-080D160US950-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1438.0	1462.8	1458.4	1446.7	1438.0
115°	1630.1	1653.4	1646.1	1641.7	1630.1
117.5°	1820.8	1852.8	1832.4	1820.8	1809.2
120°	2012.9	2044.9	2012.9	2012.9	1999.8
122.5°	2187.5	2228.4	2207.9	2196.3	2187.5
125°	2371.0	2407.3	2395.7	2382.6	2378.2
127.5°	2549.9	2595.1	2579.0	2561.6	2549.9
130°	2717.4	2769.7	2762.5	2753.7	2737.7
132.5°	2905.1	2945.9	2948.7	2928.4	2916.8
135°	3066.6	3111.8	3120.5	3116.1	3104.5
137.5°	3247.1	3283.5	3290.8	3287.9	3270.4
140°	3405.8	3442.1	3462.5	3462.5	3446.5
142.5°	3568.8	3605.2	3616.8	3621.2	3605.2
145°	3723.1	3752.2	3775.5	3779.8	3763.8
147.5°	3861.3	3897.8	3915.2	3922.5	3906.4
150°	4003.9	4028.7	4044.8	4057.8	4044.8
152.5°	4130.6	4155.3	4175.8	4191.7	4175.8
155°	4257.2	4268.9	4281.9	4302.3	4289.3
157.5°	4366.4	4375.1	4382.4	4411.5	4391.2
160°	4463.9	4472.6	4477.0	4501.7	4484.3
162.5°	4554.1	4554.1	4558.5	4586.2	4565.7
165°	4631.3	4626.9	4626.9	4656.0	4635.7
167.5°	4701.1	4688.1	4688.1	4717.1	4696.7
170°	4753.5	4741.9	4737.6	4766.7	4741.9
172.5°	4789.9	4778.3	4773.9	4803.0	4778.3
175°	4819.0	4807.4	4798.6	4827.8	4803.0
177.5°	4835.1	4823.4	4814.6	4839.5	4814.6
180°	4827.8	4827.8	4827.8	4827.8	4827.8

TEST NUMBER: P925866

CATALOG NUMBER: DFN2DIP-SQ4F0-080D160US950-RLFL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.02	8.72	9.12	9.82	11.32	3.98	4.68	5.08	5.78	7.28
	3H	9.69	10.32	10.80	11.42	12.94	5.16	5.79	6.27	6.89	8.41
	4H	10.30	10.89	11.41	12.00	13.52	5.60	6.20	6.72	7.30	8.83
	6H	10.72	11.27	11.84	12.37	13.91	5.92	6.47	7.05	7.57	9.11
	8H	10.84	11.36	11.97	12.48	14.01	6.01	6.53	7.14	7.65	9.18
	12H	10.90	11.40	12.03	12.51	14.06	6.05	6.54	7.18	7.66	9.21
4H	2H	8.02	8.62	9.15	9.72	11.25	4.56	5.16	5.69	6.26	7.79
	3H	9.84	10.34	10.97	11.47	13.01	5.90	6.40	7.03	7.53	9.07
	4H	10.53	10.99	11.67	12.11	13.67	6.44	6.90	7.58	8.02	9.58
	6H	11.05	11.44	12.19	12.58	14.13	6.86	7.25	8.00	8.39	9.94
	8H	11.22	11.59	12.36	12.72	14.29	6.98	7.35	8.12	8.48	10.05
	12H	11.31	11.64	12.47	12.79	14.36	7.04	7.38	8.20	8.52	10.09
8H	4H	10.49	10.86	11.63	11.99	13.56	6.72	7.08	7.86	8.22	9.78
	6H	11.06	11.36	12.22	12.54	14.10	7.23	7.53	8.39	8.71	10.27
	8H	11.28	11.54	12.44	12.70	14.28	7.42	7.69	8.59	8.84	10.42
	12H	11.41	11.65	12.58	12.80	14.41	7.54	7.77	8.71	8.92	10.54
12H	4H	10.44	10.77	11.60	11.91	13.49	6.72	7.05	7.87	8.19	9.76
	6H	11.03	11.30	12.20	12.45	14.03	7.28	7.55	8.45	8.70	10.28
	8H	11.25	11.48	12.42	12.63	14.25	7.49	7.72	8.66	8.87	10.49