

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P915218

Luminaire Tested: DFN2DIP-TR2F0-040D030US927-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P915218
REPORT IS A COMBINATION OF REPORTS P900236 AND P897145
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR2F0-040D030US927-RLLFLL
Description: 2 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4796.6 lumens
Efficiency: N/A
Efficacy: 83.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.04' x L: 2.36' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 57.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P915218

CATALOG NUMBER: DFN2DIP-TR2F0-040D030US927-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P915218

CATALOG NUMBER: DFN2DIP-TR2F0-040D030US927-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62
1	100	96	92	88	93	89	86	83	77	75	72	66	64	63	55	54	53
2	91	84	78	73	85	79	73	69	68	64	61	58	56	53	49	47	46
3	84	74	67	62	78	70	63	58	61	56	52	52	49	46	44	42	40
4	77	66	59	53	71	62	55	50	54	49	45	47	43	40	40	37	35
5	71	59	51	46	66	56	49	43	49	43	39	42	38	35	36	33	30
6	65	53	46	40	61	50	43	38	44	38	34	38	34	31	33	30	27
7	61	48	41	35	56	46	39	34	40	35	30	35	31	27	30	27	24
8	56	44	37	31	52	42	35	30	37	31	27	32	28	25	28	25	22
9	53	41	33	28	49	38	32	27	34	28	25	30	25	22	26	23	20
10	49	37	30	25	46	35	29	24	31	26	22	28	23	20	24	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2921	2921	2921
5°	2921	2868	2888
10°	2888	2805	2789
15°	2844	2706	2639
20°	2787	2573	2457
25°	2729	2424	2281
30°	2652	2272	2060
35°	2576	2109	1866
40°	2499	1941	1644
45°	2410	1756	1443
50°	2318	1569	1248
55°	2221	1371	1060
60°	2108	1165	868
65°	1978	956	775
70°	1821	761	694
75°	1622	658	622
80°	1337	534	525
85°	878	331	369

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2410 cd/sqm

TEST NUMBER: P915218

CATALOG NUMBER: DFN2DIP-TR2F0-040D030US927-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	122.7	2.6
10°-20°	336.9	7.0
20°-30°	473.1	9.9
30°-40°	515.7	10.8
40°-50°	473.9	9.9
50°-60°	372.2	7.8
60°-70°	242.3	5.1
70°-80°	124.7	2.6
80°-90°	34.0	0.7
90°-100°	46.5	1.0
100°-110°	147.8	3.1
110°-120°	252.9	5.3
120°-130°	332.6	6.9
130°-140°	373.3	7.8
140°-150°	366.1	7.6
150°-160°	307.1	6.4
160°-170°	203.7	4.2
170°-180°	71.2	1.5
0°-30°	932.7	19.4
0°-40°	1448.4	30.2
0°-60°	2294.6	47.8
0°-90°	2695.5	56.2
90°-120°	447.2	9.3
90°-150°	1519.2	31.7
90°-180°	2101.0	43.8
0°-180°	4796.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1310	1310	1310	1310	1310	
5°	1310	1304	1288	1299	1296	124
15°	1246	1233	1192	1170	1158	351
25°	1131	1093	1014	966	948	520
35°	974	914	810	735	709	610
45°	796	717	593	508	480	615
55°	606	513	385	314	292	541
65°	409	313	206	166	162	405
75°	218	135	95	86	85	231
85°	51	26	22	22	22	58
90°	1	8	22	21	22	5
95°	33	40	41	41	40	37
105°	136	138	140	141	141	144
115°	254	257	256	256	254	251
125°	369	375	373	371	370	330
135°	477	484	486	485	483	369
145°	580	584	588	588	586	362
155°	663	665	667	670	668	305
165°	721	720	720	725	722	203
175°	750	748	747	752	748	71
180°	752	752	752	752	752	

TEST NUMBER: P915218

CATALOG NUMBER: DFN2DIP-TR2F0-040D030US927-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1309.6	1309.6	1309.6	1309.6	1309.6
2.5°	1315.6	1309.6	1296.6	1308.5	1306.1
5°	1309.6	1303.7	1288.2	1298.9	1295.5
7.5°	1298.9	1291.9	1275.3	1279.9	1274.1
10°	1284.8	1276.4	1252.8	1249.1	1242.1
12.5°	1267.0	1256.3	1224.2	1217.2	1204.1
15°	1245.6	1232.6	1192.3	1169.8	1158.0
17.5°	1220.8	1201.7	1151.9	1125.9	1106.9
20°	1192.3	1168.5	1109.3	1079.7	1053.6
22.5°	1161.5	1134.2	1065.4	1025.2	1007.5
25°	1130.7	1092.7	1014.5	966.0	948.1
27.5°	1094.0	1053.6	967.1	911.4	884.1
30°	1054.9	1009.7	914.9	854.5	822.5
32.5°	1016.9	962.3	865.2	794.1	764.4
35°	974.3	913.8	809.5	734.8	708.7
37.5°	932.8	867.5	757.3	675.5	645.9
40°	888.9	817.8	702.8	618.7	587.9
42.5°	843.8	768.0	648.3	560.5	531.0
45°	796.5	717.0	592.6	508.4	480.0
47.5°	751.5	667.3	539.3	455.1	429.0
50°	701.6	617.5	487.1	405.3	380.5
52.5°	653.0	564.1	437.4	359.1	336.6
55°	605.6	513.2	385.2	314.1	291.6
57.5°	557.1	462.2	339.0	272.6	253.7
60°	507.2	412.4	290.3	230.0	211.0
62.5°	458.8	363.9	248.8	192.0	182.6
65°	408.9	312.8	206.2	166.0	162.3
67.5°	361.6	265.5	166.0	145.8	142.2
70°	311.7	219.3	137.4	125.6	120.8
72.5°	264.4	176.6	114.9	105.5	103.1
75°	218.0	135.1	94.8	86.5	85.4
77.5°	171.9	95.9	74.7	69.9	67.5
80°	129.1	68.8	56.8	52.2	52.2
82.5°	90.1	46.3	39.1	36.7	36.7
85°	50.9	26.1	22.5	22.5	22.5
87.5°	19.0	9.4	9.4	8.3	8.3
90°	0.7	8.2	22.2	20.8	21.5
92.5°	14.0	19.0	19.7	20.4	20.4
95°	33.1	39.5	40.6	40.6	39.5
97.5°	55.1	60.9	63.5	63.5	63.5
100°	80.4	85.6	87.5	87.5	86.8
102.5°	107.2	111.1	113.5	114.2	113.5
105°	136.4	138.2	139.6	140.7	140.7
107.5°	165.4	168.1	168.1	168.6	165.4
110°	193.5	197.2	197.2	197.2	195.4

TEST NUMBER: P915218

CATALOG NUMBER: DFN2DIP-TR2F0-040D030US927-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	223.9	227.8	227.0	225.2	223.9
115°	253.8	257.4	256.3	255.6	253.8
117.5°	283.4	288.4	285.3	283.4	281.6
120°	313.4	318.4	313.4	313.4	311.3
122.5°	340.6	346.9	343.7	341.9	340.6
125°	369.2	374.8	373.0	370.9	370.3
127.5°	397.0	404.0	401.6	398.8	397.0
130°	423.0	431.2	430.1	428.7	426.2
132.5°	452.3	458.6	459.1	455.9	454.1
135°	477.4	484.4	485.8	485.1	483.3
137.5°	505.5	511.2	512.3	511.9	509.1
140°	530.2	535.9	539.1	539.1	536.5
142.5°	555.6	561.3	563.1	563.8	561.3
145°	579.6	584.2	587.8	588.4	586.0
147.5°	601.2	606.8	609.5	610.7	608.2
150°	623.4	627.2	629.7	631.8	629.7
152.5°	643.1	646.9	650.1	652.6	650.1
155°	662.8	664.6	666.6	669.8	667.8
157.5°	679.8	681.1	682.3	686.8	683.7
160°	695.0	696.3	697.0	700.8	698.1
162.5°	709.0	709.0	709.7	714.0	710.8
165°	721.0	720.3	720.3	724.8	721.7
167.5°	731.9	729.8	729.8	734.4	731.2
170°	740.1	738.2	737.6	742.1	738.2
172.5°	745.7	743.9	743.2	747.7	743.9
175°	750.3	748.5	747.1	751.6	747.7
177.5°	752.7	750.9	749.6	753.4	749.6
180°	751.6	751.6	751.6	751.6	751.6

TEST NUMBER: P915218

CATALOG NUMBER: DFN2DIP-TR2F0-040D030US927-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.30	12.19	12.21	13.11	14.29	7.28	8.17	8.19	9.09	10.27
	3H	12.96	13.75	13.88	14.68	15.89	8.46	9.25	9.38	10.18	11.39
	4H	13.55	14.30	14.49	15.24	16.46	8.90	9.65	9.84	10.59	11.80
	6H	13.96	14.65	14.91	15.59	16.82	9.21	9.90	10.16	10.84	12.07
	8H	14.08	14.73	15.03	15.69	16.92	9.30	9.95	10.25	10.91	12.14
	12H	14.13	14.75	15.09	15.71	16.96	9.34	9.96	10.29	10.91	12.16
4H	2H	11.32	12.07	12.26	13.01	14.22	7.87	8.62	8.81	9.56	10.77
	3H	13.13	13.75	14.08	14.72	15.95	9.21	9.83	10.16	10.80	12.03
	4H	13.81	14.37	14.77	15.33	16.59	9.75	10.31	10.71	11.27	12.53
	6H	14.30	14.79	15.28	15.77	17.03	10.15	10.64	11.12	11.62	12.88
	8H	14.46	14.92	15.44	15.90	17.17	10.27	10.73	11.25	11.70	12.97
	12H	14.55	14.96	15.54	15.95	17.23	10.33	10.74	11.32	11.73	13.01
8H	4H	13.77	14.23	14.75	15.21	16.48	10.02	10.47	10.99	11.45	12.72
	6H	14.32	14.69	15.32	15.71	16.98	10.51	10.89	11.51	11.91	13.18
	8H	14.52	14.85	15.53	15.86	17.14	10.69	11.02	11.70	12.03	13.32
	12H	14.64	14.93	15.65	15.94	17.27	10.80	11.09	11.81	12.09	13.43
12H	4H	13.73	14.14	14.72	15.13	16.41	10.02	10.43	11.01	11.42	12.70
	6H	14.29	14.62	15.30	15.63	16.92	10.56	10.89	11.57	11.90	13.18
	8H	14.50	14.79	15.51	15.79	17.12	10.75	11.05	11.77	12.05	13.38