

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P925879

Luminaire Tested: DFN2DIP-SQ4F0-090D080US950-RLLONL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P925879  
REPORT IS A COMBINATION OF REPORTS P901622 AND P898471  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-SQ4F0-090D080US950-RLLONL  
Description: 4 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 14853.8 lumens  
Efficiency: N/A  
Efficacy: 104.5 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')  
CIE Type: General Diffuse  
  
Input Watts (W): 142.2  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.983  
Total Harmonic Distortion (THDi): 0.073  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P925879  
CATALOG NUMBER: DFN2DIP-SQ4F0-090D080US950-RLLONL

### Luminous Intensity Polar Plot





TEST NUMBER: P925879  
 CATALOG NUMBER: DFN2DIP-SQ4F0-090D080US950-RLLONL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	55	55	55	49			49
1	98	94	90	87	90	87	84	81	73	71	69	61	59	58	50	49	48	42			42
2	90	83	77	72	82	76	71	67	65	61	58	54	52	49	44	42	41	36			36
3	82	73	66	60	75	68	62	57	58	53	49	48	45	42	40	37	35	31			31
4	75	65	57	51	69	60	54	48	51	46	42	43	40	37	36	33	31	27			27
5	69	58	50	44	64	54	47	42	46	41	37	39	35	32	32	30	27	24			24
6	64	52	44	39	59	49	42	37	42	36	32	36	31	28	30	27	24	21			21
7	59	47	40	34	55	44	37	32	38	33	29	32	28	25	27	24	22	19			19
8	55	43	36	30	51	40	33	29	35	29	26	30	26	23	25	22	20	17			17
9	51	39	32	27	47	37	30	26	32	27	23	28	23	20	23	20	18	16			16
10	48	36	29	24	44	34	28	23	30	24	21	25	21	19	22	18	16	14			14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	2490	2490	2490
5°	2494	2451	2467
10°	2469	2403	2387
15°	2435	2324	2264
20°	2390	2215	2112
25°	2344	2093	1966
30°	2282	1968	1779
35°	2222	1833	1616
40°	2160	1693	1428
45°	2088	1538	1258
50°	2014	1381	1092
55°	1937	1214	933
60°	1847	1039	768
65°	1744	861	692
70°	1619	695	628
75°	1462	614	573
80°	1235	517	499
85°	859	348	380

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 2088 cd/sqm



TEST NUMBER: P925879

CATALOG NUMBER: DFN2DIP-SQ4F0-090D080US950-RLLONL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	332.6	2.2
10°-20°	913.0	6.1
20°-30°	1281.8	8.6
30°-40°	1397.3	9.4
40°-50°	1284.2	8.6
50°-60°	1008.6	6.8
60°-70°	656.5	4.4
70°-80°	337.9	2.3
80°-90°	90.8	0.6
90°-100°	84.9	0.6
100°-110°	316.6	2.1
110°-120°	839.7	5.7
120°-130°	1392.7	9.4
130°-140°	1479.4	10.0
140°-150°	1374.9	9.3
150°-160°	1105.4	7.4
160°-170°	712.3	4.8
170°-180°	245.2	1.7
0°-30°	2527.4	17.0
0°-40°	3924.6	26.4
0°-60°	6217.4	41.9
0°-90°	7302.7	49.2
90°-120°	1241.3	8.4
90°-150°	5488.3	36.9
90°-180°	7551.0	50.8
0°-180°	14853.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	3549	3549	3549	3549	3549	
5°	3549	3533	3491	3520	3510	336
15°	3375	3340	3231	3170	3138	951
25°	3064	2961	2749	2617	2569	1409
35°	2640	2476	2194	1991	1920	1652
45°	2158	1943	1606	1378	1300	1667
55°	1641	1390	1044	851	790	1466
65°	1108	848	559	450	440	1099
75°	591	366	257	234	231	625
85°	138	70	61	61	61	158
90°	2	22	37	47	50	14
95°	121	60	73	82	80	143
105°	567	623	114	134	142	605
115°	1072	1103	1150	287	153	1055
125°	1515	1540	1575	1588	1594	1351
135°	1875	1905	1922	1940	1936	1448
145°	2175	2173	2205	2218	2208	1360
155°	2395	2378	2401	2412	2397	1104
165°	2524	2512	2518	2531	2518	713
175°	2581	2568	2572	2585	2566	246
180°	2576	2576	2576	2576	2576	



TEST NUMBER: P925879

CATALOG NUMBER: DFN2DIP-SQ4F0-090D080US950-RLONL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	3548.6	3548.6	3548.6	3548.6	3548.6
2.5°	3564.6	3548.6	3513.1	3545.5	3539.1
5°	3548.6	3532.6	3490.7	3519.6	3510.1
7.5°	3519.6	3500.5	3455.6	3468.2	3452.1
10°	3481.1	3458.6	3394.6	3384.7	3365.6
12.5°	3433.1	3404.2	3317.2	3298.2	3262.7
15°	3375.2	3339.8	3230.7	3169.7	3137.7
17.5°	3307.7	3256.3	3121.3	3050.8	2999.4
20°	3230.7	3166.3	3005.8	2925.7	2854.8
22.5°	3147.2	3073.3	2886.9	2777.9	2729.9
25°	3063.8	2960.8	2749.0	2617.4	2569.0
27.5°	2964.3	2854.8	2620.4	2469.5	2395.6
30°	2858.3	2736.0	2479.1	2315.5	2228.6
32.5°	2755.3	2607.5	2344.5	2151.7	2071.2
35°	2639.9	2476.0	2193.5	1991.2	1920.3
37.5°	2527.4	2350.7	2052.1	1830.3	1750.3
40°	2408.6	2216.0	1904.3	1676.4	1592.9
42.5°	2286.5	2081.2	1756.7	1519.0	1438.8
45°	2158.1	1942.8	1605.8	1377.5	1300.5
47.5°	2036.1	1808.2	1461.3	1233.0	1162.5
50°	1901.2	1673.2	1320.0	1098.1	1031.0
52.5°	1769.4	1528.5	1185.1	973.1	912.1
55°	1640.9	1390.5	1043.6	851.2	790.1
57.5°	1509.4	1252.5	918.6	738.7	687.3
60°	1374.4	1117.5	786.8	623.2	571.7
62.5°	1243.0	986.1	674.3	520.3	494.7
65°	1108.0	847.7	558.8	449.7	439.9
67.5°	979.6	719.2	449.7	394.9	385.3
70°	844.7	594.2	372.4	340.4	327.4
72.5°	716.2	478.3	311.4	285.8	279.4
75°	590.8	366.0	256.9	234.4	231.3
77.5°	465.7	260.0	202.3	189.5	183.0
80°	349.9	186.4	154.0	141.4	141.4
82.5°	243.9	125.4	106.0	99.5	99.5
85°	137.9	70.5	61.0	61.0	61.0
87.5°	51.4	25.6	25.6	22.5	22.5
90°	1.8	22.3	37.2	46.7	50.3
92.5°	46.7	39.2	44.7	48.5	50.3
95°	121.1	59.5	72.6	82.1	80.1
97.5°	218.0	65.3	94.9	100.7	102.5
100°	330.0	74.6	106.3	121.1	124.8
102.5°	452.9	449.2	110.0	130.3	136.1
105°	566.6	622.6	113.7	134.1	141.7
107.5°	698.9	745.4	117.5	137.9	145.4
110°	825.8	864.7	326.3	139.9	147.2



TEST NUMBER: P925879

CATALOG NUMBER: DFN2DIP-SQ4F0-090D080US950-RLLONL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	945.0	978.4	946.8	143.4	149.2
115°	1071.6	1103.3	1150.0	287.1	152.9
117.5°	1181.6	1218.8	1250.7	984.0	495.8
120°	1304.7	1332.5	1366.2	1388.5	1136.9
122.5°	1408.9	1438.8	1476.2	1487.3	1489.3
125°	1515.1	1539.5	1574.9	1587.9	1593.5
127.5°	1612.1	1638.2	1666.4	1684.9	1686.7
130°	1703.5	1733.3	1753.7	1774.3	1772.5
132.5°	1796.7	1821.0	1841.4	1858.2	1856.4
135°	1875.0	1904.9	1921.5	1940.3	1936.5
137.5°	1956.9	1979.3	1998.1	2016.7	2011.1
140°	2037.0	2052.1	2072.5	2089.3	2079.9
142.5°	2104.3	2117.3	2141.4	2156.3	2147.0
145°	2175.1	2173.1	2204.8	2217.9	2208.5
147.5°	2236.5	2230.9	2262.5	2271.9	2264.5
150°	2296.2	2283.1	2313.0	2324.0	2314.8
152.5°	2346.5	2331.6	2359.4	2370.8	2357.7
155°	2394.9	2378.3	2400.6	2411.7	2396.9
157.5°	2434.0	2419.2	2436.0	2449.1	2434.0
160°	2467.7	2456.5	2467.7	2478.8	2465.7
162.5°	2497.4	2486.3	2495.6	2508.6	2491.8
165°	2523.5	2512.5	2518.0	2531.0	2518.0
167.5°	2544.0	2532.8	2538.5	2551.6	2534.8
170°	2560.9	2549.6	2553.4	2566.5	2549.6
172.5°	2572.0	2560.9	2564.6	2577.7	2560.9
175°	2581.2	2568.2	2572.0	2585.0	2566.5
177.5°	2585.0	2572.0	2573.9	2587.0	2570.2
180°	2575.7	2575.7	2575.7	2575.7	2575.7



TEST NUMBER: P925879  
 CATALOG NUMBER: DFN2DIP-SQ4F0-090D080US950-RLONL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.25	11.07	11.22	12.05	13.34	6.21	7.03	7.18	8.02	9.30
	3H	11.93	12.67	12.91	13.66	14.97	7.40	8.14	8.38	9.13	10.43
	4H	12.54	13.24	13.54	14.23	15.55	7.85	8.55	8.85	9.54	10.86
	6H	12.97	13.61	13.97	14.61	15.94	8.17	8.81	9.18	9.81	11.14
	8H	13.10	13.71	14.11	14.72	16.05	8.26	8.87	9.27	9.89	11.21
	12H	13.16	13.74	14.18	14.75	16.10	8.31	8.89	9.32	9.89	11.24
4H	2H	10.27	10.96	11.27	11.96	13.27	6.81	7.50	7.81	8.50	9.81
	3H	12.10	12.68	13.11	13.70	15.03	8.16	8.74	9.17	9.76	11.09
	4H	12.80	13.33	13.81	14.34	15.69	8.71	9.24	9.72	10.25	11.60
	6H	13.32	13.77	14.34	14.81	16.16	9.13	9.58	10.16	10.62	11.97
	8H	13.49	13.92	14.52	14.95	16.31	9.26	9.68	10.29	10.71	12.08
	12H	13.59	13.97	14.64	15.02	16.39	9.32	9.70	10.37	10.75	12.12
8H	4H	12.76	13.19	13.79	14.22	15.58	8.99	9.41	10.02	10.44	11.81
	6H	13.33	13.68	14.39	14.76	16.12	9.51	9.86	10.56	10.93	12.29
	8H	13.55	13.86	14.62	14.92	16.30	9.70	10.01	10.76	11.07	12.45
	12H	13.70	13.97	14.76	15.02	16.44	9.82	10.09	10.88	11.14	12.57
12H	4H	12.72	13.10	13.76	14.14	15.51	8.99	9.38	10.04	10.42	11.79
	6H	13.31	13.62	14.37	14.68	16.06	9.56	9.87	10.62	10.93	12.31
	8H	13.53	13.80	14.60	14.86	16.28	9.77	10.04	10.83	11.09	12.52