

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P917900

Luminaire Tested: DFN2DIP-TR2F0-020D020US930-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P917900
REPORT IS A COMBINATION OF REPORTS P900221 AND P897145
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR2F0-020D020US930-FLLFLL
Description: 2 foot, Triangle Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3057.4 lumens
Efficiency: N/A
Efficacy: 100.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.04' x L: 2.36' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 30.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P917900

CATALOG NUMBER: DFN2DIP-TR2F0-020D020US930-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P917900

CATALOG NUMBER: DFN2DIP-TR2F0-020D020US930-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85		71	71	71		59
1	98	94	90	87	91	87	84	81	74	72	70		63	61	59		52
2	90	82	76	71	83	76	71	66	65	61	58		55	52	50		46
3	82	72	65	59	75	67	61	55	58	53	49		49	45	42		41
4	75	64	56	50	69	60	52	47	51	46	41		43	39	36		36
5	69	57	49	43	63	53	46	40	46	40	36		39	35	31		33
6	63	51	43	37	58	48	40	35	41	36	31		35	31	27		30
7	59	46	38	33	54	43	36	31	37	32	28		32	28	24		27
8	54	42	34	29	50	39	32	27	34	29	24		29	25	22		25
9	51	38	31	26	47	36	29	24	31	26	22		27	23	19		23
10	47	35	28	23	44	33	26	22	29	23	20		25	21	18		21

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1415	1415	1415
5°	1415	1392	1402
10°	1402	1370	1381
15°	1379	1345	1349
20°	1349	1310	1316
25°	1319	1270	1279
30°	1282	1232	1232
35°	1247	1187	1182
40°	1204	1142	1135
45°	1161	1097	1086
50°	1114	1050	1030
55°	1065	995	978
60°	1009	930	918
65°	947	863	848
70°	870	780	772
75°	763	682	698
80°	633	557	564
85°	429	350	351

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1161 cd/sqm

TEST NUMBER: P917900

CATALOG NUMBER: DFN2DIP-TR2F0-020D020US930-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	59.7	2.0
10°-20°	168.0	5.5
20°-30°	246.9	8.1
30°-40°	286.8	9.4
40°-50°	286.4	9.4
50°-60°	249.7	8.2
60°-70°	184.6	6.0
70°-80°	104.5	3.4
80°-90°	29.0	1.0
90°-100°	31.9	1.0
100°-110°	101.4	3.3
110°-120°	173.5	5.7
120°-130°	228.2	7.5
130°-140°	256.1	8.4
140°-150°	251.2	8.2
150°-160°	210.7	6.9
160°-170°	139.7	4.6
170°-180°	48.8	1.6
0°-30°	474.7	15.5
0°-40°	761.5	24.9
0°-60°	1297.6	42.4
0°-90°	1615.8	52.8
90°-120°	306.8	10.0
90°-150°	1042.3	34.1
90°-180°	1442.0	47.2
0°-180°	3057.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	634	634	634	634	634	
5°	634	632	625	630	629	60
15°	604	600	592	595	592	170
25°	547	542	531	533	531	252
35°	472	466	456	452	449	295
45°	384	380	370	364	361	296
55°	290	287	279	272	269	260
65°	196	192	186	181	178	194
75°	102	101	98	95	96	109
85°	25	24	24	22	21	28
90°	0	6	15	14	15	3
95°	23	27	28	28	27	25
105°	94	95	96	96	96	99
115°	174	177	176	175	174	172
125°	253	257	256	254	254	226
135°	328	332	333	333	332	253
145°	398	401	403	404	402	248
155°	455	456	457	460	458	209
165°	495	494	494	497	495	140
175°	515	514	513	516	513	49
180°	516	516	516	516	516	

TEST NUMBER: P917900

CATALOG NUMBER: DFN2DIP-TR2F0-020D020US930-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	634.5	634.5	634.5	634.5	634.5
2.5°	638.1	635.1	628.4	634.5	633.3
5°	634.5	632.1	625.3	630.2	629.0
7.5°	630.2	626.6	619.9	624.8	623.5
10°	623.5	619.3	612.0	616.8	615.0
12.5°	614.3	610.7	603.4	606.4	605.2
15°	604.0	600.4	592.4	594.8	591.8
17.5°	591.2	587.6	579.6	582.6	579.6
20°	577.1	573.5	564.9	566.8	564.3
22.5°	563.1	557.7	549.7	549.7	548.5
25°	546.7	541.8	531.4	532.6	531.4
27.5°	528.3	524.1	516.2	514.4	511.3
30°	510.1	505.2	496.0	494.2	491.7
32.5°	490.5	486.9	477.1	473.4	471.0
35°	471.7	465.5	455.8	452.1	449.0
37.5°	450.3	444.7	435.0	430.7	427.6
40°	428.3	423.4	413.6	408.2	405.7
42.5°	406.9	402.0	392.3	386.2	382.5
45°	383.8	379.5	370.3	363.6	361.2
47.5°	361.2	356.9	347.2	340.4	336.8
50°	337.4	334.4	325.8	317.2	314.2
52.5°	314.2	309.9	302.0	295.3	291.1
55°	290.4	286.7	279.4	272.1	269.0
57.5°	266.6	263.6	255.6	248.3	245.8
60°	242.8	240.4	231.9	225.1	223.3
62.5°	219.6	215.3	209.3	203.2	200.7
65°	195.8	192.2	186.1	180.6	177.6
67.5°	171.5	168.4	162.9	158.7	156.2
70°	148.9	146.4	140.9	136.6	134.3
72.5°	125.7	123.3	120.2	115.9	114.1
75°	102.5	101.3	98.2	94.6	95.8
77.5°	81.8	79.3	78.0	76.2	74.4
80°	61.1	60.4	59.2	57.3	56.1
82.5°	41.5	41.5	40.9	38.5	38.5
85°	24.9	24.4	23.8	21.9	21.4
87.5°	11.0	9.8	8.6	6.8	6.1
90°	0.5	5.6	15.2	14.3	14.8
92.5°	9.6	13.0	13.5	14.0	14.0
95°	22.7	27.1	27.8	27.8	27.1
97.5°	37.7	41.8	43.5	43.5	43.5
100°	55.2	58.8	60.0	60.0	59.5
102.5°	73.5	76.1	77.9	78.4	77.9
105°	93.6	94.8	95.8	96.5	96.5
107.5°	113.5	115.4	115.4	115.7	113.5
110°	132.8	135.3	135.3	135.3	134.0



TEST NUMBER: P917900

CATALOG NUMBER: DFN2DIP-TR2F0-020D020US930-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	153.6	156.2	155.8	154.5	153.6
115°	174.1	176.6	175.9	175.4	174.1
117.5°	194.5	198.0	195.8	194.5	193.2
120°	215.0	218.4	215.0	215.0	213.6
122.5°	233.7	238.0	235.9	234.6	233.7
125°	253.2	257.1	255.9	254.5	254.0
127.5°	272.4	277.2	275.5	273.6	272.4
130°	290.2	295.9	295.1	294.2	292.4
132.5°	310.3	314.7	314.9	312.8	311.5
135°	327.6	332.4	333.3	332.9	331.6
137.5°	346.8	350.7	351.6	351.2	349.4
140°	363.8	367.7	369.9	369.9	368.2
142.5°	381.2	385.1	386.4	386.8	385.1
145°	397.7	400.8	403.3	403.7	402.0
147.5°	412.5	416.4	418.2	419.0	417.3
150°	427.7	430.3	432.0	433.4	432.0
152.5°	441.2	443.8	446.0	447.8	446.0
155°	454.8	456.0	457.4	459.6	458.2
157.5°	466.4	467.3	468.1	471.2	469.0
160°	476.9	477.8	478.3	480.9	479.0
162.5°	486.5	486.5	486.9	489.9	487.7
165°	494.7	494.2	494.2	497.3	495.2
167.5°	502.1	500.8	500.8	503.9	501.7
170°	507.8	506.5	506.1	509.2	506.5
172.5°	511.7	510.4	510.0	513.1	510.4
175°	514.8	513.6	512.6	515.7	513.1
177.5°	516.5	515.3	514.3	516.9	514.3
180°	515.7	515.7	515.7	515.7	515.7

TEST NUMBER: P917900

CATALOG NUMBER: DFN2DIP-TR2F0-020D020US930-FLLFL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.61	9.50	9.54	10.45	11.68	8.18	9.07	9.12	10.02	11.25
	3H	10.25	11.04	11.19	12.00	13.26	9.79	10.58	10.73	11.54	12.79
	4H	10.82	11.57	11.78	12.54	13.80	10.36	11.11	11.32	12.08	13.34
	6H	11.20	11.90	12.17	12.87	14.14	10.74	11.44	11.71	12.41	13.68
	8H	11.30	11.96	12.28	12.95	14.22	10.84	11.50	11.82	12.49	13.76
	12H	11.34	11.97	12.32	12.95	14.25	10.88	11.51	11.86	12.49	13.78
4H	2H	9.06	9.82	10.03	10.78	12.04	8.72	9.48	9.69	10.44	11.70
	3H	10.91	11.53	11.88	12.53	13.80	10.52	11.15	11.49	12.14	13.42
	4H	11.60	12.18	12.58	13.16	14.46	11.21	11.78	12.19	12.77	14.07
	6H	12.10	12.59	13.09	13.60	14.90	11.70	12.19	12.69	13.20	14.50
	8H	12.24	12.70	13.23	13.70	15.01	11.84	12.30	12.83	13.30	14.62
	12H	12.30	12.72	13.31	13.74	15.05	11.89	12.31	12.91	13.33	14.65
8H	4H	11.79	12.25	12.79	13.26	14.57	11.44	11.90	12.43	12.90	14.22
	6H	12.39	12.78	13.42	13.82	15.13	12.04	12.42	13.06	13.47	14.78
	8H	12.60	12.94	13.63	13.97	15.30	12.24	12.58	13.27	13.61	14.94
	12H	12.72	13.01	13.75	14.04	15.41	12.35	12.64	13.38	13.67	15.04
12H	4H	11.77	12.19	12.79	13.21	14.53	11.43	11.85	12.45	12.87	14.19
	6H	12.42	12.76	13.45	13.79	15.12	12.08	12.42	13.11	13.45	14.78
	8H	12.65	12.94	13.68	13.97	15.34	12.30	12.60	13.33	13.62	15.00