

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P925946

Luminaire Tested: DFN2DIP-SQ4F0-110D070US950-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P925946
REPORT IS A COMBINATION OF REPORTS P900088 AND P896915
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-110D070US950-RLLFLL
Description: 4 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 14830.0 lumens
Efficiency: N/A
Efficacy: 94.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 157.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P925946

CATALOG NUMBER: DFN2DIP-SQ4F0-110D070US950-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P925946

CATALOG NUMBER: DFN2DIP-SQ4F0-110D070US950-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	102	102	102	102	89	89	89	77	77	77	65	65	65
1	101	96	93	89	94	90	87	84	79	77	74	68	67	65	59	58	56
2	92	85	79	74	86	80	74	70	70	66	63	61	58	55	52	50	48
3	84	75	68	62	79	71	64	59	62	57	53	54	51	47	47	44	42
4	78	67	59	53	72	63	56	51	56	50	46	49	45	41	42	39	37
5	71	60	52	46	67	57	49	44	50	44	40	44	40	36	38	35	32
6	66	54	46	40	62	51	44	39	45	40	35	40	36	32	35	32	29
7	61	49	41	36	57	46	39	34	41	36	31	37	32	29	32	29	26
8	57	45	37	32	53	42	36	31	38	32	28	34	29	26	30	26	23
9	53	41	34	29	50	39	32	28	35	29	25	31	27	23	28	24	21
10	50	38	31	26	47	36	29	25	32	27	23	29	24	21	26	22	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3043	3043	3043
5°	3048	2996	3015
10°	3018	2937	2918
15°	2976	2841	2767
20°	2921	2708	2582
25°	2865	2558	2402
30°	2789	2405	2175
35°	2715	2240	1975
40°	2640	2069	1746
45°	2552	1880	1538
50°	2462	1688	1335
55°	2367	1484	1140
60°	2258	1270	939
65°	2132	1052	846
70°	1979	850	767
75°	1787	750	700
80°	1510	631	610
85°	1051	425	464

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2552 cd/sqm

TEST NUMBER: P925946

CATALOG NUMBER: DFN2DIP-SQ4F0-110D070US950-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	406.5	2.7
10°-20°	1115.9	7.5
20°-30°	1566.7	10.6
30°-40°	1707.7	11.5
40°-50°	1569.6	10.6
50°-60°	1232.7	8.3
60°-70°	802.4	5.4
70°-80°	413.0	2.8
80°-90°	111.4	0.8
90°-100°	130.7	0.9
100°-110°	415.3	2.8
110°-120°	710.6	4.8
120°-130°	934.6	6.3
130°-140°	1049.0	7.1
140°-150°	1028.7	6.9
150°-160°	862.9	5.8
160°-170°	572.3	3.9
170°-180°	200.0	1.3
0°-30°	3089.0	20.8
0°-40°	4796.8	32.3
0°-60°	7599.1	51.2
0°-90°	8925.9	60.2
90°-120°	1256.6	8.5
90°-150°	4268.9	28.8
90°-180°	5904.0	39.8
0°-180°	14830.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4337	4337	4337	4337	4337	
5°	4337	4318	4266	4302	4290	411
15°	4125	4082	3949	3874	3835	1162
25°	3744	3619	3360	3199	3140	1722
35°	3226	3026	2681	2434	2347	2019
45°	2638	2374	1963	1684	1590	2037
55°	2006	1700	1276	1040	966	1792
65°	1354	1036	683	550	538	1343
75°	722	447	314	286	283	764
85°	169	86	74	74	74	194
90°	2	23	62	59	60	15
95°	93	111	114	114	111	103
105°	383	388	392	395	395	405
115°	713	723	720	718	713	705
125°	1037	1053	1048	1042	1040	927
135°	1342	1361	1365	1363	1358	1037
145°	1629	1642	1652	1654	1647	1018
155°	1862	1868	1873	1882	1876	857
165°	2026	2024	2024	2037	2028	572
175°	2108	2103	2099	2112	2101	200
180°	2112	2112	2112	2112	2112	

TEST NUMBER: P925946

CATALOG NUMBER: DFN2DIP-SQ4F0-110D070US950-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4337.2	4337.2	4337.2	4337.2	4337.2
2.5°	4356.7	4337.2	4293.9	4333.4	4325.5
5°	4337.2	4317.6	4266.4	4301.8	4290.1
7.5°	4301.8	4278.4	4223.5	4238.9	4219.3
10°	4254.7	4227.2	4148.9	4136.8	4113.6
12.5°	4196.0	4160.6	4054.4	4031.0	3987.7
15°	4125.2	4081.9	3948.6	3874.1	3834.9
17.5°	4042.8	3979.9	3815.0	3728.7	3665.8
20°	3948.6	3869.9	3673.8	3575.9	3489.3
22.5°	3846.6	3756.2	3528.5	3395.2	3336.4
25°	3744.5	3618.8	3359.8	3199.0	3139.9
27.5°	3623.0	3489.3	3202.8	3018.3	2927.9
30°	3493.5	3344.0	3030.0	2830.0	2723.9
32.5°	3367.7	3186.9	2865.4	2629.8	2531.5
35°	3226.5	3026.2	2681.0	2433.7	2347.0
37.5°	3089.1	2873.0	2508.2	2237.0	2139.2
40°	2943.8	2708.5	2327.5	2048.8	1946.8
42.5°	2794.6	2543.6	2147.2	1856.5	1758.6
45°	2637.7	2374.5	1962.7	1683.6	1589.6
47.5°	2488.6	2210.0	1786.1	1507.0	1420.9
50°	2323.7	2045.1	1613.3	1342.2	1260.1
52.5°	2162.5	1868.1	1448.4	1189.4	1114.7
55°	2005.5	1699.5	1275.5	1040.2	965.7
57.5°	1844.8	1530.8	1122.7	902.9	839.9
60°	1679.9	1365.9	961.5	761.7	698.8
62.5°	1519.1	1205.2	824.2	635.9	604.6
65°	1354.2	1036.0	683.0	549.7	537.6
67.5°	1197.3	879.1	549.7	482.6	471.0
70°	1032.3	726.3	455.2	416.0	400.2
72.5°	875.3	584.7	380.6	349.4	341.4
75°	722.1	447.2	314.0	286.5	282.8
77.5°	569.3	317.8	247.4	231.5	223.6
80°	427.7	227.8	188.2	172.9	172.9
82.5°	298.1	153.2	129.6	121.6	121.6
85°	168.7	86.2	74.5	74.5	74.5
87.5°	62.9	31.2	31.2	27.5	27.5
90°	1.9	22.9	62.4	58.6	60.5
92.5°	39.5	53.5	55.4	57.3	57.3
95°	92.9	110.8	114.0	114.0	110.8
97.5°	154.7	171.2	178.3	178.3	178.3
100°	226.0	240.7	245.8	245.8	243.8
102.5°	301.2	312.0	319.0	320.9	319.0
105°	383.3	388.4	392.2	395.4	395.4
107.5°	464.8	472.4	472.4	473.8	464.8
110°	543.8	554.0	554.0	554.0	548.8

TEST NUMBER: P925946

CATALOG NUMBER: DFN2DIP-SQ4F0-110D070US950-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	629.1	639.9	638.0	632.9	629.1
115°	713.1	723.3	720.2	718.3	713.1
117.5°	796.5	810.5	801.6	796.5	791.4
120°	880.5	894.6	880.5	880.5	874.8
122.5°	957.0	974.8	965.9	960.8	957.0
125°	1037.2	1053.1	1048.1	1042.3	1040.4
127.5°	1115.5	1135.3	1128.3	1120.7	1115.5
130°	1188.8	1211.7	1208.5	1204.7	1197.7
132.5°	1270.9	1288.8	1290.0	1281.1	1276.0
135°	1341.6	1361.3	1365.2	1363.2	1358.1
137.5°	1420.5	1436.4	1439.6	1438.3	1430.7
140°	1490.0	1505.9	1514.8	1514.8	1507.8
142.5°	1561.2	1577.2	1582.2	1584.1	1577.2
145°	1628.8	1641.5	1651.7	1653.6	1646.6
147.5°	1689.2	1705.2	1712.8	1716.0	1709.0
150°	1751.6	1762.4	1769.5	1775.2	1769.5
152.5°	1807.0	1817.8	1826.7	1833.8	1826.7
155°	1862.4	1867.5	1873.3	1882.1	1876.4
157.5°	1910.2	1914.0	1917.2	1929.9	1921.0
160°	1952.8	1956.7	1958.6	1969.3	1961.7
162.5°	1992.3	1992.3	1994.2	2006.3	1997.4
165°	2026.0	2024.1	2024.1	2036.9	2027.9
167.5°	2056.6	2050.9	2050.9	2063.6	2054.7
170°	2079.5	2074.5	2072.6	2085.3	2074.5
172.5°	2095.5	2090.3	2088.4	2101.2	2090.3
175°	2108.1	2103.1	2099.3	2112.0	2101.2
177.5°	2115.2	2110.1	2106.2	2117.1	2106.2
180°	2112.0	2112.0	2112.0	2112.0	2112.0

TEST NUMBER: P925946

CATALOG NUMBER: DFN2DIP-SQ4F0-110D070US950-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.93	12.85	12.80	13.74	14.86	7.89	8.81	8.76	9.70	10.82
	3H	13.62	14.44	14.50	15.34	16.48	9.08	9.91	9.97	10.80	11.95
	4H	14.23	15.01	15.13	15.91	17.07	9.54	10.32	10.44	11.22	12.38
	6H	14.66	15.38	15.57	16.29	17.46	9.87	10.58	10.78	11.49	12.66
	8H	14.79	15.47	15.71	16.40	17.57	9.96	10.64	10.88	11.57	12.73
	12H	14.86	15.51	15.78	16.43	17.62	10.01	10.65	10.93	11.57	12.77
4H	2H	11.96	12.73	12.86	13.64	14.79	8.50	9.27	9.40	10.18	11.33
	3H	13.80	14.44	14.71	15.38	16.55	9.86	10.50	10.77	11.44	12.61
	4H	14.50	15.09	15.42	16.02	17.21	10.41	11.00	11.33	11.93	13.12
	6H	15.02	15.53	15.96	16.48	17.68	10.83	11.34	11.77	12.29	13.49
	8H	15.20	15.67	16.14	16.62	17.83	10.96	11.44	11.91	12.38	13.60
	12H	15.30	15.73	16.26	16.69	17.91	11.03	11.46	11.99	12.43	13.64
8H	4H	14.47	14.94	15.41	15.89	17.10	10.70	11.17	11.64	12.12	13.33
	6H	15.05	15.44	16.01	16.43	17.64	11.22	11.61	12.19	12.60	13.81
	8H	15.27	15.61	16.24	16.59	17.82	11.41	11.76	12.39	12.74	13.97
	12H	15.41	15.72	16.39	16.69	17.96	11.54	11.84	12.52	12.81	14.09
12H	4H	14.43	14.85	15.39	15.82	17.04	10.71	11.13	11.67	12.10	13.31
	6H	15.02	15.37	16.00	16.35	17.57	11.27	11.62	12.25	12.60	13.82
	8H	15.25	15.55	16.23	16.53	17.80	11.49	11.79	12.47	12.76	14.04