

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P917940

Luminaire Tested: DFN2DIP-TR2F0-040D020US930-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P917940
REPORT IS A COMBINATION OF REPORTS P900225 AND P897145
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR2F0-040D020US930-FLLFLL
Description: 2 foot, Triangle Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4671.7 lumens
Efficiency: N/A
Efficacy: 91.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.04' x L: 2.36' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 51.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P917940

CATALOG NUMBER: DFN2DIP-TR2F0-040D020US930-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P917940

CATALOG NUMBER: DFN2DIP-TR2F0-040D020US930-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	112	112	112	112	106	106	106	106	94	94	94	83	83	83	74	74	74
1	102	98	94	90	96	92	89	86	83	80	77	74	71	70	65	64	62
2	93	85	79	74	88	81	75	70	72	68	64	65	61	58	57	55	52
3	85	75	67	61	80	71	64	59	64	58	54	57	53	49	51	48	45
4	78	67	58	52	73	63	56	50	57	51	46	51	46	42	46	42	39
5	71	59	51	45	67	56	49	43	51	45	40	46	41	37	41	37	34
6	66	53	45	39	62	51	43	38	46	40	35	41	36	32	37	33	30
7	61	48	40	34	58	46	39	33	42	35	31	38	33	29	34	30	26
8	57	44	36	31	54	42	35	30	38	32	28	35	29	26	31	27	24
9	53	40	33	27	50	39	31	26	35	29	25	32	27	23	29	25	21
10	50	37	30	25	47	36	29	24	32	27	22	30	25	21	27	23	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2830	2830	2830
5°	2831	2785	2805
10°	2804	2741	2762
15°	2758	2689	2698
20°	2698	2620	2632
25°	2638	2539	2557
30°	2565	2463	2463
35°	2494	2375	2364
40°	2408	2285	2270
45°	2323	2194	2172
50°	2229	2100	2060
55°	2130	1990	1956
60°	2018	1861	1837
65°	1896	1726	1696
70°	1739	1561	1544
75°	1525	1364	1396
80°	1265	1112	1129
85°	862	701	701

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2323 cd/sqm

TEST NUMBER: P917940

CATALOG NUMBER: DFN2DIP-TR2F0-040D020US930-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	119.4	2.6
10°-20°	336.0	7.2
20°-30°	493.8	10.6
30°-40°	573.6	12.3
40°-50°	572.9	12.3
50°-60°	499.5	10.7
60°-70°	369.3	7.9
70°-80°	208.9	4.5
80°-90°	56.6	1.2
90°-100°	31.9	0.7
100°-110°	101.4	2.2
110°-120°	173.5	3.7
120°-130°	228.2	4.9
130°-140°	256.1	5.5
140°-150°	251.2	5.4
150°-160°	210.7	4.5
160°-170°	139.7	3.0
170°-180°	48.8	1.0
0°-30°	949.3	20.3
0°-40°	1522.9	32.6
0°-60°	2595.3	55.6
0°-90°	3230.1	69.1
90°-120°	306.8	6.6
90°-150°	1042.3	22.3
90°-180°	1442.0	30.9
0°-180°	4671.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1269	1269	1269	1269	1269	
5°	1269	1264	1251	1260	1258	120
15°	1208	1201	1185	1190	1184	340
25°	1093	1084	1063	1065	1063	503
35°	943	931	912	904	898	589
45°	768	759	741	727	722	592
55°	581	574	559	544	538	519
65°	392	384	372	361	355	387
75°	205	203	196	189	192	219
85°	50	49	48	44	43	56
90°	0	6	15	14	15	4
95°	23	27	28	28	27	25
105°	94	95	96	96	96	99
115°	174	177	176	175	174	172
125°	253	257	256	254	254	226
135°	328	332	333	333	332	253
145°	398	401	403	404	402	248
155°	455	456	457	460	458	209
165°	495	494	494	497	495	140
175°	515	514	513	516	513	49
180°	516	516	516	516	516	

TEST NUMBER: P917940

CATALOG NUMBER: DFN2DIP-TR2F0-040D020US930-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1268.9	1268.9	1268.9	1268.9	1268.9
2.5°	1276.3	1270.2	1256.8	1268.9	1266.6
5°	1268.9	1264.1	1250.7	1260.4	1258.1
7.5°	1260.4	1253.1	1239.7	1249.5	1247.1
10°	1247.1	1238.5	1223.9	1233.6	1230.0
12.5°	1228.7	1221.4	1206.8	1212.9	1210.4
15°	1207.9	1200.7	1184.8	1189.7	1183.6
17.5°	1182.3	1175.1	1159.2	1165.2	1159.2
20°	1154.2	1147.0	1129.9	1133.5	1128.8
22.5°	1126.3	1115.2	1099.3	1099.3	1096.9
25°	1093.2	1083.5	1062.8	1065.2	1062.8
27.5°	1056.6	1048.1	1032.3	1028.7	1022.6
30°	1020.1	1010.3	992.1	988.4	983.5
32.5°	981.0	973.8	954.2	946.9	941.9
35°	943.2	931.1	911.5	904.2	898.1
37.5°	900.5	889.5	869.9	861.4	855.3
40°	856.6	846.8	827.2	816.4	811.5
42.5°	813.9	804.0	784.6	772.3	765.1
45°	767.5	759.0	740.6	727.3	722.4
47.5°	722.4	713.8	694.3	680.9	673.6
50°	674.7	668.6	651.6	634.5	628.4
52.5°	628.4	619.9	604.1	590.6	582.0
55°	580.9	573.5	558.9	544.2	538.2
57.5°	533.2	527.2	511.2	496.6	491.7
60°	485.6	480.8	463.7	450.3	446.6
62.5°	439.3	430.7	418.6	406.3	401.5
65°	391.8	384.3	372.2	361.2	355.1
67.5°	342.9	336.7	325.9	317.3	312.4
70°	297.7	292.9	281.8	273.3	268.5
72.5°	251.4	246.5	240.4	231.9	228.2
75°	205.0	202.6	196.4	189.1	191.6
77.5°	163.5	158.6	156.1	152.5	148.9
80°	122.1	120.7	118.3	114.7	112.3
82.5°	83.0	83.0	81.9	76.9	76.9
85°	50.0	48.8	47.6	43.9	42.7
87.5°	22.0	19.6	17.1	13.5	12.1
90°	0.5	5.6	15.2	14.3	14.8
92.5°	9.6	13.0	13.5	14.0	14.0
95°	22.7	27.1	27.8	27.8	27.1
97.5°	37.7	41.8	43.5	43.5	43.5
100°	55.2	58.8	60.0	60.0	59.5
102.5°	73.5	76.1	77.9	78.4	77.9
105°	93.6	94.8	95.8	96.5	96.5
107.5°	113.5	115.4	115.4	115.7	113.5
110°	132.8	135.3	135.3	135.3	134.0

TEST NUMBER: P917940

CATALOG NUMBER: DFN2DIP-TR2F0-040D020US930-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	153.6	156.2	155.8	154.5	153.6
115°	174.1	176.6	175.9	175.4	174.1
117.5°	194.5	198.0	195.8	194.5	193.2
120°	215.0	218.4	215.0	215.0	213.6
122.5°	233.7	238.0	235.9	234.6	233.7
125°	253.2	257.1	255.9	254.5	254.0
127.5°	272.4	277.2	275.5	273.6	272.4
130°	290.2	295.9	295.1	294.2	292.4
132.5°	310.3	314.7	314.9	312.8	311.5
135°	327.6	332.4	333.3	332.9	331.6
137.5°	346.8	350.7	351.6	351.2	349.4
140°	363.8	367.7	369.9	369.9	368.2
142.5°	381.2	385.1	386.4	386.8	385.1
145°	397.7	400.8	403.3	403.7	402.0
147.5°	412.5	416.4	418.2	419.0	417.3
150°	427.7	430.3	432.0	433.4	432.0
152.5°	441.2	443.8	446.0	447.8	446.0
155°	454.8	456.0	457.4	459.6	458.2
157.5°	466.4	467.3	468.1	471.2	469.0
160°	476.9	477.8	478.3	480.9	479.0
162.5°	486.5	486.5	486.9	489.9	487.7
165°	494.7	494.2	494.2	497.3	495.2
167.5°	502.1	500.8	500.8	503.9	501.7
170°	507.8	506.5	506.1	509.2	506.5
172.5°	511.7	510.4	510.0	513.1	510.4
175°	514.8	513.6	512.6	515.7	513.1
177.5°	516.5	515.3	514.3	516.9	514.3
180°	515.7	515.7	515.7	515.7	515.7

TEST NUMBER: P917940

CATALOG NUMBER: DFN2DIP-TR2F0-040D020US930-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.36	13.43	13.13	14.22	15.19	11.94	13.00	12.71	13.80	14.77
	3H	14.01	14.97	14.80	15.77	16.77	13.55	14.51	14.34	15.31	16.31
	4H	14.59	15.50	15.40	16.31	17.32	14.13	15.04	14.94	15.85	16.86
	6H	14.99	15.82	15.80	16.64	17.66	14.53	15.36	15.34	16.18	17.20
	8H	15.09	15.88	15.91	16.72	17.75	14.63	15.42	15.45	16.26	17.29
	12H	15.13	15.89	15.97	16.73	17.78	14.67	15.43	15.50	16.26	17.31
4H	2H	12.84	13.74	13.65	14.55	15.56	12.50	13.40	13.31	14.22	15.22
	3H	14.69	15.45	15.51	16.30	17.32	14.31	15.06	15.13	15.91	16.94
	4H	15.40	16.08	16.23	16.93	17.98	15.00	15.69	15.84	16.54	17.59
	6H	15.90	16.50	16.75	17.37	18.42	15.51	16.10	16.36	16.97	18.03
	8H	16.05	16.60	16.90	17.47	18.54	15.65	16.20	16.50	17.07	18.14
	12H	16.12	16.62	16.99	17.50	18.58	15.71	16.21	16.59	17.10	18.17
8H	4H	15.60	16.16	16.45	17.02	18.09	15.25	15.80	16.10	16.67	17.74
	6H	16.21	16.67	17.09	17.58	18.65	15.86	16.32	16.74	17.23	18.30
	8H	16.42	16.83	17.31	17.73	18.82	16.06	16.47	16.96	17.37	18.46
	12H	16.55	16.90	17.44	17.80	18.94	16.18	16.54	17.07	17.43	18.57
12H	4H	15.59	16.09	16.47	16.98	18.06	15.25	15.75	16.12	16.64	17.71
	6H	16.24	16.65	17.13	17.55	18.64	15.90	16.31	16.79	17.21	18.30
	8H	16.47	16.83	17.37	17.73	18.87	16.13	16.49	17.02	17.38	18.52