

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P925979

Luminaire Tested: DFN2DIP-SQ4F0-120D060US950-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P925979
REPORT IS A COMBINATION OF REPORTS P901592 AND P898471
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-120D060US950-RLLONL
Description: 4 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 15397.5 lumens
Efficiency: N/A
Efficacy: 94.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 162.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P925979

CATALOG NUMBER: DFN2DIP-SQ4F0-120D060US950-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P925979

CATALOG NUMBER: DFN2DIP-SQ4F0-120D060US950-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	91	91	91	79	79	79	68	68	68
1	101	97	93	90	95	91	88	85	80	78	76	71	69	67	61	60	59
2	93	86	80	75	87	81	75	71	71	67	64	63	60	57	55	52	51
3	85	76	69	63	80	72	65	60	63	58	54	56	52	49	49	46	44
4	78	68	60	54	73	64	57	52	57	51	47	50	46	43	44	41	38
5	72	61	53	47	67	57	50	45	51	45	41	46	41	37	40	37	34
6	67	55	47	41	62	52	45	39	46	41	36	41	37	33	37	33	30
7	62	50	42	36	58	47	40	35	42	36	32	38	33	30	34	30	27
8	58	45	38	32	54	43	36	31	39	33	29	35	30	27	31	27	24
9	54	42	34	29	51	40	33	28	36	30	26	32	27	24	29	25	22
10	50	38	31	26	47	37	30	25	33	28	24	30	25	22	27	23	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3320	3320	3320
5°	3325	3268	3289
10°	3292	3204	3183
15°	3247	3099	3018
20°	3187	2954	2816
25°	3125	2791	2621
30°	3043	2623	2373
35°	2962	2443	2155
40°	2880	2257	1905
45°	2784	2051	1678
50°	2686	1842	1456
55°	2582	1619	1243
60°	2463	1385	1024
65°	2326	1148	923
70°	2159	927	837
75°	1950	819	763
80°	1647	689	665
85°	1147	463	507

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2784 cd/sqm

TEST NUMBER: P925979

CATALOG NUMBER: DFN2DIP-SQ4F0-120D060US950-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	443.4	2.9
10°-20°	1217.3	7.9
20°-30°	1709.1	11.1
30°-40°	1863.0	12.1
40°-50°	1712.3	11.1
50°-60°	1344.7	8.7
60°-70°	875.3	5.7
70°-80°	450.6	2.9
80°-90°	118.4	0.8
90°-100°	63.7	0.4
100°-110°	237.5	1.5
110°-120°	629.8	4.1
120°-130°	1044.5	6.8
130°-140°	1109.5	7.2
140°-150°	1031.2	6.7
150°-160°	829.1	5.4
160°-170°	534.2	3.5
170°-180°	183.9	1.2
0°-30°	3369.8	21.9
0°-40°	5232.8	34.0
0°-60°	8289.9	53.8
0°-90°	9734.2	63.2
90°-120°	930.9	6.0
90°-150°	4116.2	26.7
90°-180°	5663.0	36.8
0°-180°	15397.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4732	4732	4732	4732	4732	
5°	4732	4710	4654	4693	4680	449
15°	4500	4453	4308	4226	4184	1268
25°	4085	3948	3665	3490	3425	1879
35°	3520	3301	2925	2655	2560	2203
45°	2878	2590	2141	1837	1734	2222
55°	2188	1854	1392	1135	1054	1955
65°	1477	1130	745	600	586	1465
75°	788	488	343	312	308	833
85°	184	94	81	81	81	211
90°	1	17	28	35	38	15
95°	91	45	54	62	60	108
105°	425	467	85	101	106	454
115°	804	828	862	215	115	791
125°	1136	1155	1181	1191	1195	1014
135°	1406	1429	1441	1455	1452	1086
145°	1631	1630	1654	1663	1656	1020
155°	1796	1784	1800	1809	1798	828
165°	1893	1884	1888	1898	1888	535
175°	1936	1926	1929	1939	1925	184
180°	1932	1932	1932	1932	1932	

TEST NUMBER: P925979

CATALOG NUMBER: DFN2DIP-SQ4F0-120D060US950-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4731.5	4731.5	4731.5	4731.5	4731.5
2.5°	4752.8	4731.5	4684.2	4727.4	4718.7
5°	4731.5	4710.1	4654.2	4692.8	4680.1
7.5°	4692.8	4667.3	4607.4	4624.2	4602.9
10°	4641.5	4611.5	4526.1	4512.9	4487.5
12.5°	4577.4	4538.8	4422.9	4397.6	4350.3
15°	4500.2	4453.0	4307.6	4226.2	4183.6
17.5°	4410.2	4341.7	4161.7	4067.8	3999.2
20°	4307.6	4221.7	4007.8	3901.0	3806.5
22.5°	4196.3	4097.7	3849.2	3703.8	3639.8
25°	4085.0	3947.7	3665.2	3489.8	3425.3
27.5°	3952.3	3806.5	3493.9	3292.7	3194.1
30°	3811.0	3648.0	3305.4	3087.3	2971.5
32.5°	3673.9	3476.7	3126.0	2868.9	2761.6
35°	3519.9	3301.3	2924.7	2654.9	2560.3
37.5°	3369.9	3134.2	2736.2	2440.4	2333.7
40°	3211.4	2954.7	2539.1	2235.1	2123.8
42.5°	3048.7	2774.8	2342.4	2025.2	1918.5
45°	2877.5	2590.4	2141.1	1836.7	1734.0
47.5°	2714.8	2410.9	1948.4	1644.1	1550.1
50°	2535.0	2231.0	1759.9	1464.2	1374.7
52.5°	2359.1	2037.9	1580.0	1297.4	1216.2
55°	2187.9	1854.0	1391.5	1134.8	1053.5
57.5°	2012.5	1670.0	1224.7	984.9	916.3
60°	1832.6	1490.1	1048.9	830.9	762.3
62.5°	1657.3	1314.7	899.0	693.7	659.6
65°	1477.4	1130.3	745.1	599.7	586.5
67.5°	1306.1	959.0	599.7	526.5	513.8
70°	1126.2	792.3	496.6	453.8	436.6
72.5°	955.0	637.8	415.2	381.1	372.5
75°	787.7	487.9	342.6	312.5	308.4
77.5°	621.1	346.6	269.9	252.6	243.9
80°	466.6	248.5	205.3	188.5	188.5
82.5°	325.3	167.1	141.3	132.6	132.6
85°	184.0	94.1	81.3	81.3	81.3
87.5°	68.6	34.1	34.1	30.0	30.0
90°	1.3	16.8	27.9	35.0	37.7
92.5°	35.0	29.4	33.5	36.3	37.7
95°	90.8	44.6	54.5	61.6	60.1
97.5°	163.5	48.9	71.2	75.6	76.9
100°	247.5	55.9	79.7	90.8	93.6
102.5°	339.6	337.0	82.5	97.8	102.1
105°	424.9	466.9	85.3	100.6	106.3
107.5°	524.2	559.0	88.1	103.4	109.0
110°	619.3	648.5	244.7	104.9	110.4



TEST NUMBER: P925979

CATALOG NUMBER: DFN2DIP-SQ4F0-120D060US950-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	708.7	733.8	710.1	107.5	111.9
115°	803.7	827.5	862.5	215.3	114.7
117.5°	886.2	914.1	938.0	738.0	371.8
120°	978.5	999.4	1024.7	1041.4	852.7
122.5°	1056.7	1079.1	1107.1	1115.4	1116.9
125°	1136.4	1154.6	1181.1	1191.0	1195.1
127.5°	1209.1	1228.7	1249.7	1263.7	1265.0
130°	1277.6	1300.0	1315.3	1330.7	1329.4
132.5°	1347.5	1365.7	1381.0	1393.6	1392.3
135°	1406.3	1428.7	1441.1	1455.2	1452.4
137.5°	1467.6	1484.4	1498.5	1512.5	1508.4
140°	1527.7	1539.1	1554.4	1566.9	1560.0
142.5°	1578.2	1588.0	1606.2	1617.2	1610.3
145°	1631.3	1629.8	1653.6	1663.4	1656.4
147.5°	1677.3	1673.1	1696.9	1703.8	1698.4
150°	1722.2	1712.3	1734.8	1743.1	1736.1
152.5°	1759.8	1748.7	1769.6	1778.1	1768.2
155°	1796.2	1783.7	1800.5	1808.8	1797.6
157.5°	1825.6	1814.4	1827.0	1836.8	1825.6
160°	1850.8	1842.3	1850.8	1859.1	1849.3
162.5°	1873.0	1864.7	1871.7	1881.5	1868.9
165°	1892.6	1884.3	1888.4	1898.3	1888.4
167.5°	1908.0	1899.6	1903.9	1913.7	1901.0
170°	1920.7	1912.2	1915.1	1924.8	1912.2
172.5°	1929.0	1920.7	1923.5	1933.3	1920.7
175°	1936.0	1926.1	1929.0	1938.7	1924.8
177.5°	1938.7	1929.0	1930.4	1940.2	1927.7
180°	1931.8	1931.8	1931.8	1931.8	1931.8

TEST NUMBER: P925979

CATALOG NUMBER: DFN2DIP-SQ4F0-120D060US950-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.48	13.43	13.32	14.29	15.36	8.44	9.39	9.28	10.25	11.32
	3H	14.17	15.02	15.03	15.89	16.99	9.64	10.49	10.50	11.36	12.46
	4H	14.79	15.59	15.66	16.47	17.58	10.10	10.90	10.97	11.77	12.88
	6H	15.22	15.96	16.10	16.84	17.96	10.42	11.16	11.31	12.05	13.17
	8H	15.35	16.06	16.24	16.96	18.08	10.52	11.22	11.41	12.12	13.24
	12H	15.42	16.09	16.32	16.98	18.13	10.57	11.24	11.46	12.13	13.28
4H	2H	12.51	13.32	13.39	14.19	15.30	9.05	9.86	9.93	10.73	11.84
	3H	14.36	15.03	15.25	15.93	17.06	10.42	11.08	11.30	11.99	13.12
	4H	15.06	15.67	15.96	16.57	17.72	10.97	11.58	11.87	12.48	13.63
	6H	15.59	16.11	16.50	17.04	18.19	11.40	11.92	12.31	12.85	14.00
	8H	15.77	16.25	16.68	17.18	18.34	11.53	12.02	12.44	12.94	14.10
	12H	15.87	16.31	16.80	17.25	18.42	11.60	12.04	12.53	12.98	14.15
8H	4H	15.04	15.52	15.95	16.45	17.61	11.26	11.75	12.18	12.67	13.84
	6H	15.61	16.01	16.55	16.98	18.14	11.79	12.19	12.73	13.15	14.32
	8H	15.83	16.19	16.78	17.14	18.33	11.98	12.33	12.93	13.29	14.47
	12H	15.98	16.29	16.93	17.24	18.47	12.10	12.42	13.06	13.36	14.60
12H	4H	14.99	15.43	15.93	16.37	17.54	11.27	11.71	12.21	12.65	13.82
	6H	15.59	15.94	16.54	16.90	18.08	11.84	12.19	12.79	13.15	14.33
	8H	15.82	16.13	16.77	17.08	18.31	12.05	12.37	13.01	13.31	14.55