

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P925990

Luminaire Tested: DFN2DIP-SQ4F0-120D090US950-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P925990
REPORT IS A COMBINATION OF REPORTS P900126 AND P896915
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-120D090US950-RLLFLL
Description: 4 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 17329.4 lumens
Efficiency: N/A
Efficacy: 94.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 184.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P925990

CATALOG NUMBER: DFN2DIP-SQ4F0-120D090US950-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P925990

CATALOG NUMBER: DFN2DIP-SQ4F0-120D090US950-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62
1	100	96	92	88	93	89	86	83	77	75	72	66	64	63	55	54	53
2	91	84	78	73	85	79	73	69	68	64	61	58	56	53	49	47	46
3	84	74	67	62	78	70	63	58	61	56	52	52	49	46	44	42	40
4	77	66	59	53	71	62	55	50	54	49	45	47	43	40	40	37	35
5	71	59	51	46	66	56	49	43	49	43	39	42	38	35	36	33	30
6	65	53	46	40	61	50	43	38	44	38	34	38	34	31	33	30	27
7	61	48	41	35	56	46	39	34	40	35	30	35	31	27	30	27	24
8	56	44	37	31	52	42	35	30	37	31	27	32	28	25	28	25	22
9	53	41	33	28	49	38	32	27	34	28	25	30	25	22	26	23	20
10	49	37	30	25	46	35	29	24	31	26	22	28	23	20	24	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3320	3320	3320
5°	3325	3268	3289
10°	3292	3204	3183
15°	3247	3099	3018
20°	3187	2954	2816
25°	3125	2791	2621
30°	3043	2623	2373
35°	2962	2443	2155
40°	2880	2257	1905
45°	2784	2051	1678
50°	2686	1842	1456
55°	2582	1619	1243
60°	2463	1385	1024
65°	2326	1148	923
70°	2159	927	837
75°	1950	819	763
80°	1647	689	665
85°	1147	463	507

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2784 cd/sqm

TEST NUMBER: P925990

CATALOG NUMBER: DFN2DIP-SQ4F0-120D090US950-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	443.4	2.6
10°-20°	1217.3	7.0
20°-30°	1709.1	9.9
30°-40°	1863.0	10.8
40°-50°	1712.3	9.9
50°-60°	1344.7	7.8
60°-70°	875.3	5.1
70°-80°	450.6	2.6
80°-90°	122.7	0.7
90°-100°	168.0	1.0
100°-110°	533.9	3.1
110°-120°	913.7	5.3
120°-130°	1201.6	6.9
130°-140°	1348.7	7.8
140°-150°	1322.6	7.6
150°-160°	1109.5	6.4
160°-170°	735.8	4.2
170°-180°	257.2	1.5
0°-30°	3369.8	19.4
0°-40°	5232.8	30.2
0°-60°	8289.9	47.8
0°-90°	9738.5	56.2
90°-120°	1615.6	9.3
90°-150°	5488.5	31.7
90°-180°	7591.0	43.8
0°-180°	17329.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4732	4732	4732	4732	4732	
5°	4732	4710	4654	4693	4680	449
15°	4500	4453	4308	4226	4184	1268
25°	4085	3948	3665	3490	3425	1879
35°	3520	3301	2925	2655	2560	2203
45°	2878	2590	2141	1837	1734	2222
55°	2188	1854	1392	1135	1054	1955
65°	1477	1130	745	600	586	1465
75°	788	488	343	312	308	833
85°	184	94	81	81	81	211
90°	2	30	80	75	78	17
95°	120	142	146	146	142	133
105°	493	499	504	508	508	520
115°	917	930	926	924	917	907
125°	1334	1354	1348	1340	1338	1192
135°	1725	1750	1755	1753	1746	1333
145°	2094	2110	2124	2126	2117	1308
155°	2394	2401	2408	2420	2413	1102
165°	2605	2602	2602	2619	2607	735
175°	2710	2704	2699	2716	2702	258
180°	2716	2716	2716	2716	2716	

TEST NUMBER: P925990

CATALOG NUMBER: DFN2DIP-SQ4F0-120D090US950-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4731.5	4731.5	4731.5	4731.5	4731.5
2.5°	4752.8	4731.5	4684.2	4727.4	4718.7
5°	4731.5	4710.1	4654.2	4692.8	4680.1
7.5°	4692.8	4667.3	4607.4	4624.2	4602.9
10°	4641.5	4611.5	4526.1	4512.9	4487.5
12.5°	4577.4	4538.8	4422.9	4397.6	4350.3
15°	4500.2	4453.0	4307.6	4226.2	4183.6
17.5°	4410.2	4341.7	4161.7	4067.8	3999.2
20°	4307.6	4221.7	4007.8	3901.0	3806.5
22.5°	4196.3	4097.7	3849.2	3703.8	3639.8
25°	4085.0	3947.7	3665.2	3489.8	3425.3
27.5°	3952.3	3806.5	3493.9	3292.7	3194.1
30°	3811.0	3648.0	3305.4	3087.3	2971.5
32.5°	3673.9	3476.7	3126.0	2868.9	2761.6
35°	3519.9	3301.3	2924.7	2654.9	2560.3
37.5°	3369.9	3134.2	2736.2	2440.4	2333.7
40°	3211.4	2954.7	2539.1	2235.1	2123.8
42.5°	3048.7	2774.8	2342.4	2025.2	1918.5
45°	2877.5	2590.4	2141.1	1836.7	1734.0
47.5°	2714.8	2410.9	1948.4	1644.1	1550.1
50°	2535.0	2231.0	1759.9	1464.2	1374.7
52.5°	2359.1	2037.9	1580.0	1297.4	1216.2
55°	2187.9	1854.0	1391.5	1134.8	1053.5
57.5°	2012.5	1670.0	1224.7	984.9	916.3
60°	1832.6	1490.1	1048.9	830.9	762.3
62.5°	1657.3	1314.7	899.0	693.7	659.6
65°	1477.4	1130.3	745.1	599.7	586.5
67.5°	1306.1	959.0	599.7	526.5	513.8
70°	1126.2	792.3	496.6	453.8	436.6
72.5°	955.0	637.8	415.2	381.1	372.5
75°	787.7	487.9	342.6	312.5	308.4
77.5°	621.1	346.6	269.9	252.6	243.9
80°	466.6	248.5	205.3	188.5	188.5
82.5°	325.3	167.1	141.3	132.6	132.6
85°	184.0	94.1	81.3	81.3	81.3
87.5°	68.6	34.1	34.1	30.0	30.0
90°	2.5	29.5	80.2	75.3	77.8
92.5°	50.8	68.8	71.3	73.6	73.6
95°	119.5	142.4	146.5	146.5	142.4
97.5°	198.9	220.2	229.2	229.2	229.2
100°	290.6	309.5	316.0	316.0	313.6
102.5°	387.2	401.2	410.1	412.6	410.1
105°	492.8	499.3	504.3	508.4	508.4
107.5°	597.6	607.4	607.4	609.0	597.6
110°	699.1	712.3	712.3	712.3	705.7

TEST NUMBER: P925990

CATALOG NUMBER: DFN2DIP-SQ4F0-120D090US950-RLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	808.8	822.7	820.2	813.8	808.8
115°	916.9	930.0	925.9	923.5	916.9
117.5°	1024.1	1042.1	1030.7	1024.1	1017.5
120°	1132.2	1150.1	1132.2	1132.2	1124.8
122.5°	1230.4	1253.4	1241.9	1235.3	1230.4
125°	1333.6	1354.0	1347.5	1340.1	1337.7
127.5°	1434.2	1459.6	1450.7	1440.8	1434.2
130°	1528.4	1557.9	1553.8	1548.8	1539.9
132.5°	1634.0	1656.9	1658.5	1647.1	1640.6
135°	1724.8	1750.2	1755.2	1752.7	1746.2
137.5°	1826.3	1846.8	1851.0	1849.3	1839.5
140°	1915.6	1936.0	1947.5	1947.5	1938.5
142.5°	2007.3	2027.7	2034.3	2036.8	2027.7
145°	2094.1	2110.4	2123.5	2126.0	2117.0
147.5°	2171.9	2192.3	2202.1	2206.2	2197.3
150°	2252.1	2266.0	2275.0	2282.3	2275.0
152.5°	2323.3	2337.2	2348.7	2357.7	2348.7
155°	2394.5	2401.0	2408.5	2419.9	2412.6
157.5°	2455.9	2460.8	2464.9	2481.3	2469.8
160°	2510.7	2515.7	2518.2	2532.0	2522.2
162.5°	2561.5	2561.5	2564.0	2579.5	2568.1
165°	2604.9	2602.4	2602.4	2618.8	2607.4
167.5°	2644.2	2636.9	2636.9	2653.2	2641.7
170°	2673.7	2667.1	2664.7	2681.0	2667.1
172.5°	2694.1	2687.6	2685.1	2701.5	2687.6
175°	2710.5	2703.9	2699.1	2715.5	2701.5
177.5°	2719.5	2713.0	2708.0	2722.0	2708.0
180°	2715.5	2715.5	2715.5	2715.5	2715.5

TEST NUMBER: P925990

CATALOG NUMBER: DFN2DIP-SQ4F0-120D090US950-RLFL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.89	12.77	12.80	13.69	14.88	7.85	8.73	8.76	9.65	10.84
	3H	13.57	14.36	14.49	15.30	16.50	9.04	9.83	9.96	10.76	11.97
	4H	14.19	14.93	15.12	15.87	17.09	9.49	10.24	10.43	11.18	12.40
	6H	14.62	15.30	15.56	16.25	17.48	9.82	10.51	10.77	11.45	12.68
	8H	14.75	15.40	15.70	16.36	17.59	9.91	10.56	10.87	11.53	12.75
	12H	14.81	15.43	15.77	16.39	17.64	9.96	10.58	10.92	11.53	12.78
4H	2H	11.91	12.66	12.85	13.60	14.81	8.45	9.20	9.39	10.14	11.35
	3H	13.75	14.37	14.70	15.34	16.57	9.81	10.43	10.76	11.40	12.63
	4H	14.45	15.01	15.41	15.98	17.23	10.36	10.92	11.32	11.89	13.14
	6H	14.97	15.46	15.94	16.44	17.70	10.78	11.27	11.76	12.25	13.51
	8H	15.15	15.60	16.13	16.58	17.85	10.91	11.37	11.89	12.35	13.61
	12H	15.25	15.66	16.24	16.66	17.93	10.98	11.39	11.97	12.39	13.66
8H	4H	14.42	14.87	15.40	15.85	17.12	10.65	11.10	11.62	12.08	13.35
	6H	14.99	15.37	15.99	16.39	17.66	11.17	11.54	12.17	12.56	13.83
	8H	15.21	15.54	16.22	16.55	17.84	11.36	11.69	12.37	12.70	13.99
	12H	15.36	15.65	16.37	16.65	17.98	11.48	11.77	12.49	12.78	14.11
12H	4H	14.38	14.78	15.37	15.78	17.05	10.65	11.06	11.65	12.06	13.33
	6H	14.97	15.30	15.98	16.31	17.60	11.22	11.55	12.23	12.56	13.84
	8H	15.20	15.49	16.21	16.49	17.82	11.43	11.72	12.44	12.73	14.06

END OF REPORT