

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P926019

Luminaire Tested: DFN2DIP-SQ4F0-140D070US950-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P926019
REPORT IS A COMBINATION OF REPORTS P901612 AND P898471
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-140D070US950-RLLONL
Description: 4 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 17963.8 lumens
Efficiency: N/A
Efficacy: 91.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 196
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P926019

CATALOG NUMBER: DFN2DIP-SQ4F0-140D070US950-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P926019

CATALOG NUMBER: DFN2DIP-SQ4F0-140D070US950-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	91	91	91	79	79	79	68	68	68
1	101	97	93	90	95	91	88	85	80	78	76	71	69	67	61	60	59
2	93	86	80	75	87	81	75	71	71	67	64	63	60	57	55	52	51
3	85	76	69	63	80	72	65	60	63	58	54	56	52	49	49	46	44
4	78	68	60	54	73	64	57	52	57	51	47	50	46	43	44	41	38
5	72	61	53	47	67	57	50	45	51	45	41	46	41	37	40	37	34
6	67	55	47	41	62	52	45	39	46	41	36	41	37	33	37	33	30
7	62	50	42	36	58	47	40	35	42	36	32	38	33	30	34	30	27
8	58	45	38	32	54	43	36	31	39	33	29	35	30	27	31	27	24
9	54	42	34	29	51	40	33	28	36	30	26	32	27	24	29	25	22
10	50	38	31	26	47	37	30	25	33	28	24	30	25	22	27	23	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3873	3873	3873
5°	3879	3813	3837
10°	3841	3739	3714
15°	3788	3616	3522
20°	3718	3446	3286
25°	3646	3256	3058
30°	3550	3061	2768
35°	3456	2851	2514
40°	3360	2634	2222
45°	3248	2392	1958
50°	3133	2149	1699
55°	3013	1889	1451
60°	2873	1616	1195
65°	2713	1339	1077
70°	2519	1081	976
75°	2275	955	891
80°	1922	803	777
85°	1337	540	591

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 3248 cd/sqm

TEST NUMBER: P926019

CATALOG NUMBER: DFN2DIP-SQ4F0-140D070US950-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	517.3	2.9
10°-20°	1420.2	7.9
20°-30°	1993.9	11.1
30°-40°	2173.5	12.1
40°-50°	1997.7	11.1
50°-60°	1568.9	8.7
60°-70°	1021.2	5.7
70°-80°	525.7	2.9
80°-90°	138.2	0.8
90°-100°	74.3	0.4
100°-110°	277.0	1.5
110°-120°	734.8	4.1
120°-130°	1218.6	6.8
130°-140°	1294.5	7.2
140°-150°	1203.1	6.7
150°-160°	967.2	5.4
160°-170°	623.3	3.5
170°-180°	214.5	1.2
0°-30°	3931.5	21.9
0°-40°	6105.0	34.0
0°-60°	9671.6	53.8
0°-90°	11356.6	63.2
90°-120°	1086.1	6.0
90°-150°	4802.2	26.7
90°-180°	6607.0	36.8
0°-180°	17963.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	5520	5520	5520	5520	5520	
5°	5520	5495	5430	5475	5460	523
15°	5250	5195	5026	4931	4881	1479
25°	4766	4606	4276	4072	3996	2192
35°	4106	3852	3412	3097	2987	2570
45°	3357	3022	2498	2143	2023	2593
55°	2552	2163	1623	1324	1229	2281
65°	1724	1319	869	700	684	1709
75°	919	569	400	365	360	972
85°	215	110	95	95	95	246
90°	2	20	32	41	44	17
95°	106	52	64	72	70	125
105°	496	545	100	117	124	530
115°	938	965	1006	251	134	923
125°	1326	1347	1378	1390	1394	1182
135°	1641	1667	1681	1698	1694	1267
145°	1903	1902	1929	1941	1932	1190
155°	2096	2081	2100	2110	2097	966
165°	2208	2198	2203	2215	2203	624
175°	2259	2247	2250	2262	2246	215
180°	2254	2254	2254	2254	2254	

TEST NUMBER: P926019

CATALOG NUMBER: DFN2DIP-SQ4F0-140D070US950-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	5520.0	5520.0	5520.0	5520.0	5520.0
2.5°	5544.9	5520.0	5464.9	5515.3	5505.2
5°	5520.0	5495.1	5429.9	5475.0	5460.1
7.5°	5475.0	5445.2	5375.3	5395.0	5370.1
10°	5415.1	5380.1	5280.5	5265.0	5235.4
12.5°	5340.3	5295.3	5160.1	5130.4	5075.4
15°	5250.2	5195.1	5025.5	4930.7	4880.9
17.5°	5145.3	5065.3	4855.4	4745.7	4665.6
20°	5025.5	4925.3	4675.7	4551.2	4441.0
22.5°	4895.6	4780.7	4490.8	4321.1	4246.4
25°	4765.8	4605.7	4276.1	4071.5	3996.2
27.5°	4611.1	4441.0	4076.3	3841.5	3726.5
30°	4446.2	4256.0	3856.4	3601.9	3466.7
32.5°	4286.1	4056.1	3647.0	3347.0	3221.9
35°	4106.5	3851.6	3412.2	3097.4	2987.1
37.5°	3931.6	3656.5	3192.2	2847.2	2722.6
40°	3746.6	3447.2	2962.2	2607.7	2477.8
42.5°	3556.9	3237.3	2732.7	2362.8	2238.2
45°	3357.0	3022.1	2498.0	2142.8	2023.1
47.5°	3167.3	2812.8	2273.2	1918.1	1808.4
50°	2957.4	2602.9	2053.2	1708.2	1603.8
52.5°	2752.3	2377.6	1843.3	1513.7	1418.8
55°	2552.5	2162.9	1623.4	1324.0	1229.0
57.5°	2347.9	1948.3	1428.9	1149.1	1069.1
60°	2138.0	1738.4	1223.8	969.4	889.3
62.5°	1933.5	1533.8	1048.9	809.3	769.6
65°	1723.6	1318.6	869.2	699.6	684.2
67.5°	1523.7	1118.9	699.6	614.3	599.4
70°	1313.8	924.3	579.3	529.5	509.3
72.5°	1114.1	744.1	484.4	444.7	434.6
75°	919.0	569.3	399.6	364.6	359.8
77.5°	724.6	404.4	314.8	294.7	284.6
80°	544.4	289.9	239.5	220.0	220.0
82.5°	379.5	195.0	164.9	154.7	154.7
85°	214.6	109.7	94.8	94.8	94.8
87.5°	80.0	39.8	39.8	35.0	35.0
90°	1.5	19.6	32.5	40.8	44.0
92.5°	40.8	34.2	39.1	42.5	44.0
95°	105.9	52.1	63.5	71.8	70.1
97.5°	190.7	57.1	83.1	88.1	89.7
100°	288.8	65.3	92.9	105.9	109.2
102.5°	396.2	393.1	96.3	114.1	119.1
105°	495.8	544.7	99.5	117.3	123.9
107.5°	611.5	652.2	102.8	120.7	127.3
110°	722.6	756.6	285.4	122.4	128.8

TEST NUMBER: P926019

CATALOG NUMBER: DFN2DIP-SQ4F0-140D070US950-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	826.9	856.1	828.5	125.5	130.5
115°	937.7	965.4	1006.2	251.2	133.8
117.5°	1033.9	1066.5	1094.3	861.0	433.8
120°	1141.6	1166.0	1195.5	1215.0	994.8
122.5°	1232.8	1258.9	1291.7	1301.4	1303.1
125°	1325.8	1347.0	1378.1	1389.5	1394.3
127.5°	1410.6	1433.4	1458.0	1474.3	1475.8
130°	1490.5	1516.7	1534.5	1552.5	1551.0
132.5°	1572.1	1593.4	1611.2	1625.9	1624.4
135°	1640.6	1666.7	1681.3	1697.7	1694.5
137.5°	1712.2	1731.9	1748.3	1764.6	1759.7
140°	1782.4	1795.5	1813.4	1828.1	1819.9
142.5°	1841.2	1852.7	1873.8	1886.7	1878.6
145°	1903.2	1901.5	1929.2	1940.6	1932.5
147.5°	1956.8	1952.1	1979.7	1987.8	1981.5
150°	2009.1	1997.8	2023.9	2033.5	2025.4
152.5°	2053.1	2040.1	2064.6	2074.4	2063.0
155°	2095.6	2081.0	2100.5	2110.2	2097.3
157.5°	2129.8	2116.8	2131.5	2143.0	2129.8
160°	2159.3	2149.4	2159.3	2168.9	2157.5
162.5°	2185.2	2175.5	2183.6	2195.1	2180.4
165°	2208.0	2198.4	2203.2	2214.6	2203.2
167.5°	2226.1	2216.1	2221.2	2232.6	2218.0
170°	2240.8	2230.9	2234.2	2245.6	2230.9
172.5°	2250.5	2240.8	2244.1	2255.4	2240.8
175°	2258.6	2247.1	2250.5	2261.8	2245.6
177.5°	2261.8	2250.5	2252.2	2263.7	2248.9
180°	2253.7	2253.7	2253.7	2253.7	2253.7

TEST NUMBER: P926019

CATALOG NUMBER: DFN2DIP-SQ4F0-140D070US950-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.02	13.97	13.86	14.83	15.90	8.98	9.93	9.82	10.79	11.86
	3H	14.71	15.56	15.56	16.43	17.53	10.18	11.03	11.03	11.90	12.99
	4H	15.32	16.13	16.20	17.00	18.11	10.63	11.43	11.50	12.31	13.42
	6H	15.76	16.50	16.64	17.38	18.50	10.96	11.70	11.84	12.58	13.70
	8H	15.89	16.59	16.78	17.49	18.61	11.05	11.76	11.95	12.66	13.78
	12H	15.96	16.63	16.85	17.52	18.67	11.10	11.77	12.00	12.66	13.81
4H	2H	13.05	13.85	13.93	14.73	15.84	9.59	10.39	10.47	11.27	12.38
	3H	14.89	15.56	15.78	16.47	17.59	10.95	11.62	11.84	12.53	13.65
	4H	15.59	16.20	16.49	17.10	18.26	11.51	12.11	12.40	13.02	14.17
	6H	16.12	16.64	17.03	17.57	18.72	11.93	12.45	12.85	13.38	14.54
	8H	16.30	16.79	17.22	17.71	18.88	12.06	12.55	12.98	13.47	14.64
	12H	16.40	16.84	17.34	17.78	18.95	12.13	12.57	13.07	13.51	14.69
8H	4H	15.57	16.06	16.49	16.98	18.15	11.80	12.28	12.71	13.21	14.37
	6H	16.15	16.55	17.09	17.51	18.68	12.32	12.72	13.26	13.69	14.85
	8H	16.37	16.72	17.32	17.68	18.86	12.51	12.87	13.47	13.83	15.01
	12H	16.51	16.83	17.47	17.78	19.01	12.64	12.95	13.59	13.90	15.13
12H	4H	15.53	15.97	16.46	16.91	18.08	11.81	12.25	12.74	13.19	14.36
	6H	16.12	16.48	17.07	17.43	18.62	12.37	12.73	13.32	13.68	14.87
	8H	16.35	16.67	17.31	17.61	18.85	12.59	12.90	13.54	13.85	15.08

END OF REPORT