

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P917984

Luminaire Tested: DFN2DIP-TR2F0-060D030US930-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P917984
REPORT IS A COMBINATION OF REPORTS P900239 AND P897145
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR2F0-060D030US930-FLLFLL
Description: 2 foot, Triangle Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7007.5 lumens
Efficiency: N/A
Efficacy: 86.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.04' x L: 2.36' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 81.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P917984

CATALOG NUMBER: DFN2DIP-TR2F0-060D030US930-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P917984

CATALOG NUMBER: DFN2DIP-TR2F0-060D030US930-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	112	112	112	112	106	106	106	106	94	94	94	83	83	83	74	74	74
1	102	98	94	90	96	92	89	86	83	80	77	74	71	70	65	64	62
2	93	85	79	74	88	81	75	70	72	68	64	65	61	58	57	55	52
3	85	75	67	61	80	71	64	59	64	58	54	57	53	49	51	48	45
4	78	67	58	52	73	63	56	50	57	51	46	51	46	42	46	42	39
5	71	59	51	45	67	56	49	43	51	45	40	46	41	37	41	37	34
6	66	53	45	39	62	51	43	38	46	40	35	41	36	32	37	33	30
7	61	48	40	34	58	46	39	33	42	36	31	38	33	29	34	30	26
8	57	44	36	31	54	42	35	30	38	32	28	35	29	26	31	27	24
9	53	40	33	27	50	39	31	26	35	29	25	32	27	23	29	25	21
10	50	37	30	25	47	36	29	24	32	27	22	30	25	21	27	23	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4245	4245	4245
5°	4246	4177	4207
10°	4205	4111	4143
15°	4137	4034	4047
20°	4047	3930	3948
25°	3958	3809	3836
30°	3847	3695	3695
35°	3742	3562	3546
40°	3613	3427	3404
45°	3484	3292	3258
50°	3343	3149	3091
55°	3195	2985	2934
60°	3027	2791	2755
65°	2843	2588	2544
70°	2609	2341	2316
75°	2287	2046	2094
80°	1896	1669	1693
85°	1292	1051	1052

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3484 cd/sqm

TEST NUMBER: P917984

CATALOG NUMBER: DFN2DIP-TR2F0-060D030US930-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	179.1	2.6
10°-20°	504.1	7.2
20°-30°	740.8	10.6
30°-40°	860.4	12.3
40°-50°	859.3	12.3
50°-60°	749.3	10.7
60°-70°	553.9	7.9
70°-80°	313.4	4.5
80°-90°	84.9	1.2
90°-100°	47.9	0.7
100°-110°	152.1	2.2
110°-120°	260.3	3.7
120°-130°	342.3	4.9
130°-140°	384.2	5.5
140°-150°	376.8	5.4
150°-160°	316.1	4.5
160°-170°	209.6	3.0
170°-180°	73.3	1.0
0°-30°	1424.0	20.3
0°-40°	2284.3	32.6
0°-60°	3892.9	55.6
0°-90°	4845.1	69.1
90°-120°	460.2	6.6
90°-150°	1563.5	22.3
90°-180°	2162.0	30.9
0°-180°	7007.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1903	1903	1903	1903	1903	
5°	1903	1896	1876	1891	1887	181
15°	1812	1801	1777	1785	1776	510
25°	1640	1625	1594	1598	1594	755
35°	1415	1397	1367	1356	1347	884
45°	1151	1138	1111	1091	1084	889
55°	871	860	838	816	807	779
65°	588	577	558	542	533	581
75°	307	304	295	284	287	328
85°	75	73	71	66	64	84
90°	1	8	23	21	22	7
95°	34	41	42	42	41	38
105°	140	142	144	145	145	148
115°	261	265	264	263	261	258
125°	380	386	384	382	381	339
135°	491	499	500	499	497	380
145°	597	601	605	606	603	373
155°	682	684	686	689	687	314
165°	742	741	741	746	743	209
175°	772	770	769	774	770	73
180°	774	774	774	774	774	

TEST NUMBER: P917984

CATALOG NUMBER: DFN2DIP-TR2F0-060D030US930-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1903.4	1903.4	1903.4	1903.4	1903.4
2.5°	1914.5	1905.4	1885.1	1903.4	1899.9
5°	1903.4	1896.2	1876.0	1890.6	1887.1
7.5°	1890.6	1879.8	1859.5	1874.3	1870.6
10°	1870.6	1857.8	1835.8	1850.4	1844.9
12.5°	1843.1	1832.1	1810.2	1819.3	1815.7
15°	1811.9	1801.1	1777.2	1784.6	1775.5
17.5°	1773.5	1762.7	1738.8	1747.8	1738.8
20°	1731.4	1720.5	1694.8	1700.3	1693.1
22.5°	1689.5	1672.9	1649.0	1649.0	1645.4
25°	1639.9	1625.4	1594.2	1597.7	1594.2
27.5°	1584.9	1572.1	1548.4	1543.0	1533.9
30°	1530.2	1515.4	1488.1	1482.6	1475.2
32.5°	1471.5	1460.7	1431.3	1420.2	1412.9
35°	1414.9	1396.6	1367.3	1356.2	1347.0
37.5°	1350.8	1334.2	1305.0	1292.1	1283.0
40°	1284.9	1270.2	1240.9	1224.6	1217.2
42.5°	1220.8	1206.1	1177.0	1158.5	1147.6
45°	1151.4	1138.5	1110.9	1091.0	1083.5
47.5°	1083.5	1070.7	1041.5	1021.2	1010.3
50°	1012.1	1003.0	977.4	951.7	942.6
52.5°	942.6	929.8	906.0	885.9	873.1
55°	871.3	860.2	838.3	816.4	807.2
57.5°	799.9	790.8	766.9	744.9	737.5
60°	728.4	721.2	695.6	675.4	669.9
62.5°	658.8	646.0	627.8	609.5	602.2
65°	587.6	576.6	558.3	541.8	532.6
67.5°	514.4	505.1	488.8	476.0	468.6
70°	446.6	439.3	422.7	409.9	402.8
72.5°	377.1	369.7	360.6	347.8	342.3
75°	307.4	303.9	294.6	283.7	287.4
77.5°	245.2	237.9	234.2	228.8	223.3
80°	183.1	181.2	177.5	172.0	168.4
82.5°	124.5	124.5	122.7	115.4	115.4
85°	74.9	73.2	71.4	65.8	64.1
87.5°	33.0	29.4	25.6	20.2	18.3
90°	0.7	8.4	22.8	21.4	22.2
92.5°	14.4	19.6	20.3	21.0	21.0
95°	34.1	40.6	41.7	41.7	40.6
97.5°	56.7	62.7	65.3	65.3	65.3
100°	82.8	88.1	90.0	90.0	89.4
102.5°	110.3	114.3	116.8	117.6	116.8
105°	140.4	142.3	143.7	144.8	144.8
107.5°	170.2	173.0	173.0	173.5	170.2
110°	199.2	202.9	202.9	202.9	201.1



TEST NUMBER: P917984

CATALOG NUMBER: DFN2DIP-TR2F0-060D030US930-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	230.4	234.4	233.7	231.8	230.4
115°	261.2	264.9	263.7	263.1	261.2
117.5°	291.7	296.9	293.6	291.7	289.8
120°	322.5	327.7	322.5	322.5	320.4
122.5°	350.5	357.0	353.8	351.9	350.5
125°	379.9	385.7	383.8	381.7	381.1
127.5°	408.5	415.8	413.3	410.4	408.5
130°	435.4	443.8	442.6	441.2	438.6
132.5°	465.5	472.0	472.5	469.2	467.3
135°	491.4	498.6	500.0	499.3	497.4
137.5°	520.2	526.1	527.3	526.8	524.0
140°	545.7	551.5	554.8	554.8	552.2
142.5°	571.9	577.6	579.5	580.2	577.6
145°	596.6	601.2	605.0	605.6	603.1
147.5°	618.7	624.5	627.3	628.5	625.9
150°	641.6	645.6	648.1	650.2	648.1
152.5°	661.9	665.8	669.0	671.6	669.0
155°	682.2	684.0	686.1	689.3	687.3
157.5°	699.6	701.0	702.2	706.9	703.6
160°	715.3	716.6	717.4	721.3	718.5
162.5°	729.7	729.7	730.4	734.8	731.6
165°	742.1	741.4	741.4	746.0	742.7
167.5°	753.3	751.1	751.1	755.8	752.5
170°	761.7	759.8	759.1	763.8	759.8
172.5°	767.4	765.6	764.9	769.6	765.6
175°	772.2	770.3	768.9	773.6	769.6
177.5°	774.7	772.8	771.4	775.4	771.4
180°	773.6	773.6	773.6	773.6	773.6

TEST NUMBER: P917984

CATALOG NUMBER: DFN2DIP-TR2F0-060D030US930-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.77	14.83	14.54	15.63	16.60	13.35	14.41	14.12	15.21	16.18
	3H	15.42	16.38	16.21	17.18	18.18	14.96	15.92	15.75	16.72	17.72
	4H	16.00	16.91	16.81	17.72	18.73	15.54	16.45	16.35	17.26	18.27
	6H	16.39	17.23	17.21	18.05	19.07	15.93	16.77	16.75	17.59	18.61
	8H	16.50	17.29	17.32	18.13	19.15	16.04	16.83	16.86	17.67	18.70
	12H	16.54	17.30	17.37	18.13	19.18	16.08	16.84	16.91	17.67	18.72
4H	2H	14.25	15.15	15.05	15.96	16.97	13.91	14.81	14.71	15.62	16.63
	3H	16.10	16.86	16.92	17.70	18.73	15.72	16.47	16.54	17.32	18.35
	4H	16.81	17.49	17.64	18.34	19.39	16.41	17.10	17.25	17.94	19.00
	6H	17.31	17.91	18.16	18.78	19.83	16.91	17.51	17.76	18.38	19.44
	8H	17.45	18.01	18.31	18.87	19.95	17.06	17.61	17.91	18.48	19.55
	12H	17.53	18.03	18.40	18.91	19.99	17.12	17.62	17.99	18.51	19.58
8H	4H	17.01	17.56	17.86	18.43	19.50	16.66	17.21	17.51	18.08	19.15
	6H	17.62	18.08	18.50	18.99	20.06	17.27	17.73	18.15	18.64	19.71
	8H	17.83	18.24	18.72	19.14	20.23	17.47	17.88	18.36	18.78	19.87
	12H	17.95	18.31	18.85	19.21	20.35	17.58	17.94	18.48	18.84	19.98
12H	4H	17.00	17.50	17.88	18.39	19.46	16.66	17.16	17.53	18.04	19.12
	6H	17.65	18.06	18.54	18.96	20.05	17.31	17.72	18.20	18.62	19.70
	8H	17.88	18.24	18.78	19.14	20.28	17.54	17.90	18.43	18.79	19.93