

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P926047

Luminaire Tested: DFN2DIP-SQ4F0-140D160US950-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P926047
REPORT IS A COMBINATION OF REPORTS P901738 AND P898471
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-140D160US950-RLLONL
Description: 4 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 26464.0 lumens
Efficiency: N/A
Efficacy: 99.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 265.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P926047

CATALOG NUMBER: DFN2DIP-SQ4F0-140D160US950-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P926047

CATALOG NUMBER: DFN2DIP-SQ4F0-140D160US950-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	79	79	79	64	64	64	50	50	50
1	97	92	89	85	88	85	82	79	70	68	66	57	55	54	44	44	43
2	88	81	75	70	81	75	70	65	62	58	55	50	48	46	40	38	37
3	81	72	65	59	74	66	60	55	55	51	47	45	42	39	36	33	32
4	74	64	56	50	68	59	52	47	49	44	40	40	37	34	32	30	28
5	68	57	49	43	62	53	46	41	44	39	35	36	33	30	29	26	24
6	63	51	43	38	57	47	40	35	40	35	31	33	29	26	26	24	22
7	58	46	39	33	53	43	36	31	36	31	27	30	26	23	24	21	19
8	54	42	35	29	49	39	32	28	33	28	24	28	24	21	22	20	17
9	50	38	31	26	46	36	29	25	30	25	22	25	22	19	21	18	16
10	47	35	28	24	43	33	27	22	28	23	20	24	20	17	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3873	3873	3873
5°	3879	3813	3837
10°	3841	3739	3714
15°	3788	3616	3522
20°	3718	3446	3286
25°	3646	3256	3058
30°	3550	3061	2768
35°	3456	2851	2514
40°	3360	2634	2222
45°	3248	2392	1958
50°	3133	2149	1699
55°	3013	1889	1451
60°	2873	1616	1195
65°	2713	1339	1077
70°	2519	1081	976
75°	2275	955	891
80°	1922	803	777
85°	1337	540	591

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3248 cd/sqm

TEST NUMBER: P926047

CATALOG NUMBER: DFN2DIP-SQ4F0-140D160US950-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	517.3	2.0
10°-20°	1420.2	5.4
20°-30°	1993.9	7.5
30°-40°	2173.5	8.2
40°-50°	1997.7	7.5
50°-60°	1568.9	5.9
60°-70°	1021.2	3.9
70°-80°	525.7	2.0
80°-90°	143.3	0.5
90°-100°	169.9	0.6
100°-110°	633.2	2.4
110°-120°	1679.4	6.3
120°-130°	2785.4	10.5
130°-140°	2958.8	11.2
140°-150°	2749.9	10.4
150°-160°	2210.8	8.4
160°-170°	1424.6	5.4
170°-180°	490.3	1.9
0°-30°	3931.5	14.9
0°-40°	6105.0	23.1
0°-60°	9671.6	36.5
0°-90°	11361.7	42.9
90°-120°	2482.5	9.4
90°-150°	10976.6	41.5
90°-180°	15102.0	57.1
0°-180°	26464.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	5520	5520	5520	5520	5520	
5°	5520	5495	5430	5475	5460	523
15°	5250	5195	5026	4931	4881	1479
25°	4766	4606	4276	4072	3996	2192
35°	4106	3852	3412	3097	2987	2570
45°	3357	3022	2498	2143	2023	2593
55°	2552	2163	1623	1324	1229	2281
65°	1724	1319	869	700	684	1709
75°	919	569	400	365	360	972
85°	215	110	95	95	95	246
90°	4	45	74	93	100	25
95°	242	119	145	164	160	287
105°	1133	1245	228	268	283	1211
115°	2143	2206	2300	574	306	2110
125°	3030	3079	3150	3176	3187	2703
135°	3750	3810	3843	3881	3873	2897
145°	4350	4346	4410	4436	4417	2721
155°	4790	4756	4801	4823	4794	2207
165°	5047	5025	5036	5062	5036	1426
175°	5162	5136	5144	5170	5133	491
180°	5151	5151	5151	5151	5151	

TEST NUMBER: P926047

CATALOG NUMBER: DFN2DIP-SQ4F0-140D160US950-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	5520.0	5520.0	5520.0	5520.0	5520.0
2.5°	5544.9	5520.0	5464.9	5515.3	5505.2
5°	5520.0	5495.1	5429.9	5475.0	5460.1
7.5°	5475.0	5445.2	5375.3	5395.0	5370.1
10°	5415.1	5380.1	5280.5	5265.0	5235.4
12.5°	5340.3	5295.3	5160.1	5130.4	5075.4
15°	5250.2	5195.1	5025.5	4930.7	4880.9
17.5°	5145.3	5065.3	4855.4	4745.7	4665.6
20°	5025.5	4925.3	4675.7	4551.2	4441.0
22.5°	4895.6	4780.7	4490.8	4321.1	4246.4
25°	4765.8	4605.7	4276.1	4071.5	3996.2
27.5°	4611.1	4441.0	4076.3	3841.5	3726.5
30°	4446.2	4256.0	3856.4	3601.9	3466.7
32.5°	4286.1	4056.1	3647.0	3347.0	3221.9
35°	4106.5	3851.6	3412.2	3097.4	2987.1
37.5°	3931.6	3656.5	3192.2	2847.2	2722.6
40°	3746.6	3447.2	2962.2	2607.7	2477.8
42.5°	3556.9	3237.3	2732.7	2362.8	2238.2
45°	3357.0	3022.1	2498.0	2142.8	2023.1
47.5°	3167.3	2812.8	2273.2	1918.1	1808.4
50°	2957.4	2602.9	2053.2	1708.2	1603.8
52.5°	2752.3	2377.6	1843.3	1513.7	1418.8
55°	2552.5	2162.9	1623.4	1324.0	1229.0
57.5°	2347.9	1948.3	1428.9	1149.1	1069.1
60°	2138.0	1738.4	1223.8	969.4	889.3
62.5°	1933.5	1533.8	1048.9	809.3	769.6
65°	1723.6	1318.6	869.2	699.6	684.2
67.5°	1523.7	1118.9	699.6	614.3	599.4
70°	1313.8	924.3	579.3	529.5	509.3
72.5°	1114.1	744.1	484.4	444.7	434.6
75°	919.0	569.3	399.6	364.6	359.8
77.5°	724.6	404.4	314.8	294.7	284.6
80°	544.4	289.9	239.5	220.0	220.0
82.5°	379.5	195.0	164.9	154.7	154.7
85°	214.6	109.7	94.8	94.8	94.8
87.5°	80.0	39.8	39.8	35.0	35.0
90°	3.5	44.7	74.3	93.4	100.5
92.5°	93.4	78.3	89.4	96.9	100.5
95°	242.1	119.1	145.2	164.2	160.3
97.5°	436.0	130.6	189.8	201.4	204.9
100°	660.0	149.2	212.5	242.1	249.7
102.5°	905.6	898.6	220.0	260.7	272.2
105°	1133.2	1245.2	227.5	268.3	283.2
107.5°	1397.8	1490.8	235.1	275.8	290.8
110°	1651.5	1729.4	652.4	279.7	294.3

TEST NUMBER: P926047

CATALOG NUMBER: DFN2DIP-SQ4F0-140D160US950-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1890.1	1956.9	1893.6	286.9	298.3
115°	2143.3	2206.5	2299.9	574.1	305.9
117.5°	2363.2	2437.6	2501.4	1968.0	991.5
120°	2609.4	2665.1	2732.4	2777.1	2273.9
122.5°	2817.8	2877.6	2952.3	2974.5	2978.5
125°	3030.3	3078.9	3149.8	3176.0	3187.0
127.5°	3224.1	3276.4	3332.6	3369.8	3373.3
130°	3407.0	3466.7	3507.5	3548.6	3545.1
132.5°	3593.3	3642.0	3682.7	3716.4	3712.9
135°	3750.0	3809.8	3843.0	3880.6	3873.0
137.5°	3913.8	3958.5	3996.1	4033.3	4022.3
140°	4074.1	4104.1	4144.8	4178.5	4159.9
142.5°	4208.6	4234.7	4283.0	4312.7	4294.0
145°	4350.2	4346.2	4409.6	4435.6	4417.1
147.5°	4472.8	4461.8	4525.1	4543.7	4529.0
150°	4592.4	4566.2	4626.0	4648.2	4629.6
152.5°	4692.8	4663.2	4719.0	4741.6	4715.4
155°	4789.7	4756.5	4801.3	4823.4	4793.8
157.5°	4868.2	4838.5	4872.1	4898.2	4868.2
160°	4935.4	4912.8	4935.4	4957.6	4931.4
162.5°	4994.8	4972.6	4991.1	5017.3	4983.7
165°	5046.9	5024.8	5035.9	5062.0	5035.9
167.5°	5088.2	5065.5	5077.1	5103.1	5069.6
170°	5121.7	5099.2	5106.7	5132.8	5099.2
172.5°	5143.9	5121.7	5129.3	5155.4	5121.7
175°	5162.5	5136.3	5143.9	5170.0	5132.8
177.5°	5170.0	5143.9	5147.9	5174.0	5140.3
180°	5151.4	5151.4	5151.4	5151.4	5151.4

TEST NUMBER: P926047

CATALOG NUMBER: DFN2DIP-SQ4F0-140D160US950-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.17	11.94	12.19	12.97	14.34	7.13	7.90	8.15	8.93	10.30
	3H	12.84	13.54	13.88	14.57	15.96	8.31	9.01	9.34	10.04	11.43
	4H	13.45	14.11	14.50	15.15	16.55	8.76	9.42	9.81	10.45	11.85
	6H	13.88	14.48	14.93	15.52	16.93	9.08	9.68	10.13	10.73	12.14
	8H	14.00	14.58	15.06	15.63	17.04	9.17	9.74	10.23	10.80	12.21
	12H	14.07	14.61	15.13	15.66	17.09	9.21	9.76	10.27	10.81	12.24
4H	2H	11.18	11.83	12.23	12.87	14.27	7.72	8.38	8.77	9.41	10.81
	3H	13.01	13.55	14.07	14.62	16.03	9.06	9.61	10.12	10.68	12.09
	4H	13.70	14.20	14.76	15.26	16.69	9.61	10.11	10.68	11.17	12.60
	6H	14.22	14.65	15.29	15.73	17.15	10.03	10.46	11.10	11.54	12.97
	8H	14.39	14.79	15.47	15.87	17.31	10.16	10.56	11.23	11.63	13.07
	12H	14.49	14.85	15.58	15.94	17.38	10.22	10.58	11.31	11.67	13.12
8H	4H	13.66	14.06	14.74	15.14	16.58	9.89	10.29	10.96	11.36	12.81
	6H	14.23	14.56	15.33	15.68	17.12	10.41	10.74	11.50	11.85	13.29
	8H	14.45	14.74	15.56	15.84	17.30	10.60	10.89	11.70	11.99	13.45
	12H	14.59	14.85	15.70	15.94	17.44	10.72	10.97	11.82	12.06	13.56
12H	4H	13.61	13.98	14.71	15.06	16.51	9.89	10.25	10.98	11.34	12.79
	6H	14.21	14.50	15.31	15.60	17.06	10.46	10.75	11.56	11.84	13.30
	8H	14.43	14.68	15.54	15.78	17.28	10.67	10.92	11.77	12.01	13.51

END OF REPORT