

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P926053

Luminaire Tested: DFN2DIP-SQ4F0-160D070US950-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P926053
REPORT IS A COMBINATION OF REPORTS P901613 AND P898471
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-160D070US950-FLLONL
Description: 4 foot, Square Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 21722.6 lumens
Efficiency: N/A
Efficacy: 99.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 218.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P926053

CATALOG NUMBER: DFN2DIP-SQ4F0-160D070US950-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P926053

CATALOG NUMBER: DFN2DIP-SQ4F0-160D070US950-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	112	112	112	112	106	106	106	106	94	94	94	84	84	84	74	74	74
1	102	98	94	90	96	93	89	86	83	80	78	74	72	70	66	64	63
2	93	85	79	74	88	81	75	70	73	68	64	65	61	58	58	55	53
3	85	75	68	61	80	71	64	59	64	59	54	57	53	49	51	48	45
4	78	67	58	52	73	63	56	50	57	51	46	51	46	42	46	42	39
5	72	59	51	45	67	57	49	43	51	45	40	46	41	37	41	37	34
6	66	53	45	39	62	51	43	38	46	40	35	42	36	32	37	33	30
7	61	48	40	34	58	46	39	33	42	36	31	38	33	29	34	30	27
8	57	44	36	31	54	42	35	30	38	32	28	35	30	26	31	27	24
9	53	40	33	27	50	39	31	27	35	29	25	32	27	23	29	25	22
10	50	37	30	25	47	36	29	24	33	27	23	30	25	21	27	23	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4167	4167	4167
5°	4174	4110	4138
10°	4140	4056	4083
15°	4079	3990	3997
20°	3997	3898	3909
25°	3915	3788	3806
30°	3812	3685	3675
35°	3715	3564	3537
40°	3595	3442	3406
45°	3476	3320	3272
50°	3346	3192	3116
55°	3209	3043	2973
60°	3054	2867	2809
65°	2886	2684	2616
70°	2672	2462	2409
75°	2374	2196	2220
80°	2017	1857	1855
85°	1458	1270	1246

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3476 cd/sqm

TEST NUMBER: P926053

CATALOG NUMBER: DFN2DIP-SQ4F0-160D070US950-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	559.0	2.6
10°-20°	1572.8	7.2
20°-30°	2311.4	10.6
30°-40°	2684.6	12.4
40°-50°	2681.3	12.3
50°-60°	2338.0	10.8
60°-70°	1728.3	8.0
70°-80°	977.8	4.5
80°-90°	262.0	1.2
90°-100°	74.3	0.3
100°-110°	277.0	1.3
110°-120°	734.8	3.4
120°-130°	1218.6	5.6
130°-140°	1294.5	6.0
140°-150°	1203.1	5.5
150°-160°	967.2	4.5
160°-170°	623.3	2.9
170°-180°	214.5	1.0
0°-30°	4443.3	20.5
0°-40°	7127.9	32.8
0°-60°	12147.2	55.9
0°-90°	15115.3	69.6
90°-120°	1086.1	5.0
90°-150°	4802.2	22.1
90°-180°	6607.0	30.4
0°-180°	21722.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	5939	5939	5939	5939	5939	
5°	5939	5917	5854	5899	5888	564
15°	5654	5620	5545	5568	5540	1592
25°	5117	5072	4975	4986	4975	2355
35°	4415	4358	4266	4232	4203	2757
45°	3593	3552	3466	3404	3381	2773
55°	2719	2684	2616	2547	2519	2431
65°	1834	1799	1742	1691	1662	1813
75°	959	948	919	885	897	1024
85°	234	228	223	205	200	261
90°	2	20	32	41	44	20
95°	106	52	64	72	70	125
105°	496	545	100	117	124	530
115°	938	965	1006	251	134	923
125°	1326	1347	1378	1390	1394	1182
135°	1641	1667	1681	1698	1694	1267
145°	1903	1902	1929	1941	1932	1190
155°	2096	2081	2100	2110	2097	966
165°	2208	2198	2203	2215	2203	624
175°	2259	2247	2250	2262	2246	215
180°	2254	2254	2254	2254	2254	

TEST NUMBER: P926053

CATALOG NUMBER: DFN2DIP-SQ4F0-160D070US950-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	5939.3	5939.3	5939.3	5939.3	5939.3
2.5°	5973.9	5945.3	5882.4	5939.3	5928.3
5°	5939.3	5916.9	5853.8	5899.3	5888.4
7.5°	5899.3	5865.4	5802.3	5848.4	5836.9
10°	5836.9	5796.9	5728.5	5773.9	5756.9
12.5°	5750.9	5716.9	5648.4	5677.0	5665.4
15°	5653.9	5620.0	5545.4	5568.5	5540.0
17.5°	5534.0	5500.0	5425.5	5453.9	5425.5
20°	5402.4	5368.5	5288.5	5305.5	5283.1
22.5°	5271.6	5220.1	5145.5	5145.5	5134.0
25°	5117.1	5071.7	4974.6	4985.6	4974.6
27.5°	4945.5	4905.6	4831.6	4814.7	4786.2
30°	4774.7	4728.7	4643.2	4626.2	4603.2
32.5°	4591.7	4557.8	4466.2	4431.7	4408.7
35°	4414.8	4357.9	4266.3	4231.8	4203.3
37.5°	4214.9	4163.4	4071.9	4031.8	4003.4
40°	4009.4	3963.4	3871.9	3821.0	3798.0
42.5°	3809.5	3763.4	3672.5	3615.0	3581.0
45°	3592.6	3552.5	3466.5	3404.1	3381.1
47.5°	3381.1	3341.1	3249.6	3186.6	3152.7
50°	3158.1	3129.6	3049.7	2969.6	2941.2
52.5°	2941.2	2901.2	2827.3	2764.2	2724.2
55°	2718.8	2684.3	2615.8	2547.3	2518.8
57.5°	2495.9	2467.3	2392.8	2324.3	2301.3
60°	2272.8	2250.4	2170.4	2107.4	2090.4
62.5°	2055.9	2015.9	1958.9	1902.0	1879.0
65°	1833.5	1799.0	1742.0	1690.6	1662.1
67.5°	1605.1	1576.0	1525.2	1485.1	1462.1
70°	1393.6	1370.6	1319.1	1279.1	1256.7
72.5°	1176.7	1153.7	1125.2	1085.2	1068.3
75°	959.2	948.3	919.2	885.2	896.8
77.5°	765.3	742.3	730.8	713.8	696.8
80°	571.4	565.3	553.8	536.8	525.4
82.5°	388.4	388.4	382.9	359.9	359.9
85°	233.9	228.4	222.9	205.4	200.0
87.5°	103.0	91.5	79.9	63.1	57.0
90°	1.5	19.6	32.5	40.8	44.0
92.5°	40.8	34.2	39.1	42.5	44.0
95°	105.9	52.1	63.5	71.8	70.1
97.5°	190.7	57.1	83.1	88.1	89.7
100°	288.8	65.3	92.9	105.9	109.2
102.5°	396.2	393.1	96.3	114.1	119.1
105°	495.8	544.7	99.5	117.3	123.9
107.5°	611.5	652.2	102.8	120.7	127.3
110°	722.6	756.6	285.4	122.4	128.8

TEST NUMBER: P926053

CATALOG NUMBER: DFN2DIP-SQ4F0-160D070US950-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	826.9	856.1	828.5	125.5	130.5
115°	937.7	965.4	1006.2	251.2	133.8
117.5°	1033.9	1066.5	1094.3	861.0	433.8
120°	1141.6	1166.0	1195.5	1215.0	994.8
122.5°	1232.8	1258.9	1291.7	1301.4	1303.1
125°	1325.8	1347.0	1378.1	1389.5	1394.3
127.5°	1410.6	1433.4	1458.0	1474.3	1475.8
130°	1490.5	1516.7	1534.5	1552.5	1551.0
132.5°	1572.1	1593.4	1611.2	1625.9	1624.4
135°	1640.6	1666.7	1681.3	1697.7	1694.5
137.5°	1712.2	1731.9	1748.3	1764.6	1759.7
140°	1782.4	1795.5	1813.4	1828.1	1819.9
142.5°	1841.2	1852.7	1873.8	1886.7	1878.6
145°	1903.2	1901.5	1929.2	1940.6	1932.5
147.5°	1956.8	1952.1	1979.7	1987.8	1981.5
150°	2009.1	1997.8	2023.9	2033.5	2025.4
152.5°	2053.1	2040.1	2064.6	2074.4	2063.0
155°	2095.6	2081.0	2100.5	2110.2	2097.3
157.5°	2129.8	2116.8	2131.5	2143.0	2129.8
160°	2159.3	2149.4	2159.3	2168.9	2157.5
162.5°	2185.2	2175.5	2183.6	2195.1	2180.4
165°	2208.0	2198.4	2203.2	2214.6	2203.2
167.5°	2226.1	2216.1	2221.2	2232.6	2218.0
170°	2240.8	2230.9	2234.2	2245.6	2230.9
172.5°	2250.5	2240.8	2244.1	2255.4	2240.8
175°	2258.6	2247.1	2250.5	2261.8	2245.6
177.5°	2261.8	2250.5	2252.2	2263.7	2248.9
180°	2253.7	2253.7	2253.7	2253.7	2253.7

TEST NUMBER: P926053

CATALOG NUMBER: DFN2DIP-SQ4F0-160D070US950-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.88	14.95	14.65	15.74	16.70	13.44	14.51	14.20	15.30	16.26
	3H	15.56	16.52	16.34	17.32	18.31	15.07	16.03	15.85	16.83	17.82
	4H	16.16	17.07	16.96	17.88	18.88	15.67	16.57	16.47	17.38	18.39
	6H	16.57	17.41	17.39	18.23	19.25	16.07	16.91	16.89	17.73	18.75
	8H	16.69	17.49	17.51	18.32	19.34	16.19	16.98	17.01	17.82	18.84
	12H	16.74	17.51	17.57	18.34	19.38	16.23	17.00	17.06	17.83	18.87
4H	2H	14.37	15.27	15.17	16.08	17.09	14.01	14.92	14.82	15.73	16.73
	3H	16.26	17.01	17.07	17.86	18.88	15.85	16.61	16.66	17.45	18.47
	4H	16.98	17.67	17.81	18.51	19.56	16.56	17.25	17.39	18.09	19.14
	6H	17.51	18.11	18.36	18.98	20.03	17.08	17.68	17.93	18.54	19.60
	8H	17.67	18.23	18.52	19.09	20.15	17.23	17.79	18.08	18.65	19.72
	12H	17.76	18.26	18.63	19.14	20.21	17.31	17.81	18.18	18.69	19.76
8H	4H	17.20	17.75	18.05	18.62	19.68	16.82	17.38	17.67	18.24	19.30
	6H	17.84	18.30	18.72	19.21	20.27	17.46	17.92	18.33	18.82	19.89
	8H	18.07	18.48	18.95	19.37	20.46	17.67	18.08	18.56	18.98	20.06
	12H	18.21	18.57	19.10	19.46	20.60	17.80	18.16	18.69	19.05	20.19
12H	4H	17.19	17.69	18.06	18.58	19.65	16.82	17.33	17.69	18.21	19.28
	6H	17.87	18.28	18.76	19.18	20.26	17.50	17.91	18.39	18.81	19.89
	8H	18.13	18.49	19.02	19.38	20.51	17.75	18.11	18.64	19.00	20.13