

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P926077

Luminaire Tested: DFN2DIP-SQ4F0-160D140US950-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P926077
REPORT IS A COMBINATION OF REPORTS P901721 AND P898471
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-160D140US950-FLLONL
Description: 4 foot, Square Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 28333.8 lumens
Efficiency: N/A
Efficacy: 104.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 272.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P926077

CATALOG NUMBER: DFN2DIP-SQ4F0-160D140US950-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P926077

CATALOG NUMBER: DFN2DIP-SQ4F0-160D140US950-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59
1	99	94	90	87	91	87	84	81	75	72	70	63	61	60	52	51	50
2	90	82	76	71	83	76	71	66	65	61	58	55	52	50	46	44	42
3	82	72	65	59	76	67	61	56	58	53	49	49	45	42	41	38	36
4	75	64	56	50	69	60	53	47	51	46	42	44	40	36	37	33	31
5	69	57	49	43	63	53	46	41	46	40	36	39	35	31	33	30	27
6	63	51	43	37	59	48	41	35	41	36	31	35	31	28	30	26	24
7	59	46	38	33	54	43	36	31	38	32	28	32	28	24	27	24	21
8	54	42	34	29	50	39	32	27	34	29	25	30	25	22	25	22	19
9	51	38	31	26	47	36	29	25	31	26	22	27	23	20	23	20	17
10	47	35	28	23	44	33	26	22	29	24	20	25	21	18	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4167	4167	4167
5°	4174	4110	4138
10°	4140	4056	4083
15°	4079	3990	3997
20°	3997	3898	3909
25°	3915	3788	3806
30°	3812	3685	3675
35°	3715	3564	3537
40°	3595	3442	3406
45°	3476	3320	3272
50°	3346	3192	3116
55°	3209	3043	2973
60°	3054	2867	2809
65°	2886	2684	2616
70°	2672	2462	2409
75°	2374	2196	2220
80°	2017	1857	1855
85°	1458	1270	1246

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3476 cd/sqm

TEST NUMBER: P926077

CATALOG NUMBER: DFN2DIP-SQ4F0-160D140US950-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	559.0	2.0
10°-20°	1572.8	5.6
20°-30°	2311.4	8.2
30°-40°	2684.6	9.5
40°-50°	2681.3	9.5
50°-60°	2338.0	8.3
60°-70°	1728.3	6.1
70°-80°	977.8	3.5
80°-90°	266.0	0.9
90°-100°	148.7	0.5
100°-110°	554.1	2.0
110°-120°	1469.5	5.2
120°-130°	2437.3	8.6
130°-140°	2588.9	9.1
140°-150°	2406.1	8.5
150°-160°	1934.5	6.8
160°-170°	1246.5	4.4
170°-180°	429.0	1.5
0°-30°	4443.3	15.7
0°-40°	7127.9	25.2
0°-60°	12147.2	42.9
0°-90°	15119.3	53.4
90°-120°	2172.2	7.7
90°-150°	9604.5	33.9
90°-180°	13215.0	46.6
0°-180°	28333.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	5939	5939	5939	5939	5939	
5°	5939	5917	5854	5899	5888	564
15°	5654	5620	5545	5568	5540	1592
25°	5117	5072	4975	4986	4975	2355
35°	4415	4358	4266	4232	4203	2757
45°	3593	3552	3466	3404	3381	2773
55°	2719	2684	2616	2547	2519	2431
65°	1834	1799	1742	1691	1662	1813
75°	959	948	919	885	897	1024
85°	234	228	223	205	200	261
90°	3	39	65	82	88	26
95°	212	104	127	144	140	251
105°	992	1090	199	235	248	1059
115°	1875	1931	2012	502	268	1846
125°	2652	2694	2756	2779	2789	2365
135°	3281	3334	3363	3396	3389	2535
145°	3806	3803	3858	3881	3865	2381
155°	4191	4162	4201	4220	4194	1931
165°	4416	4397	4406	4429	4406	1248
175°	4517	4494	4501	4524	4491	430
180°	4508	4508	4508	4508	4508	



TEST NUMBER: P926077

CATALOG NUMBER: DFN2DIP-SQ4F0-160D140US950-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	5939.3	5939.3	5939.3	5939.3	5939.3
2.5°	5973.9	5945.3	5882.4	5939.3	5928.3
5°	5939.3	5916.9	5853.8	5899.3	5888.4
7.5°	5899.3	5865.4	5802.3	5848.4	5836.9
10°	5836.9	5796.9	5728.5	5773.9	5756.9
12.5°	5750.9	5716.9	5648.4	5677.0	5665.4
15°	5653.9	5620.0	5545.4	5568.5	5540.0
17.5°	5534.0	5500.0	5425.5	5453.9	5425.5
20°	5402.4	5368.5	5288.5	5305.5	5283.1
22.5°	5271.6	5220.1	5145.5	5145.5	5134.0
25°	5117.1	5071.7	4974.6	4985.6	4974.6
27.5°	4945.5	4905.6	4831.6	4814.7	4786.2
30°	4774.7	4728.7	4643.2	4626.2	4603.2
32.5°	4591.7	4557.8	4466.2	4431.7	4408.7
35°	4414.8	4357.9	4266.3	4231.8	4203.3
37.5°	4214.9	4163.4	4071.9	4031.8	4003.4
40°	4009.4	3963.4	3871.9	3821.0	3798.0
42.5°	3809.5	3763.4	3672.5	3615.0	3581.0
45°	3592.6	3552.5	3466.5	3404.1	3381.1
47.5°	3381.1	3341.1	3249.6	3186.6	3152.7
50°	3158.1	3129.6	3049.7	2969.6	2941.2
52.5°	2941.2	2901.2	2827.3	2764.2	2724.2
55°	2718.8	2684.3	2615.8	2547.3	2518.8
57.5°	2495.9	2467.3	2392.8	2324.3	2301.3
60°	2272.8	2250.4	2170.4	2107.4	2090.4
62.5°	2055.9	2015.9	1958.9	1902.0	1879.0
65°	1833.5	1799.0	1742.0	1690.6	1662.1
67.5°	1605.1	1576.0	1525.2	1485.1	1462.1
70°	1393.6	1370.6	1319.1	1279.1	1256.7
72.5°	1176.7	1153.7	1125.2	1085.2	1068.3
75°	959.2	948.3	919.2	885.2	896.8
77.5°	765.3	742.3	730.8	713.8	696.8
80°	571.4	565.3	553.8	536.8	525.4
82.5°	388.4	388.4	382.9	359.9	359.9
85°	233.9	228.4	222.9	205.4	200.0
87.5°	103.0	91.5	79.9	63.1	57.0
90°	3.1	39.1	65.1	81.8	88.0
92.5°	81.8	68.6	78.2	84.8	88.0
95°	211.9	104.2	127.1	143.7	140.2
97.5°	381.5	114.3	166.2	176.2	179.4
100°	577.5	130.5	185.9	211.9	218.5
102.5°	792.4	786.2	192.5	228.1	238.2
105°	991.5	1089.5	199.1	234.7	247.8
107.5°	1223.1	1304.4	205.7	241.3	254.4
110°	1445.0	1513.2	570.9	244.8	257.6

TEST NUMBER: P926077

CATALOG NUMBER: DFN2DIP-SQ4F0-160D140US950-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1653.8	1712.2	1656.9	251.0	261.0
115°	1875.4	1930.7	2012.5	502.4	267.6
117.5°	2067.8	2132.9	2188.7	1722.0	867.6
120°	2283.2	2332.0	2390.8	2429.9	1989.6
122.5°	2465.6	2517.9	2583.3	2602.7	2606.2
125°	2651.5	2694.1	2756.1	2778.9	2788.6
127.5°	2821.2	2866.9	2916.0	2948.5	2951.7
130°	2981.1	3033.4	3069.0	3105.1	3101.9
132.5°	3144.2	3186.7	3222.4	3251.8	3248.8
135°	3281.3	3333.6	3362.6	3395.5	3388.9
137.5°	3424.6	3463.7	3496.6	3529.1	3519.5
140°	3564.8	3591.1	3626.7	3656.2	3639.9
142.5°	3682.5	3705.3	3747.6	3773.5	3757.2
145°	3806.5	3802.9	3858.4	3881.3	3864.9
147.5°	3913.8	3904.1	3959.5	3975.7	3962.9
150°	4018.3	3995.4	4047.7	4067.1	4050.9
152.5°	4106.2	4080.3	4129.1	4148.9	4126.0
155°	4191.0	4162.0	4201.1	4220.5	4194.5
157.5°	4259.6	4233.7	4263.1	4285.9	4259.6
160°	4318.5	4298.7	4318.5	4337.8	4315.0
162.5°	4370.4	4351.0	4367.3	4390.1	4360.7
165°	4416.1	4396.7	4406.4	4429.2	4406.4
167.5°	4452.1	4432.4	4442.4	4465.3	4435.8
170°	4481.5	4461.8	4468.3	4491.2	4461.8
172.5°	4500.9	4481.5	4488.1	4511.0	4481.5
175°	4517.2	4494.3	4500.9	4523.8	4491.2
177.5°	4523.8	4500.9	4504.4	4527.2	4497.8
180°	4507.5	4507.5	4507.5	4507.5	4507.5

TEST NUMBER: P926077

CATALOG NUMBER: DFN2DIP-SQ4F0-160D140US950-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.55	13.44	13.48	14.39	15.61	12.10	13.00	13.03	13.94	15.16
	3H	14.22	15.02	15.16	15.97	17.22	13.73	14.53	14.66	15.48	16.73
	4H	14.81	15.57	15.76	16.52	17.78	14.31	15.07	15.27	16.03	17.29
	6H	15.21	15.91	16.18	16.88	18.14	14.71	15.41	15.68	16.38	17.64
	8H	15.32	15.99	16.29	16.97	18.23	14.82	15.48	15.79	16.47	17.73
	12H	15.37	16.00	16.35	16.98	18.27	14.86	15.49	15.84	16.47	17.76
4H	2H	13.01	13.77	13.97	14.73	15.99	12.66	13.42	13.62	14.38	15.63
	3H	14.89	15.52	15.86	16.51	17.78	14.48	15.11	15.45	16.10	17.37
	4H	15.61	16.18	16.59	17.17	18.46	15.18	15.76	16.16	16.74	18.04
	6H	16.13	16.63	17.12	17.63	18.92	15.70	16.19	16.69	17.20	18.49
	8H	16.28	16.75	17.27	17.75	19.05	15.84	16.31	16.84	17.31	18.61
	12H	16.36	16.78	17.37	17.79	19.10	15.91	16.33	16.92	17.34	18.65
8H	4H	15.81	16.27	16.80	17.27	18.58	15.43	15.89	16.42	16.89	18.20
	6H	16.44	16.83	17.46	17.87	19.17	16.06	16.44	17.08	17.49	18.79
	8H	16.67	17.01	17.69	18.04	19.36	16.27	16.61	17.30	17.64	18.97
	12H	16.80	17.10	17.83	18.12	19.49	16.39	16.69	17.42	17.71	19.08
12H	4H	15.79	16.21	16.80	17.23	18.54	15.43	15.85	16.44	16.86	18.17
	6H	16.47	16.81	17.50	17.84	19.16	16.10	16.44	17.13	17.47	18.79
	8H	16.72	17.02	17.75	18.04	19.41	16.34	16.64	17.37	17.66	19.03