

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P904266

Luminaire Tested: DFN2DIP-TR2F0-020D030US830-RLFL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P904266
REPORT IS A COMBINATION OF REPORTS P900232 AND P897145
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR2F0-020D030US830-RLLFLL
Description: 2 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4104.8 lumens
Efficiency: N/A
Efficacy: 110.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.04' x L: 2.36' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 37
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P904266

CATALOG NUMBER: DFN2DIP-TR2F0-020D030US830-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P904266

CATALOG NUMBER: DFN2DIP-TR2F0-020D030US830-RLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	95	95	95	95	77	77	77	61	61	61	46	46	46
1	96	92	88	85	87	83	80	78	68	66	64	54	53	51	41	40	40
2	87	80	75	70	79	73	68	64	60	57	54	48	46	44	37	35	34
3	80	71	64	58	73	65	59	54	53	49	46	43	40	37	33	31	29
4	73	63	55	50	66	58	51	46	48	43	39	38	35	32	30	27	26
5	67	56	48	43	61	52	45	40	43	38	34	35	31	28	27	24	22
6	62	51	43	37	56	46	40	35	39	33	30	31	28	25	25	22	20
7	57	46	38	33	52	42	35	30	35	30	26	29	25	22	22	20	18
8	53	41	34	29	49	38	32	27	32	27	23	26	22	20	21	18	16
9	50	38	31	26	45	35	29	24	29	24	21	24	20	18	19	17	15
10	46	35	28	23	42	32	26	22	27	22	19	22	19	16	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1738	1738	1738
5°	1738	1706	1718
10°	1718	1669	1659
15°	1692	1610	1570
20°	1658	1531	1462
25°	1623	1442	1357
30°	1578	1351	1226
35°	1533	1255	1110
40°	1487	1155	978
45°	1434	1045	859
50°	1379	934	742
55°	1321	816	630
60°	1254	693	516
65°	1177	569	461
70°	1083	453	413
75°	965	392	370
80°	795	318	312
85°	522	197	220

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1434 cd/sqm

TEST NUMBER: P904266

CATALOG NUMBER: DFN2DIP-TR2F0-020D030US830-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	73.0	1.8
10°-20°	200.4	4.9
20°-30°	281.4	6.9
30°-40°	306.8	7.5
40°-50°	282.0	6.9
50°-60°	221.4	5.4
60°-70°	144.1	3.5
70°-80°	74.2	1.8
80°-90°	21.5	0.5
90°-100°	55.3	1.3
100°-110°	175.8	4.3
110°-120°	300.9	7.3
120°-130°	395.7	9.6
130°-140°	444.2	10.8
140°-150°	435.6	10.6
150°-160°	365.4	8.9
160°-170°	242.3	5.9
170°-180°	84.7	2.1
0°-30°	554.9	13.5
0°-40°	861.7	21.0
0°-60°	1365.1	33.3
0°-90°	1604.9	39.1
90°-120°	532.1	13.0
90°-150°	1807.5	44.0
90°-180°	2500.0	60.9
0°-180°	4104.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	779	779	779	779	779	
5°	779	776	766	773	771	74
15°	741	733	709	696	689	209
25°	673	650	604	575	564	309
35°	580	544	482	437	422	363
45°	474	426	353	302	286	366
55°	360	305	229	187	173	322
65°	243	186	123	99	97	241
75°	130	80	56	52	51	137
85°	30	16	13	13	13	35
90°	1	10	26	25	26	4
95°	39	47	48	48	47	44
105°	162	164	166	167	167	171
115°	302	306	305	304	302	299
125°	439	446	444	441	440	392
135°	568	576	578	577	575	439
145°	690	695	699	700	697	431
155°	789	791	793	797	795	363
165°	858	857	857	862	859	242
175°	893	890	889	894	890	85
180°	894	894	894	894	894	

TEST NUMBER: P904266

CATALOG NUMBER: DFN2DIP-TR2F0-020D030US830-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	779.1	779.1	779.1	779.1	779.1
2.5°	782.6	779.1	771.3	778.4	777.0
5°	779.1	775.6	766.4	772.8	770.6
7.5°	772.8	768.5	758.7	761.5	757.9
10°	764.3	759.3	745.3	743.1	739.0
12.5°	753.8	747.3	728.3	724.2	716.3
15°	741.0	733.2	709.3	695.9	688.9
17.5°	726.2	714.9	685.3	669.8	658.6
20°	709.3	695.1	660.0	642.3	626.8
22.5°	691.0	674.8	633.9	609.9	599.4
25°	672.7	650.1	603.5	574.7	564.0
27.5°	650.8	626.8	575.3	542.2	525.9
30°	627.5	600.7	544.3	508.4	489.3
32.5°	604.9	572.5	514.7	472.4	454.8
35°	579.6	543.7	481.6	437.2	421.6
37.5°	554.9	516.0	450.5	401.9	384.3
40°	528.8	486.5	418.1	368.1	349.7
42.5°	502.0	456.9	385.7	333.5	315.9
45°	473.8	426.5	352.6	302.5	285.5
47.5°	447.0	397.0	320.8	270.7	255.2
50°	417.5	367.4	289.8	241.1	226.4
52.5°	388.4	335.5	260.1	213.7	200.3
55°	360.2	305.3	229.1	186.9	173.4
57.5°	331.4	274.9	201.7	162.2	150.9
60°	301.8	245.3	172.8	136.9	125.5
62.5°	272.9	216.5	148.1	114.2	108.6
65°	243.3	186.2	122.7	98.8	96.6
67.5°	215.1	157.9	98.8	86.7	84.6
70°	185.4	130.4	81.7	74.7	71.9
72.5°	157.2	105.0	68.3	62.8	61.4
75°	129.7	80.3	56.4	51.5	50.8
77.5°	102.3	57.1	44.4	41.6	40.2
80°	76.8	40.9	33.8	31.0	31.0
82.5°	53.5	27.5	23.3	21.9	21.9
85°	30.3	15.5	13.4	13.4	13.4
87.5°	11.3	5.7	5.7	4.9	4.9
90°	0.8	9.7	26.4	24.8	25.6
92.5°	16.7	22.6	23.5	24.2	24.2
95°	39.4	46.9	48.3	48.3	46.9
97.5°	65.5	72.5	75.5	75.5	75.5
100°	95.7	101.9	104.1	104.1	103.3
102.5°	127.5	132.1	135.1	135.9	135.1
105°	162.3	164.5	166.1	167.4	167.4
107.5°	196.8	200.0	200.0	200.6	196.8
110°	230.3	234.6	234.6	234.6	232.4

TEST NUMBER: P904266

CATALOG NUMBER: DFN2DIP-TR2F0-020D030US830-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	266.4	271.0	270.1	268.0	266.4
115°	302.0	306.2	304.9	304.2	302.0
117.5°	337.2	343.2	339.4	337.2	335.1
120°	372.9	378.8	372.9	372.9	370.4
122.5°	405.2	412.7	409.0	406.8	405.2
125°	439.2	445.9	443.7	441.3	440.5
127.5°	472.3	480.7	477.8	474.5	472.3
130°	503.3	513.0	511.7	510.1	507.1
132.5°	538.1	545.6	546.2	542.4	540.3
135°	568.1	576.4	578.1	577.2	575.0
137.5°	601.4	608.2	609.5	609.1	605.8
140°	630.8	637.6	641.4	641.4	638.4
142.5°	661.1	667.8	670.0	670.8	667.8
145°	689.7	695.0	699.4	700.1	697.2
147.5°	715.3	722.0	725.2	726.6	723.6
150°	741.7	746.3	749.2	751.7	749.2
152.5°	765.2	769.7	773.5	776.5	773.5
155°	788.6	790.7	793.1	796.9	794.6
157.5°	808.8	810.4	811.8	817.2	813.4
160°	826.9	828.5	829.3	833.9	830.7
162.5°	843.6	843.6	844.4	849.5	845.7
165°	857.9	857.1	857.1	862.4	858.7
167.5°	870.8	868.4	868.4	873.7	870.0
170°	880.5	878.4	877.6	883.0	878.4
172.5°	887.2	885.1	884.3	889.7	885.1
175°	892.7	890.5	888.9	894.3	889.7
177.5°	895.6	893.4	891.8	896.5	891.8
180°	894.3	894.3	894.3	894.3	894.3

TEST NUMBER: P904266

CATALOG NUMBER: DFN2DIP-TR2F0-020D030US830-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.82	8.57	8.88	9.62	11.05	3.81	4.56	4.86	5.61	7.03
	3H	9.47	10.14	10.53	11.20	12.64	4.97	5.64	6.04	6.70	8.14
	4H	10.06	10.69	11.13	11.76	13.20	5.41	6.04	6.48	7.11	8.55
	6H	10.46	11.04	11.54	12.11	13.57	5.71	6.30	6.79	7.36	8.82
	8H	10.57	11.13	11.66	12.21	13.66	5.79	6.35	6.88	7.43	8.88
	12H	10.62	11.15	11.71	12.22	13.70	5.83	6.36	6.92	7.43	8.91
4H	2H	7.83	8.46	8.91	9.52	10.97	4.38	5.01	5.46	6.08	7.52
	3H	9.62	10.15	10.71	11.24	12.70	5.70	6.23	6.79	7.32	8.78
	4H	10.29	10.78	11.38	11.86	13.34	6.24	6.72	7.33	7.80	9.28
	6H	10.78	11.20	11.88	12.30	13.77	6.63	7.05	7.73	8.15	9.63
	8H	10.94	11.33	12.04	12.42	13.91	6.75	7.14	7.85	8.23	9.72
	12H	11.02	11.37	12.14	12.48	13.97	6.80	7.15	7.92	8.26	9.76
8H	4H	10.25	10.64	11.35	11.73	13.22	6.50	6.88	7.59	7.98	9.47
	6H	10.79	11.11	11.91	12.25	13.73	6.99	7.31	8.11	8.44	9.93
	8H	10.99	11.27	12.12	12.39	13.89	7.17	7.45	8.29	8.57	10.07
	12H	11.11	11.35	12.24	12.47	14.01	7.27	7.52	8.40	8.63	10.18
12H	4H	10.20	10.55	11.31	11.66	13.15	6.49	6.84	7.61	7.95	9.45
	6H	10.76	11.04	11.89	12.16	13.67	7.03	7.31	8.16	8.43	9.94
	8H	10.96	11.21	12.09	12.32	13.87	7.22	7.47	8.35	8.58	10.13