

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P904291

Luminaire Tested: DFN2DIP-TR2F0-030D040US830-RLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P904291
REPORT IS A COMBINATION OF REPORTS P901764 AND P897145
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR2F0-030D040US830-RLLONL
Description: 2 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5740.1 lumens
Efficiency: N/A
Efficacy: 105.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.04' x L: 2.36' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 54.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P904291

CATALOG NUMBER: DFN2DIP-TR2F0-030D040US830-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P904291

CATALOG NUMBER: DFN2DIP-TR2F0-030D040US830-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	49	49	49
1	96	92	89	85	88	84	81	78	70	67	65	56	55	53	44	43	42
2	88	81	75	70	80	74	69	65	61	58	55	50	47	45	39	37	36
3	81	72	65	59	73	66	60	55	55	50	47	44	41	39	35	33	31
4	74	64	56	50	67	58	52	47	49	44	40	40	36	33	31	29	27
5	68	57	49	43	62	52	45	40	44	39	35	36	32	29	28	26	24
6	63	51	43	38	57	47	40	35	40	34	30	33	29	26	26	23	21
7	58	46	38	33	53	43	36	31	36	31	27	30	26	23	24	21	19
8	54	42	34	29	49	39	32	28	33	28	24	27	23	21	22	19	17
9	50	38	31	26	46	36	29	25	30	25	22	25	21	19	20	18	16
10	47	35	28	24	43	33	26	22	28	23	19	23	19	17	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2607	2607	2607
5°	2607	2559	2577
10°	2577	2503	2489
15°	2538	2415	2355
20°	2487	2296	2193
25°	2435	2163	2036
30°	2366	2027	1838
35°	2299	1882	1665
40°	2230	1732	1467
45°	2151	1567	1288
50°	2068	1401	1113
55°	1982	1224	946
60°	1881	1040	774
65°	1765	853	692
70°	1625	679	620
75°	1447	588	555
80°	1194	477	469
85°	783	296	330

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 2151 cd/sqm

TEST NUMBER: P904291

CATALOG NUMBER: DFN2DIP-TR2F0-030D040US830-RLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	109.5	1.9
10°-20°	300.7	5.2
20°-30°	422.1	7.4
30°-40°	460.2	8.0
40°-50°	422.9	7.4
50°-60°	332.2	5.8
60°-70°	216.2	3.8
70°-80°	111.3	1.9
80°-90°	31.8	0.6
90°-100°	73.8	1.3
100°-110°	234.4	4.1
110°-120°	401.2	7.0
120°-130°	527.6	9.2
130°-140°	592.2	10.3
140°-150°	580.8	10.1
150°-160°	487.2	8.5
160°-170°	323.1	5.6
170°-180°	112.9	2.0
0°-30°	832.3	14.5
0°-40°	1292.5	22.5
0°-60°	2047.6	35.7
0°-90°	2406.9	41.9
90°-120°	709.4	12.4
90°-150°	2410.0	42.0
90°-180°	3333.0	58.1
0°-180°	5740.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1169	1169	1169	1169	1169	
5°	1169	1163	1150	1159	1156	111
15°	1112	1100	1064	1044	1033	313
25°	1009	975	905	862	846	464
35°	869	815	722	656	632	544
45°	711	640	529	454	428	549
55°	540	458	344	280	260	483
65°	365	279	184	148	145	362
75°	194	121	85	77	76	206
85°	45	23	20	20	20	52
90°	1	13	35	33	34	6
95°	52	63	64	64	63	58
105°	216	219	221	223	223	228
115°	403	408	406	406	403	398
125°	586	595	592	588	587	523
135°	757	768	771	770	767	585
145°	920	927	932	934	930	575
155°	1051	1054	1058	1063	1059	484
165°	1144	1143	1143	1150	1145	323
175°	1190	1187	1185	1192	1186	113
180°	1192	1192	1192	1192	1192	

TEST NUMBER: P904291

CATALOG NUMBER: DFN2DIP-TR2F0-030D040US830-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1168.7	1168.7	1168.7	1168.7	1168.7
2.5°	1173.9	1168.7	1157.0	1167.6	1165.5
5°	1168.7	1163.4	1149.6	1159.1	1155.9
7.5°	1159.1	1152.8	1138.0	1142.2	1136.9
10°	1146.4	1139.1	1117.9	1114.7	1108.4
12.5°	1130.6	1121.1	1092.5	1086.2	1074.5
15°	1111.5	1099.9	1063.9	1043.9	1033.3
17.5°	1089.3	1072.4	1027.9	1004.8	987.8
20°	1063.9	1042.7	989.9	963.6	940.2
22.5°	1036.5	1012.1	950.7	914.8	899.0
25°	1009.0	975.1	905.3	862.0	846.0
27.5°	976.2	940.2	863.0	813.3	788.9
30°	941.3	901.1	816.4	762.6	734.0
32.5°	907.4	858.8	772.1	708.6	682.1
35°	869.4	815.4	722.4	655.7	632.4
37.5°	832.4	774.1	675.8	602.8	576.5
40°	793.2	729.8	627.2	552.0	524.6
42.5°	753.0	685.4	578.5	500.2	473.8
45°	710.8	639.8	528.9	453.6	428.3
47.5°	670.5	595.5	481.3	406.0	382.9
50°	626.1	551.0	434.7	361.7	339.5
52.5°	582.7	503.4	390.3	320.5	300.4
55°	540.4	457.9	343.7	280.3	260.2
57.5°	497.1	412.5	302.6	243.3	226.3
60°	452.6	368.1	259.1	205.2	188.3
62.5°	409.3	324.7	222.1	171.4	163.0
65°	364.9	279.2	184.0	148.1	144.9
67.5°	322.6	236.9	148.1	130.1	126.9
70°	278.1	195.7	122.6	112.1	107.8
72.5°	235.8	157.5	102.5	94.2	92.0
75°	194.5	120.6	84.6	77.2	76.2
77.5°	153.4	85.6	66.6	62.4	60.2
80°	115.3	61.4	50.7	46.6	46.6
82.5°	80.3	41.3	34.9	32.8	32.8
85°	45.4	23.2	20.1	20.1	20.1
87.5°	17.0	8.4	8.4	7.4	7.4
90°	1.0	12.9	35.3	33.1	34.1
92.5°	22.2	30.2	31.3	32.3	32.3
95°	52.5	62.6	64.4	64.4	62.6
97.5°	87.4	96.7	100.7	100.7	100.7
100°	127.6	135.9	138.7	138.7	137.7
102.5°	170.0	176.2	180.1	181.2	180.1
105°	216.4	219.2	221.4	223.2	223.2
107.5°	262.4	266.7	266.7	267.4	262.4
110°	307.0	312.7	312.7	312.7	309.9

TEST NUMBER: P904291

CATALOG NUMBER: DFN2DIP-TR2F0-030D040US830-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	355.1	361.3	360.1	357.3	355.1
115°	402.6	408.4	406.5	405.5	402.6
117.5°	449.7	457.6	452.6	449.7	446.9
120°	497.2	505.0	497.2	497.2	493.9
122.5°	540.3	550.4	545.4	542.4	540.3
125°	585.6	594.6	591.7	588.4	587.4
127.5°	629.8	640.9	637.0	632.6	629.8
130°	671.1	684.1	682.3	680.1	676.2
132.5°	717.5	727.5	728.3	723.2	720.4
135°	757.4	768.5	770.7	769.6	766.8
137.5°	802.0	811.0	812.8	812.0	807.8
140°	841.1	850.2	855.2	855.2	851.2
142.5°	881.5	890.4	893.2	894.4	890.4
145°	919.5	926.7	932.5	933.6	929.6
147.5°	953.7	962.6	967.0	968.7	964.8
150°	988.9	995.0	999.0	1002.2	999.0
152.5°	1020.2	1026.2	1031.3	1035.3	1031.3
155°	1051.4	1054.3	1057.5	1062.6	1059.3
157.5°	1078.5	1080.5	1082.3	1089.6	1084.5
160°	1102.5	1104.7	1105.7	1111.8	1107.5
162.5°	1124.7	1124.7	1125.9	1132.7	1127.7
165°	1143.9	1142.7	1142.7	1149.9	1144.9
167.5°	1161.1	1157.8	1157.8	1165.1	1160.0
170°	1174.0	1171.1	1170.1	1177.2	1171.1
172.5°	1183.0	1180.2	1179.0	1186.3	1180.2
175°	1190.2	1187.3	1185.2	1192.3	1186.3
177.5°	1194.2	1191.3	1189.1	1195.2	1189.1
180°	1192.3	1192.3	1192.3	1192.3	1192.3

TEST NUMBER: P904291

CATALOG NUMBER: DFN2DIP-TR2F0-030D040US830-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.54	10.31	10.57	11.34	12.73	5.52	6.29	6.55	7.33	8.71
	3H	11.19	11.88	12.23	12.92	14.32	6.69	7.38	7.73	8.42	9.83
	4H	11.78	12.43	12.83	13.48	14.89	7.13	7.78	8.18	8.82	10.24
	6H	12.18	12.78	13.24	13.83	15.25	7.43	8.03	8.49	9.08	10.50
	8H	12.29	12.86	13.36	13.93	15.35	7.52	8.08	8.58	9.15	10.57
	12H	12.34	12.89	13.41	13.94	15.38	7.55	8.09	8.62	9.15	10.59
4H	2H	9.55	10.20	10.61	11.24	12.66	6.10	6.75	7.16	7.79	9.21
	3H	11.35	11.89	12.41	12.96	14.38	7.42	7.97	8.49	9.04	10.46
	4H	12.02	12.51	13.09	13.58	15.02	7.96	8.45	9.03	9.52	10.96
	6H	12.51	12.93	13.59	14.02	15.46	8.36	8.78	9.44	9.87	11.31
	8H	12.67	13.06	13.75	14.14	15.60	8.47	8.87	9.56	9.95	11.41
	12H	12.75	13.10	13.84	14.20	15.66	8.53	8.89	9.63	9.98	11.44
8H	4H	11.98	12.37	13.06	13.45	14.91	8.22	8.62	9.30	9.69	11.15
	6H	12.51	12.84	13.62	13.96	15.42	8.71	9.04	9.82	10.16	11.61
	8H	12.72	13.00	13.83	14.11	15.58	8.89	9.18	10.00	10.28	11.75
	12H	12.84	13.09	13.95	14.19	15.70	8.99	9.25	10.11	10.35	11.86
12H	4H	11.92	12.28	13.02	13.38	14.84	8.22	8.58	9.31	9.67	11.13
	6H	12.49	12.78	13.60	13.88	15.35	8.76	9.04	9.87	10.15	11.62
	8H	12.69	12.94	13.80	14.04	15.55	8.95	9.20	10.06	10.30	11.81