

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P923380

Luminaire Tested: DFN2DIP-TR2F0-030D030US940-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P923380
REPORT IS A COMBINATION OF REPORTS P900233 AND P897145
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR2F0-030D030US940-FLLFLL
Description: 2 foot, Triangle Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5015.9 lumens
Efficiency: N/A
Efficacy: 106.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.04' x L: 2.36' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 47
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P923380
CATALOG NUMBER: DFN2DIP-TR2F0-030D030US940-FLLFLL

Luminous Intensity Polar Plot





TEST NUMBER: P923380
 CATALOG NUMBER: DFN2DIP-TR2F0-030D030US940-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59	53
1	98	94	90	87	91	87	84	81	74	72	70	63	61	59	52	51	50	45
2	90	82	76	71	83	76	71	66	65	61	58	55	52	50	46	44	42	37
3	82	72	65	59	75	67	61	55	58	53	49	49	45	42	41	38	36	32
4	75	64	56	50	69	60	52	47	51	46	41	43	39	36	36	33	31	27
5	69	57	49	43	63	53	46	40	46	40	36	39	35	31	33	29	27	24
6	63	51	43	37	58	48	40	35	41	36	31	35	31	27	30	26	24	21
7	59	46	38	33	54	43	36	31	37	32	28	32	28	24	27	24	21	18
8	54	42	34	29	50	39	32	27	34	29	24	29	25	22	25	21	19	16
9	51	38	31	26	47	36	29	24	31	26	22	27	23	19	23	20	17	15
10	47	35	28	23	44	33	26	22	29	23	20	25	21	18	21	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2322	2322	2322
5°	2322	2284	2301
10°	2300	2248	2266
15°	2262	2206	2213
20°	2213	2149	2159
25°	2164	2083	2098
30°	2104	2021	2021
35°	2046	1948	1939
40°	1976	1874	1862
45°	1905	1800	1782
50°	1828	1722	1690
55°	1747	1632	1605
60°	1655	1526	1507
65°	1555	1415	1391
70°	1426	1281	1266
75°	1251	1119	1146
80°	1037	912	926
85°	707	576	574

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1905 cd/sqm



TEST NUMBER: P923380

CATALOG NUMBER: DFN2DIP-TR2F0-030D030US940-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	98.0	2.0
10°-20°	275.6	5.5
20°-30°	405.1	8.1
30°-40°	470.5	9.4
40°-50°	469.9	9.4
50°-60°	409.8	8.2
60°-70°	302.9	6.0
70°-80°	171.4	3.4
80°-90°	47.6	0.9
90°-100°	52.3	1.0
100°-110°	166.3	3.3
110°-120°	284.7	5.7
120°-130°	374.4	7.5
130°-140°	420.2	8.4
140°-150°	412.1	8.2
150°-160°	345.7	6.9
160°-170°	229.2	4.6
170°-180°	80.1	1.6
0°-30°	778.7	15.5
0°-40°	1249.2	24.9
0°-60°	2128.9	42.4
0°-90°	2650.8	52.8
90°-120°	503.4	10.0
90°-150°	1710.0	34.1
90°-180°	2365.0	47.2
0°-180°	5015.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1041	1041	1041	1041	1041	
5°	1041	1037	1026	1034	1032	99
15°	991	985	972	976	971	279
25°	897	889	872	874	872	413
35°	774	764	748	742	737	483
45°	630	623	608	597	592	486
55°	476	470	458	446	442	426
65°	321	315	305	296	291	318
75°	168	166	161	155	157	179
85°	41	40	39	36	35	46
90°	1	9	25	24	24	5
95°	37	44	46	46	44	41
105°	154	156	157	158	158	162
115°	286	290	288	288	286	283
125°	416	422	420	418	417	371
135°	537	545	547	546	544	415
145°	652	658	662	662	660	408
155°	746	748	750	754	752	343
165°	812	811	811	816	812	229
175°	844	842	841	846	842	80
180°	846	846	846	846	846	



TEST NUMBER: P923380

CATALOG NUMBER: DFN2DIP-TR2F0-030D030US940-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1040.9	1040.9	1040.9	1040.9	1040.9
2.5°	1047.0	1042.0	1030.9	1040.9	1039.0
5°	1040.9	1037.0	1025.9	1033.9	1032.0
7.5°	1033.9	1028.0	1016.9	1025.0	1023.0
10°	1023.0	1015.9	1004.0	1011.9	1009.0
12.5°	1007.9	1001.9	990.0	994.9	992.9
15°	990.9	985.0	971.9	975.9	970.9
17.5°	969.8	963.9	950.8	955.8	950.8
20°	946.8	940.8	926.8	929.8	925.9
22.5°	923.9	914.9	901.8	901.8	899.7
25°	896.8	888.9	871.8	873.8	871.8
27.5°	866.7	859.7	846.8	843.8	838.8
30°	836.8	828.8	813.8	810.7	806.7
32.5°	804.8	798.8	782.7	776.7	772.7
35°	773.7	763.7	747.7	741.6	736.6
37.5°	738.7	729.7	713.6	706.6	701.6
40°	702.7	694.6	678.6	669.7	665.7
42.5°	667.6	659.6	643.6	633.6	627.6
45°	629.6	622.6	607.5	596.6	592.5
47.5°	592.5	585.6	569.5	558.5	552.5
50°	553.5	548.5	534.5	520.5	515.5
52.5°	515.5	508.5	495.5	484.5	477.4
55°	476.5	470.5	458.4	446.5	441.5
57.5°	437.4	432.4	419.4	407.3	403.3
60°	398.3	394.4	380.4	369.3	366.4
62.5°	360.3	353.3	343.3	333.3	329.3
65°	321.4	315.3	305.3	296.3	291.3
67.5°	281.3	276.3	267.2	260.3	256.3
70°	244.2	240.2	231.2	224.2	220.3
72.5°	206.3	202.2	197.2	190.2	187.3
75°	168.1	166.2	161.1	155.2	157.2
77.5°	134.1	130.1	128.0	125.1	122.2
80°	100.1	99.1	97.0	94.1	92.1
82.5°	68.0	68.0	67.1	63.0	63.0
85°	41.0	40.0	39.1	36.0	35.0
87.5°	18.0	16.1	14.0	11.1	10.0
90°	0.8	9.2	25.0	23.5	24.3
92.5°	15.8	21.4	22.2	22.9	22.9
95°	37.3	44.4	45.7	45.7	44.4
97.5°	62.0	68.6	71.4	71.4	71.4
100°	90.5	96.4	98.4	98.4	97.7
102.5°	120.6	125.0	127.8	128.6	127.8
105°	153.6	155.6	157.1	158.4	158.4
107.5°	186.2	189.2	189.2	189.8	186.2
110°	217.8	221.9	221.9	221.9	219.9



TEST NUMBER: P923380

CATALOG NUMBER: DFN2DIP-TR2F0-030D030US940-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	252.0	256.4	255.6	253.5	252.0
115°	285.7	289.7	288.5	287.8	285.7
117.5°	319.1	324.7	321.1	319.1	317.0
120°	352.8	358.4	352.8	352.8	350.4
122.5°	383.3	390.5	386.9	384.9	383.3
125°	415.5	421.9	419.8	417.5	416.8
127.5°	446.8	454.8	452.0	448.9	446.8
130°	476.2	485.4	484.1	482.6	479.7
132.5°	509.1	516.2	516.7	513.2	511.1
135°	537.4	545.3	546.9	546.1	544.0
137.5°	569.0	575.4	576.7	576.2	573.1
140°	596.8	603.2	606.8	606.8	604.0
142.5°	625.4	631.8	633.8	634.6	631.8
145°	652.5	657.5	661.6	662.4	659.6
147.5°	676.7	683.1	686.1	687.4	684.6
150°	701.7	706.1	708.8	711.1	708.8
152.5°	723.9	728.2	731.7	734.6	731.7
155°	746.1	748.1	750.4	753.9	751.7
157.5°	765.2	766.7	768.0	773.1	769.5
160°	782.3	783.8	784.6	788.9	785.9
162.5°	798.1	798.1	798.9	803.7	800.1
165°	811.6	810.8	810.8	815.9	812.3
167.5°	823.9	821.5	821.5	826.6	823.0
170°	833.0	831.0	830.3	835.4	831.0
172.5°	839.4	837.4	836.6	841.7	837.4
175°	844.5	842.5	841.0	846.1	841.7
177.5°	847.3	845.3	843.7	848.1	843.7
180°	846.1	846.1	846.1	846.1	846.1



TEST NUMBER: P923380
 CATALOG NUMBER: DFN2DIP-TR2F0-030D030US940-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.33	11.22	11.26	12.17	13.40	9.90	10.79	10.84	11.74	12.97
	3H	11.97	12.76	12.91	13.72	14.98	11.51	12.30	12.45	13.26	14.51
	4H	12.54	13.29	13.50	14.26	15.52	12.08	12.83	13.04	13.80	15.06
	6H	12.92	13.62	13.89	14.59	15.86	12.46	13.16	13.43	14.13	15.40
	8H	13.02	13.68	13.99	14.67	15.94	12.56	13.22	13.54	14.21	15.48
	12H	13.06	13.69	14.04	14.67	15.97	12.60	13.23	13.58	14.21	15.50
4H	2H	10.78	11.54	11.75	12.50	13.76	10.44	11.20	11.41	12.16	13.42
	3H	12.62	13.25	13.60	14.25	15.52	12.24	12.87	13.21	13.86	15.14
	4H	13.32	13.90	14.30	14.88	16.18	12.93	13.50	13.91	14.49	15.79
	6H	13.82	14.31	14.81	15.32	16.62	13.42	13.92	14.41	14.93	16.22
	8H	13.95	14.42	14.95	15.42	16.73	13.56	14.02	14.55	15.02	16.34
	12H	14.02	14.44	15.03	15.45	16.77	13.61	14.03	14.63	15.05	16.37
8H	4H	13.51	13.97	14.51	14.98	16.29	13.16	13.62	14.15	14.62	15.94
	6H	14.11	14.50	15.14	15.54	16.85	13.76	14.15	14.78	15.19	16.50
	8H	14.32	14.66	15.35	15.69	17.02	13.96	14.30	14.99	15.33	16.66
	12H	14.44	14.73	15.47	15.76	17.13	14.07	14.36	15.10	15.39	16.76
12H	4H	13.49	13.91	14.51	14.93	16.25	13.15	13.57	14.17	14.59	15.91
	6H	14.14	14.48	15.17	15.51	16.84	13.80	14.14	14.83	15.17	16.50
	8H	14.36	14.66	15.40	15.69	17.06	14.02	14.32	15.05	15.34	16.72