

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P904344

Luminaire Tested: DFN2DIP-TR2F0-060D030US830-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P904344
REPORT IS A COMBINATION OF REPORTS P900239 AND P897145
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR2F0-060D030US830-FLLFLL
Description: 2 foot, Triangle Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8101.2 lumens
Efficiency: N/A
Efficacy: 99.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.04' x L: 2.36' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 81.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P904344
CATALOG NUMBER: DFN2DIP-TR2F0-060D030US830-FLLFLL

Luminous Intensity Polar Plot





TEST NUMBER: P904344

CATALOG NUMBER: DFN2DIP-TR2F0-060D030US830-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	112	112	112	112	106	106	106	106	94	94	94	83	83	83	74	74	74	69			
1	102	98	94	90	96	92	89	86	83	80	77	74	71	70	65	64	62	58			
2	93	85	79	74	88	81	75	70	72	68	64	65	61	58	57	55	52	49			
3	85	75	67	61	80	71	64	59	64	58	54	57	53	49	51	48	45	41			
4	78	67	58	52	73	63	56	50	57	51	46	51	46	42	46	42	39	35			
5	71	59	51	45	67	56	49	43	51	45	40	46	41	37	41	37	34	31			
6	66	53	45	39	62	51	43	38	46	40	35	41	36	32	37	33	30	27			
7	61	48	40	34	58	46	39	33	42	35	31	38	33	29	34	30	26	24			
8	57	44	36	31	54	42	35	30	38	32	28	35	29	26	31	27	24	22			
9	53	40	33	27	50	39	31	26	35	29	25	32	27	23	29	25	21	19			
10	50	37	30	25	47	36	29	24	32	27	22	30	25	21	27	23	20	18			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4908	4908	4908
5°	4909	4829	4864
10°	4862	4753	4789
15°	4783	4664	4678
20°	4679	4544	4565
25°	4575	4403	4434
30°	4448	4271	4272
35°	4325	4118	4100
40°	4176	3962	3935
45°	4028	3805	3767
50°	3865	3641	3573
55°	3694	3450	3392
60°	3500	3227	3185
65°	3287	2993	2941
70°	3016	2707	2677
75°	2644	2365	2421
80°	2192	1929	1957
85°	1493	1216	1216

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 4028 cd/sqm



TEST NUMBER: P904344

CATALOG NUMBER: DFN2DIP-TR2F0-060D030US830-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	207.1	2.6
10°-20°	582.7	7.2
20°-30°	856.4	10.6
30°-40°	994.6	12.3
40°-50°	993.4	12.3
50°-60°	866.2	10.7
60°-70°	640.3	7.9
70°-80°	362.3	4.5
80°-90°	98.2	1.2
90°-100°	55.3	0.7
100°-110°	175.8	2.2
110°-120°	300.9	3.7
120°-130°	395.7	4.9
130°-140°	444.2	5.5
140°-150°	435.6	5.4
150°-160°	365.4	4.5
160°-170°	242.3	3.0
170°-180°	84.7	1.0
0°-30°	1646.2	20.3
0°-40°	2640.9	32.6
0°-60°	4500.5	55.6
0°-90°	5601.2	69.1
90°-120°	532.1	6.6
90°-150°	1807.5	22.3
90°-180°	2500.0	30.9
0°-180°	8101.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2200	2200	2200	2200	2200	
5°	2200	2192	2169	2186	2182	209
15°	2095	2082	2055	2063	2053	590
25°	1896	1879	1843	1847	1843	872
35°	1636	1615	1581	1568	1557	1021
45°	1331	1316	1284	1261	1253	1027
55°	1007	994	969	944	933	901
65°	679	667	646	626	616	672
75°	355	351	340	328	332	379
85°	87	85	83	76	74	97
90°	1	10	26	25	26	8
95°	39	47	48	48	47	44
105°	162	164	166	167	167	171
115°	302	306	305	304	302	299
125°	439	446	444	441	440	392
135°	568	576	578	577	575	439
145°	690	695	699	700	697	431
155°	789	791	793	797	795	363
165°	858	857	857	862	859	242
175°	893	890	889	894	890	85
180°	894	894	894	894	894	



TEST NUMBER: P904344

CATALOG NUMBER: DFN2DIP-TR2FO-060D030US830-FLLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2200.5	2200.5	2200.5	2200.5	2200.5
2.5°	2213.3	2202.7	2179.3	2200.5	2196.4
5°	2200.5	2192.2	2168.8	2185.7	2181.6
7.5°	2185.7	2173.1	2149.8	2166.8	2162.6
10°	2162.6	2147.8	2122.3	2139.2	2132.9
12.5°	2130.7	2118.1	2092.7	2103.3	2099.0
15°	2094.7	2082.2	2054.6	2063.1	2052.6
17.5°	2050.3	2037.8	2010.2	2020.6	2010.2
20°	2001.6	1989.0	1959.4	1965.7	1957.4
22.5°	1953.1	1934.0	1906.4	1906.4	1902.1
25°	1895.8	1879.1	1843.0	1847.1	1843.0
27.5°	1832.3	1817.5	1790.1	1783.9	1773.3
30°	1769.1	1751.9	1720.3	1714.0	1705.4
32.5°	1701.2	1688.7	1654.7	1641.9	1633.4
35°	1635.7	1614.6	1580.6	1567.8	1557.3
37.5°	1561.6	1542.5	1508.6	1493.7	1483.2
40°	1485.4	1468.4	1434.5	1415.7	1407.1
42.5°	1411.4	1394.3	1360.7	1339.4	1326.7
45°	1331.1	1316.2	1284.3	1261.2	1252.6
47.5°	1252.6	1237.8	1204.0	1180.6	1168.0
50°	1170.1	1159.5	1129.9	1100.2	1089.7
52.5°	1089.7	1074.9	1047.4	1024.2	1009.4
55°	1007.3	994.5	969.1	943.8	933.2
57.5°	924.7	914.2	886.6	861.2	852.6
60°	842.1	833.8	804.2	780.8	774.5
62.5°	761.7	746.9	725.8	704.6	696.2
65°	679.3	666.6	645.5	626.3	615.8
67.5°	594.6	583.9	565.1	550.3	541.7
70°	516.3	507.8	488.7	473.9	465.6
72.5°	435.9	427.4	416.9	402.1	395.8
75°	355.3	351.4	340.5	328.0	332.2
77.5°	283.5	275.0	270.7	264.5	258.2
80°	211.7	209.4	205.2	198.9	194.6
82.5°	143.9	143.9	141.9	133.4	133.4
85°	86.6	84.6	82.6	76.1	74.1
87.5°	38.2	33.9	29.6	23.4	21.1
90°	0.8	9.7	26.4	24.8	25.6
92.5°	16.7	22.6	23.5	24.2	24.2
95°	39.4	46.9	48.3	48.3	46.9
97.5°	65.5	72.5	75.5	75.5	75.5
100°	95.7	101.9	104.1	104.1	103.3
102.5°	127.5	132.1	135.1	135.9	135.1
105°	162.3	164.5	166.1	167.4	167.4
107.5°	196.8	200.0	200.0	200.6	196.8
110°	230.3	234.6	234.6	234.6	232.4



TEST NUMBER: P904344

CATALOG NUMBER: DFN2DIP-TR2FO-060D030US830-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	266.4	271.0	270.1	268.0	266.4
115°	302.0	306.2	304.9	304.2	302.0
117.5°	337.2	343.2	339.4	337.2	335.1
120°	372.9	378.8	372.9	372.9	370.4
122.5°	405.2	412.7	409.0	406.8	405.2
125°	439.2	445.9	443.7	441.3	440.5
127.5°	472.3	480.7	477.8	474.5	472.3
130°	503.3	513.0	511.7	510.1	507.1
132.5°	538.1	545.6	546.2	542.4	540.3
135°	568.1	576.4	578.1	577.2	575.0
137.5°	601.4	608.2	609.5	609.1	605.8
140°	630.8	637.6	641.4	641.4	638.4
142.5°	661.1	667.8	670.0	670.8	667.8
145°	689.7	695.0	699.4	700.1	697.2
147.5°	715.3	722.0	725.2	726.6	723.6
150°	741.7	746.3	749.2	751.7	749.2
152.5°	765.2	769.7	773.5	776.5	773.5
155°	788.6	790.7	793.1	796.9	794.6
157.5°	808.8	810.4	811.8	817.2	813.4
160°	826.9	828.5	829.3	833.9	830.7
162.5°	843.6	843.6	844.4	849.5	845.7
165°	857.9	857.1	857.1	862.4	858.7
167.5°	870.8	868.4	868.4	873.7	870.0
170°	880.5	878.4	877.6	883.0	878.4
172.5°	887.2	885.1	884.3	889.7	885.1
175°	892.7	890.5	888.9	894.3	889.7
177.5°	895.6	893.4	891.8	896.5	891.8
180°	894.3	894.3	894.3	894.3	894.3



TEST NUMBER: P904344
 CATALOG NUMBER: DFN2DIP-TR2F0-060D030US830-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.27	15.34	15.05	16.13	17.10	13.85	14.91	14.62	15.71	16.68
	3H	15.93	16.88	16.71	17.69	18.69	15.46	16.42	16.25	17.23	18.22
	4H	16.51	17.41	17.31	18.22	19.23	16.05	16.95	16.85	17.76	18.77
	6H	16.90	17.73	17.71	18.55	19.58	16.44	17.27	17.25	18.09	19.12
	8H	17.00	17.79	17.83	18.63	19.66	16.54	17.33	17.37	18.18	19.20
	12H	17.05	17.80	17.88	18.64	19.69	16.58	17.34	17.41	18.17	19.23
4H	2H	14.75	15.65	15.56	16.47	17.48	14.41	15.31	15.22	16.13	17.14
	3H	16.61	17.36	17.43	18.21	19.23	16.22	16.98	17.04	17.82	18.85
	4H	17.31	18.00	18.14	18.84	19.90	16.92	17.60	17.75	18.45	19.50
	6H	17.81	18.41	18.66	19.28	20.34	17.42	18.01	18.27	18.88	19.94
	8H	17.96	18.51	18.81	19.38	20.45	17.56	18.12	18.41	18.98	20.05
	12H	18.03	18.53	18.90	19.42	20.49	17.62	18.12	18.50	19.01	20.09
8H	4H	17.51	18.07	18.37	18.93	20.00	17.16	17.72	18.01	18.58	19.65
	6H	18.12	18.58	19.01	19.49	20.56	17.77	18.23	18.65	19.14	20.21
	8H	18.33	18.74	19.22	19.64	20.73	17.98	18.38	18.87	19.29	20.37
	12H	18.46	18.82	19.35	19.71	20.85	18.09	18.45	18.98	19.34	20.48
12H	4H	17.51	18.01	18.38	18.89	19.97	17.16	17.66	18.04	18.55	19.62
	6H	18.15	18.56	19.04	19.46	20.55	17.81	18.22	18.70	19.12	20.21
	8H	18.39	18.75	19.28	19.64	20.78	18.04	18.40	18.94	19.29	20.43