

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P904355

Luminaire Tested: DFN2DIP-TR2F0-060D050US830-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P904355
REPORT IS A COMBINATION OF REPORTS P901780 AND P897145
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR2F0-060D050US830-RLLONL
Description: 2 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8977.7 lumens
Efficiency: N/A
Efficacy: 91.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.04' x L: 2.36' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 97.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P904355

CATALOG NUMBER: DFN2DIP-TR2F0-060D050US830-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P904355

CATALOG NUMBER: DFN2DIP-TR2F0-060D050US830-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85		72	72	72		59
1	99	95	91	88	92	88	85	82	76	73	71		64	62	61		53
2	91	84	78	73	84	78	73	68	67	63	60		57	54	52		48
3	83	74	67	61	77	69	63	58	59	55	51		51	47	44		43
4	76	66	58	52	71	61	55	49	53	48	44		46	42	38		38
5	70	59	51	45	65	55	48	43	48	42	38		41	37	34		35
6	65	53	45	39	60	50	43	37	43	38	34		37	33	30		32
7	60	48	40	35	56	45	38	33	39	34	30		34	30	27		29
8	56	44	36	31	52	41	34	30	36	31	27		31	27	24		27
9	52	40	33	28	48	38	31	27	33	28	24		29	25	22		25
10	49	37	30	25	45	35	28	24	31	25	22		27	23	20		23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5213	5213	5213
5°	5214	5119	5154
10°	5154	5007	4978
15°	5076	4830	4710
20°	4974	4591	4385
25°	4870	4326	4071
30°	4733	4054	3677
35°	4598	3764	3330
40°	4460	3464	2934
45°	4301	3134	2576
50°	4137	2801	2227
55°	3963	2447	1891
60°	3762	2079	1548
65°	3531	1707	1384
70°	3250	1358	1240
75°	2896	1175	1111
80°	2387	953	936
85°	1567	592	660

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 4301 cd/sqm

TEST NUMBER: P904355

CATALOG NUMBER: DFN2DIP-TR2F0-060D050US830-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	219.1	2.4
10°-20°	601.3	6.7
20°-30°	844.3	9.4
30°-40°	920.3	10.3
40°-50°	845.9	9.4
50°-60°	664.3	7.4
60°-70°	432.4	4.8
70°-80°	222.6	2.5
80°-90°	61.1	0.7
90°-100°	92.2	1.0
100°-110°	293.0	3.3
110°-120°	501.5	5.6
120°-130°	659.5	7.3
130°-140°	740.3	8.2
140°-150°	725.9	8.1
150°-160°	609.0	6.8
160°-170°	403.9	4.5
170°-180°	141.2	1.6
0°-30°	1664.7	18.5
0°-40°	2585.0	28.8
0°-60°	4095.1	45.6
0°-90°	4811.2	53.6
90°-120°	886.7	9.9
90°-150°	3012.5	33.6
90°-180°	4167.0	46.4
0°-180°	8977.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2337	2337	2337	2337	2337	
5°	2337	2327	2299	2318	2312	222
15°	2223	2200	2128	2088	2067	626
25°	2018	1950	1811	1724	1692	928
35°	1739	1631	1445	1312	1265	1088
45°	1421	1280	1058	907	857	1098
55°	1081	916	687	561	520	966
65°	730	558	368	296	290	724
75°	389	241	169	154	152	412
85°	91	46	40	40	40	104
90°	1	16	44	41	43	9
95°	66	78	80	80	78	73
105°	270	274	277	279	279	285
115°	503	510	508	507	503	498
125°	732	743	740	736	734	654
135°	947	961	963	962	958	732
145°	1149	1158	1166	1167	1162	718
155°	1314	1318	1322	1328	1324	605
165°	1430	1428	1428	1438	1431	403
175°	1488	1484	1482	1490	1483	141
180°	1490	1490	1490	1490	1490	

TEST NUMBER: P904355

CATALOG NUMBER: DFN2DIP-TR2F0-060D050US830-RLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2337.3	2337.3	2337.3	2337.3	2337.3
2.5°	2347.9	2337.3	2313.9	2335.2	2331.0
5°	2337.3	2326.8	2299.1	2318.3	2312.0
7.5°	2318.3	2305.6	2276.1	2284.3	2273.8
10°	2292.8	2278.0	2235.9	2229.4	2216.8
12.5°	2261.3	2242.1	2184.9	2172.4	2149.0
15°	2223.1	2199.7	2127.9	2087.7	2066.6
17.5°	2178.7	2144.8	2055.9	2009.4	1975.6
20°	2127.9	2085.5	1979.8	1927.0	1880.4
22.5°	2072.9	2024.2	1901.5	1829.7	1798.0
25°	2018.0	1950.2	1810.6	1724.0	1692.1
27.5°	1952.5	1880.4	1726.0	1626.5	1577.9
30°	1882.6	1802.0	1632.9	1525.1	1467.9
32.5°	1814.9	1717.5	1544.3	1417.2	1364.2
35°	1738.8	1630.9	1444.8	1311.5	1264.8
37.5°	1664.7	1548.2	1351.7	1205.6	1152.8
40°	1586.4	1459.6	1254.2	1104.1	1049.1
42.5°	1506.1	1370.7	1157.1	1000.4	947.7
45°	1421.4	1279.6	1057.7	907.3	856.6
47.5°	1341.1	1191.0	962.5	812.2	765.7
50°	1252.3	1102.1	869.4	723.3	679.1
52.5°	1165.4	1006.7	780.5	640.9	600.8
55°	1080.8	915.9	687.4	560.6	520.4
57.5°	994.2	824.9	605.0	486.5	452.6
60°	905.3	736.1	518.2	410.5	376.5
62.5°	818.7	649.5	444.1	342.7	325.8
65°	729.8	558.4	368.1	296.2	289.7
67.5°	645.2	473.7	296.2	260.1	253.8
70°	556.3	391.3	245.2	224.2	215.7
72.5°	471.7	315.1	205.1	188.3	184.0
75°	389.2	241.0	169.2	154.4	152.4
77.5°	306.8	171.3	133.3	124.8	120.6
80°	230.5	122.7	101.4	93.1	93.1
82.5°	160.7	82.6	69.7	65.5	65.5
85°	90.9	46.5	40.2	40.2	40.2
87.5°	33.9	16.9	16.9	14.8	14.8
90°	1.3	16.2	44.0	41.4	42.7
92.5°	27.9	37.7	39.1	40.4	40.4
95°	65.6	78.2	80.4	80.4	78.2
97.5°	109.1	120.8	125.8	125.8	125.8
100°	159.5	169.8	173.4	173.4	172.1
102.5°	212.5	220.2	225.1	226.5	225.1
105°	270.5	274.1	276.8	279.0	279.0
107.5°	328.0	333.4	333.4	334.3	328.0
110°	383.7	391.0	391.0	391.0	387.3

TEST NUMBER: P904355

CATALOG NUMBER: DFN2DIP-TR2F0-060D050US830-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	443.9	451.6	450.3	446.7	443.9
115°	503.2	510.5	508.2	506.9	503.2
117.5°	562.1	572.0	565.7	562.1	558.6
120°	621.4	631.3	621.4	621.4	617.4
122.5°	675.3	688.0	681.6	678.1	675.3
125°	732.0	743.2	739.6	735.6	734.2
127.5°	787.2	801.2	796.3	790.8	787.2
130°	839.0	855.1	852.8	850.2	845.2
132.5°	896.9	909.5	910.4	904.1	900.5
135°	946.8	960.6	963.4	962.1	958.5
137.5°	1002.5	1013.7	1016.0	1015.0	1009.7
140°	1051.4	1062.7	1068.9	1068.9	1064.0
142.5°	1101.7	1113.0	1116.6	1117.9	1113.0
145°	1149.4	1158.4	1165.5	1167.0	1162.0
147.5°	1192.1	1203.3	1208.7	1211.0	1206.0
150°	1236.1	1243.8	1248.7	1252.7	1248.7
152.5°	1275.3	1282.9	1289.1	1294.1	1289.1
155°	1314.3	1317.9	1321.9	1328.2	1324.2
157.5°	1348.0	1350.7	1352.9	1362.0	1355.7
160°	1378.1	1380.8	1382.1	1389.8	1384.4
162.5°	1406.0	1406.0	1407.3	1415.9	1409.6
165°	1429.8	1428.4	1428.4	1437.5	1431.2
167.5°	1451.3	1447.3	1447.3	1456.3	1450.0
170°	1467.5	1464.0	1462.6	1471.6	1464.0
172.5°	1478.8	1475.2	1473.9	1482.8	1475.2
175°	1487.8	1484.1	1481.5	1490.4	1482.8
177.5°	1492.7	1489.1	1486.4	1494.0	1486.4
180°	1490.4	1490.4	1490.4	1490.4	1490.4

TEST NUMBER: P904355

CATALOG NUMBER: DFN2DIP-TR2F0-060D050US830-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.08	13.94	14.02	14.89	16.11	9.06	9.93	10.00	10.87	12.09
	3H	14.74	15.51	15.68	16.46	17.71	10.24	11.01	11.18	11.96	13.21
	4H	15.33	16.06	16.29	17.02	18.27	10.68	11.41	11.64	12.37	13.62
	6H	15.74	16.41	16.71	17.37	18.64	10.99	11.66	11.96	12.62	13.89
	8H	15.85	16.49	16.83	17.47	18.74	11.07	11.71	12.05	12.69	13.96
	12H	15.91	16.51	16.89	17.49	18.78	11.11	11.72	12.09	12.69	13.98
4H	2H	13.10	13.83	14.07	14.79	16.04	9.65	10.38	10.62	11.34	12.59
	3H	14.91	15.51	15.88	16.50	17.77	10.99	11.59	11.96	12.58	13.85
	4H	15.58	16.13	16.56	17.12	18.41	11.52	12.07	12.50	13.06	14.35
	6H	16.08	16.55	17.07	17.56	18.85	11.93	12.40	12.92	13.41	14.70
	8H	16.24	16.68	17.23	17.68	18.99	12.05	12.49	13.04	13.49	14.79
	12H	16.32	16.72	17.34	17.74	19.05	12.10	12.50	13.12	13.52	14.83
8H	4H	15.55	15.99	16.54	16.99	18.29	11.79	12.23	12.79	13.23	14.54
	6H	16.09	16.45	17.11	17.50	18.80	12.29	12.65	13.31	13.69	15.00
	8H	16.29	16.61	17.32	17.64	18.96	12.47	12.79	13.49	13.82	15.14
	12H	16.41	16.70	17.45	17.72	19.09	12.57	12.86	13.60	13.88	15.25
12H	4H	15.50	15.90	16.51	16.91	18.22	11.79	12.19	12.81	13.21	14.52
	6H	16.06	16.39	17.09	17.41	18.74	12.33	12.65	13.36	13.68	15.00
	8H	16.27	16.55	17.30	17.57	18.94	12.53	12.81	13.56	13.83	15.20