

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P906994

Luminaire Tested: DFN2DIP-TR2F0-020D030US835-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P906994
REPORT IS A COMBINATION OF REPORTS P900232 AND P897145
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR2F0-020D030US835-RLLFLL
Description: 2 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4355.0 lumens
Efficiency: N/A
Efficacy: 117.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.04' x L: 2.36' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 37
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P906994
CATALOG NUMBER: DFN2DIP-TR2F0-020D030US835-RLLFLL

Luminous Intensity Polar Plot





TEST NUMBER: P906994

CATALOG NUMBER: DFN2DIP-TR2F0-020D030US835-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	105	105	105	105	95	95	95	95	77	77	77	61	61	61	46	46	46	39			
1	96	92	88	85	87	83	80	78	68	66	64	54	53	51	41	40	40	34			
2	87	80	75	70	79	73	68	64	60	57	54	48	46	44	37	35	34	29			
3	80	71	64	58	73	65	59	54	53	49	46	43	40	37	33	31	29	25			
4	73	63	55	50	66	58	51	46	48	43	39	38	35	32	30	27	26	22			
5	67	56	48	43	61	52	45	40	43	38	34	35	31	28	27	24	22	19			
6	62	51	43	37	56	46	40	35	39	33	30	31	28	25	25	22	20	17			
7	57	46	38	33	52	42	35	30	35	30	26	29	25	22	22	20	18	15			
8	53	41	34	29	49	38	32	27	32	27	23	26	22	20	21	18	16	14			
9	50	38	31	26	45	35	29	24	29	24	21	24	20	18	19	17	15	12			
10	46	35	28	23	42	32	26	22	27	22	19	22	19	16	18	15	13	11			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1844	1844	1844
5°	1844	1810	1823
10°	1823	1771	1760
15°	1795	1708	1666
20°	1759	1624	1551
25°	1722	1530	1440
30°	1674	1434	1300
35°	1626	1331	1178
40°	1577	1225	1038
45°	1521	1108	911
50°	1463	991	788
55°	1401	866	669
60°	1331	735	548
65°	1249	604	490
70°	1149	480	439
75°	1024	415	393
80°	844	338	331
85°	554	209	233

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1521 cd/sqm



TEST NUMBER: P906994

CATALOG NUMBER: DFN2DIP-TR2F0-020D030US835-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	77.5	1.8
10°-20°	212.7	4.9
20°-30°	298.6	6.9
30°-40°	325.5	7.5
40°-50°	299.1	6.9
50°-60°	234.9	5.4
60°-70°	152.9	3.5
70°-80°	78.7	1.8
80°-90°	22.8	0.5
90°-100°	58.7	1.3
100°-110°	186.5	4.3
110°-120°	319.2	7.3
120°-130°	419.8	9.6
130°-140°	471.2	10.8
140°-150°	462.1	10.6
150°-160°	387.7	8.9
160°-170°	257.1	5.9
170°-180°	89.9	2.1
0°-30°	588.7	13.5
0°-40°	914.2	21.0
0°-60°	1448.3	33.3
0°-90°	1702.7	39.1
90°-120°	564.5	13.0
90°-150°	1917.7	44.0
90°-180°	2652.0	60.9
0°-180°	4355.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	827	827	827	827	827	
5°	827	823	813	820	818	78
15°	786	778	752	738	731	222
25°	714	690	640	610	598	328
35°	615	577	511	464	447	385
45°	503	452	374	321	303	388
55°	382	324	243	198	184	342
65°	258	198	130	105	102	256
75°	138	85	60	55	54	146
85°	32	16	14	14	14	37
90°	1	10	28	26	27	4
95°	42	50	51	51	50	46
105°	172	174	176	178	178	182
115°	320	325	324	323	320	317
125°	466	473	471	468	467	416
135°	603	612	613	612	610	466
145°	732	737	742	743	740	457
155°	837	839	842	846	843	385
165°	910	909	909	915	911	257
175°	947	945	943	949	944	90
180°	949	949	949	949	949	



TEST NUMBER: P906994

CATALOG NUMBER: DFN2DIP-TR2F0-020D030US835-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	826.6	826.6	826.6	826.6	826.6
2.5°	830.3	826.6	818.3	825.9	824.4
5°	826.6	822.9	813.1	819.9	817.6
7.5°	819.9	815.4	804.9	807.9	804.1
10°	810.9	805.6	790.7	788.4	784.0
12.5°	799.7	792.9	772.7	768.3	760.0
15°	786.2	777.9	752.5	738.3	730.9
17.5°	770.5	758.5	727.1	710.6	698.7
20°	752.5	737.5	700.2	681.5	665.0
22.5°	733.1	715.9	672.5	647.1	635.9
25°	713.7	689.7	640.3	609.7	598.4
27.5°	690.5	665.0	610.4	575.2	558.0
30°	665.8	637.3	577.5	539.4	519.1
32.5°	641.8	607.4	546.1	501.2	482.5
35°	614.9	576.8	511.0	463.8	447.3
37.5°	588.7	547.5	478.0	426.4	407.7
40°	561.0	516.2	443.6	390.5	371.0
42.5°	532.6	484.8	409.2	353.8	335.2
45°	502.7	452.5	374.1	320.9	302.9
47.5°	474.3	421.2	340.4	287.2	270.8
50°	442.9	389.8	307.5	255.8	240.2
52.5°	412.1	356.0	276.0	226.7	212.5
55°	382.2	323.9	243.1	198.3	184.0
57.5°	351.6	291.7	214.0	172.1	160.1
60°	320.2	260.3	183.3	145.2	133.2
62.5°	289.5	229.7	157.1	121.2	115.2
65°	258.1	197.5	130.2	104.8	102.5
67.5°	228.2	167.5	104.8	92.0	89.8
70°	196.7	138.4	86.7	79.3	76.3
72.5°	166.8	111.4	72.5	66.6	65.1
75°	137.6	85.2	59.8	54.6	53.9
77.5°	108.5	60.6	47.1	44.1	42.6
80°	81.5	43.4	35.9	32.9	32.9
82.5°	56.8	29.2	24.7	23.2	23.2
85°	32.1	16.4	14.2	14.2	14.2
87.5°	12.0	6.0	6.0	5.2	5.2
90°	0.9	10.3	28.0	26.3	27.2
92.5°	17.7	24.0	24.9	25.7	25.7
95°	41.8	49.8	51.2	51.2	49.8
97.5°	69.5	76.9	80.1	80.1	80.1
100°	101.5	108.1	110.4	110.4	109.6
102.5°	135.3	140.2	143.3	144.2	143.3
105°	172.2	174.5	176.2	177.6	177.6
107.5°	208.8	212.2	212.2	212.8	208.8
110°	244.3	248.9	248.9	248.9	246.6



TEST NUMBER: P906994

CATALOG NUMBER: DFN2DIP-TR2F0-020D030US835-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	282.6	287.5	286.6	284.3	282.6
115°	320.4	324.9	323.5	322.7	320.4
117.5°	357.8	364.1	360.1	357.8	355.5
120°	395.6	401.9	395.6	395.6	393.0
122.5°	429.9	437.9	433.9	431.6	429.9
125°	466.0	473.1	470.8	468.2	467.4
127.5°	501.1	510.0	506.9	503.4	501.1
130°	534.0	544.3	542.9	541.2	538.0
132.5°	570.9	578.9	579.5	575.5	573.2
135°	602.7	611.5	613.3	612.4	610.1
137.5°	638.1	645.3	646.7	646.2	642.7
140°	669.3	676.5	680.5	680.5	677.3
142.5°	701.4	708.5	710.8	711.7	708.5
145°	731.7	737.4	742.0	742.8	739.7
147.5°	758.9	766.0	769.4	770.9	767.7
150°	786.9	791.8	794.9	797.5	794.9
152.5°	811.8	816.6	820.6	823.8	820.6
155°	836.7	838.9	841.5	845.5	843.0
157.5°	858.1	859.8	861.3	867.0	863.0
160°	877.3	879.0	879.9	884.7	881.3
162.5°	895.0	895.0	895.9	901.3	897.3
165°	910.2	909.3	909.3	915.0	911.0
167.5°	923.9	921.3	921.3	927.0	923.0
170°	934.2	931.9	931.1	936.8	931.9
172.5°	941.3	939.1	938.2	943.9	939.1
175°	947.1	944.8	943.1	948.8	943.9
177.5°	950.2	947.9	946.2	951.1	946.2
180°	948.8	948.8	948.8	948.8	948.8



TEST NUMBER: P906994
 CATALOG NUMBER: DFN2DIP-TR2F0-020D030US835-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.03	8.78	9.08	9.83	11.25	4.01	4.76	5.07	5.81	7.24
	3H	9.68	10.35	10.74	11.41	12.85	5.18	5.85	6.24	6.91	8.35
	4H	10.27	10.90	11.34	11.96	13.41	5.62	6.25	6.69	7.31	8.76
	6H	10.66	11.25	11.75	12.31	13.77	5.92	6.50	7.00	7.57	9.03
	8H	10.78	11.33	11.86	12.41	13.87	6.00	6.55	7.09	7.64	9.09
	12H	10.83	11.35	11.92	12.43	13.91	6.03	6.56	7.12	7.64	9.11
4H	2H	8.03	8.67	9.11	9.73	11.18	4.59	5.22	5.67	6.28	7.73
	3H	9.83	10.36	10.92	11.45	12.91	5.91	6.44	7.00	7.53	8.99
	4H	10.50	10.98	11.59	12.06	13.54	6.44	6.92	7.53	8.01	9.49
	6H	10.99	11.40	12.09	12.51	13.98	6.84	7.25	7.94	8.36	9.83
	8H	11.15	11.54	12.25	12.63	14.12	6.96	7.34	8.06	8.44	9.93
	12H	11.23	11.58	12.34	12.68	14.18	7.01	7.36	8.12	8.47	9.96
8H	4H	10.46	10.84	11.56	11.94	13.43	6.70	7.09	7.80	8.18	9.67
	6H	11.00	11.31	12.12	12.45	13.94	7.19	7.51	8.31	8.65	10.14
	8H	11.20	11.48	12.32	12.59	14.10	7.37	7.65	8.50	8.77	10.28
	12H	11.31	11.56	12.44	12.68	14.22	7.47	7.72	8.61	8.84	10.38
12H	4H	10.40	10.75	11.52	11.86	13.36	6.70	7.05	7.81	8.16	9.65
	6H	10.97	11.25	12.10	12.37	13.87	7.24	7.52	8.36	8.64	10.14
	8H	11.17	11.41	12.30	12.53	14.07	7.43	7.67	8.56	8.79	10.33