

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P907032

Luminaire Tested: DFN2DIP-TR2F0-040D030US835-FLLFLL

Issue Date: 11/21/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P907032  
REPORT IS A COMBINATION OF REPORTS P900235 AND P897145  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-TR2F0-040D030US835-FLLFLL  
Description: 2 foot, Triangle Define Geo, with Direct Frosted Lens, Indirect Frosted Lens  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6615.0 lumens  
Efficiency: N/A  
Efficacy: 114.4 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29  
Luminous Opening: Rectangular w/ Sides (W: 2.04' x L: 2.36' x H: 0.1')  
CIE Type: General Diffuse

Input Watts (W): 57.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9933  
Total Harmonic Distortion (THDi): 0.066  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P907032  
CATALOG NUMBER: DFN2DIP-TR2F0-040D030US835-FLLFLL

### Luminous Intensity Polar Plot





TEST NUMBER: P907032

CATALOG NUMBER: DFN2DIP-TR2F0-040D030US835-FLLFLL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	102	102	102	102	89	89	89	77	77	77	65	65	65	60
1	100	96	92	88	93	89	86	83	78	75	73	67	66	64	58	56	55	50
2	91	84	77	72	85	78	73	68	68	64	61	59	56	53	51	48	46	42
3	83	73	66	60	77	69	62	57	60	55	51	52	48	45	45	42	40	36
4	76	65	57	51	71	61	54	48	54	48	43	47	42	39	40	37	34	31
5	70	58	50	44	65	55	47	42	48	42	38	42	37	34	36	33	30	27
6	64	52	44	38	60	49	42	36	43	37	33	38	33	29	33	29	26	23
7	60	47	39	33	56	44	37	32	39	33	29	35	30	26	30	26	23	21
8	55	43	35	30	52	40	33	28	36	30	26	32	27	23	28	24	21	19
9	52	39	32	26	48	37	30	25	33	27	23	29	24	21	26	22	19	17
10	48	36	29	24	45	34	27	23	30	25	21	27	22	19	24	20	17	15

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	3471	3471	3471
5°	3472	3415	3440
10°	3439	3362	3388
15°	3383	3299	3309
20°	3309	3214	3229
25°	3236	3114	3137
30°	3146	3021	3021
35°	3059	2913	2900
40°	2954	2802	2784
45°	2849	2692	2664
50°	2734	2575	2527
55°	2613	2441	2399
60°	2475	2282	2253
65°	2325	2116	2081
70°	2133	1915	1893
75°	1871	1673	1713
80°	1550	1364	1385
85°	1057	860	860

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 2849 cd/sqm



TEST NUMBER: P907032

CATALOG NUMBER: DFN2DIP-TR2F0-040D030US835-FLLFLL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	146.5	2.2
10°-20°	412.2	6.2
20°-30°	605.7	9.2
30°-40°	703.5	10.6
40°-50°	702.6	10.6
50°-60°	612.7	9.3
60°-70°	452.9	6.8
70°-80°	256.2	3.9
80°-90°	70.3	1.1
90°-100°	58.7	0.9
100°-110°	186.5	2.8
110°-120°	319.2	4.8
120°-130°	419.8	6.3
130°-140°	471.2	7.1
140°-150°	462.1	7.0
150°-160°	387.7	5.9
160°-170°	257.1	3.9
170°-180°	89.9	1.4
0°-30°	1164.4	17.6
0°-40°	1867.9	28.2
0°-60°	3183.2	48.1
0°-90°	3962.7	59.9
90°-120°	564.5	8.5
90°-150°	1917.7	29.0
90°-180°	2652.0	40.1
0°-180°	6615.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1556	1556	1556	1556	1556	
5°	1556	1550	1534	1546	1543	148
15°	1482	1473	1453	1459	1452	417
25°	1341	1329	1304	1306	1304	617
35°	1157	1142	1118	1109	1102	722
45°	941	931	908	892	886	727
55°	712	703	686	668	660	637
65°	480	471	456	443	436	475
75°	251	248	241	232	235	268
85°	61	60	58	54	52	68
90°	1	10	28	26	27	6
95°	42	50	51	51	50	46
105°	172	174	176	178	178	182
115°	320	325	324	323	320	317
125°	466	473	471	468	467	416
135°	603	612	613	612	610	466
145°	732	737	742	743	740	457
155°	837	839	842	846	843	385
165°	910	909	909	915	911	257
175°	947	945	943	949	944	90
180°	949	949	949	949	949	



TEST NUMBER: P907032

CATALOG NUMBER: DFN2DIP-TR2F0-040D030US835-FLLFL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1556.4	1556.4	1556.4	1556.4	1556.4
2.5°	1565.5	1558.0	1541.5	1556.4	1553.6
5°	1556.4	1550.5	1534.0	1545.9	1543.1
7.5°	1545.9	1537.0	1520.5	1532.6	1529.6
10°	1529.6	1519.1	1501.2	1513.1	1508.6
12.5°	1507.0	1498.1	1480.2	1487.7	1484.6
15°	1481.6	1472.7	1453.2	1459.2	1451.8
17.5°	1450.2	1441.3	1421.8	1429.2	1421.8
20°	1415.7	1406.8	1385.9	1390.3	1384.5
22.5°	1381.4	1367.9	1348.4	1348.4	1345.4
25°	1340.9	1329.0	1303.6	1306.5	1303.6
27.5°	1296.0	1285.5	1266.2	1261.7	1254.3
30°	1251.2	1239.2	1216.8	1212.3	1206.3
32.5°	1203.3	1194.4	1170.4	1161.4	1155.3
35°	1156.9	1142.0	1118.0	1109.0	1101.5
37.5°	1104.5	1091.0	1067.0	1056.6	1049.1
40°	1050.7	1038.6	1014.6	1001.3	995.3
42.5°	998.3	986.2	962.4	947.3	938.4
45°	941.4	931.0	908.4	892.1	886.0
47.5°	886.0	875.5	851.6	835.1	826.2
50°	827.6	820.1	799.2	778.2	770.7
52.5°	770.7	760.3	740.9	724.4	713.9
55°	712.5	703.4	685.5	667.5	660.1
57.5°	654.0	646.6	627.0	609.1	603.1
60°	595.6	589.7	568.8	552.3	547.8
62.5°	538.8	528.3	513.4	498.4	492.4
65°	480.5	471.4	456.5	443.0	435.6
67.5°	420.6	413.0	399.7	389.2	383.2
70°	365.2	359.2	345.7	335.2	329.3
72.5°	308.4	302.3	294.9	284.4	279.9
75°	251.4	248.5	240.9	232.0	235.0
77.5°	200.5	194.5	191.5	187.0	182.6
80°	149.7	148.1	145.1	140.7	137.7
82.5°	101.8	101.8	100.4	94.3	94.3
85°	61.3	59.9	58.4	53.8	52.4
87.5°	27.0	24.0	21.0	16.5	14.9
90°	0.9	10.3	28.0	26.3	27.2
92.5°	17.7	24.0	24.9	25.7	25.7
95°	41.8	49.8	51.2	51.2	49.8
97.5°	69.5	76.9	80.1	80.1	80.1
100°	101.5	108.1	110.4	110.4	109.6
102.5°	135.3	140.2	143.3	144.2	143.3
105°	172.2	174.5	176.2	177.6	177.6
107.5°	208.8	212.2	212.2	212.8	208.8
110°	244.3	248.9	248.9	248.9	246.6



TEST NUMBER: P907032

CATALOG NUMBER: DFN2DIP-TR2F0-040D030US835-FLLFLL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	282.6	287.5	286.6	284.3	282.6
115°	320.4	324.9	323.5	322.7	320.4
117.5°	357.8	364.1	360.1	357.8	355.5
120°	395.6	401.9	395.6	395.6	393.0
122.5°	429.9	437.9	433.9	431.6	429.9
125°	466.0	473.1	470.8	468.2	467.4
127.5°	501.1	510.0	506.9	503.4	501.1
130°	534.0	544.3	542.9	541.2	538.0
132.5°	570.9	578.9	579.5	575.5	573.2
135°	602.7	611.5	613.3	612.4	610.1
137.5°	638.1	645.3	646.7	646.2	642.7
140°	669.3	676.5	680.5	680.5	677.3
142.5°	701.4	708.5	710.8	711.7	708.5
145°	731.7	737.4	742.0	742.8	739.7
147.5°	758.9	766.0	769.4	770.9	767.7
150°	786.9	791.8	794.9	797.5	794.9
152.5°	811.8	816.6	820.6	823.8	820.6
155°	836.7	838.9	841.5	845.5	843.0
157.5°	858.1	859.8	861.3	867.0	863.0
160°	877.3	879.0	879.9	884.7	881.3
162.5°	895.0	895.0	895.9	901.3	897.3
165°	910.2	909.3	909.3	915.0	911.0
167.5°	923.9	921.3	921.3	927.0	923.0
170°	934.2	931.9	931.1	936.8	931.9
172.5°	941.3	939.1	938.2	943.9	939.1
175°	947.1	944.8	943.1	948.8	943.9
177.5°	950.2	947.9	946.2	951.1	946.2
180°	948.8	948.8	948.8	948.8	948.8



TEST NUMBER: P907032  
 CATALOG NUMBER: DFN2DIP-TR2F0-040D030US835-FLLFL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.33	13.29	13.20	14.18	15.30	11.91	12.87	12.78	13.76	14.88
	3H	13.98	14.84	14.86	15.74	16.88	13.52	14.38	14.40	15.27	16.42
	4H	14.55	15.37	15.45	16.27	17.43	14.09	14.91	14.99	15.81	16.97
	6H	14.94	15.69	15.85	16.60	17.77	14.48	15.23	15.39	16.14	17.31
	8H	15.04	15.75	15.95	16.68	17.85	14.58	15.29	15.49	16.22	17.39
	12H	15.08	15.76	16.00	16.68	17.88	14.62	15.30	15.54	16.22	17.42
4H	2H	12.80	13.61	13.70	14.51	15.67	12.46	13.27	13.36	14.18	15.33
	3H	14.64	15.32	15.56	16.26	17.43	14.26	14.94	15.17	15.87	17.05
	4H	15.34	15.96	16.27	16.89	18.09	14.95	15.57	15.87	16.50	17.70
	6H	15.84	16.38	16.78	17.33	18.53	15.45	15.98	16.38	16.94	18.13
	8H	15.98	16.48	16.92	17.43	18.64	15.59	16.09	16.52	17.03	18.25
	12H	16.05	16.50	17.01	17.47	18.69	15.64	16.09	16.60	17.06	18.28
8H	4H	15.54	16.04	16.48	16.99	18.20	15.19	15.69	16.13	16.63	17.85
	6H	16.15	16.56	17.11	17.55	18.76	15.79	16.21	16.76	17.20	18.41
	8H	16.35	16.72	17.33	17.70	18.93	16.00	16.36	16.97	17.34	18.57
	12H	16.47	16.79	17.45	17.77	19.05	16.10	16.43	17.08	17.40	18.68
12H	4H	15.53	15.98	16.48	16.94	18.16	15.18	15.63	16.14	16.60	17.82
	6H	16.17	16.54	17.15	17.52	18.75	15.83	16.20	16.80	17.18	18.41
	8H	16.40	16.72	17.38	17.70	18.97	16.06	16.38	17.03	17.35	18.63