

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P926101

Luminaire Tested: DFN2DIP-TR2F0-020D060US950-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P926101
REPORT IS A COMBINATION OF REPORTS P901781 AND P897145
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR2F0-020D060US950-FLLONL
Description: 2 foot, Triangle Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6954.7 lumens
Efficiency: N/A
Efficacy: 109.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.04' x L: 2.36' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 63.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P926101

CATALOG NUMBER: DFN2DIP-TR2F0-020D060US950-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P926101

CATALOG NUMBER: DFN2DIP-TR2F0-020D060US950-FLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	91	91	91	91	71	71	71	52	52	52	35	35	35
1	93	88	85	81	83	79	76	73	62	60	58	46	44	43	31	30	30
2	84	77	71	66	75	69	64	60	54	51	48	40	38	36	27	26	25
3	77	68	61	55	68	61	55	50	48	44	40	35	33	30	24	23	21
4	70	60	52	47	62	54	47	42	42	38	34	32	29	26	22	20	18
5	64	53	45	40	57	48	41	36	38	33	29	28	25	22	19	17	16
6	59	48	40	34	53	43	36	31	34	29	25	25	22	20	18	16	14
7	55	43	35	30	49	39	32	27	31	26	22	23	20	17	16	14	12
8	51	39	31	26	45	35	28	24	28	23	20	21	18	15	15	13	11
9	47	35	28	23	42	32	26	21	25	21	17	19	16	14	14	11	10
10	44	32	25	21	39	29	23	19	23	19	16	18	15	12	13	10	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1656	1656	1656
5°	1656	1629	1641
10°	1640	1604	1616
15°	1614	1573	1578
20°	1579	1533	1540
25°	1544	1486	1496
30°	1500	1441	1441
35°	1459	1389	1383
40°	1409	1337	1328
45°	1359	1284	1271
50°	1304	1228	1206
55°	1246	1164	1144
60°	1181	1089	1075
65°	1109	1010	993
70°	1018	913	903
75°	892	798	817
80°	740	652	660
85°	503	411	410

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 2362 cd/sqm

TEST NUMBER: P926101

CATALOG NUMBER: DFN2DIP-TR2F0-020D060US950-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	69.9	1.0
10°-20°	196.6	2.8
20°-30°	288.9	4.2
30°-40°	335.6	4.8
40°-50°	335.2	4.8
50°-60°	292.2	4.2
60°-70°	216.0	3.1
70°-80°	122.2	1.8
80°-90°	37.4	0.5
90°-100°	112.0	1.6
100°-110°	355.9	5.1
110°-120°	609.1	8.8
120°-130°	801.1	11.5
130°-140°	899.2	12.9
140°-150°	881.7	12.7
150°-160°	739.6	10.6
160°-170°	490.5	7.1
170°-180°	171.4	2.5
0°-30°	555.4	8.0
0°-40°	891.0	12.8
0°-60°	1518.4	21.8
0°-90°	1894.1	27.2
90°-120°	1077.0	15.5
90°-150°	3659.0	52.6
90°-180°	5061.0	72.8
0°-180°	6954.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	742	742	742	742	742	
5°	742	740	732	737	736	70
15°	707	702	693	696	692	199
25°	640	634	622	623	622	294
35°	552	545	533	529	525	345
45°	449	444	433	426	423	347
55°	340	336	327	318	315	304
65°	229	225	218	211	208	227
75°	120	119	115	111	112	128
85°	29	28	28	26	25	33
90°	2	20	54	50	52	7
95°	80	95	98	98	95	89
105°	329	333	336	339	339	347
115°	611	620	617	616	611	605
125°	889	903	898	893	892	794
135°	1150	1167	1170	1168	1164	889
145°	1396	1407	1416	1417	1411	872
155°	1596	1601	1606	1613	1608	735
165°	1737	1735	1735	1746	1738	490
175°	1807	1803	1799	1810	1801	172
180°	1810	1810	1810	1810	1810	

TEST NUMBER: P926101

CATALOG NUMBER: DFN2DIP-TR2F0-020D060US950-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	742.4	742.4	742.4	742.4	742.4
2.5°	746.7	743.2	735.2	742.4	741.1
5°	742.4	739.6	731.7	737.4	736.0
7.5°	737.4	733.1	725.3	731.1	729.6
10°	729.6	724.7	716.1	721.7	719.6
12.5°	718.8	714.6	706.1	709.6	708.2
15°	706.7	702.5	693.2	696.0	692.5
17.5°	691.7	687.5	678.2	681.7	678.2
20°	675.3	671.0	661.0	663.2	660.4
22.5°	658.9	652.5	643.2	643.2	641.8
25°	639.7	633.9	621.8	623.2	621.8
27.5°	618.2	613.2	604.0	601.9	598.3
30°	596.8	591.1	580.4	578.3	575.4
32.5°	573.9	569.7	558.3	554.0	551.1
35°	551.9	544.7	533.3	529.0	525.4
37.5°	526.9	520.4	509.0	504.0	500.4
40°	501.1	495.4	484.0	477.7	474.7
42.5°	476.1	470.4	459.1	451.9	447.6
45°	449.0	444.1	433.3	425.5	422.6
47.5°	422.6	417.7	406.2	398.3	394.1
50°	394.8	391.2	381.2	371.2	367.7
52.5°	367.7	362.6	353.4	345.5	340.6
55°	339.8	335.5	326.9	318.4	314.8
57.5°	312.0	308.4	299.1	290.6	287.6
60°	284.1	281.3	271.3	263.4	261.3
62.5°	257.0	252.0	244.9	237.7	234.9
65°	229.2	224.9	217.8	211.3	207.8
67.5°	200.6	197.0	190.6	185.6	182.8
70°	174.2	171.3	164.9	159.9	157.1
72.5°	147.1	144.2	140.6	135.7	133.6
75°	119.9	118.6	114.9	110.7	112.1
77.5°	95.7	92.8	91.3	89.2	87.1
80°	71.5	70.7	69.3	67.1	65.6
82.5°	48.6	48.6	47.9	45.0	45.0
85°	29.2	28.5	27.9	25.7	25.0
87.5°	12.9	11.4	10.0	7.9	7.2
90°	1.6	19.7	53.5	50.2	51.8
92.5°	33.9	45.9	47.5	49.1	49.1
95°	79.7	94.9	97.7	97.7	94.9
97.5°	132.6	146.8	152.8	152.8	152.8
100°	193.8	206.3	210.6	210.6	209.0
102.5°	258.2	267.4	273.4	275.0	273.4
105°	328.6	332.9	336.2	339.0	339.0
107.5°	398.4	405.0	405.0	406.0	398.4
110°	466.1	474.8	474.8	474.8	470.4

TEST NUMBER: P926101

CATALOG NUMBER: DFN2DIP-TR2F0-020D060US950-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	539.2	548.5	546.8	542.4	539.2
115°	611.2	620.0	617.2	615.6	611.2
117.5°	682.8	694.8	687.1	682.8	678.4
120°	754.8	766.8	754.8	754.8	749.8
122.5°	820.2	835.5	827.9	823.6	820.2
125°	889.0	902.7	898.3	893.4	891.8
127.5°	956.2	973.1	967.1	960.6	956.2
130°	1019.0	1038.6	1035.9	1032.6	1026.6
132.5°	1089.4	1104.6	1105.7	1098.1	1093.7
135°	1150.0	1166.8	1170.1	1168.5	1164.1
137.5°	1217.6	1231.2	1234.0	1232.9	1226.4
140°	1277.1	1290.8	1298.4	1298.4	1292.4
142.5°	1338.2	1351.8	1356.2	1357.8	1351.8
145°	1396.1	1407.0	1415.7	1417.4	1411.3
147.5°	1447.9	1461.5	1468.1	1470.8	1464.8
150°	1501.4	1510.7	1516.7	1521.5	1516.7
152.5°	1548.8	1558.2	1565.8	1571.8	1565.8
155°	1596.3	1600.7	1605.6	1613.3	1608.3
157.5°	1637.3	1640.6	1643.3	1654.2	1646.6
160°	1673.9	1677.1	1678.8	1688.0	1681.5
162.5°	1707.7	1707.7	1709.3	1719.7	1712.0
165°	1736.6	1734.9	1734.9	1745.9	1738.3
167.5°	1762.8	1757.9	1757.9	1768.8	1761.2
170°	1782.5	1778.1	1776.4	1787.3	1778.1
172.5°	1796.1	1791.7	1790.1	1801.0	1791.7
175°	1807.0	1802.7	1799.3	1810.3	1801.0
177.5°	1813.0	1808.7	1805.3	1814.6	1805.3
180°	1810.3	1810.3	1810.3	1810.3	1810.3

TEST NUMBER: P926101

CATALOG NUMBER: DFN2DIP-TR2F0-020D060US950-FLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.28	6.97	7.42	8.10	9.66	5.86	6.55	6.99	7.67	9.24
	3H	7.91	8.52	9.05	9.66	11.23	7.45	8.06	8.59	9.20	10.77
	4H	8.47	9.06	9.62	10.19	11.77	8.01	8.60	9.16	9.73	11.31
	6H	8.85	9.38	10.00	10.52	12.11	8.38	8.92	9.54	10.06	11.65
	8H	8.94	9.45	10.09	10.60	12.18	8.48	8.99	9.64	10.14	11.73
	12H	8.97	9.46	10.13	10.60	12.21	8.51	8.99	9.67	10.14	11.75
4H	2H	6.72	7.30	7.87	8.43	10.02	6.38	6.96	7.53	8.09	9.68
	3H	8.54	9.03	9.70	10.18	11.78	8.16	8.64	9.32	9.80	11.40
	4H	9.23	9.68	10.39	10.82	12.44	8.83	9.28	10.00	10.43	12.04
	6H	9.71	10.10	10.88	11.26	12.87	9.31	9.70	10.48	10.87	12.47
	8H	9.84	10.20	11.01	11.36	12.99	9.45	9.81	10.61	10.97	12.59
	12H	9.90	10.22	11.08	11.40	13.02	9.49	9.82	10.68	10.99	12.62
8H	4H	9.40	9.76	10.57	10.92	12.54	9.05	9.41	10.22	10.57	12.19
	6H	10.00	10.29	11.18	11.49	13.11	9.64	9.94	10.83	11.14	12.76
	8H	10.20	10.46	11.39	11.64	13.28	9.84	10.10	11.04	11.28	12.92
	12H	10.31	10.53	11.50	11.71	13.38	9.94	10.16	11.13	11.34	13.01
12H	4H	9.37	9.70	10.56	10.87	12.50	9.03	9.36	10.21	10.53	12.15
	6H	10.02	10.28	11.21	11.46	13.10	9.68	9.94	10.87	11.12	12.76
	8H	10.24	10.46	11.43	11.64	13.31	9.89	10.12	11.09	11.29	12.97

END OF REPORT