

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P926110

Luminaire Tested: DFN2DIP-TR2F0-030D030US950-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P926110
REPORT IS A COMBINATION OF REPORTS P900234 AND P897145
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR2F0-030D030US950-RLLFLL
Description: 2 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4965.5 lumens
Efficiency: N/A
Efficacy: 105.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.04' x L: 2.36' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 47
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P926110

CATALOG NUMBER: DFN2DIP-TR2F0-030D030US950-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P926110

CATALOG NUMBER: DFN2DIP-TR2F0-030D030US950-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83	68	68	68	55	55	55
1	98	94	90	87	90	87	84	81	73	71	69	61	59	58	50	49	48
2	90	83	77	72	82	76	71	67	65	61	58	54	51	49	44	42	41
3	82	73	66	60	75	68	61	57	58	53	49	48	45	42	40	37	35
4	75	65	57	51	69	60	54	48	51	46	42	43	40	36	36	33	31
5	69	58	50	44	64	54	47	42	46	41	37	39	35	32	32	29	27
6	64	52	44	39	59	49	42	37	42	36	32	35	31	28	30	26	24
7	59	47	40	34	55	44	37	32	38	33	29	32	28	25	27	24	22
8	55	43	36	30	51	40	33	29	35	29	26	30	26	23	25	22	20
9	51	39	32	27	47	37	30	26	32	27	23	27	23	20	23	20	18
10	48	36	29	24	44	34	28	23	30	24	21	25	21	19	22	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2638	2638	2638
5°	2639	2591	2608
10°	2609	2534	2519
15°	2569	2444	2384
20°	2517	2324	2219
25°	2465	2189	2060
30°	2395	2052	1861
35°	2327	1905	1685
40°	2258	1753	1485
45°	2177	1586	1304
50°	2093	1418	1127
55°	2005	1238	957
60°	1904	1052	784
65°	1787	863	700
70°	1644	687	627
75°	1465	595	562
80°	1209	482	474
85°	793	299	333

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2177 cd/sqm

TEST NUMBER: P926110

CATALOG NUMBER: DFN2DIP-TR2F0-030D030US950-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	110.9	2.2
10°-20°	304.3	6.1
20°-30°	427.3	8.6
30°-40°	465.7	9.4
40°-50°	428.1	8.6
50°-60°	336.2	6.8
60°-70°	218.8	4.4
70°-80°	112.6	2.3
80°-90°	31.3	0.6
90°-100°	56.0	1.1
100°-110°	178.0	3.6
110°-120°	304.6	6.1
120°-130°	400.5	8.1
130°-140°	449.6	9.1
140°-150°	440.9	8.9
150°-160°	369.8	7.4
160°-170°	245.3	4.9
170°-180°	85.7	1.7
0°-30°	842.5	17.0
0°-40°	1308.2	26.3
0°-60°	2072.5	41.7
0°-90°	2435.2	49.0
90°-120°	538.5	10.8
90°-150°	1829.5	36.8
90°-180°	2530.0	51.0
0°-180°	4965.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1183	1183	1183	1183	1183	
5°	1183	1178	1164	1173	1170	112
15°	1125	1113	1077	1057	1046	317
25°	1021	987	916	872	856	470
35°	880	825	731	664	640	551
45°	719	648	535	459	434	556
55°	547	464	348	284	263	489
65°	369	283	186	150	147	366
75°	197	122	86	78	77	208
85°	46	24	20	20	20	53
90°	1	10	27	25	26	5
95°	40	48	49	49	48	44
105°	164	166	168	169	169	173
115°	306	310	309	308	306	302
125°	445	451	449	447	446	397
135°	575	583	585	584	582	444
145°	698	704	708	709	706	436
155°	798	800	803	807	804	367
165°	868	868	868	873	869	245
175°	904	901	900	905	900	86
180°	905	905	905	905	905	

TEST NUMBER: P926110

CATALOG NUMBER: DFN2DIP-TR2F0-030D030US950-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1182.9	1182.9	1182.9	1182.9	1182.9
2.5°	1188.2	1182.9	1171.0	1181.8	1179.7
5°	1182.9	1177.5	1163.6	1173.2	1170.0
7.5°	1173.2	1166.8	1151.9	1156.1	1150.7
10°	1160.4	1152.9	1131.5	1128.2	1121.9
12.5°	1144.3	1134.7	1105.8	1099.4	1087.6
15°	1125.1	1113.2	1076.9	1056.6	1045.9
17.5°	1102.5	1085.5	1040.4	1017.0	999.8
20°	1076.9	1055.4	1001.9	975.3	951.6
22.5°	1049.1	1024.4	962.3	926.0	909.9
25°	1021.3	986.9	916.3	872.4	856.3
27.5°	988.1	951.6	873.5	823.2	798.5
30°	952.8	912.0	826.4	771.9	742.9
32.5°	918.4	869.2	781.5	717.2	690.4
35°	880.0	825.3	731.1	663.7	640.1
37.5°	842.5	783.5	684.0	610.1	583.5
40°	802.9	738.7	634.8	558.8	531.0
42.5°	762.2	693.7	585.6	506.3	479.6
45°	719.4	647.6	535.3	459.2	433.5
47.5°	678.7	602.7	487.1	411.0	387.5
50°	633.7	557.7	440.0	366.0	343.6
52.5°	589.8	509.5	395.1	324.4	304.0
55°	546.9	463.5	347.8	283.7	263.4
57.5°	503.1	417.5	306.2	246.2	229.1
60°	458.1	372.5	262.3	207.7	190.6
62.5°	414.3	328.7	224.8	173.4	164.9
65°	369.3	282.6	186.2	149.9	146.6
67.5°	326.6	239.7	149.9	131.7	128.4
70°	281.5	198.1	124.1	113.4	109.1
72.5°	238.7	159.4	103.8	95.3	93.1
75°	196.9	122.0	85.7	78.1	77.1
77.5°	155.2	86.6	67.4	63.2	61.0
80°	116.7	62.1	51.3	47.1	47.1
82.5°	81.3	41.8	35.3	33.2	33.2
85°	46.0	23.5	20.3	20.3	20.3
87.5°	17.2	8.5	8.5	7.5	7.5
90°	0.9	9.8	26.7	25.1	25.9
92.5°	16.9	22.9	23.8	24.5	24.5
95°	39.9	47.5	48.8	48.8	47.5
97.5°	66.3	73.4	76.4	76.4	76.4
100°	96.8	103.1	105.3	105.3	104.6
102.5°	129.1	133.8	136.7	137.6	136.7
105°	164.3	166.5	168.1	169.4	169.4
107.5°	199.2	202.4	202.4	203.0	199.2
110°	233.1	237.5	237.5	237.5	235.3

TEST NUMBER: P926110

CATALOG NUMBER: DFN2DIP-TR2F0-030D030US950-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	269.6	274.3	273.4	271.2	269.6
115°	305.7	310.0	308.6	307.9	305.7
117.5°	341.3	347.4	343.5	341.3	339.1
120°	377.4	383.4	377.4	377.4	374.9
122.5°	410.1	417.8	413.9	411.7	410.1
125°	444.6	451.3	449.1	446.7	445.9
127.5°	478.0	486.5	483.6	480.2	478.0
130°	509.4	519.3	517.9	516.3	513.3
132.5°	544.6	552.3	552.8	549.0	546.8
135°	575.0	583.4	585.1	584.2	582.0
137.5°	608.7	615.6	617.0	616.5	613.1
140°	638.5	645.4	649.2	649.2	646.1
142.5°	669.1	675.9	678.1	679.0	675.9
145°	698.0	703.5	707.9	708.6	705.7
147.5°	724.0	730.8	734.0	735.4	732.4
150°	750.7	755.4	758.3	760.8	758.3
152.5°	774.5	779.0	782.9	785.9	782.9
155°	798.2	800.3	802.8	806.6	804.2
157.5°	818.6	820.2	821.7	827.1	823.3
160°	836.9	838.6	839.4	844.0	840.8
162.5°	853.8	853.8	854.7	859.8	856.0
165°	868.3	867.5	867.5	872.9	869.1
167.5°	881.4	878.9	878.9	884.4	880.5
170°	891.2	889.0	888.3	893.7	889.0
172.5°	898.0	895.9	895.0	900.5	895.9
175°	903.5	901.3	899.7	905.2	900.5
177.5°	906.5	904.3	902.7	907.3	902.7
180°	905.2	905.2	905.2	905.2	905.2

TEST NUMBER: P926110

CATALOG NUMBER: DFN2DIP-TR2F0-030D030US950-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.30	11.12	11.27	12.10	13.39	6.28	7.10	7.25	8.08	9.37
	3H	11.95	12.69	12.93	13.68	14.99	7.45	8.19	8.43	9.18	10.49
	4H	12.54	13.24	13.54	14.23	15.55	7.89	8.59	8.89	9.58	10.90
	6H	12.94	13.58	13.95	14.58	15.91	8.20	8.84	9.20	9.84	11.17
	8H	13.06	13.67	14.07	14.68	16.01	8.28	8.89	9.29	9.90	11.23
	12H	13.11	13.69	14.13	14.70	16.05	8.32	8.89	9.33	9.90	11.25
4H	2H	10.31	11.01	11.31	12.00	13.32	6.86	7.56	7.86	8.55	9.87
	3H	12.11	12.69	13.12	13.71	15.04	8.19	8.77	9.20	9.79	11.12
	4H	12.79	13.31	13.80	14.33	15.68	8.72	9.25	9.74	10.27	11.62
	6H	13.28	13.73	14.31	14.77	16.12	9.13	9.58	10.16	10.62	11.97
	8H	13.44	13.86	14.47	14.90	16.26	9.25	9.67	10.28	10.70	12.07
	12H	13.52	13.90	14.57	14.95	16.32	9.30	9.68	10.35	10.73	12.10
8H	4H	12.75	13.17	13.78	14.20	15.57	8.99	9.41	10.02	10.45	11.81
	6H	13.29	13.64	14.34	14.71	16.08	9.49	9.84	10.54	10.91	12.27
	8H	13.49	13.80	14.55	14.86	16.24	9.66	9.97	10.73	11.03	12.41
	12H	13.61	13.88	14.68	14.94	16.36	9.77	10.04	10.84	11.09	12.52
12H	4H	12.70	13.08	13.75	14.13	15.50	8.99	9.37	10.04	10.42	11.79
	6H	13.26	13.57	14.32	14.63	16.01	9.53	9.84	10.59	10.90	12.28
	8H	13.47	13.74	14.53	14.79	16.22	9.73	10.00	10.79	11.05	12.47

END OF REPORT