

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P907074

Luminaire Tested: DFN2DIP-TR2F0-060D030US835-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P907074
REPORT IS A COMBINATION OF REPORTS P900240 AND P897145
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR2F0-060D030US835-RLLFLL
Description: 2 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7755.0 lumens
Efficiency: N/A
Efficacy: 95.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.04' x L: 2.36' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 81.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P907074

CATALOG NUMBER: DFN2DIP-TR2F0-060D030US835-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P907074

CATALOG NUMBER: DFN2DIP-TR2F0-060D030US835-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	111	111	111	111	104	104	104	104	92	92	92	81	81	81	71	71	71
1	102	98	94	91	96	92	89	86	82	79	77	72	70	69	63	62	61
2	93	86	80	75	88	81	76	72	72	68	65	64	61	58	57	54	52
3	86	76	69	63	80	72	66	61	65	59	55	57	53	50	51	48	45
4	79	68	60	54	74	65	58	52	58	52	48	52	47	44	46	42	40
5	73	61	53	47	68	58	51	45	52	46	42	47	42	38	42	38	35
6	67	55	47	41	63	52	45	40	47	41	37	42	38	34	38	34	31
7	62	50	42	37	59	48	40	35	43	37	33	39	34	30	35	31	28
8	58	46	38	33	55	44	37	32	40	34	29	36	31	27	32	28	25
9	54	42	35	29	51	40	33	29	36	31	27	33	28	25	30	26	23
10	51	39	31	27	48	37	30	26	34	28	24	31	26	23	28	24	21

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5531	5531	5531
5°	5532	5431	5469
10°	5469	5312	5281
15°	5385	5124	4997
20°	5277	4871	4652
25°	5167	4589	4320
30°	5021	4301	3901
35°	4878	3993	3533
40°	4732	3675	3113
45°	4564	3325	2733
50°	4389	2972	2362
55°	4205	2597	2007
60°	3992	2206	1643
65°	3746	1810	1468
70°	3448	1441	1315
75°	3073	1247	1178
80°	2532	1012	993
85°	1662	627	699

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4564 cd/sqm

TEST NUMBER: P907074

CATALOG NUMBER: DFN2DIP-TR2F0-060D030US835-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	232.4	3.0
10°-20°	638.0	8.2
20°-30°	895.7	11.6
30°-40°	976.4	12.6
40°-50°	897.4	11.6
50°-60°	704.8	9.1
60°-70°	458.8	5.9
70°-80°	236.1	3.0
80°-90°	63.0	0.8
90°-100°	58.7	0.8
100°-110°	186.5	2.4
110°-120°	319.2	4.1
120°-130°	419.8	5.4
130°-140°	471.2	6.1
140°-150°	462.1	6.0
150°-160°	387.7	5.0
160°-170°	257.1	3.3
170°-180°	89.9	1.2
0°-30°	1766.2	22.8
0°-40°	2742.6	35.4
0°-60°	4344.8	56.0
0°-90°	5102.7	65.8
90°-120°	564.5	7.3
90°-150°	1917.7	24.7
90°-180°	2652.0	34.2
0°-180°	7755.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2480	2480	2480	2480	2480	
5°	2480	2469	2439	2460	2453	235
15°	2359	2334	2258	2215	2193	665
25°	2141	2069	1921	1829	1795	985
35°	1845	1730	1533	1391	1342	1155
45°	1508	1358	1122	963	909	1165
55°	1147	972	729	595	552	1025
65°	774	592	390	314	307	768
75°	413	256	180	164	162	437
85°	96	49	43	43	43	111
90°	1	10	28	26	27	8
95°	42	50	51	51	50	46
105°	172	174	176	178	178	182
115°	320	325	324	323	320	317
125°	466	473	471	468	467	416
135°	603	612	613	612	610	466
145°	732	737	742	743	740	457
155°	837	839	842	846	843	385
165°	910	909	909	915	911	257
175°	947	945	943	949	944	90
180°	949	949	949	949	949	

TEST NUMBER: P907074

CATALOG NUMBER: DFN2DIP-TR2F0-060D030US835-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2479.8	2479.8	2479.8	2479.8	2479.8
2.5°	2491.0	2479.8	2455.0	2477.6	2473.1
5°	2479.8	2468.6	2439.3	2459.6	2452.9
7.5°	2459.6	2446.2	2414.8	2423.6	2412.4
10°	2432.6	2416.9	2372.2	2365.3	2351.9
12.5°	2399.1	2378.8	2318.1	2304.8	2280.0
15°	2358.6	2333.8	2257.6	2215.0	2192.6
17.5°	2311.5	2275.5	2181.2	2131.9	2096.0
20°	2257.6	2212.6	2100.5	2044.5	1995.0
22.5°	2199.3	2147.6	2017.4	1941.2	1907.6
25°	2141.0	2069.1	1921.0	1829.1	1795.3
27.5°	2071.5	1995.0	1831.2	1725.7	1674.1
30°	1997.4	1911.9	1732.4	1618.1	1557.4
32.5°	1925.5	1822.2	1638.4	1503.6	1447.4
35°	1844.8	1730.3	1532.9	1391.4	1341.9
37.5°	1766.2	1642.6	1434.1	1279.1	1223.1
40°	1683.1	1548.6	1330.7	1171.4	1113.1
42.5°	1597.9	1454.3	1227.6	1061.4	1005.5
45°	1508.1	1357.6	1122.2	962.6	908.8
47.5°	1422.9	1263.6	1021.2	861.7	812.4
50°	1328.6	1169.3	922.4	767.4	720.5
52.5°	1236.4	1068.1	828.1	680.0	637.4
55°	1146.7	971.7	729.3	594.8	552.1
57.5°	1054.8	875.2	641.9	516.2	480.2
60°	960.5	781.0	549.8	435.5	399.5
62.5°	868.6	689.1	471.2	363.6	345.7
65°	774.3	592.4	390.5	314.3	307.4
67.5°	684.5	502.6	314.3	276.0	269.3
70°	590.2	415.2	260.2	237.9	228.8
72.5°	500.5	334.3	217.6	199.8	195.2
75°	412.9	255.7	179.5	163.8	161.7
77.5°	325.5	181.7	141.4	132.4	127.9
80°	244.5	130.2	107.6	98.8	98.8
82.5°	170.5	87.6	74.0	69.5	69.5
85°	96.4	49.3	42.6	42.6	42.6
87.5°	36.0	17.9	17.9	15.7	15.7
90°	0.9	10.3	28.0	26.3	27.2
92.5°	17.7	24.0	24.9	25.7	25.7
95°	41.8	49.8	51.2	51.2	49.8
97.5°	69.5	76.9	80.1	80.1	80.1
100°	101.5	108.1	110.4	110.4	109.6
102.5°	135.3	140.2	143.3	144.2	143.3
105°	172.2	174.5	176.2	177.6	177.6
107.5°	208.8	212.2	212.2	212.8	208.8
110°	244.3	248.9	248.9	248.9	246.6



TEST NUMBER: P907074

CATALOG NUMBER: DFN2DIP-TR2F0-060D030US835-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	282.6	287.5	286.6	284.3	282.6
115°	320.4	324.9	323.5	322.7	320.4
117.5°	357.8	364.1	360.1	357.8	355.5
120°	395.6	401.9	395.6	395.6	393.0
122.5°	429.9	437.9	433.9	431.6	429.9
125°	466.0	473.1	470.8	468.2	467.4
127.5°	501.1	510.0	506.9	503.4	501.1
130°	534.0	544.3	542.9	541.2	538.0
132.5°	570.9	578.9	579.5	575.5	573.2
135°	602.7	611.5	613.3	612.4	610.1
137.5°	638.1	645.3	646.7	646.2	642.7
140°	669.3	676.5	680.5	680.5	677.3
142.5°	701.4	708.5	710.8	711.7	708.5
145°	731.7	737.4	742.0	742.8	739.7
147.5°	758.9	766.0	769.4	770.9	767.7
150°	786.9	791.8	794.9	797.5	794.9
152.5°	811.8	816.6	820.6	823.8	820.6
155°	836.7	838.9	841.5	845.5	843.0
157.5°	858.1	859.8	861.3	867.0	863.0
160°	877.3	879.0	879.9	884.7	881.3
162.5°	895.0	895.0	895.9	901.3	897.3
165°	910.2	909.3	909.3	915.0	911.0
167.5°	923.9	921.3	921.3	927.0	923.0
170°	934.2	931.9	931.1	936.8	931.9
172.5°	941.3	939.1	938.2	943.9	939.1
175°	947.1	944.8	943.1	948.8	943.9
177.5°	950.2	947.9	946.2	951.1	946.2
180°	948.8	948.8	948.8	948.8	948.8

TEST NUMBER: P907074

CATALOG NUMBER: DFN2DIP-TR2F0-060D030US835-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.32	15.30	15.14	16.13	17.16	10.30	11.28	11.12	12.11	13.14
	3H	15.99	16.86	16.82	17.70	18.76	11.49	12.36	12.32	13.21	14.26
	4H	16.59	17.41	17.43	18.26	19.33	11.93	12.76	12.78	13.61	14.68
	6H	17.00	17.76	17.85	18.61	19.69	12.25	13.01	13.11	13.87	14.95
	8H	17.12	17.84	17.98	18.71	19.80	12.34	13.06	13.20	13.93	15.02
	12H	17.17	17.86	18.04	18.73	19.84	12.38	13.07	13.25	13.93	15.04
4H	2H	14.35	15.18	15.20	16.03	17.10	10.90	11.73	11.75	12.58	13.65
	3H	16.17	16.85	17.03	17.74	18.82	12.25	12.93	13.11	13.82	14.90
	4H	16.85	17.47	17.72	18.35	19.46	12.79	13.41	13.66	14.29	15.40
	6H	17.35	17.89	18.24	18.79	19.90	13.20	13.74	14.09	14.64	15.75
	8H	17.51	18.02	18.41	18.91	20.04	13.32	13.82	14.21	14.72	15.85
	12H	17.60	18.05	18.51	18.97	20.10	13.38	13.83	14.29	14.75	15.88
8H	4H	16.82	17.32	17.72	18.22	19.35	13.07	13.57	13.96	14.47	15.59
	6H	17.37	17.78	18.29	18.72	19.85	13.57	13.98	14.49	14.92	16.05
	8H	17.57	17.94	18.50	18.87	20.01	13.75	14.11	14.68	15.05	16.19
	12H	17.70	18.02	18.63	18.95	20.14	13.86	14.18	14.79	15.11	16.30
12H	4H	16.78	17.23	17.69	18.15	19.28	13.07	13.52	13.98	14.44	15.57
	6H	17.34	17.71	18.27	18.64	19.79	13.61	13.98	14.54	14.91	16.06
	8H	17.55	17.88	18.49	18.80	20.00	13.81	14.14	14.74	15.06	16.26