

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P909729

Luminaire Tested: DFN2DIP-TR2F0-020D050US840-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P909729
REPORT IS A COMBINATION OF REPORTS P901771 AND P897145
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR2F0-020D050US840-FLLONL
Description: 2 foot, Triangle Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6468.2 lumens
Efficiency: N/A
Efficacy: 120.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.04' x L: 2.36' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 53.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P909729

CATALOG NUMBER: DFN2DIP-TR2F0-020D050US840-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P909729

CATALOG NUMBER: DFN2DIP-TR2F0-020D050US840-FLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	39	39	39
1	94	89	86	82	84	80	77	74	64	61	60	48	47	46	34	33	33
2	85	78	72	67	76	70	65	61	56	52	49	42	40	38	30	29	27
3	78	68	61	56	69	62	56	51	49	45	41	37	35	32	27	25	23
4	71	60	53	47	63	55	48	43	44	39	35	33	30	28	24	22	20
5	65	54	46	40	58	49	42	37	39	34	30	30	26	24	21	19	17
6	60	48	40	35	54	44	37	32	35	30	26	27	23	21	19	17	15
7	55	43	36	30	49	39	33	28	32	27	23	24	21	18	18	15	14
8	51	39	32	27	46	36	29	24	29	24	20	22	19	16	16	14	12
9	47	36	28	24	43	32	26	22	26	21	18	20	17	15	15	13	11
10	44	33	26	21	40	30	24	19	24	19	16	19	15	13	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1753	1753	1753
5°	1753	1725	1737
10°	1736	1697	1710
15°	1708	1666	1671
20°	1671	1623	1630
25°	1634	1573	1584
30°	1588	1526	1525
35°	1545	1471	1464
40°	1492	1415	1405
45°	1438	1359	1345
50°	1380	1300	1276
55°	1319	1232	1211
60°	1250	1152	1137
65°	1174	1069	1050
70°	1077	967	956
75°	944	844	865
80°	783	689	699
85°	533	434	435

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 2084 cd/sqm

TEST NUMBER: P909729

CATALOG NUMBER: DFN2DIP-TR2F0-020D050US840-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	74.0	1.1
10°-20°	208.1	3.2
20°-30°	305.8	4.7
30°-40°	355.2	5.5
40°-50°	354.8	5.5
50°-60°	309.4	4.8
60°-70°	228.7	3.5
70°-80°	129.4	2.0
80°-90°	38.7	0.6
90°-100°	98.8	1.5
100°-110°	314.0	4.9
110°-120°	537.3	8.3
120°-130°	706.6	10.9
130°-140°	793.2	12.3
140°-150°	777.8	12.0
150°-160°	652.5	10.1
160°-170°	432.7	6.7
170°-180°	151.2	2.3
0°-30°	587.9	9.1
0°-40°	943.2	14.6
0°-60°	1607.3	24.8
0°-90°	2004.1	31.0
90°-120°	950.1	14.7
90°-150°	3227.7	49.9
90°-180°	4464.0	69.0
0°-180°	6468.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	786	786	786	786	786	
5°	786	783	775	781	779	75
15°	748	744	734	737	733	211
25°	677	671	658	660	658	312
35°	584	577	564	560	556	365
45°	475	470	459	450	447	367
55°	360	355	346	337	333	322
65°	243	238	231	224	220	240
75°	127	126	122	117	119	135
85°	31	30	30	27	26	35
90°	1	17	47	44	46	6
95°	70	84	86	86	84	78
105°	290	294	297	299	299	306
115°	539	547	544	543	539	533
125°	784	796	792	788	787	701
135°	1014	1029	1032	1031	1027	784
145°	1232	1241	1249	1250	1245	769
155°	1408	1412	1416	1423	1419	648
165°	1532	1530	1530	1540	1533	432
175°	1594	1590	1587	1597	1589	151
180°	1597	1597	1597	1597	1597	

TEST NUMBER: P909729

CATALOG NUMBER: DFN2DIP-TR2F0-020D050US840-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	785.9	785.9	785.9	785.9	785.9
2.5°	790.4	786.7	778.3	785.9	784.5
5°	785.9	782.9	774.6	780.6	779.1
7.5°	780.6	776.1	767.8	773.9	772.3
10°	772.3	767.1	758.0	764.0	761.7
12.5°	760.9	756.5	747.4	751.1	749.6
15°	748.1	743.7	733.8	736.8	733.1
17.5°	732.3	727.8	717.9	721.6	717.9
20°	714.9	710.3	699.7	702.1	699.0
22.5°	697.5	690.7	680.9	680.9	679.3
25°	677.1	671.1	658.2	659.6	658.2
27.5°	654.4	649.1	639.3	637.1	633.3
30°	631.8	625.7	614.4	612.2	609.0
32.5°	607.5	603.1	591.0	586.4	583.4
35°	584.2	576.6	564.5	560.0	556.1
37.5°	557.7	550.9	538.8	533.5	529.7
40°	530.5	524.4	512.3	505.6	502.5
42.5°	504.0	498.0	485.9	478.4	473.8
45°	475.3	470.1	458.7	450.4	447.4
47.5°	447.4	442.1	430.0	421.6	417.2
50°	417.9	414.1	403.5	392.9	389.2
52.5°	389.2	383.8	374.1	365.8	360.5
55°	359.7	355.2	346.1	337.1	333.3
57.5°	330.2	326.5	316.6	307.6	304.5
60°	300.7	297.8	287.2	278.8	276.6
62.5°	272.1	266.7	259.2	251.7	248.6
65°	242.6	238.0	230.6	223.7	219.9
67.5°	212.4	208.5	201.8	196.5	193.5
70°	184.4	181.4	174.5	169.3	166.3
72.5°	155.7	152.7	148.9	143.6	141.4
75°	126.9	125.5	121.6	117.1	118.7
77.5°	101.3	98.3	96.6	94.4	92.2
80°	75.6	74.8	73.3	71.0	69.5
82.5°	51.4	51.4	50.7	47.7	47.7
85°	30.9	30.2	29.5	27.2	26.5
87.5°	13.6	12.1	10.6	8.4	7.6
90°	1.4	17.4	47.2	44.3	45.7
92.5°	29.9	40.4	41.9	43.3	43.3
95°	70.3	83.8	86.1	86.1	83.8
97.5°	116.9	129.5	134.8	134.8	134.8
100°	170.9	182.0	185.8	185.8	184.4
102.5°	227.7	235.9	241.2	242.7	241.2
105°	289.8	293.7	296.6	298.9	298.9
107.5°	351.4	357.2	357.2	358.2	351.4
110°	411.1	418.9	418.9	418.9	415.0

TEST NUMBER: P909729

CATALOG NUMBER: DFN2DIP-TR2F0-020D050US840-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	475.6	483.8	482.4	478.6	475.6
115°	539.2	546.9	544.5	543.1	539.2
117.5°	602.3	612.9	606.1	602.3	598.4
120°	665.8	676.4	665.8	665.8	661.5
122.5°	723.6	737.1	730.3	726.5	723.6
125°	784.3	796.3	792.4	788.1	786.7
127.5°	843.4	858.4	853.1	847.3	843.4
130°	898.9	916.2	913.7	910.9	905.5
132.5°	961.0	974.4	975.4	968.7	964.8
135°	1014.4	1029.3	1032.2	1030.8	1026.9
137.5°	1074.1	1086.1	1088.5	1087.5	1081.8
140°	1126.5	1138.6	1145.3	1145.3	1140.0
142.5°	1180.4	1192.6	1196.4	1197.8	1192.6
145°	1231.5	1241.1	1248.8	1250.3	1245.0
147.5°	1277.3	1289.3	1295.1	1297.5	1292.1
150°	1324.4	1332.6	1337.9	1342.2	1337.9
152.5°	1366.3	1374.5	1381.2	1386.5	1381.2
155°	1408.2	1412.0	1416.3	1423.1	1418.8
157.5°	1444.3	1447.1	1449.6	1459.3	1452.5
160°	1476.5	1479.5	1480.9	1489.0	1483.3
162.5°	1506.4	1506.4	1507.8	1517.0	1510.3
165°	1532.0	1530.5	1530.5	1540.1	1533.4
167.5°	1555.0	1550.6	1550.6	1560.3	1553.6
170°	1572.4	1568.5	1567.1	1576.7	1568.5
172.5°	1584.4	1580.5	1579.1	1588.7	1580.5
175°	1594.1	1590.1	1587.3	1596.9	1588.7
177.5°	1599.3	1595.5	1592.6	1600.7	1592.6
180°	1596.9	1596.9	1596.9	1596.9	1596.9

TEST NUMBER: P909729

CATALOG NUMBER: DFN2DIP-TR2F0-020D050US840-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.01	7.72	8.11	8.82	10.34	6.59	7.30	7.69	8.40	9.92
	3H	8.63	9.27	9.75	10.38	11.92	8.17	8.81	9.29	9.92	11.46
	4H	9.20	9.81	10.32	10.92	12.46	8.74	9.35	9.86	10.46	12.00
	6H	9.57	10.13	10.71	11.24	12.80	9.11	9.67	10.25	10.78	12.34
	8H	9.66	10.20	10.80	11.32	12.87	9.21	9.74	10.34	10.87	12.41
	12H	9.70	10.20	10.84	11.33	12.90	9.24	9.74	10.38	10.86	12.43
4H	2H	7.44	8.05	8.57	9.16	10.70	7.10	7.71	8.24	8.82	10.36
	3H	9.27	9.77	10.40	10.91	12.46	8.88	9.39	10.02	10.53	12.08
	4H	9.96	10.42	11.10	11.55	13.12	9.56	10.03	10.70	11.15	12.73
	6H	10.44	10.84	11.59	11.99	13.55	10.05	10.44	11.19	11.59	13.16
	8H	10.58	10.95	11.72	12.09	13.67	10.18	10.55	11.32	11.69	13.27
	12H	10.63	10.97	11.79	12.12	13.71	10.23	10.56	11.39	11.72	13.30
8H	4H	10.13	10.50	11.28	11.64	13.23	9.78	10.15	10.93	11.29	12.87
	6H	10.73	11.04	11.90	12.22	13.80	10.38	10.68	11.54	11.87	13.44
	8H	10.93	11.20	12.10	12.36	13.96	10.58	10.84	11.75	12.01	13.60
	12H	11.04	11.28	12.22	12.44	14.07	10.67	10.91	11.85	12.07	13.70
12H	4H	10.11	10.45	11.27	11.60	13.18	9.76	10.10	10.93	11.25	12.84
	6H	10.75	11.02	11.93	12.18	13.78	10.41	10.68	11.58	11.84	13.44
	8H	10.97	11.21	12.15	12.36	14.00	10.62	10.86	11.80	12.02	13.65

END OF REPORT