

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P909738

Luminaire Tested: DFN2DIP-TR2F0-030D020US840-RLFL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P909738
REPORT IS A COMBINATION OF REPORTS P900224 AND P897145
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR2F0-030D020US840-RLLFLL
Description: 2 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4362.6 lumens
Efficiency: N/A
Efficacy: 107.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.04' x L: 2.36' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 40.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P909738

CATALOG NUMBER: DFN2DIP-TR2F0-030D020US840-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P909738

CATALOG NUMBER: DFN2DIP-TR2F0-030D020US840-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64
1	100	96	92	89	94	90	87	84	78	76	74	68	66	64	58	57	56
2	92	85	79	74	86	79	74	70	69	65	62	60	57	55	52	50	48
3	84	75	68	62	78	70	64	59	62	57	53	54	50	47	46	44	41
4	77	67	59	53	72	63	56	51	55	50	46	48	44	41	42	39	36
5	71	60	52	46	66	56	49	44	50	44	40	44	39	36	38	34	32
6	66	54	46	40	61	51	44	39	45	39	35	40	35	32	35	31	28
7	61	49	41	36	57	46	39	34	41	35	31	36	32	28	32	28	25
8	57	45	37	32	53	42	35	30	38	32	28	33	29	25	29	26	23
9	53	41	34	29	50	39	32	27	35	29	25	31	26	23	27	24	21
10	50	38	31	26	47	36	29	25	32	27	23	29	24	21	25	22	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2793	2793	2793
5°	2793	2742	2761
10°	2761	2682	2667
15°	2719	2587	2523
20°	2665	2460	2349
25°	2609	2317	2181
30°	2536	2172	1970
35°	2463	2016	1784
40°	2390	1856	1572
45°	2304	1679	1380
50°	2216	1501	1193
55°	2123	1311	1013
60°	2015	1114	830
65°	1891	914	741
70°	1741	728	664
75°	1551	630	595
80°	1279	511	502
85°	840	317	353

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2304 cd/sqm

TEST NUMBER: P909738

CATALOG NUMBER: DFN2DIP-TR2F0-030D020US840-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	117.4	2.7
10°-20°	322.1	7.4
20°-30°	452.3	10.4
30°-40°	493.0	11.3
40°-50°	453.1	10.4
50°-60°	355.9	8.2
60°-70°	231.6	5.3
70°-80°	119.2	2.7
80°-90°	32.2	0.7
90°-100°	39.5	0.9
100°-110°	125.6	2.9
110°-120°	214.9	4.9
120°-130°	282.7	6.5
130°-140°	317.3	7.3
140°-150°	311.1	7.1
150°-160°	261.0	6.0
160°-170°	173.1	4.0
170°-180°	60.5	1.4
0°-30°	891.8	20.4
0°-40°	1384.8	31.7
0°-60°	2193.8	50.3
0°-90°	2576.9	59.1
90°-120°	380.0	8.7
90°-150°	1291.1	29.6
90°-180°	1786.0	40.9
0°-180°	4362.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1252	1252	1252	1252	1252	
5°	1252	1246	1232	1242	1238	119
15°	1191	1178	1140	1118	1107	336
25°	1081	1045	970	924	906	497
35°	932	874	774	703	678	583
45°	762	686	567	486	459	588
55°	579	491	368	300	279	517
65°	391	299	197	159	155	388
75°	208	129	91	83	82	220
85°	49	25	22	22	22	56
90°	1	7	19	18	18	4
95°	28	34	34	34	34	31
105°	116	117	119	120	120	122
115°	216	219	218	217	216	213
125°	314	318	317	315	315	280
135°	406	412	413	412	411	314
145°	493	496	500	500	498	308
155°	563	565	566	569	568	259
165°	613	612	612	616	613	173
175°	638	636	635	639	636	61
180°	639	639	639	639	639	

TEST NUMBER: P909738

CATALOG NUMBER: DFN2DIP-TR2F0-030D020US840-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1252.1	1252.1	1252.1	1252.1	1252.1
2.5°	1257.8	1252.1	1239.6	1251.0	1248.8
5°	1252.1	1246.5	1231.7	1241.9	1238.5
7.5°	1241.9	1235.2	1219.3	1223.8	1218.1
10°	1228.3	1220.4	1197.8	1194.3	1187.6
12.5°	1211.3	1201.1	1170.5	1163.8	1151.2
15°	1190.9	1178.4	1139.9	1118.4	1107.1
17.5°	1167.1	1149.0	1101.4	1076.5	1058.3
20°	1139.9	1117.2	1060.6	1032.4	1007.3
22.5°	1110.5	1084.4	1018.7	980.2	963.2
25°	1081.1	1044.7	970.0	923.5	906.5
27.5°	1045.9	1007.3	924.6	871.4	845.3
30°	1008.6	965.4	874.7	817.1	786.4
32.5°	972.2	920.1	827.3	759.2	730.8
35°	931.5	873.6	774.0	702.6	677.6
37.5°	891.8	829.4	724.1	645.8	617.6
40°	849.9	781.9	672.0	591.5	562.1
42.5°	806.8	734.4	619.9	535.9	507.7
45°	761.5	685.5	566.6	486.0	458.9
47.5°	718.4	638.0	515.6	435.1	410.2
50°	670.9	590.4	465.7	387.5	363.8
52.5°	624.3	539.4	418.2	343.4	321.8
55°	579.0	490.6	368.2	300.3	278.8
57.5°	532.6	441.9	324.2	260.6	242.5
60°	484.9	394.4	277.6	219.8	201.8
62.5°	438.6	347.9	237.9	183.6	174.6
65°	390.9	299.1	197.1	158.6	155.2
67.5°	345.7	253.8	158.6	139.4	135.9
70°	298.0	209.6	131.4	120.1	115.5
72.5°	252.7	168.7	109.9	100.9	98.6
75°	208.4	129.2	90.7	82.7	81.6
77.5°	164.3	91.7	71.4	66.9	64.5
80°	123.5	65.7	54.3	49.9	49.9
82.5°	86.0	44.2	37.4	35.1	35.1
85°	48.7	24.8	21.5	21.5	21.5
87.5°	18.2	9.0	9.0	8.0	8.0
90°	0.6	7.0	18.9	17.7	18.3
92.5°	11.9	16.2	16.8	17.4	17.4
95°	28.1	33.5	34.4	34.4	33.5
97.5°	46.8	51.8	53.9	53.9	53.9
100°	68.4	72.8	74.3	74.3	73.7
102.5°	91.1	94.3	96.4	97.0	96.4
105°	115.9	117.4	118.7	119.6	119.6
107.5°	140.6	142.9	142.9	143.3	140.6
110°	164.5	167.5	167.5	167.5	166.0

TEST NUMBER: P909738

CATALOG NUMBER: DFN2DIP-TR2F0-030D020US840-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	190.3	193.5	193.0	191.4	190.3
115°	215.7	218.7	217.8	217.2	215.7
117.5°	241.0	245.2	242.5	241.0	239.3
120°	266.3	270.5	266.3	266.3	264.6
122.5°	289.4	294.8	292.2	290.6	289.4
125°	313.7	318.5	317.0	315.3	314.7
127.5°	337.4	343.4	341.2	338.9	337.4
130°	359.5	366.5	365.5	364.4	362.2
132.5°	384.4	389.8	390.1	387.5	385.9
135°	405.8	411.7	412.8	412.3	410.7
137.5°	429.6	434.4	435.5	435.1	432.7
140°	450.6	455.4	458.2	458.2	456.1
142.5°	472.2	477.0	478.6	479.1	477.0
145°	492.6	496.4	499.6	500.1	498.0
147.5°	510.9	515.7	518.1	519.0	516.8
150°	529.8	533.0	535.1	536.8	535.1
152.5°	546.5	549.8	552.5	554.6	552.5
155°	563.3	564.8	566.5	569.3	567.5
157.5°	577.7	578.9	579.9	583.7	581.0
160°	590.7	591.8	592.4	595.6	593.3
162.5°	602.6	602.6	603.1	606.8	604.1
165°	612.8	612.2	612.2	616.0	613.4
167.5°	622.0	620.3	620.3	624.1	621.5
170°	628.9	627.4	626.8	630.7	627.4
172.5°	633.8	632.2	631.7	635.5	632.2
175°	637.6	636.1	634.9	638.7	635.5
177.5°	639.7	638.2	637.0	640.3	637.0
180°	638.7	638.7	638.7	638.7	638.7

TEST NUMBER: P909738

CATALOG NUMBER: DFN2DIP-TR2F0-030D020US840-RLFL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.39	12.30	12.28	13.20	14.34	7.37	8.28	8.26	9.18	10.32
	3H	13.05	13.87	13.95	14.77	15.94	8.55	9.37	9.45	10.27	11.44
	4H	13.65	14.42	14.56	15.33	16.50	9.00	9.76	9.91	10.68	11.85
	6H	14.05	14.76	14.98	15.68	16.87	9.31	10.01	10.23	10.93	12.12
	8H	14.17	14.85	15.10	15.78	16.97	9.39	10.07	10.32	11.00	12.19
	12H	14.23	14.87	15.16	15.80	17.01	9.43	10.07	10.37	11.00	12.21
4H	2H	11.42	12.18	12.33	13.10	14.27	7.97	8.73	8.88	9.65	10.82
	3H	13.23	13.86	14.15	14.81	16.00	9.30	9.94	10.23	10.89	12.08
	4H	13.90	14.48	14.84	15.42	16.64	9.84	10.42	10.78	11.36	12.58
	6H	14.40	14.90	15.35	15.86	17.08	10.25	10.75	11.20	11.71	12.93
	8H	14.56	15.03	15.51	15.99	17.22	10.37	10.84	11.32	11.79	13.02
	12H	14.65	15.07	15.62	16.04	17.28	10.43	10.85	11.40	11.83	13.06
8H	4H	13.87	14.34	14.82	15.30	16.53	10.11	10.58	11.07	11.54	12.77
	6H	14.42	14.80	15.39	15.80	17.03	10.61	11.00	11.59	12.00	13.23
	8H	14.62	14.96	15.60	15.95	17.19	10.79	11.13	11.78	12.12	13.37
	12H	14.74	15.04	15.73	16.02	17.32	10.90	11.20	11.89	12.18	13.48
12H	4H	13.83	14.25	14.80	15.22	16.46	10.12	10.54	11.09	11.51	12.75
	6H	14.39	14.73	15.38	15.72	16.96	10.66	11.00	11.64	11.99	13.23
	8H	14.60	14.90	15.59	15.88	17.17	10.86	11.16	11.85	12.14	13.43