

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P909754

Luminaire Tested: DFN2DIP-TR2F0-030D060US840-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P909754
REPORT IS A COMBINATION OF REPORTS P900264 AND P897145
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR2F0-030D060US840-RLLFLL
Description: 2 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7937.5 lumens
Efficiency: N/A
Efficacy: 107.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.04' x L: 2.36' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 73.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P909754

CATALOG NUMBER: DFN2DIP-TR2F0-030D060US840-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P909754

CATALOG NUMBER: DFN2DIP-TR2F0-030D060US840-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	93	93	93	93	74	74	74	56	56	56	40	40	40
1	94	90	86	83	85	81	78	75	65	63	61	50	48	47	36	35	34
2	86	79	73	68	77	71	67	62	57	54	51	44	42	40	32	31	29
3	79	70	63	57	71	63	57	52	51	46	43	39	36	34	29	27	25
4	72	62	54	49	65	56	50	45	45	41	37	35	32	29	26	24	22
5	66	55	47	42	59	50	43	38	40	36	32	32	28	26	23	21	19
6	61	49	42	36	55	45	38	33	36	32	28	29	25	23	21	19	17
7	56	45	37	32	51	41	34	29	33	28	25	26	23	20	19	17	15
8	52	40	33	28	47	37	30	26	30	25	22	24	20	18	18	16	14
9	49	37	30	25	44	34	27	23	28	23	20	22	19	16	17	14	13
10	45	34	27	22	41	31	25	21	25	21	18	20	17	15	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2793	2793	2793
5°	2793	2742	2761
10°	2761	2682	2667
15°	2719	2587	2523
20°	2665	2460	2349
25°	2609	2317	2181
30°	2536	2172	1970
35°	2463	2016	1784
40°	2390	1856	1572
45°	2304	1679	1380
50°	2216	1501	1193
55°	2123	1311	1013
60°	2015	1114	830
65°	1891	914	741
70°	1741	728	664
75°	1551	630	595
80°	1279	511	502
85°	840	317	353

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 2499 cd/sqm

TEST NUMBER: P909754

CATALOG NUMBER: DFN2DIP-TR2F0-030D060US840-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	117.4	1.5
10°-20°	322.1	4.1
20°-30°	452.3	5.7
30°-40°	493.0	6.2
40°-50°	453.1	5.7
50°-60°	355.9	4.5
60°-70°	231.6	2.9
70°-80°	119.2	1.5
80°-90°	35.9	0.5
90°-100°	118.6	1.5
100°-110°	376.8	4.7
110°-120°	644.8	8.1
120°-130°	848.0	10.7
130°-140°	951.8	12.0
140°-150°	933.4	11.8
150°-160°	783.0	9.9
160°-170°	519.2	6.5
170°-180°	181.5	2.3
0°-30°	891.8	11.2
0°-40°	1384.8	17.4
0°-60°	2193.8	27.6
0°-90°	2580.6	32.5
90°-120°	1140.1	14.4
90°-150°	3873.3	48.8
90°-180°	5357.0	67.5
0°-180°	7937.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1252	1252	1252	1252	1252	
5°	1252	1246	1232	1242	1238	119
15°	1191	1178	1140	1118	1107	336
25°	1081	1045	970	924	906	497
35°	932	874	774	703	678	583
45°	762	686	567	486	459	588
55°	579	491	368	300	279	517
65°	391	299	197	159	155	388
75°	208	129	91	83	82	220
85°	49	25	22	22	22	56
90°	2	21	57	53	55	8
95°	84	100	103	103	100	94
105°	348	352	356	359	359	367
115°	647	656	653	652	647	640
125°	941	956	951	946	944	841
135°	1217	1235	1239	1237	1232	941
145°	1478	1489	1499	1500	1494	923
155°	1690	1694	1700	1708	1702	778
165°	1838	1836	1836	1848	1840	519
175°	1913	1908	1905	1916	1906	182
180°	1916	1916	1916	1916	1916	

TEST NUMBER: P909754

CATALOG NUMBER: DFN2DIP-TR2F0-030D060US840-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1252.1	1252.1	1252.1	1252.1	1252.1
2.5°	1257.8	1252.1	1239.6	1251.0	1248.8
5°	1252.1	1246.5	1231.7	1241.9	1238.5
7.5°	1241.9	1235.2	1219.3	1223.8	1218.1
10°	1228.3	1220.4	1197.8	1194.3	1187.6
12.5°	1211.3	1201.1	1170.5	1163.8	1151.2
15°	1190.9	1178.4	1139.9	1118.4	1107.1
17.5°	1167.1	1149.0	1101.4	1076.5	1058.3
20°	1139.9	1117.2	1060.6	1032.4	1007.3
22.5°	1110.5	1084.4	1018.7	980.2	963.2
25°	1081.1	1044.7	970.0	923.5	906.5
27.5°	1045.9	1007.3	924.6	871.4	845.3
30°	1008.6	965.4	874.7	817.1	786.4
32.5°	972.2	920.1	827.3	759.2	730.8
35°	931.5	873.6	774.0	702.6	677.6
37.5°	891.8	829.4	724.1	645.8	617.6
40°	849.9	781.9	672.0	591.5	562.1
42.5°	806.8	734.4	619.9	535.9	507.7
45°	761.5	685.5	566.6	486.0	458.9
47.5°	718.4	638.0	515.6	435.1	410.2
50°	670.9	590.4	465.7	387.5	363.8
52.5°	624.3	539.4	418.2	343.4	321.8
55°	579.0	490.6	368.2	300.3	278.8
57.5°	532.6	441.9	324.2	260.6	242.5
60°	484.9	394.4	277.6	219.8	201.8
62.5°	438.6	347.9	237.9	183.6	174.6
65°	390.9	299.1	197.1	158.6	155.2
67.5°	345.7	253.8	158.6	139.4	135.9
70°	298.0	209.6	131.4	120.1	115.5
72.5°	252.7	168.7	109.9	100.9	98.6
75°	208.4	129.2	90.7	82.7	81.6
77.5°	164.3	91.7	71.4	66.9	64.5
80°	123.5	65.7	54.3	49.9	49.9
82.5°	86.0	44.2	37.4	35.1	35.1
85°	48.7	24.8	21.5	21.5	21.5
87.5°	18.2	9.0	9.0	8.0	8.0
90°	1.7	20.8	56.7	53.1	54.8
92.5°	35.9	48.6	50.3	52.0	52.0
95°	84.3	100.5	103.4	103.4	100.5
97.5°	140.4	155.4	161.8	161.8	161.8
100°	205.1	218.3	223.0	223.0	221.3
102.5°	273.3	283.1	289.4	291.1	289.4
105°	347.8	352.4	355.9	358.8	358.8
107.5°	421.7	428.7	428.7	429.8	421.7
110°	493.4	502.6	502.6	502.6	498.0

TEST NUMBER: P909754

CATALOG NUMBER: DFN2DIP-TR2F0-030D060US840-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	570.8	580.6	578.9	574.2	570.8
115°	647.0	656.3	653.4	651.7	647.0
117.5°	722.8	735.5	727.3	722.8	718.1
120°	799.0	811.7	799.0	799.0	793.8
122.5°	868.3	884.4	876.4	871.8	868.3
125°	941.1	955.5	950.9	945.7	944.0
127.5°	1012.2	1030.1	1023.7	1016.8	1012.2
130°	1078.6	1099.4	1096.5	1093.1	1086.7
132.5°	1153.2	1169.3	1170.4	1162.4	1157.7
135°	1217.3	1235.2	1238.6	1236.9	1232.2
137.5°	1288.9	1303.3	1306.3	1305.0	1298.2
140°	1351.9	1366.3	1374.4	1374.4	1368.1
142.5°	1416.5	1431.0	1435.6	1437.3	1431.0
145°	1477.8	1489.3	1498.6	1500.4	1494.0
147.5°	1532.7	1547.1	1554.1	1556.9	1550.5
150°	1589.3	1599.1	1605.5	1610.6	1605.5
152.5°	1639.5	1649.4	1657.5	1663.9	1657.5
155°	1689.8	1694.5	1699.6	1707.8	1702.5
157.5°	1733.1	1736.7	1739.5	1751.1	1743.0
160°	1771.9	1775.3	1777.1	1786.9	1780.0
162.5°	1807.7	1807.7	1809.4	1820.4	1812.3
165°	1838.3	1836.5	1836.5	1848.2	1840.1
167.5°	1866.0	1860.9	1860.9	1872.4	1864.3
170°	1886.8	1882.2	1880.5	1892.0	1882.2
172.5°	1901.3	1896.6	1894.9	1906.4	1896.6
175°	1912.8	1908.2	1904.7	1916.3	1906.4
177.5°	1919.1	1914.6	1911.1	1920.9	1911.1
180°	1916.3	1916.3	1916.3	1916.3	1916.3

TEST NUMBER: P909754

CATALOG NUMBER: DFN2DIP-TR2F0-030D060US840-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.69	9.39	9.78	10.48	11.99	4.67	5.37	5.77	6.46	7.97
	3H	10.33	10.96	11.44	12.06	13.58	5.83	6.46	6.94	7.56	9.08
	4H	10.92	11.51	12.03	12.62	14.14	6.26	6.86	7.38	7.96	9.49
	6H	11.31	11.86	12.44	12.97	14.50	6.56	7.11	7.69	8.22	9.76
	8H	11.42	11.95	12.55	13.07	14.60	6.64	7.17	7.77	8.29	9.82
	12H	11.47	11.97	12.61	13.08	14.64	6.68	7.17	7.81	8.29	9.84
4H	2H	8.68	9.28	9.81	10.38	11.91	5.23	5.83	6.36	6.93	8.46
	3H	10.47	10.97	11.61	12.10	13.64	6.55	7.05	7.68	8.18	9.72
	4H	11.14	11.60	12.28	12.72	14.28	7.08	7.54	8.22	8.66	10.22
	6H	11.63	12.02	12.77	13.16	14.71	7.48	7.87	8.62	9.01	10.56
	8H	11.79	12.15	12.93	13.29	14.85	7.60	7.96	8.74	9.09	10.66
	12H	11.86	12.20	13.02	13.34	14.91	7.65	7.98	8.80	9.12	10.69
8H	4H	11.10	11.46	12.24	12.60	14.16	7.34	7.71	8.48	8.84	10.40
	6H	11.63	11.94	12.79	13.11	14.67	7.83	8.13	8.99	9.31	10.87
	8H	11.83	12.10	13.00	13.25	14.83	8.01	8.27	9.18	9.43	11.01
	12H	11.95	12.18	13.12	13.33	14.95	8.11	8.34	9.28	9.49	11.11
12H	4H	11.04	11.37	12.20	12.52	14.09	7.34	7.67	8.49	8.81	10.38
	6H	11.61	11.87	12.77	13.03	14.61	7.87	8.14	9.04	9.29	10.87
	8H	11.81	12.04	12.98	13.19	14.81	8.06	8.30	9.23	9.45	11.06