

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P926183

Luminaire Tested: DFN2DIP-TR2F0-060D060US950-RLONL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P926183  
REPORT IS A COMBINATION OF REPORTS P901790 AND P897145  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-TR2F0-060D060US950-RLLONL  
Description: 2 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 9931.1 lumens  
Efficiency: N/A  
Efficacy: 92.1 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular w/ Sides (W: 2.04' x L: 2.36' x H: 0.1')  
CIE Type: General Diffuse  
  
Input Watts (W): 107.8  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9971  
Total Harmonic Distortion (THDi): 0.049  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P926183  
CATALOG NUMBER: DFN2DIP-TR2F0-060D060US950-RLLONL

### Luminous Intensity Polar Plot





TEST NUMBER: P926183  
 CATALOG NUMBER: DFN2DIP-TR2F0-060D060US950-RLLONL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	99	99	99	99	83	83	83	68	68	68	55	55	55	49				49
1	98	94	90	87	90	87	84	81	73	71	69	61	59	58	50	49	48	42				42
2	90	83	77	72	82	76	71	67	65	61	58	54	51	49	44	42	41	36				36
3	82	73	66	60	75	68	61	57	58	53	49	48	45	42	40	37	35	31				31
4	75	65	57	51	69	60	54	48	51	46	42	43	40	36	36	33	31	27				27
5	69	58	50	44	64	54	47	42	46	41	37	39	35	32	32	29	27	24				24
6	64	52	44	39	59	49	42	37	42	36	32	35	31	28	30	26	24	21				21
7	59	47	40	34	55	44	37	32	38	33	29	32	28	25	27	24	22	19				19
8	55	43	36	30	51	40	33	29	35	29	26	30	26	23	25	22	20	17				17
9	51	39	32	27	47	37	30	26	32	27	23	27	23	20	23	20	18	16				16
10	48	36	29	24	44	34	28	23	30	24	21	25	21	19	22	18	16	14				14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	5277	5277	5277
5°	5277	5181	5217
10°	5217	5068	5038
15°	5137	4889	4767
20°	5035	4647	4438
25°	4929	4378	4121
30°	4790	4104	3722
35°	4654	3810	3370
40°	4515	3506	2970
45°	4354	3172	2607
50°	4187	2835	2254
55°	4011	2477	1914
60°	3808	2104	1567
65°	3574	1727	1401
70°	3289	1375	1255
75°	2931	1189	1124
80°	2416	966	948
85°	1586	598	666

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 4354 cd/sqm



TEST NUMBER: P926183

CATALOG NUMBER: DFN2DIP-TR2F0-060D060US950-RLLONL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	221.7	2.2
10°-20°	608.7	6.1
20°-30°	854.5	8.6
30°-40°	931.5	9.4
40°-50°	856.2	8.6
50°-60°	672.4	6.8
60°-70°	437.7	4.4
70°-80°	225.3	2.3
80°-90°	62.7	0.6
90°-100°	112.0	1.1
100°-110°	355.9	3.6
110°-120°	609.1	6.1
120°-130°	801.1	8.1
130°-140°	899.2	9.1
140°-150°	881.7	8.9
150°-160°	739.6	7.4
160°-170°	490.5	4.9
170°-180°	171.4	1.7
0°-30°	1684.9	17.0
0°-40°	2616.4	26.3
0°-60°	4144.9	41.7
0°-90°	4870.5	49.0
90°-120°	1077.0	10.8
90°-150°	3659.0	36.8
90°-180°	5061.0	51.0
0°-180°	9931.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2366	2366	2366	2366	2366	
5°	2366	2355	2327	2346	2340	224
15°	2250	2226	2154	2113	2092	634
25°	2042	1974	1833	1745	1713	939
35°	1760	1651	1462	1327	1280	1102
45°	1439	1295	1071	918	867	1111
55°	1094	927	696	567	527	978
65°	739	565	372	300	293	732
75°	394	244	171	156	154	417
85°	92	47	41	41	41	106
90°	2	20	54	50	52	10
95°	80	95	98	98	95	89
105°	329	333	336	339	339	347
115°	611	620	617	616	611	605
125°	889	903	898	893	892	794
135°	1150	1167	1170	1168	1164	889
145°	1396	1407	1416	1417	1411	872
155°	1596	1601	1606	1613	1608	735
165°	1737	1735	1735	1746	1738	490
175°	1807	1803	1799	1810	1801	172
180°	1810	1810	1810	1810	1810	



TEST NUMBER: P926183

CATALOG NUMBER: DFN2DIP-TR2FO-060D060US950-RLLONL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2365.7	2365.7	2365.7	2365.7	2365.7
2.5°	2376.4	2365.7	2342.1	2363.6	2359.3
5°	2365.7	2355.0	2327.1	2346.5	2340.1
7.5°	2346.5	2333.7	2303.7	2312.1	2301.4
10°	2320.7	2305.7	2263.1	2256.5	2243.7
12.5°	2288.7	2269.4	2211.5	2198.8	2175.1
15°	2250.1	2226.4	2153.8	2113.1	2091.7
17.5°	2205.2	2170.8	2080.9	2033.8	1999.6
20°	2153.8	2110.8	2003.9	1950.5	1903.2
22.5°	2098.1	2048.8	1924.6	1851.9	1819.9
25°	2042.5	1973.9	1832.6	1745.0	1712.7
27.5°	1976.2	1903.2	1747.0	1646.3	1597.1
30°	1905.5	1824.0	1652.7	1543.7	1485.8
32.5°	1836.9	1738.4	1563.0	1434.4	1380.8
35°	1759.9	1650.7	1462.4	1327.4	1280.2
37.5°	1685.0	1567.0	1368.1	1220.3	1166.8
40°	1605.7	1477.4	1269.5	1117.5	1061.9
42.5°	1524.4	1387.4	1171.1	1012.6	959.2
45°	1438.7	1295.2	1070.6	918.3	867.0
47.5°	1357.4	1205.5	974.2	822.1	775.0
50°	1267.5	1115.5	880.0	732.1	687.4
52.5°	1179.5	1019.0	790.0	648.7	608.1
55°	1094.0	927.0	695.8	567.4	526.7
57.5°	1006.3	834.9	612.4	492.5	458.1
60°	916.3	745.1	524.5	415.5	381.1
62.5°	828.6	657.4	449.5	346.9	329.8
65°	738.7	565.1	372.5	299.8	293.3
67.5°	653.0	479.5	299.8	263.3	256.9
70°	563.1	396.1	248.2	227.0	218.3
72.5°	477.5	318.9	207.6	190.6	186.2
75°	393.9	243.9	171.2	156.3	154.3
77.5°	310.5	173.3	134.9	126.3	122.0
80°	233.3	124.2	102.7	94.3	94.3
82.5°	162.7	83.6	70.6	66.3	66.3
85°	92.0	47.0	40.6	40.6	40.6
87.5°	34.3	17.1	17.1	15.0	15.0
90°	1.6	19.7	53.5	50.2	51.8
92.5°	33.9	45.9	47.5	49.1	49.1
95°	79.7	94.9	97.7	97.7	94.9
97.5°	132.6	146.8	152.8	152.8	152.8
100°	193.8	206.3	210.6	210.6	209.0
102.5°	258.2	267.4	273.4	275.0	273.4
105°	328.6	332.9	336.2	339.0	339.0
107.5°	398.4	405.0	405.0	406.0	398.4
110°	466.1	474.8	474.8	474.8	470.4



TEST NUMBER: P926183

CATALOG NUMBER: DFN2DIP-TR2F0-060D060US950-RLLONL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	539.2	548.5	546.8	542.4	539.2
115°	611.2	620.0	617.2	615.6	611.2
117.5°	682.8	694.8	687.1	682.8	678.4
120°	754.8	766.8	754.8	754.8	749.8
122.5°	820.2	835.5	827.9	823.6	820.2
125°	889.0	902.7	898.3	893.4	891.8
127.5°	956.2	973.1	967.1	960.6	956.2
130°	1019.0	1038.6	1035.9	1032.6	1026.6
132.5°	1089.4	1104.6	1105.7	1098.1	1093.7
135°	1150.0	1166.8	1170.1	1168.5	1164.1
137.5°	1217.6	1231.2	1234.0	1232.9	1226.4
140°	1277.1	1290.8	1298.4	1298.4	1292.4
142.5°	1338.2	1351.8	1356.2	1357.8	1351.8
145°	1396.1	1407.0	1415.7	1417.4	1411.3
147.5°	1447.9	1461.5	1468.1	1470.8	1464.8
150°	1501.4	1510.7	1516.7	1521.5	1516.7
152.5°	1548.8	1558.2	1565.8	1571.8	1565.8
155°	1596.3	1600.7	1605.6	1613.3	1608.3
157.5°	1637.3	1640.6	1643.3	1654.2	1646.6
160°	1673.9	1677.1	1678.8	1688.0	1681.5
162.5°	1707.7	1707.7	1709.3	1719.7	1712.0
165°	1736.6	1734.9	1734.9	1745.9	1738.3
167.5°	1762.8	1757.9	1757.9	1768.8	1761.2
170°	1782.5	1778.1	1776.4	1787.3	1778.1
172.5°	1796.1	1791.7	1790.1	1801.0	1791.7
175°	1807.0	1802.7	1799.3	1810.3	1801.0
177.5°	1813.0	1808.7	1805.3	1814.6	1805.3
180°	1810.3	1810.3	1810.3	1810.3	1810.3



TEST NUMBER: P926183  
 CATALOG NUMBER: DFN2DIP-TR2F0-060D060US950-RLONL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.70	13.53	13.68	14.51	15.80	8.69	9.51	9.66	10.49	11.78
	3H	14.36	15.09	15.34	16.08	17.39	9.86	10.60	10.84	11.59	12.90
	4H	14.95	15.65	15.95	16.64	17.96	10.30	10.99	11.30	11.99	13.31
	6H	15.35	15.99	16.36	16.99	18.32	10.61	11.25	11.61	12.25	13.58
	8H	15.47	16.08	16.48	17.09	18.42	10.69	11.30	11.70	12.31	13.64
	12H	15.52	16.10	16.54	17.11	18.46	10.73	11.30	11.74	12.31	13.66
4H	2H	12.72	13.41	13.72	14.41	15.73	9.27	9.96	10.27	10.96	12.28
	3H	14.52	15.10	15.53	16.12	17.45	10.60	11.18	11.61	12.20	13.53
	4H	15.19	15.72	16.21	16.74	18.09	11.13	11.66	12.15	12.68	14.03
	6H	15.69	16.14	16.72	17.18	18.53	11.54	11.99	12.57	13.03	14.38
	8H	15.85	16.27	16.88	17.30	18.67	11.66	12.08	12.69	13.11	14.48
	12H	15.93	16.31	16.98	17.36	18.73	11.71	12.09	12.76	13.14	14.51
8H	4H	15.16	15.58	16.19	16.61	17.98	11.40	11.82	12.43	12.86	14.22
	6H	15.70	16.05	16.75	17.12	18.48	11.90	12.25	12.95	13.32	14.68
	8H	15.90	16.21	16.96	17.26	18.65	12.07	12.38	13.14	13.44	14.82
	12H	16.02	16.29	17.09	17.34	18.77	12.18	12.45	13.24	13.50	14.93
12H	4H	15.11	15.49	16.16	16.54	17.91	11.40	11.78	12.45	12.83	14.20
	6H	15.67	15.98	16.73	17.04	18.42	11.94	12.25	13.00	13.31	14.69
	8H	15.87	16.15	16.94	17.20	18.62	12.13	12.40	13.20	13.46	14.88