

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P912456

Luminaire Tested: DFN2DIP-TR2F0-020D050US850-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P912456
REPORT IS A COMBINATION OF REPORTS P900251 AND P897145
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR2F0-020D050US850-FLLFLL
Description: 2 foot, Triangle Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7103.2 lumens
Efficiency: N/A
Efficacy: 132.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.04' x L: 2.36' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 53.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P912456

CATALOG NUMBER: DFN2DIP-TR2F0-020D050US850-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P912456

CATALOG NUMBER: DFN2DIP-TR2F0-020D050US850-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	39	39	39
1	94	89	86	82	84	80	77	74	64	61	60	48	47	46	34	33	33
2	85	78	72	67	76	70	65	61	56	52	49	42	40	38	30	29	27
3	78	68	61	56	69	62	56	51	49	45	41	37	35	32	27	25	23
4	71	60	53	47	63	55	48	43	44	39	35	33	30	28	24	22	20
5	65	54	46	40	58	49	42	37	39	34	30	30	26	24	21	19	17
6	60	48	40	35	54	44	37	32	35	30	26	27	23	21	19	17	15
7	55	43	36	30	49	39	33	28	32	27	23	24	21	18	18	15	14
8	51	39	32	27	46	36	29	24	29	24	20	22	19	16	16	14	12
9	47	36	28	24	43	32	26	22	26	21	18	20	17	15	15	13	11
10	44	33	26	21	40	30	24	19	24	19	16	19	15	13	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1925	1925	1925
5°	1925	1894	1907
10°	1907	1864	1878
15°	1876	1829	1835
20°	1835	1782	1790
25°	1795	1727	1739
30°	1744	1675	1675
35°	1697	1615	1608
40°	1638	1554	1543
45°	1580	1492	1477
50°	1516	1428	1401
55°	1448	1353	1330
60°	1373	1265	1249
65°	1289	1174	1154
70°	1183	1061	1050
75°	1037	927	950
80°	861	757	767
85°	585	477	478

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 2289 cd/sqm

TEST NUMBER: P912456

CATALOG NUMBER: DFN2DIP-TR2F0-020D050US850-FLLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	81.2	1.1
10°-20°	228.6	3.2
20°-30°	335.9	4.7
30°-40°	390.1	5.5
40°-50°	389.6	5.5
50°-60°	339.7	4.8
60°-70°	251.1	3.5
70°-80°	142.1	2.0
80°-90°	42.5	0.6
90°-100°	108.5	1.5
100°-110°	344.8	4.9
110°-120°	590.1	8.3
120°-130°	776.0	10.9
130°-140°	871.0	12.3
140°-150°	854.2	12.0
150°-160°	716.5	10.1
160°-170°	475.2	6.7
170°-180°	166.1	2.3
0°-30°	645.7	9.1
0°-40°	1035.8	14.6
0°-60°	1765.1	24.8
0°-90°	2200.8	31.0
90°-120°	1043.4	14.7
90°-150°	3544.6	49.9
90°-180°	4902.0	69.0
0°-180°	7103.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	863	863	863	863	863	
5°	863	860	851	857	856	82
15°	822	817	806	809	805	231
25°	744	737	723	724	723	342
35°	642	633	620	615	611	401
45°	522	516	504	495	491	403
55°	395	390	380	370	366	353
65°	266	261	253	246	242	263
75°	139	138	134	129	130	149
85°	34	33	32	30	29	38
90°	2	19	52	49	50	7
95°	77	92	95	95	92	86
105°	318	322	326	328	328	336
115°	592	601	598	596	592	586
125°	861	874	870	866	864	770
135°	1114	1130	1134	1132	1128	861
145°	1352	1363	1371	1373	1367	845
155°	1546	1551	1555	1563	1558	712
165°	1682	1681	1681	1691	1684	475
175°	1751	1746	1743	1754	1745	166
180°	1754	1754	1754	1754	1754	

TEST NUMBER: P912456

CATALOG NUMBER: DFN2DIP-TR2F0-020D050US850-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	863.0	863.0	863.0	863.0	863.0
2.5°	868.0	863.9	854.7	863.0	861.5
5°	863.0	859.8	850.6	857.3	855.6
7.5°	857.3	852.3	843.2	849.8	848.2
10°	848.2	842.4	832.4	839.0	836.5
12.5°	835.6	830.8	820.8	824.9	823.2
15°	821.5	816.7	805.8	809.1	805.0
17.5°	804.1	799.3	788.4	792.5	788.4
20°	785.1	780.1	768.4	771.0	767.6
22.5°	766.0	758.6	747.7	747.7	746.0
25°	743.6	736.9	722.8	724.4	722.8
27.5°	718.6	712.9	702.1	699.7	695.5
30°	693.8	687.1	674.7	672.3	668.8
32.5°	667.2	662.3	649.0	644.0	640.7
35°	641.6	633.2	619.9	614.9	610.7
37.5°	612.5	605.0	591.7	585.9	581.7
40°	582.6	575.9	562.6	555.3	551.8
42.5°	553.5	546.8	533.7	525.3	520.3
45°	522.0	516.2	503.7	494.6	491.3
47.5°	491.3	485.5	472.2	463.0	458.1
50°	458.9	454.8	443.2	431.5	427.4
52.5°	427.4	421.5	410.8	401.7	395.9
55°	395.0	390.0	380.1	370.2	366.0
57.5°	362.6	358.5	347.7	337.8	334.4
60°	330.3	327.0	315.4	306.2	303.8
62.5°	298.8	292.9	284.7	276.4	273.0
65°	266.4	261.4	253.2	245.6	241.5
67.5°	233.2	229.0	221.6	215.8	212.5
70°	202.5	199.2	191.6	185.9	182.7
72.5°	171.0	167.7	163.5	157.7	155.3
75°	139.4	137.8	133.5	128.6	130.3
77.5°	111.2	107.9	106.1	103.7	101.3
80°	83.1	82.2	80.5	78.0	76.3
82.5°	56.4	56.4	55.7	52.3	52.3
85°	33.9	33.2	32.4	29.8	29.1
87.5°	15.0	13.3	11.6	9.2	8.3
90°	1.6	19.1	51.8	48.7	50.2
92.5°	32.8	44.4	46.0	47.6	47.6
95°	77.2	92.0	94.6	94.6	92.0
97.5°	128.4	142.2	148.1	148.1	148.1
100°	187.6	199.8	204.1	204.1	202.5
102.5°	250.1	259.1	264.8	266.5	264.8
105°	318.3	322.5	325.7	328.3	328.3
107.5°	385.9	392.3	392.3	393.4	385.9
110°	451.5	460.0	460.0	460.0	455.7

TEST NUMBER: P912456

CATALOG NUMBER: DFN2DIP-TR2F0-020D050US850-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	522.3	531.3	529.8	525.6	522.3
115°	592.1	600.6	598.0	596.4	592.1
117.5°	661.4	673.1	665.6	661.4	657.2
120°	731.2	742.8	731.2	731.2	726.4
122.5°	794.6	809.5	802.0	797.8	794.6
125°	861.2	874.4	870.2	865.5	863.9
127.5°	926.2	942.6	936.9	930.5	926.2
130°	987.1	1006.1	1003.4	1000.3	994.4
132.5°	1055.3	1070.1	1071.2	1063.8	1059.5
135°	1114.0	1130.3	1133.5	1132.0	1127.7
137.5°	1179.5	1192.7	1195.4	1194.3	1188.0
140°	1237.1	1250.4	1257.7	1257.7	1252.0
142.5°	1296.3	1309.6	1313.8	1315.4	1309.6
145°	1352.4	1363.0	1371.4	1373.1	1367.2
147.5°	1402.7	1415.9	1422.2	1424.8	1419.0
150°	1454.5	1463.4	1469.2	1474.0	1469.2
152.5°	1500.5	1509.5	1516.8	1522.7	1516.8
155°	1546.4	1550.6	1555.4	1562.8	1558.0
157.5°	1586.1	1589.2	1591.9	1602.5	1595.1
160°	1621.5	1624.7	1626.2	1635.2	1628.9
162.5°	1654.3	1654.3	1655.8	1665.9	1658.5
165°	1682.4	1680.7	1680.7	1691.3	1683.9
167.5°	1707.6	1702.9	1702.9	1713.5	1706.1
170°	1726.7	1722.5	1720.9	1731.5	1722.5
172.5°	1739.9	1735.7	1734.1	1744.7	1735.7
175°	1750.6	1746.2	1743.1	1753.7	1744.7
177.5°	1756.3	1752.1	1748.9	1757.9	1748.9
180°	1753.7	1753.7	1753.7	1753.7	1753.7

TEST NUMBER: P912456

CATALOG NUMBER: DFN2DIP-TR2F0-020D050US850-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.33	8.05	8.44	9.15	10.67	6.91	7.62	8.02	8.73	10.24
	3H	8.96	9.60	10.07	10.71	12.24	8.50	9.14	9.61	10.25	11.78
	4H	9.52	10.13	10.65	11.24	12.78	9.07	9.67	10.19	10.78	12.32
	6H	9.90	10.46	11.03	11.57	13.12	9.44	10.00	10.57	11.11	12.66
	8H	9.99	10.52	11.12	11.65	13.20	9.53	10.06	10.67	11.19	12.74
	12H	10.02	10.53	11.16	11.65	13.22	9.56	10.07	10.70	11.19	12.76
4H	2H	7.77	8.37	8.90	9.49	11.03	7.43	8.04	8.56	9.15	10.69
	3H	9.59	10.10	10.73	11.24	12.79	9.21	9.72	10.35	10.85	12.41
	4H	10.28	10.75	11.42	11.87	13.45	9.89	10.35	11.03	11.48	13.05
	6H	10.77	11.17	11.91	12.31	13.88	10.37	10.77	11.52	11.92	13.48
	8H	10.90	11.27	12.05	12.41	14.00	10.50	10.88	11.65	12.02	13.60
	12H	10.96	11.29	12.12	12.45	14.03	10.55	10.89	11.71	12.04	13.63
8H	4H	10.46	10.83	11.60	11.97	13.55	10.11	10.48	11.25	11.62	13.20
	6H	11.05	11.36	12.22	12.54	14.12	10.70	11.01	11.87	12.19	13.77
	8H	11.26	11.53	12.43	12.69	14.29	10.90	11.17	12.07	12.33	13.93
	12H	11.37	11.60	12.54	12.76	14.39	11.00	11.23	12.17	12.39	14.02
12H	4H	10.43	10.77	11.59	11.92	13.51	10.09	10.43	11.25	11.58	13.16
	6H	11.08	11.35	12.25	12.51	14.11	10.74	11.01	11.91	12.17	13.76
	8H	11.30	11.53	12.47	12.69	14.32	10.95	11.19	12.13	12.34	13.98

END OF REPORT